

**NXP Semiconductors
Reactivation List
Exhibit B**

| MAG | 6TG | 12NC | Description | Product Status |
|------------|------------|--------------|---------------------|-----------------------|
| R25 | 846002 | 935273213518 | TDA8271HN/C1 | RFS |
| R53 | 52313J | 934055833118 | UZZ9001 | RFS |
| R32 | 557209 | 935219650518 | SAA7388GP/M1 | RFS |
| R75 | 4541C1 | 934054808115 | PDTC144WK | RFS |
| R73 | 4116HC | 934056663118 | PIP3202-DC | RFS |
| R79 | 506813 | 935276621551 | TDA8768AH/5/C4 | RFS |
| R42 | 809113 | 935284401005 | PCD8001U/10/521/3 | RFS |
| R05 | 837599 | 935274646518 | P89LPC935FDH | RFS |
| R45 | 563383 | 935264976557 | VP27299A2 | RFS |
| R76 | 5241C1 | 934046690115 | PZM3.3NB | RFS |
| R05 | 837428 | 935267867512 | P87LPC764BDH | RFS |
| R07 | 56545D | 935262846118 | 74LVT1403DR | RFS |
| R75 | 4543A1 | 934051790115 | PDTA143EE | RFS |
| R73 | 410694 | 934058544127 | PHP191NQ06LT | RFS |
| R45 | 405520 | 935284963118 | UMA1021M/C2. | RFS |
| R77 | 452980 | 935283392557 | OQ0258HL/N1 | RFS |
| R75 | 4541C1 | 934054805135 | PDTA143ZK | RFS |
| R25 | 846002 | 935273213157 | TDA8271HN/C1 | RFS |
| R07 | 5687MC | 935277206115 | 74LVC1G74GM | RFS |
| R05 | 837566 | 935278017118 | P83LPC915FDH/CV9609 | RFS |
| R01 | 5003LY | 935282518115 | SC16C852VIET | RFS |
| R01 | 5678LS | 935281499518 | SSTUA32964ET/G | RFS |
| R53 | 52313J | 934055063118 | UZZ9000 | RFS |
| R45 | 518804 | 935279323518 | PCF5213EL1/165/3I | RFS |
| R79 | 403411 | 935261644112 | TEA1402/N2 | RFS |
| R79 | 554340 | 935283832518 | UBA2014T/N1/S36 | RFS |
| R75 | 4541D2 | 934059033135 | BCM857DS | RFS |
| R01 | 5003LY | 935282854115 | SC16C850LIET | RFS |
| R01 | 5678LS | 935281691518 | SSTUB32865ET/G | RFS |
| R01 | 5678LS | 935281498518 | SSTUB32964ET/G | RFS |
| R05 | 837233 | 935271978157 | P80C58X2BBD/CV8416 | RFS |
| R01 | 5678LS | 935279445518 | SSTUA32S865ET/G | RFS |
| R25 | 846002 | 935273213557 | TDA8271HN/C1 | RFS |
| R07 | 56545D | 935262846112 | 74LVT1403DR | RFS |
| R01 | 5678LS | 935283143518 | SSTUB32865ET/S | RFS |