



## Flanged ceramic package; 2 mounting holes; 2 leads

SOT390A



### DIMENSIONS (millimetre dimensions are derived from the original inch dimensions)

UNIT	A	b	c	D	D <sub>1</sub>	E	E <sub>1</sub>	F	L	p	Q	q	U <sub>1</sub>	U <sub>2</sub>	w <sub>1</sub>	w <sub>2</sub>
mm	5.03 4.22	5.72 5.46	0.16 0.10	8.18 8.08	8.26 8.00	6.40 6.30	6.43 6.17	1.66 1.39	6.10 5.33	3.43 3.17	2.32 2.00	14.22	19.03 18.77	6.43 6.17	0.25	0.51
inches	0.198 0.166	0.225 0.215	0.006 0.004	0.322 0.318	0.325 0.315	0.252 0.248	0.253 0.243	0.065 0.055	0.24 0.21	0.135 0.125	0.091 0.079	0.560	0.749 0.739	0.253 0.243	0.010	0.020

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT390A						99-03-29