

PART INFORMATION	
Mfg Item Number	MP3V5004GP
Mfg Item Name	SENSOR 8PIN GP
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2013-01-08
Response Document ID	0848K50010S248A1.8
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	No
Plating Indicator	e4
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MP3V5004GP
Mfg Item Name	SENSOR 8PIN GP
Version	ALL
Weight	1.755100
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	
Peak Processing Temperature	
Max Time at Peak Temperature	
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemptions in this part	
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

SubPart	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		REACHPPM	REACH%
Non-Conductive Epoxy/Adhesive	0.002						g					
Non-Conductive Epoxy/Adhesive		Solvents, additives, and other materials	Other organic Silicon Compounds	-		0.000005	g	2681	0.2681		2	0.0002
Non-Conductive Epoxy/Adhesive		Solvents, additives, and other materials	Other siloxanes and silicones	-		0.001673	g	836461	83.6461		953	0.0953
Non-Conductive Epoxy/Adhesive		Glass	Other silica compounds	-		0.000322	g	160858	16.0858		183	0.0183
Cap/Cover	0.1958						g					
Cap/Cover		Metals	Chromium, metal	7440-47-3		0.035286	g	180216	18.0216		20104	2.0104
Cap/Cover		Solvents, additives, and other materials	Sulfur	7704-34-9		0.000059	g	300	0.03		33	0.0033
Cap/Cover		Solvents, additives, and other materials	Phosphorus	7723-14-0		0.000078	g	400	0.04		44	0.0044
Cap/Cover		Solvents, additives, and other materials	Silicon	7440-21-3		0.00147	g	7509	0.7509		837	0.0837
Cap/Cover		Metals	Iron, metal	7439-89-6		0.156947	g	801563	80.1563		89424	8.9424
Cap/Cover		Metals	Manganese, metal	7439-96-5		0.00196	g	10012	1.0012		1116	0.1116
Port	0.6882						g					
Port		Plastics/polymers	Polyphenylene Sulfide (PPS)	26125-40-6		0.41014	g	595960	59.596		233687	23.3687
Port		Glass	Proprietary Material-Other glass compounds (without lead, chromium, cadmium or mercury)	-		0.27806	g	404040	40.404		158431	15.8431
Bonding Wire	0.0011						g					
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0011	g	1000000	100		626	0.0626
Gel Die Encapsulant	0.0368						g					
Gel Die Encapsulant		Solvents, additives, and other materials	Proprietary Material-Other inorganic fluorine compounds and their aqueous salts	-		0.0368	g	1000000	100		20967	2.0967
Copper Lead Frame	0.796						g					
Copper Lead Frame		Metals	Copper, metal	7440-50-8		0.440787	g	553753	55.3753		251153	25.1153
Copper Lead Frame		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.016773	g	21072	2.1072		9556	0.9556
Copper Lead Frame		Metals	Gold, metal	7440-57-5		0.000626	g	787	0.0787		356	0.0356
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus	7723-14-0		0.000369	g	463	0.0463		210	0.021
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.010533	g	13232	1.3232		6001	0.6001
Copper Lead Frame		Metals	Nickel, metal	7440-02-0		0.006593	g	8283	0.8283		3756	0.3756
Copper Lead Frame		Metals	Palladium, metal	7440-05-3		0.000323	g	406	0.0406		184	0.0184
Copper Lead Frame		Plastics/polymers	Polyphenylene Sulfide (PPS)	26125-40-6		0.100875	g	126727	12.6727		57475	5.7475
Copper Lead Frame		Glass	Fibrous-glass-wool	65997-17-3		0.218562	g	274575	27.4575		124530	12.453
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.000559	g	702	0.0702		318	0.0318
Bonding Agent	0.0207						g					
Bonding Agent		Metals	Proprietary Material-Other aluminum compounds	-		0.009315	g	450000	45		5307	0.5307
Bonding Agent		Solvents, additives, and other materials	Other guanidine compounds	-		0.000518	g	25000	2.5		295	0.0295
Bonding Agent		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.000518	g	25000	2.5		295	0.0295
Bonding Agent		Plastics/polymers	Other phenolic resins	-		0.010349	g	500000	50		5896	0.5896
Silicon Semiconductor Die	0.0145						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.00029	g	20000	2		165	0.0165
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.01421	g	980000	98		8096	0.8096

LINKS	
MCD LINK	
Freescal website	http://www.freescal.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ROHS_Freescal_Response.pdf
China RoHS	http://www.freescal.com/chinarohs
REACH signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_REACH_Freescal_Response.pdf
ELV signed letter	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_ELV_Freescal_Reponse.pdf
Conflict Minerals statement	http://www.freescal.com/files/abstract/corporate/ehs_epp/ENV_CONFLICT_METAL_Freescal_Response.pdf
FREESCALE ENVIRONMENTAL INFORMATION	
EPP website	http://www.freescal.com/epp
FAQ	http://www.freescal.com/webapp/sps/site/overview.jsp?code=ENVIRON_FAQ
Technical Service Request	https://www.freescal.com/webapp/servicerequest.create_SR.framework?defaultCategory=Hardware Product Support&defaultTopic=Environmentally Preferred Prod
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v0.9 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v0.9_MCD_Template.pdf
Blank IPC1752 v1.1 Form	http://www.freescal.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MP3V5004GP_IPC1752_v09.xml

http://www.freescale.com/mcds/MP3V5004GP_IPC1752_v11.xml

http://www.freescale.com/mcds/MP3V5004GP_IPC1752A.xml