


| | | |
|---|--------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE: MAPLGA, THIN PROFILE, 3 X 5 X 1 PKG, 0.5MM PITCH, 24 I/O | DOCUMENT NO: 98ASA00355D | REV: B |
| | STANDARD: NON-JEDEC | |
| | SOT1766-1 | 07 JAN 2016 |



DETAIL E
VIEW ROTATED 90° CW

| | | | |
|---|--------------------|----------------------------|-------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE | |
| TITLE: MAPLGA, THIN PROFILE, 3 X 5 X 1 PKG, 0.5MM PITCH, 24 I/O | | DOCUMENT NO: 98ASA00355D | REV: B |
| | | STANDARD: NON-JEDEC | |
| | | SOT1766-1 | 07 JAN 2016 |



NOTES:

- 1. ALL DIMENSIONS IN MILLIMETERS.
- 2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.

3. DIMENSION APPLIES TO ALL LEADS.

4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

| | | | |
|---|---------------------------|----------------------------|-------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE | |
| TITLE: MAPLGA, THIN PROFILE, 3 X 5 X 1 PKG, 0.5MM PITCH, 24 I/O | | DOCUMENT NO: 98ASA00355D | REV: B |
| | | STANDARD: NON-JEDEC | |
| | | SOT1766-1 | 07 JAN 2016 |