



DETAIL "Y"



© NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	<b>MECHANICAL OUTLINE</b>	PRINT VERSION NOT TO SCALE
TITLE:  NI-780GS-4L4L	DOCUMENT NO: 98ASA00407D	REV: B
	STANDARD: NON-JEDEC	
	SOT1809-1	23 FEB 2016



NOTES:

1. CONTROLLING DIMENSION: INCH.
2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

3. DIMENSION A1/A2 IS MEASURED WITH REFERENCE TO DATUM T. THE POSITIVE VALUE IMPLIES THAT THE PACKAGE BOTTOM IS HIGHER THAN THE LEAD BOTTOM. A1 APPLIES TO PINS 2, 3, 6 & 7. A2 APPLIES TO PINS 1, 4, 5 & 8.

DIM	INCH		MILLIMETER		DIM	INCH		MILLIMETER	
	MIN	MAX	MIN	MAX		MIN	MAX	MIN	MAX
AA	.805	.815	20.45	20.70	R	.365	.375	9.27	9.53
A1	.002	.008	0.05	0.20	S	.365	.375	9.27	9.53
A2	.002	.008	0.05	0.20	U	.035	.045	0.89	1.14
BB	.380	.390	9.65	9.91	Y	.956 BSC		24.28 BSC	
B1	.546	.562	13.87	14.27	Z	R.000	R.040	R0.00	R1.02
CC	.125	.170	3.18	4.32	AB	.145	.155	3.68	3.94
E	.035	.045	0.89	1.14	t	0	8	0	8
F	.004	.007	0.10	0.18	aaa	.005		0.13	
J	.350 BSC		8.89 BSC		bbb	.010		0.25	
L	.038	.046	0.97	1.17	ccc	.015		0.38	
L1	.01 BSC		0.25 BSC						
M	.774	.786	19.66	19.96					
N	.772	.788	19.61	20.02					

© NXP SEMICONDUCTORS N.V.  
ALL RIGHTS RESERVED

**MECHANICAL OUTLINE**

PRINT VERSION NOT TO SCALE

TITLE:  NI-780GS-4L4L	DOCUMENT NO: 98ASA00407D	REV: B
	STANDARD: NON-JEDEC	
	SOT1809-1	23 FEB 2016