



TOP VIEW



BOTTOM VIEW

VIEW D-D

| | | |
|---|---------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE: MAPLGA, THIN PROFILE, 5 X 5 X 0.91 PKG, 0.5 MM PITCH, 41 I/O | DOCUMENT NO: 98ASA00424D | REV: A |
| | STANDARD: NON-JEDEC | |
| | SOT1648-1 | 08 JAN 2016 |



DETAIL E
VIEW ROTATED 90° CW

| | | | |
|---|--------------------|----------------------------|-------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE | |
| TITLE: MAPLGA, THIN PROFILE, 5 X 5 X 0.91 PKG, 0.5 MM PITCH, 41 I/O | | DOCUMENT NO: 98ASA00424D | REV: A |
| | | STANDARD: NON-JEDEC | |
| | | SOT1648-1 | 08 JAN 2016 |



NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.

3. DIMENSION APPLIES TO ALL LEADS.

4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

| | | | |
|---|---------------------------|----------------------------|-------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE | |
| TITLE: MAPLGA, THIN PROFILE, 5 X 5 X 0.91 PKG, 0.5 MM PITCH, 41 I/O | | DOCUMENT NO: 98ASA00424D | REV: A |
| | | STANDARD: NON-JEDEC | |
| | | SOT1648-1 | 08 JAN 2016 |