


|   |                          |                            |
|---|--------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V.<br>ALL RIGHTS RESERVED                                | MECHANICAL OUTLINE       | PRINT VERSION NOT TO SCALE |
| TITLE: LAMINATE QFN, THIN PROFILE,<br>5 X 5 X 0.91 PKG,<br>0.5 MM PITCH, 41 I/O | DOCUMENT NO: 98ASA00693D | REV: B                     |
|   | STANDARD: NON-JEDEC      |                            |
|   | SOT1648-2                | 11 JAN 2016                |



DETAIL E  
VIEW ROTATED 90° CW

|   |                          |                            |  |
|---|--------------------------|----------------------------|--|
| © NXP SEMICONDUCTORS N.V.<br>ALL RIGHTS RESERVED                                | MECHANICAL OUTLINE       | PRINT VERSION NOT TO SCALE |  |
| TITLE: LAMINATE QFN, THIN PROFILE,<br>5 X 5 X 0.91 PKG,<br>0.5 MM PITCH, 41 I/O | DOCUMENT NO: 98ASA00693D | REV: B                     |  |
|   | STANDARD: NON-JEDEC      |                            |  |
|   | SOT1648-2                | 11 JAN 2016                |  |



NOTES:

1. ALL DIMENSIONS IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.

3. DIMENSION APPLIES TO ALL LEADS.

4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

|   |                           |                            |             |
|---|---------------------------|----------------------------|-------------|
| © NXP SEMICONDUCTORS N.V.<br>ALL RIGHTS RESERVED                                | <b>MECHANICAL OUTLINE</b> | PRINT VERSION NOT TO SCALE |             |
| TITLE: LAMINATE QFN, THIN PROFILE,<br>5 X 5 X 0.91 PKG,<br>0.5 MM PITCH, 41 I/O |                           | DOCUMENT NO: 98ASA00693D   | REV: B      |
|   |                           | STANDARD: NON-JEDEC        |             |
|   |                           | SOT1648-2                  | 11 JAN 2016 |