





28	1	Ceramic Capacitor	Nichicon	UWT1V331MNL1GS (330uF 20% 35V AL)
27	2	Ceramic Capacitor	AVX	12065C473KAT2A (47nF 10% 50V X7R)
26	6	Ceramic Capacitor	AVX	12065C334KAT2A (330nF 10% 50V X7R)
25	2	Ceramic Capacitor	AVX	08055C472KAT2A (4.7nF 10% 50V X7R)
24	4	Tantalum Capacitor	AVX	TPSA156K010R1000 (15uF 10% 10V)
23	3	Ceramic Capacitor	AVX	18125C105KAT2A (1uF 10% 50V X7R)
22	12	Ceramic Capacitor	AVX	08055C102KAT2A (1nF 10% 50V)
21	27	Ceramic Capacitor	AVX	08055C104KAT2A (100nF 10% 50V)
20	4	Tantalum Capacitor	AVX	TPSD107K010R0065 (100uF 10% 10V)
19	4	Ceramic Capacitor	AVX	08052C103KAT2A (10nF 10% 200V X7R)
18	1	4 Pos. Terminal Block	Phoenix Contact	1729034
17	3	2 Pos. Terminal Block	Phoenix Contact	1729018
16	5	Banana Jack Conn.	Johnson Comp	108-0740-001
15	1	Black Test Point	Keystone	5001
14	1	Red Test Point	Keystone	5000
13	3	3X2 Header Male	Sullins	PBC03DAAN
12	11	4X1 Header Female	Sullins	PPPC041LFBN-RC
11	3	8X1 Header Female	Sullins	PPPC081LFBN-RC
10	10	2X1 Header Male	Sullins	PZC02SAAN
9	10	3X1 Header Male	Sullins	PZC03SAAN
8	1	Power Jack	CUI	PJ-102AH (2.1x5.5mm)
7	2	9 Pin D-SUB Conn.	AMP	5745781-4 (Female)
6	1	4x1 Molex Connector	Molex	39-30-3045 (Mini-Fit)
5	2	2X2 Molex Connector	Molex	39-29-1048 (Mini-Fit)
4	1	Polyswitch	Raychem	RXEF185 (1.85 Amp Hold)
3	5	Yellow Mom Switch	Omron	B3S-1002
2	3	4 Pos. DIP Switch	C&K	SDA04H1KD
1	1	PCB	Freescalo Semi.	CCI
ITEM	QTY	NAME	MATERIAL	DESCRIPTION

Parts List					
FILE NAME LFEB12UB.DWG		 NXP Semiconductors 28125 Cabot Drive, Suite 100 Novi, Michigan 48377 LFEB12UB Student Developmental Board			
CONTRACT NO —					
DRAWN 11/05/07 MJL					
CHECK					
APPR.					
ISSUED					
		SIZE	FSCM NO	DWG NO	REV
		B	—	LFEB12UB	B
NOTE: DIMENSIONS ARE IN MILLIMETERS DO NOT SCALE DRAWING		SCALE N/A		WEIGHT	SHEET 1 of 4