


PLCC FOOTPRINT (WAVE SOLDERING)



Wave soldering

PACKAGE NAME	PHILIPS OUTLINE CODE	Nx	Ny	FOOTPRINT DIMENSIONS (mm)							PLACEMENT ACCURACY
				Ax	Ay	Bx	By	C	F	G	
PLCC20	SOT380-1	5	5	9.70	9.70	6.60	6.60	1.55	15.35	15.35	±0.25
PLCC28	SOT261-2	7	7	12.20	12.20	9.10	9.10	1.55	17.85	17.85	±0.25
PLCC28	SOT261-3	7	7	12.20	12.20	9.10	9.10	1.55	17.85	17.85	±0.25
PLCC44	SOT187-2	11	11	17.30	17.30	14.20	14.20	1.55	22.95	22.95	±0.25
PLCC52	SOT238-2	13	13	19.80	19.80	16.70	16.70	1.55	25.50	25.50	±0.25
PLCC52	SOT238-3	13	13	19.80	19.80	16.70	16.70	1.55	25.50	25.50	±0.25
PLCC68	SOT188-2	17	17	24.30	24.30	21.80	21.80	1.55	30.55	30.55	±0.25
PLCC68	SOT188-3	17	17	24.30	24.30	21.80	21.80	1.55	30.55	30.55	±0.25
PLCC84	SOT189-2	21	21	30.00	30.00	26.90	26.90	1.55	35.65	35.65	±0.25
PLCC84	SOT189-3	21	21	30.00	30.00	26.90	26.90	1.55	35.65	35.65	±0.25