

JN5179-M10M13

E2

OM15061-1

SH1

CON2

U1

R4

R3

C1

L1

L4

L2

C4

C18

C2

R1

C3

C5

C7

C8

C9

IC1

C13

C16

C14

Y1

R2

C6

C5

