

Table of Contents


Revisions

1	TITLE & REVISION STATUS
2	CIRCUITRY

Rev	Description	Date
0	Original Release	xxxxxx

NOTES:

- Unless Otherwise Specified:
 All resistors are in ohms, most are 1%, 1/10 Watt.
 Otherwise are 5%, 1/8 Watt.
 All capacitors are in uF, some are 10% or 20%
 All voltages are DC
 All polarized capacitors are tantalum
- Interrupted lines coded with the same letter or letter combinations are electrically connected.
- Device type number is for reference only. The number varies with the manufacturer.
- Special signal usage:
 _B Denotes - Active-Low Signal
 <> or [] Denotes - Vectored Signals
- Interpret diagram in accordance with American National Standards Institute specifications, current revision, with the exception of logic block symbology.

		<p>Detroit Automotive Technology Center 28125 Cabot Drive, Suite 100 Novi, MI 48377</p>		
Drawn by: CDC Technologies, Inc.	Date: 02/07/2012	TITLE: LFMAJ43LT3		
Designer: CDC Technologies, Inc.	Ref: CDC2259	SIZE B	GEDTTL: GEDABV:	DWG. NO. LFMAJ43LT3
Approved: Daniel Beeker	Date: xx/xx/xxxx	LAST MODIFIED= Tuesday, February 07, 2012		REV: O
Quality: Daniel Beeker	Date: xx/xx/xxxx	SHEET 1 of 2		

