PF1510

Power management integrated circuit (PMIC) for low power application processors

Rev. 4 — 5 March 2021

Product data sheet

1 General description

The PF1510 is a power management integrated circuit (PMIC) designed specifically for use with i.MX processors on low-power portable, smart wearable and Internet-of-Things (IoT) applications. It is also capable of providing full power solution to i.MX 7ULP, i.MX 6SL, 6UL, 6ULL and 6SX processors.

With three high efficiency buck converters, three linear regulators, DDR reference and RTC supply, the PF1510 can provide power for a complete system, including application processors, memory, and system peripherals.

1.1 Features and benefits

This section summarizes the PF1510 features:

- Input voltage VIN from 5V bus, USB, or AC adapter (4.1 V to 6.0 V)
 - Linear front-end input LDO (1500 mA input limit)
 - Up to 6.5 V input operating range
 - VIN can withstand transient and DC inputs from 0 V up to +22 V
- · Buck converters:
 - SW1, 1.0 A; 0.6 V to 1.3875 V in 12.5 mV steps, or 1.1 V to 3.3 V in variable steps
 - SW2, 1.0 A; 0.6 V to 1.3875 V in 12.5 mV steps, or 1.1 V to 3.3 V in variable steps
 - SW3, 1.0 A; 1.8 V to 3.3 V in 100 mV steps
 - Internal digital soft start
 - Quiescent current 1.0 µA in ULP mode with light load
 - Peak efficiency > 90 %
 - Dynamic voltage scaling on SW1 and SW2
 - Modes: forced PWM quasi-fixed frequency mode, adaptive variable-frequency mode
 - Programmable output voltage, current limit and soft start
- LDO regulators
 - LDO1, 0.75 to 1.5 V/1.8 to 3.3 V, 300 mA with load switch mode
 - LDO2, 1.8 to 3.3 V, 400 mA
 - LDO3, 0.75 to 1.5 V/1.8 to 3.3 V, 300 mA with load switch mode
 - Quiescent current < 1.5 µA in Low-power mode
 - Programmable output voltage
 - Soft start and ramp
 - Current limit protection
 - USB_PHY low dropout linear regulator
 - LDO2P7 always on regulator output
- · LDO/switch supply
 - RTC supply VSNVS 3.0 V, 2.0 mA
 - Coin cell charger





- DDR memory reference voltage, VREFDDR, 0.5 to 0.9 V, 10 mA
- OTP (One time programmable) memory for device configuration
 - User programmable start-up sequence, timing, soft-start and power-down sequence
 Programmable regulator output voltages
- I²C interface
- User programmable Standby, Sleep/Low-power, and Off (REGS_DISABLE) modes
- Ambient temperature range -40 °C to 105 °C


1.2 Applications


- Low-power IoT applications
- Wireless game controllers
- Embedded monitoring systems
- Home automation
- POS
- E-Reader
- Smart mobile/wearable devices

2 Application diagram









2.2 Internal block diagram



The PF1510 is available only with preprogrammed configurations. These preprogrammed devices are identified using the program codes from <u>Table 1</u>, which also list the associated NXP reference designs where applicable. Details of the OTP programming for each device can be found in <u>Table 53</u>.


Table 1. Orderable part variations

Part number ^[1]	Temperature (T _A)	Package	Programming options
MC32PF1510A0EP			0 - not programmed
MC32PF1510A1EP	_		1 (Default)
MC32PF1510A2EP	Temperature (T _A) I -40 °C to 85 °C (for use in consumer applications) I -40 °C to 105 °C (for use in industrial applications) I		2 (i.MX 7ULP with LPDDR3) ^[2]
MC32PF1510A3EP			3 (i.MX 6UL with DDR3L)
MC32PF1510A4EP			4 (i.MX 7ULP with LPDDR3)
MC32PF1510A5EP		98ASA00913D, 40-pin QFN	5 (i.MX 6UL with DDR3)
MC32PF1510A6EP			6 (i.MX 6ULL with DDR3L)
MC32PF1510A7EP			7 (i.MX 6UL with LPDDR2)
MC34PF1510A0EP		5.0 mm x 5.0 mm with exposed pad	0 - not programmed
MC34PF1510A1EP	in consumer applications) −40 °C to 105 °C (for use		1 (Default)
MC34PF1510A2EP			2 (i.MX 7ULP with LPDDR3) [2]
MC34PF1510A3EP	−40 °C to 105 °C (for use		3 (i.MX 6UL with DDR3L)
MC34PF1510A4EP	in industrial applications)		4 (i.MX 7ULP with LPDDR3)
MC34PF1510A5EP			5 (i.MX 6UL with DDR3)
MC34PF1510A6EP			6 (i.MX 6ULL with DDR3L)
MC34PF1510A7EP			7 (i.MX 6UL with LPDDR2)

For tape and reel, add an R2 suffix to the part number.
 For internal validation only

4 Pinning information

4.1 Pinning



4.2 Pin definitions

Table 2. Pin description

Pin number	Block	Pin name	Recommended connection	Recommended connection when not used
1	WDI	Watchdog input from processor	Connect to WDI signal from processor. Pull up via 8 k Ω - 100 k Ω to VDDIO	Connect via 100 k Ω to regulator with output voltage < 3.6 V
2	SDA	I ² C data line	Pull-up to VDDIO	Leave floating
3	SCL	I ² C clock line	Pull-up to VDDIO	Leave floating
4	VDDIO	Supply for I ² C bus	Connect to 1.7 to 3.6 V supply. Bypass with 0.1 μF capacitor to ground	Leave floating
5	VDDOTP	Supply to program OTP fuses	Connect to ground for the fuse loading	N/A
6	PWRON	Power On/Off from processor	Connect to PMIC_ON_REQ from processor. Pull up via 8 k Ω - 100 k Ω to VSNVS if required	N/A
7	STANDBY	Standby input signal from processor	Connect to PMIC_STBY_REQ signal from processor	Connect to ground
8	ONKEY	ONKEY push button input	Connect to push button and pull up via $8k\Omega$ - 100 $k\Omega$ to VIN	Connect via 100 k Ω to VSYS
9	INTB	Open drain interrupt signal to processor	Pull-up via 68 k Ω - 100 k Ω to VSNVS or other rail at voltage less than or equal to VDDIO	Leave floating
10	RESETBMCU	Open drain reset output to processor	Pull-up via 68 k Ω - 100 k Ω to VSNVS or other rail at voltage less than or equal to VDDIO	Leave floating
11	VLDO3IN	LDO3 regulator input	Connect to VSYS and bypass with 1.0 mF capacitor to ground	Connect to regulator with output voltage < 4.5 V
12	VLDO3	LDO3 regulator output	Bypass with 4.7 µF capacitor to ground	Leave floating
13	SW3LX	SW3 switching node	Connect to SW3 inductor	Leave floating
14	SW3IN	Input to SW3 regulator	Connect to VSYS and bypass with 0.1 μ F + 4.7 μ F capacitors to ground	Connect to VSYS
15	SW3FB	Output voltage feedback for SW3	Connect to SW3 output voltage rail near load	Leave floating
16	SW2FB	Output voltage feedback for SW2	Connect to SW2 output voltage rail near load	Leave floating
17	SW2IN	Input to SW2 regulator	Connect to VSYS and bypass with 0.1 μF + 4.7 μF capacitors to ground	Connect to VSYS
18	SW2LX	SW2 switching node	Connect to SW2 inductor	Leave floating
19	VLDO2	LDO2 regulator output	Bypass with 10 µF capacitor to ground	Leave floating
20	VLDO2IN	LDO2 regulator input	Connect to VSYS and bypass with 1.0 mF capacitor to ground	Connect to regulator with output voltage < 4.5 V
21	VREFDDR	VREFDDR regulator output	Bypass with 1.0 µF capacitor to ground	Leave floating
22	VINREFDDR	VREFDDR regulator input	Ensure there is at least 1.0 µF net capacitance from VINREFDDR to ground	Leave floating
23	VDIG	Digital core supply	Bypass with 1.0 µF capacitor to ground	N/A
24	VCORE	Analog core supply	Bypass with 1.0 µF capacitor to ground	N/A
25	SW1LX	SW1 switching node	Connect to SW1 inductor	Leave floating
26	SW1IN	Input to SW1 regulator	Connect to VSYS and bypass with 0.1 μF + 4.7 μF capacitors to ground	Connect to VSYS
27	SW1FB	Output voltage feedback for SW1	Connect to SW1 output voltage rail near load	Leave floating
28	VLDO1IN	LDO1 regulators input	Connect to VSYS and bypass with 1.0 μF capacitor to ground	Connect to regulator with output voltage < 4.5 V
29	VLDO1	LDO1 regulator output	Bypass with 4.7 µF capacitor to ground	Leave floating

 Table 2. Pin description...continued

Pin number	Block	Pin name	Recommended connection	Recommended connection when not used
30	VSNVS	VSNVS regulator/switch output	Bypass with 0.47 µF capacitor to ground	Bypass with 0.47 µF capacitor to ground
31	LICELL	Coin cell supply input/output	Bypass with 0.1 µF capacitor. Connect to optional coin cell.	Bypass with 0.1 µF capacitor to ground
32	GND	Ground	Connect to ground	Connect to ground
33	NC	Net connected	Net comported	Loove floating
34	NC	Not connected	Not connected	Leave floating
35	VSYS	Main input voltage to PMIC	Bypass with 2x 22 μ F/10 V capacitors	N/A
36	VSYS		or a 47 µF/10 V capacitor to ground	
37	VIN	Main IC supply	Connect to a valid 5.0 V input, bypass with a 2.2 $\mu F/25$ V capacitor to ground	Leave floating
38	LDO2P7	LDO2P7 regulator output	Bypass with 2.2 µF capacitor to ground mandatory	Bypass with 2.2 µF capacitor to ground mandatory
39	USBPHY	USBPHY regulator output	Bypass with 1.0 µF capacitor to ground	Leave floating
40	GND	Ground	Connect to ground	Connect to ground
_	EP	Expose pad. Functions as ground return for buck and boost regulators	Ground. Connect this pad to the inner and external ground planes through multiple vias to allow effective thermal dissipation.	N/A

5 General product characteristics

5.1 Thermal characteristics

Table 3. Thermal ratings

Symbol	Description (Rating)		Min	Max	Unit
THERMAL R	ATINGS				
T _A	Ambient operating temperature range (industrial) Ambient operating temperature range (consumer)		-40 -40	105 85	°C
TJ	Operating junction temperature range	[1]	-40	125	°C
T _{ST}	Storage temperature range		-65	150	°C
T _{PPRT}	Peak package reflow temperature	[2] [3]	-	—	°C
QFN40 THEF	MAL RESISTANCE AND PACKAGE DISSIPATION RATINGS				
R _{oja}	Junction to ambient thermal resistance, natural convection Four layer board (2s2p) Six layer board (2s4p) Eight layer board (2s6p)	[4] [5] [6]		27 20.6 17.8	°C/W
R _{ØJMA}	Junction to ambient (@200ft/min) Four layer board (2s2p)	[4] [6]	—	21.4	°C/W
R _{OJB}	Junction to board	[7]	-	8.8	°C/W
R _{ØJCBOTTOM}	Junction to case bottom	[8]	-	1.4	°C/W
Ψ_{JT}	Junction to package top – Natural convection	[9]	_	0.6	°C/W

[1] Do not operate beyond 125 °C for extended periods of time. Operation above 150 °C may cause permanent damage to the IC. See Thermal Protection Thresholds for thermal protection features.

[2] Pin soldering temperature limit is for 10 seconds maximum duration. Not designed for immersion soldering. Exceeding these limits may cause a malfunction or permanent damage to the device.

PF1510

9 / 108

[3] NXP's package reflow capability meets Pb-free requirements for JEDEC standard J-STD-020C. For peak package reflow temperature and moisture sensitivity levels (MSL), go to <u>http://www.nxp.com</u>, search by part number [remove prefixes/suffixes and enter the core ID to view all orderable parts (for MC33xxxD enter 33xxx), and review parametrics.

[5] The Board uses the JEDEC specifications for thermal testing (and simulation) JESD51-7 and JESD51-5.

[6] Per JEDEC JESD51-6 with the board horizontal.

[7] Thermal resistance between the die and the printed circuit board per JEDEC JESD51-8. Board temperature is measured on the top surface of the board near the package.

- [8] Thermal resistance between the die and the case top surface as measured by the cold plate method (MIL SPEC-883 Method 1012.1).
- [9] Thermal characterization parameter indicating the temperature difference between package top and the junction temperature per JEDEC JESD51-2. When Greek letters are not available, the thermal characterization parameter is written as Psi-JT.

5.2 Absolute maximum ratings

	Table 4.	Maximum	ratings
--	----------	---------	---------

Symbol	Description (Rating)	Min	Мах	Unit
I/Os				
VIN	Main IC supply	-0.3	24	V
VDDIO	I/O supply voltage. Connect to voltage rail between 1.7 V and 3.3 V.	-0.3	3.6	V
SCL	SCL when used in I ² C mode. SCLK when used in SPI mode.	-0.3	3.6	V
SDA	SDA when used in I ² C mode. MISO when used in SPI mode.	-0.3	3.6	V
RESETBMCU	RESETBMCU open drain output	-0.3	3.6	V
PWRON	PWRON input	-0.3	3.6	V
STANDBY	STANDBY input	-0.3	3.6	V
ONKEY	ONKEY push button input	-0.3	4.8	V
INTB	INTB open-drain output	-0.3	3.6	V
WDI	Watchdog input from processor	-0.3	3.6	V
VDDOTP				
VDDOTP	Connect to ground in the application	-0.3	10	V
BUCK 1				
SW1IN	Buck 1 input supply	-0.3	4.8	V
SW1LX	Buck 1 switching node	-0.3	4.8	V
SW1FB	Buck 1 feedback input	-0.3	3.6	V
BUCK 2				
SW2IN	Buck 2 input supply	-0.3	4.8	V
SW2LX	Buck 2 switching node	-0.3	4.8	V
SW2FB	Buck 2 output voltage feedback	-0.3	3.6	V
BUCK 3		1	1	
SW3IN	Buck 3 input supply	-0.3	4.8	V
SW3LX	Buck 3 switching node	-0.3	4.8	V
SW3FB	Buck 3 output voltage feedback	-0.3	3.6	V
LDO1	· · · · · · · · · · · · · · · · · · ·			
VLDO1IN	LDO1 input supply	-0.3	4.8	V
VLDO1	LDO1 output	-0.3	3.6	V

PF1510 Product data sheet © NXP B.V. 2021. All rights reserved.

^[4] Junction temperature is a function of die size, on-chip power dissipation, package thermal resistance, mounting site (board) temperature, ambient temperature, air flow, power dissipation of other components on the board, and board thermal resistance.

Symbol	Description (Rating)	Min	Мах	Unit
LDO2				
VLDO2IN	LDO2 input supply	-0.3	4.8	V
VLDO2	LDO2 output	-0.3	3.6	V
LDO3				
VLDO3IN	LDO3 input supply	-0.3	4.8	V
VLDO3	LDO3 output	-0.3	3.6	V
VSNVS			·	
VSNVS	VSNVS regulator output	-0.3	3.6	V
LICELL	Coin cell input	-0.3	3.6	V
FRONT-END LI	00			
LDO2P7	LDO2P7 regulator output	-0.3	3.6	V
USBPHY	USBPHY regulator output	-0.3	5.5	V
INPUT/OUTPUT	r Supply		1	
VINREFDDR	VREFDDR input supply	-0.3	3.6	V
VREFDDR	VREFDDR output	-0.3	3.6	V
IC CORE			·	
VSYS	Main input voltage to PMIC	-0.3	4.8	V
VDIG	VDIG regulator output (used within PF1510)	-0.3	1.65	
VCORE	VCORE regulator output (used within PF1510)	-0.3	1.65	V
	ATINGS		·	
V _{ESD}	ESD ratings Human body model ^{[1}]	±2000	V
	Charge device model (corner pins) Charge device model (all other pins)		±750 ±500	

[1] Testing is performed in accordance with the human body model (HBM) (C_{ZAP} = 100 pF, R_{ZAP} = 1500 Ω), and the charge device model (CDM), Robotic (C_{ZAP} = 4.0 pF).

5.3 Electrical characteristics

5.3.1 Electrical characteristics – Front-end LDO

All parameters are specified at $T_A = -40$ to 105 °C, VIN = 5.0 V, VSYS = 3.7 V, typical external component values, unless otherwise noted. Typical values are characterized at VIN = 5.0 V, VSYS = 3.7 V and 25 °C, unless otherwise noted.

Symbol	Parameter	Measurement condition	Min	Тур	Max	Unit
FRONT-END LI	DO INPUT	1			I	
V _{IN}	VIN voltage range	Operating voltage	V _{UVLO}		V _{OVLO}	V
VIN_WITHSTAND	VIN maximum withstand voltage rating		_	_	22	V
V _{IN_OVLO}	VIN overvoltage threshold	Rising	6.0	6.5	7.0	V
V _{OVLO_HYS}	VIN overvoltage threshold hysteresis	Falling	50	150	250	mV
t _{D-OVLO}	VIN overvoltage delay		5.0	10	15	μs
V _{UVLO}	VIN to GND minimum turn on threshold accuracy	VIN rising	3.8	4.0	4.2	V
V _{UVLO-HYS}	VIN UVLO hysteresis		400	500	600	mV
V _{IN2SYS_50}	VIN to VSYS minimum turn on threshold accuracy	VIN rising, 50 mV setting	20	50	80	mV
VIN2SYS_175	VIN to VSYS minimum turn on threshold accuracy	VIN rising, 175 mV setting	100	175	250	mV

Table 5. Front-end LDO

Table 6. Input currents

Symbol	Parameter	Measurement condition	Min	Тур	Max	Unit
VIN CURREI	NT LIMIT					
ILIM ₁₀	VIN current limit (10 mA settings)	10 mA	6.0	8.5	11	mA
ILIM ₁₅	VIN current limit (15 mA settings)	15 mA	10.5	12.75	16	mA
ILIM ₂₀	VIN current limit (20 mA settings)	20 mA	14	17	21	mA
ILIM ₂₅	VIN current limit (25 mA settings)	25 mA	17.5	21.25	26	mA
ILIM ₃₀	VIN current limit (30 mA setting)	30 mA	21	25.5	30	mA
ILIM ₃₅	VIN current limit (35 mA settings)	35 mA	24.5	29.75	35	mA
ILIM ₄₀	VIN current limit (40 mA settings)	40 mA	28	34	40	mA
ILIM ₄₅	VIN current limit (45 mA settings)	45 mA	31.5	38.25	45	mA
ILIM ₅₀	VIN current limit (50 mA settings)	50 mA	35	42.5	50	mA
ILIM ₁₀₀	VIN current limit (100 mA settings)	100 mA	85	95	105	mA
ILIM ₁₅₀	VIN current limit (150 mA settings)	150 mA	125	137.5	160	mA
ILIM ₂₀₀	VIN current limit (200 mA settings)	200 mA	170	190	210	mA
ILIM ₃₀₀	VIN current limit (300 mA setting)	300 mA	260	285	320	mA
ILIM ₄₀₀	VIN current limit (400 mA settings)	400 mA	345	380	425	mA

Table 6. Input currents...continued

Symbol	Parameter	Measurement condition	Min	Тур	Мах	Unit
ILIM ₅₀₀	VIN current limit (500 mA settings)	500 mA	430	475	530	mA
ILIM ₆₀₀	VIN current limit (600 mA settings)	600 mA	520	570	640	mA
ILIM ₇₀₀	VIN current limit (700 mA settings)	700 mA	610	665	750	mA
ILIM ₈₀₀	VIN current limit (800 mA settings)	800 mA	690	760	850	mA
ILIM ₉₀₀	VIN current limit (900 mA settings)	900 mA	780	855	950	mA
ILIM ₁₀₀₀	VIN current limit (1000 mA settings)	1000 mA	855	950	1100	mA
ILIM ₁₅₀₀	VIN current limit (1500 mA settings)	1500 mA	1260	1400	1700	mA
R _{INSD}	Input self discharge resistance		18	30	42	kΩ

Table 7. Switch impedances and leakage currents

Symbol	Parameter	Measurement Condition	Min	Тур	Max	Unit
R _{VIN2SYS}	VIN to VSYS resistance		100	250	550	mΩ
I _{SYS}	VSYS leakage current	VSYS = 0 V	0	0.2	10	μA

Table 8. Watchdog timer

Symbol	Parameter	Measurement condition	Min	Тур	Мах	Unit
t _{WD}	Watchdog timer period		_	80	—	s
t _{WDACC}	Watchdog timer accuracy		-20	0	20	%

Table 9. Internal 2.7 V Regulator (LDO2P7)

Symbol	Parameter	Measurement condition	Min	Тур	Мах	Unit
V _{GDRV}	Output voltage		2.6	2.7	2.8	V
I _{GDRV}	Output current		5.0	—	_	mA
V _{DO(GDRV)}	Dropout voltage		0	—	800	mV

Table 10. USBPHY LDO

Symbol	Parameter	Measurement condition	Min	Тур	Мах	Unit
V _{USB_PHY}	Output voltage	I _{OUT} = 10 mA; 3.3 V and 4.9 V settings. VIN = 5.5 V	-5.0	_	5.0	%
I _{USB_PHY}	Maximum output current		60	_	_	mA
USB _{RDIS}	Internal discharge resistance		500	1000	1500	Ω
USB _{CAPSTA}	Output capacitor for stable operation	0 μA < I _{OUT} < 60 mA, MAX ESR = 10 mΩ	0.7	1.0	2.2	μF
I _{QUSB}	Quiescent supply current		_	35	_	μA
USBPHY _{LDREG}	DC load regulation	VIN = 5.5 V, 30 µA < I _{OUT} < 60 mA	0	5.0	13	mV
PF1510	All information provided in	this document is subject to legal disclaimers.		©	NXP B.V. 2021.	All rights rese

Table 10. USBPHY LDO...continued

Symbol	Parameter	Measurement condition	Min	Тур	Мах	Unit
USBPHY _{DO}	Dropout voltage	VIN = 5.0 V, I _{OUT} = 60 mA	_	200	350	mV
USBPHYI _{LIM}	Output current limit		65	150	200	mA
PSRR _{USB_PHY}	PSRR	VIN = 5.5 V, C _{OUT} = 1.0 μF	55	60	75	dB

5.3.2 Electrical characteristics – SW1 and SW2

All parameters are specified at $T_A = -40$ to 105 °C, VSYS = $V_{SWxIN} = 2.5$ to 4.5 V, $V_{SWx} = 1.2$ V, $I_{SWx} = 200$ mA, typical external component values, $f_{SWx} = 2.0$ MHz, unless otherwise noted. Typical values are characterized at VSYS = $V_{SWxIN} = 3.6$ V, $V_{SWx} = 1.1$ V, $I_{SWx} = 100$ mA, and 25 °C, unless otherwise noted.

Table 11. SW1 and SW2 electrical characteristics

Symbol	Parameter	Min	Тур	Мах	Unit
V _{SWxIN}	Operating input voltage	2.5	—	4.5	V
I _{SWx}	Rated output current	1000	_		mA
V _{SWx}	Output voltage accuracy DVS enabled mode (OTP_SWx_DVS_SEL = 0) Normal power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 1.0 A 0.6 V ≤ V_{SWx} ≤ 1.0 V	-15		15	mV
V _{SWx}	Output voltage accuracy DVS enabled mode (OTP_SWx_DVS_SEL = 0) Normal power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 1.0 A 1.0 V < $V_{SWx} \le$ 1.3875 V	-2.0		2.0	%
V _{SWx}	Output voltage accuracy DVS enabled mode (OTP_SWx_DVS_SEL = 0) Low-power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < ISWx < 0.1 A 0.6 V ≤ V_{SWx} ≤ 1.0 V	-30		30	mV
V _{SWx}	Output voltage accuracy DVS enabled mode (OTP_SWx_DVS_SEL = 0) Low-power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 0.1 A 1.0 V < $V_{SWx} \le 1.3875$ V	-3.0		3.0	%
V _{SWx}	Output voltage accuracy DVS disabled mode (OTP_SWx_DVS_SEL = 1) Normal power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 1.0 A 1.1 V ≤ V_{SWx} ≤ 1.5 V	-45	_	45	mV
V _{SWx}	Output voltage accuracy DVS disabled mode (OTP_SWx_DVS_SEL = 1) Normal power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 1.0 A 1.8 V ≤ V_{SWx} ≤ 3.3 V	-3.0	_	3.0	%
V _{SWx}	Output voltage accuracy DVS disabled mode (OTP_SWx_DVS_SEL = 1) Low-power mode, $2.5 \text{ V} < \text{V}_{SWxIN} < 4.5 \text{ V}$, $0 < \text{I}_{SWx} < 0.1 \text{ A}$ 1.1 V $< \text{V}_{SWx} \le 1.5 \text{ V}$	-55	_	55	mV

Table 11. SW1 and SW2 electrical characteristics...continued

Symbol	Parameter	Min	Тур	Max	Unit
V _{SWx}	Output voltage accuracy DVS disabled mode (OTP_SWx_DVS_SEL = 1) Low-power mode, 2.5 V < V_{SWxIN} < 4.5 V, 0 < I_{SWx} < 0.1 A 1.8 V ≤ V_{SWx} ≤ 3.3 V	-4.0	_	4.0	%
ΔV _{SWx}	Output ripple	_	5.0	_	mV
SWxEFF	Efficiency V_{SWxIN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 mΩ LP/ ULP mode, 1.2 V, 1.0 mA		88	_	%
SWxEFF	Efficiency V_{SWxIN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.2 V, 50 mA		90	-	%
SWxEFF	Efficiency V_{SWxIN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.2 V, 150 mA		92	_	%
SWxEFF	Efficiency V_{SWxIN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.2 V, 400 mA		89	-	%
SWxEFF	Efficiency V_{SWxIN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.2 V, 1000 mA		83	_	%
I _{SWXLIMH}	Current limiter peak (high-side MOSFET) current detection SWxILIM[1:0] = 00 SWxILIM[1:0] = 01 SWxILIM[1:0] = 10 SWxILIM[1:0] = 11	0.7 0.8 1.0 1.4	1.0 1.2 1.5 2.0	1.3 1.6 2.0 2.6	A
I _{SWxLIML}	Current limiter low-side MOSFET current detection (sinking current)	0.7	1.0	1.3	A
I _{SWxQ}	Quiescent current (at 25 °C) Low-power mode with DVS disabled (OTP_SWx_DVS_SEL = 1)	_	1.0		μΑ
I _{SWxQ}	Quiescent current (at 25 °C) Low-power mode with DVS enabled (OTP_SWx_DVS_SEL = 0)	_	6.0	_	μA
I _{SWxQ}	Quiescent current (at 25 °C) Normal power mode with DVS disabled (OTP_SWx_DVS_SEL = 1)	_	5.5	_	μA
I _{SWxQ}	Quiescent current (at 25 °C) Normal power mode with DVS enabled (OTP_SWx_DVS_SEL = 0)	_	10	_	μΑ
V _{SWxOSH}	Startup overshoot (Normal mode) I _{SWx} = 0 mA DVS speed = 12.5 mV/4 µs, VSYS = V _{SWxIN} = 3.6 V, V _{SWx} = 1.35 V		-	25	mV
t _{ONSWx}	Turn on time 10 % to 90 % of end value DVS speed = 12.5 mV/4 μ s, VSYS = V _{SWxIN} = 3.6 V, V _{SWx} = 1.35 V		-	500	μs

Table 11. SW1 and SW2 electrical characteristics...continued

Symbol	Parameter	Min	Тур	Мах	Unit
V _{SWxLOTR}	Transient load regulation (Normal power mode) Transient load = 50 mA to 250 mA, di/dt = 200 mA/µs				mV
	Overshoot Undershoot		25 25	_	
R _{ONSWxP}	SWx P-MOSFET R _{DS(on)} at V _{SWxIN} = 3.6 V		200	_	mΩ
R _{ONSWxN}	SWx N-MOSFET R _{DS(on)} at V _{SWxIN} = 3.6 V		150	_	mΩ
R _{SWxDIS}	Turn off discharge resistance	_	500	_	Ω

5.3.3 Electrical characteristics – SW3

All parameters are specified at $T_A = -40$ to 105 °C, VSYS = $V_{SW3IN} = 2.5$ to 4.5 V, $V_{SW3} = 1.8$ V, $I_{SW3} = 200$ mA, typical external component values, $f_{SW3} = 2.0$ MHz, unless otherwise noted. Typical values are characterized at VSYS = $V_{SW3IN} = 3.6$ V, $V_{SW3} = 1.8$ V, $I_{SW3} = 200$ mA, and 25 °C, unless otherwise noted.

Table 12. SW3 electrical characteristics

Symbol	Parameter	Min	Тур	Мах	Unit
V _{SW3IN}	Operating input voltage	2.5	—	4.5	V
V _{SW3}	Output voltage accuracy (all voltage settings) Normal power mode, 2.5 V < V _{SW3IN} < 4.5 V, 0 < I _{SW3} < 1.0 A	-2.0	_	2.0	%
V _{SW3}	Output voltage accuracy (all voltage settings) Low-power mode, 2.5 V < V _{SW3IN} < 4.5 V, 0 < I _{SW3} < 0.1 A	-3.0	_	3.0	%
ΔV _{SW3}	Output ripple	_	5.0	_	mV
SW3EFF	Efficiency V_{SW3IN} = 3.6 V, L_{SW3} = 1.0 µH, DCR = 50 m Ω LP/ ULP Mode, 1.8 V, 1.0 mA		88	_	%
SW3EFF	Efficiency V_{SW3IN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.8 V, 50 mA		90	_	%
SW3EFF	Efficiency V_{SW3IN} = 3.6 V, L_{SWx} = 1.0 mH, DCR = 50 m Ω Normal power mode, 1.8 V, 100 mA	_	91	_	%
SW3EFF	Efficiency V_{SW3IN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.8 V, 400 mA		92	_	%
SW3EFF	Efficiency V_{SW3IN} = 3.6 V, L_{SWx} = 1.0 µH, DCR = 50 m Ω Normal power mode, 1.8 V, 1000 mA		83	_	%
I _{SW3LIMH}	Current limiter peak (high-side MOSFET) current detection SW3ILIM[1:0] = 00 SW3ILIM[1:0] = 01 SW3ILIM[1:0] = 10 SW3ILIM[1:0] = 11	0.7 0.8 1.0 1.4	1.0 1.2 1.5 2.0	1.3 1.6 2.0 2.6	A
I _{SW3LIML}	Current limiter low-side MOSFET current detection (sinking current)	0.7	1.0	1.3	A

© NXP B.V. 2021. All rights reserved.

Table 12.	SW3 electrical	characteristicscontinued
-----------	----------------	--------------------------

Symbol	Parameter	Min	Тур	Max	Unit
I _{SW3Q}	Quiescent current (at 25 °C) Low-power mode	_	1.0	_	μA
V _{SW3OSH}	Start-up overshoot (Normal mode) I _{SW3} = 0 mA VSYS = V _{SW3IN} = 3.6 V, V _{SW3} = 1.8 V		-	50	mV
t _{onsw3}	Turn on time 10 % to 90 % of end value VSYS = V_{SW3IN} = 3.6 V, V_{SW3} = 1.8 V		_	500	μs
V _{SW3LOTR}	Transient load regulation (Normal power mode) Transient load = 50 mA to 250 mA, di/dt = 200 mA/µs Overshoot Undershoot		50 50		mV
R _{ONSW3N}	SW3 N-MOSFET R _{DS(on)} at V _{SW3IN} = 3.6 V	—	150	_	mΩ
R _{ONSW3P}	SW3 P-MOSFET R _{DS(on)} at V _{SW3IN} = 3.6 V	—	200	—	mΩ
R _{SW3DIS}	Turn off discharge resistance		300	_	Ω

5.3.4 Electrical characteristics – LDO1

All parameters are specified at $T_A = -40$ to 105 °C, VSYS = 2.5 to 4.5 V, $V_{LDOIN1} = 3.6$ V, VLDO1[4:0] = 11111, $I_{LDO1} = 10$ mA, typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, $V_{LDOIN1} = 3.6$ V, VLDO1[4:0] = 11111, $I_{LDO1} = 10$ mA, and 25 °C, unless otherwise noted.

Table 13. LDO1 electrical characteristics

Symbol	Parameter	Min	Тур	Мах	Unit
V _{LDO1IN}	Operating input voltage V _{LDO1} + 250 mV ≤ VSYS ≤ 4.5 V	1.0	_	4.5	V
V _{LDO1NOM}	Nominal output voltage	_	See Table 33	_	V
I _{LDO1MAX}	Rated output load current, Normal mode	300	_	—	mA
ILDO1MAXLPM	Rated output load current, Low-power mode	10	—	_	mA
V _{LDO1TOL}	$ \begin{array}{l} \mbox{Output voltage tolerance, Normal mode} \\ V_{LDO1INMIN} < V_{LDO1IN} < 4.5 \mbox{V}, 0 \mbox{ mA < I}_{LDO1} \leq 300 \mbox{ mA} \\ 0.8 \mbox{V} \leq V_{LDO1} < 1.8 \mbox{V} \\ 1.8 \mbox{V} \leq V_{LDO1} \leq 3.3 \mbox{V} \\ V_{LDO1INMIN} < V_{LDO1IN} < 4.5 \mbox{V}, 0 \mbox{ mA < I}_{LDO1} < 10 \mbox{ mA} \mbox{(Low-power mode)} \end{array} $	-2.5 -2.5 -4.0		2.5 2.5 4.0	%
I _{LDO1LIM}	Current limit I_{LDO1} when V_{LDO1} is forced to $V_{LDO1NOM}/2$	320	_	1000	mA
I _{LDO10CP}	LDO1FAULTI threshold (also used to disable LDO1 when REGSCPEN = 1)	320	_	1000	mA
I _{LDO1Q}	Quiescent current (at 25 °C) No load, change in I _{VSYS} and I _{VLDOIN1} When LDO1 enabled in Normal mode When LDO1 enabled in Low-power mode		17 2.5		μA

Symbol	Parameter	Min	Тур	Max	Unit
R _{DSON_QFN_LDO1}	Dropout on resistance	—	_	350	mΩ
PSRR _{LDO1}	PSRR I _{LDO1} = 150 mA, 20 Hz to 20 kHz V _{LDO1} = 3.30 V, V _{LDO1IN} = 3.8 V, VSYS = 4.2 V		56		dB
TR _{VLDO1}	Turn on time 10 % to 90 % of end value $V_{LDO1INMIN} < V_{LDO1IN} \le 4.5 V$, $I_{LDO1} = 0.0 \text{ mA}$	_	200	500	μs
R _{LDO1DIS}	Turn off discharge resistance	—	250	_	Ω
LDO10UT _{OSHT}	Start-up overshoot (% of final value) V _{LDO1INMIN} < V _{LDO1IN} ≤ 4.5 V, I _{LDO1} = 0.0 mA		1.0	2.0	%
V _{LD01LOTR}	Transient load response V _{LDO1INMIN} < V _{LDO1IN} ≤ 4.5 V, I _{LDO1} = 10 mA to 200 mA in 10 μs Overshoot Undershoot		50 50		mV

Table 13. LDO1 electrical characteristics...continued

5.3.5 Electrical characteristics – LDO2

All parameters are specified at $T_A = -40$ to 105 °C, VSYS = 3.6 V, $V_{LDOIN2} = 3.6$ V, VLDO2[3:0] = 1111, $I_{LDO2} = 10$ mA, typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, $V_{LDOIN2} = 3.6$ V, VLDO2[3:0] = 1111, $I_{LDO2} = 10$ mA, and 25 °C, unless otherwise noted.

Table 14. LDO2 electrical characteristics

Symbol	Parameter	Min	Тур	Мах	Unit
V _{LDO2IN}	Operating input voltage $1.8 V \le V_{LDO2NOM} \le 2.5 V$	2.8	_	4.5	V
	$2.6 \text{ V} \le \text{V}_{\text{LDO2NOM}} \le 3.3 \text{ V}$	V _{LDO2NOM} + 0.250	-	4.5	
V _{LDO2NOM}	Nominal output voltage	—	See Table 35	_	V
I _{LDO2MAX}	Rated output load current, Normal mode	400	—	_	mA
I _{LDO2MAXLPM}	Rated output load current, Low-power mode	10	-	—	mA
V _{LDO2TOL}	Output voltage tolerance $V_{LDO2INMIN} < V_{LDO2IN} < 4.5 V$ 10.0 mA $\leq I_{LDO2} < 400$ mA 0.0 mA $< I_{LDO2} < 10$ mA (Low-power mode)	-2.0 -4.0		2.0 4.0	%
I _{LDO2LIM}	Current limit I_{LDO2} when V_{LDO2} is forced to $V_{LDO2NOM}/2$	450	750	1050	mA
I _{LDO2OCP}	LDO2FAULTI threshold (also used to disable LDO2 when REGSCPEN = 1)	450	—	1050	mA
I _{LDO2Q}	Quiescent Current (25 °C) No load, change in I_{VSYS} and $I_{VLDO2IN}$ When V_{LDO2} enabled in Normal mode When V_{LDO2} enabled in Low-power mode		15 1.5		μA
R _{DSON_QFN_LDO2}	2 Dropout on resistance	—	_	300	mΩ

Power management integrated circuit (PMIC) for low power application processors

Symbol	Parameter	Min	Тур	Мах	Unit
PSRR _{VLDO2}	PSRR I _{LDO2} = 200 mA, 20 Hz to 20 kHz V _{LDO2} = 3.30 V, V _{LDO2IN} = 3.9 V, VSYS = 4.2 V	_	60	_	dB
t _{onldo2}	Turn on time 10 % to 90 % of end value $V_{LDO2INMIN} < V_{LDO2IN} \le 4.5$ V, I _{LDO2} = 0.0 mA	-	200	500	μs
R _{LDO2DIS}	Turn off discharge resistance	—	250	—	Ω
LDO2OUT _{OSHT}	Start-up overshoot (% of final value) $V_{LDO2INMIN} < V_{LDO2IN} \le 4.5$ V, $I_{LDO2} = 0.0$ mA	—	1.0	2.0	%
V _{LDO2LOTR}	Transient load response $V_{LDO2INMIN} < V_{LDO2IN} \le 4.5$ V, $I_{LDO2} = 10$ mA to 100 mA in 10 μ s				mV
	Overshoot Undershoot		50 50	_	

Table 14. LDO2 electrical characteristics...continued

5.3.6 Electrical characteristics – LDO3

All parameters are specified at T_A = –40 to 105 °C, VSYS = 2.5 to 4.5 V, V_{LDOIN3} = 3.6 V, VLDO3[4:0] = 11111, I_{LDO3} = 10 mA, typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, V_{LDOIN3} = 3.6 V, VLDO3[4:0] = 11111, I_{LDO3} = 10 mA, and 25 °C, unless otherwise noted.

Table 15. LDO3 electrical characteristics

Symbol	Parameter	Min	Тур	Max	Unit
V _{LDO3IN}	Operating input voltage V _{LDO3} + 250 mV ≤ VSYS ≤ 4.5 V	1.0	-	4.5	V
V _{LDO3NOM}	Nominal output voltage		See Table 33	_	V
I _{LDO3MAX}	Rated output load current, Normal mode	300	—	_	mA
I _{LDO3MAXLPM}	Rated output load current, Low-power mode	10	—	—	mA
V _{LDO3TOL}	Output voltage tolerance, Normal mode $V_{LDO3INMIN} < V_{LDO3IN} < 4.5 V$, 0 mA < $I_{LDO3} < 300$ mA 0.8 V $\leq V_{LDO3} < 1.8 V$ 1.8 V $\leq V_{LDO3} \leq 3.3 V$ $V_{LDO3INMIN} < V_{LDO3IN} < 4.5 V$, 0 mA < $I_{LDO3} < 10$ mA (Low-power mode)	-2.5 -2.5 -4.0		2.5 2.5 4.0	%
I _{LDO3LIM}	Current limit I_{LDO3} when V_{LDO3} is forced to $V_{LDO3NOM}/2$	320	-	1000	mA
I _{LDO3OCP}	LDO3FAULTI threshold (also used to disable LDO3 when REGSCPEN = 1)	320	-	1000	mA
I _{LDO3Q}	Quiescent current (at 25 °C) No load, change in I _{VSYS} and I _{VLDOIN3} When LDO3 enabled in Normal mode When LDO3 enabled in Low-power mode	_	17 2.5		μA
R _{DSON_QFN_LDO3}	Dropout on resistance	_	_	350	mΩ

Symbol	Parameter	Min	Тур	Max	Unit
PSRR _{LDO3}	PSRR I _{LDO3} = 150 mA, 20 Hz to 20 kHz V _{LDO3} = 3.30 V, V _{LDO3IN} = 3.8 V, VSYS = 4.2 V	_	56	_	dB
TR _{VLDO3}	Turn on time 10 % to 90 % of end value V _{LDO3INMIN} < V _{LDO3IN} < 4.5 V, I _{LDO3} = 0.0 mA	_	200	500	μs
R _{LDO3DIS}	Turn off discharge resistance	—	250	—	Ω
LDO3OUT _{OSHT}	Start-up overshoot (% of final value) $V_{LDO3INMIN} < V_{LDO3IN} \le 4.5 \text{ V}, I_{LDO3} = 0.0 \text{ mA}$		1.0	2.0	%
V _{LDO3LOTR}	Transient load response V _{LDO3INMIN} < V _{LDO3IN} ≤ 4.5 V, I _{LDO3} = 10 mA to 100 mA in 10 μs Overshoot				mV
	Undershoot	_	50	_	
		—	50	<u> </u>	

Table 15. LDO3 electrical characteristics...continued

5.3.7 Electrical characteristics – VREFDDR

 T_A = -40 to 105 °C, VSYS = 2.5 to 4.5 V, I_{REFDDR} = 0.0 mA, $V_{INREFDDR}$ = 1.35 V and typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, I_{REFDDR} = 0.0 mA, $V_{INREFDDR}$ = 1.35 V, and 25 °C, unless otherwise noted.

Table 16. VREFDDR electrical characteristics

Symbol	Parameter	Min	Тур	Мах	Unit
V _{INREFDDR}	Operating input voltage range	0.9	_	1.8	V
V _{REFDDR}	Output voltage, 0.9 V < V _{INREFDDR} < 1.8 V, 0 mA < I_{REFDDR} < 10 mA	—	V _{INREFDDR} /2	_	V
V _{REFDDRTOL}	Output voltage tolerance, as a percentage of V _{INREFDDR} , 1.2 V < V _{INREFDDR} < 1.65 V, 0 mA < I _{REFDDR} < 10 mA	49.25	50	50.75	%
I _{REFDDRQ}	Quiescent current (at 25 °C)	_	1.1	_	μA
IREFDDRLM	Current limit, I_{REFDDR} when V_{REFDDR} is forced to $V_{INREFDDR}/4$	10.5	24	38	mA
t _{ONREFDDR}	Turn on time, 10 % to 90 % of end value, $V_{\rm INREFDDR}$ = 1.2 V to 1.65 V, $I_{\rm REFDDR}$ = 0.0 mA	-	_	100	μs

5.3.8 Electrical characteristics – VSNVS

All parameters are specified at $T_A = -40$ to 105 °C, VSYS = 3.6 V, $V_{SNVS} = 3.0$ V, $I_{SNVS} = 5.0 \ \mu$ A, typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, $V_{SNVS} = 3.0$ V, $I_{SNVS} = 5.0 \ \mu$ A, and 25 °C, unless otherwise noted.

 Table 17. VSNVS electrical characteristics

Symbol	Parameter	Min	Тур	Max	Unit
V _{SNVSIN}	Operating input voltage				V
	Valid coin cell range	1.8		3.3	
	Valid VSYS	2.45		4.5	

© NXP B.V. 2021. All rights reserved.

Table 17.	VSNVS	electrical	characteristicscontinued
-----------	-------	------------	--------------------------

Symbol	Parameter	Min	Тур	Max	Unit
I _{SNVS}	Operating load current V _{SNVSINMIN} < V _{SNVSIN} < V _{SNVSINMAX}	2000			μA
V _{TL1}	VSYS threshold (VSYS powered to coin cell powered)	—	UVDET failing	_	V
V _{TH1}	VSYS threshold (coin cell powered to VSYS powered)	—	UVDET rising	_	V
V _{SNVS}	Output voltage (when running from VSYS) 0 μA < I _{SNVS} < 2000 μA	-7.0 %	3.0	7.0 %	V
	Output voltage (when running from LICELL) 0 μA < I _{SNVS} < 2000 μA 2.84 V < V _{COIN} < 3.3 V	VCOIN - 0.20	_	_	
V _{SNVSDROP}	Dropout voltage VSYS = 2.9 V I _{SNVS} = 2000 μA	_	_	220	mV
I _{SNVSLIM}	Current limit VSYS > V _{TH1}	5200	_	24000	μA
V _{SNVSTON}	Turn on time (load capacitor, 0.47 μ F) 10 % to 90 % of final value V _{SNVS} V _{COIN} = 0.0 V, I _{SNVS} = 0 μ A	_	_	3.0	ms
V _{SNVSOSH}	Start-up overshoot I _{SNVS} = 5.0 μA dVSYS/dt = 50 mV/μs	_	40	70	mV
R _{DSONSNVS}	Internal switch R _{DS(on)} V _{COIN} = 2.6 V	_	_	100	Ω

5.3.9 Electrical characteristics – IC level bias currents

All parameters are specified at 25 °C, VSYS = 3.6 V, VIN = 0 V, typical external component values, unless otherwise noted. Typical values are characterized at VSYS = 3.6 V, V_{SNVS} = 3.0 V, and 25 °C, unless otherwise noted.

Table 18. IC level electrical characteristics

Mode	PF1510 conditions	System conditions	Тур	Max	Unit
Coin cell	VSNVS from LICELL All other blocks off VSYS = 0.0 V	No load on VSNVS	1.5	4.0	μA
CORE_OFF	VSNVS from VSYS Wake-up from ONKEY active All other blocks off VSYS > UVDET	No load on VSNVS, PMIC able to wake-up	1.5	4.0	μA
Sleep	VSNVS from VSYS Wake-up from PWRON active Trimmed reference active DDR I/O rail in Low-power mode VREFDDR disabled	No load on VSNVS. DDR memories in self refresh.	12.5	25	μΑ

Table 18. IC level electrical characteristics...continued

Mode	PF1510 conditions	System conditions	Тур	Мах	Unit
Standby/Suspend	VSNVS from either VSYS or LICELL SW1 in ultra Low-power mode SW2 in ultra Low-power mode SW3 in ultra Low-power mode Trimmed reference active VLDO1 is disabled VLDO2 enabled in Low-power mode VLDO3 enabled in Low-power mode VREFDDR enabled	No load on VSNVS. Processor enabled in Low-power mode.	23	46	μΑ
REGS_DISABLE	VSNVS from VSYS Wake-up from ONKEY active Other blocks are off VSYS > UVDET	No load on VSNVS, PMIC able to wake-up	14	20	μA

6 Detailed description

The PF1510 PMIC features three high efficiency low quiescent current buck regulators, three LDO regulators, a DDR voltage reference to supply voltages for the application processor and peripheral devices.

The buck regulators provide the supply to processor cores and to other low voltage circuits such as I/O and memory. Dynamic voltage scaling is provided to allow controlled supply rail adjustments for the processor cores for power optimization.

The three LDO regulators are general purpose to power various processor rails, system connectivity devices and/or peripherals. Depending on the system power configuration, the general purpose LDO regulators can be directly supplied from the main system supply VSYS or from the switching regulators to power peripherals, such as audio, camera, Bluetooth, Wireless LAN.

A specific VREFDDR voltage reference is included to provide accurate reference voltage for DDR memories operation.

The VSNVS block behaves as an LDO, or as a bypass switch to supply the SNVS (Secure Non-Volatile Storage)/RTC (Real Time Clock) circuitry on the processor. VSNVS is powered from VSYS or from a coin cell.

The PF1510 uses an integrated linear front-end LDO that provides 4.5 V at VSYS from the 5.0 V VIN.

Supply	Output voltage (V)	Programming step size (mV)	Load current (mA)
SW1 / SW2	0.60 to 1.3875 / 1.1 to 3.3	12.5/variable	1000
SW3	1.80 to 3.30	100	1000
LDO1	0.75 to 1.50 1.80 to 3.30	50 100	300
LDO2	1.80 to 3.30	100	400

Table 19. Voltage regulators

Table 19. Voltage regulators...continued

Supply	Output voltage (V)	Programming step size (mV)	Load current (mA)
LDO3	0.75 to 1.50 1.80 to 3.30	50 100	300
USBPHY	3.3 or 4.9		60
VSNVS	3.0	N/A	2
VREFDDR	0.5*VINREFDDR	N/A	10

6.1 Buck regulators

The PF1510 features three high efficiency buck regulators with internal compensation. Each buck regulator is capable of meeting optimum power efficiency operation using reduced power variable-frequency pulse skip switching scheme at light loads as well as operating in forced PWM quasi-fixed frequency switching mode at higher loads. The switching regulator controller combines the advantages of hysteretic and voltage mode control which provides outstanding load regulation and transient response, low output ripple voltage and seamless transition between pulse-skip mode and Active Quasi-fixed frequency switching mode. The control circuitry includes an AC loop which senses the output voltage (at SWxFB pin) and directly feeds it to a fast comparator stage. This comparator sets the switching frequency, which is almost constant for steady state operating conditions. It also provides immediate response to dynamic load changes.

In order to achieve accurate DC load regulation, a voltage feedback loop is used. The internally compensated regulation network achieves fast and stable operation with small external components and low ESR capacitors. The transition into and out of low power pulse-skip switching mode takes place automatically according to the load current to maintain optimum power efficiency. Additionally, further power savings through cutting the buck circuitry quiescent current can be achieved by activating a Low-power mode upon entering either STANDBY or SLEEP PMIC power mode or as commanded via I²C control bits. In SW1 and SW2. An OTP option enables or disables DVS in the regulators. When DVS is disabled and the low-power bit is set, the regulator enters an Ultra Low Power (ULP) mode cuts the operating quiescent current even in order to reach extremely low standby power levels needed for ultra low power processors such as that from Kinetis K and L series.

As indicated above, the buck controller supports PWM (Pulse Width Modulation) mode for medium and high load conditions and low-power variable-frequency pulse skip mode at light loads. During high current mode, it operates in continuous conduction and the switching frequency is up to 2.0 MHz with a controlled on-time variation depending on the input voltage and output voltage. If the load current decreases, the converter seamlessly enters the pulse-skip mode to cut the operating quiescent current and maintain high efficiency down to very light loads. In pulse-skip mode the switching frequency varies linearly with the load current. Since the controller supports both power modes within one single building block, the transition from normal power mode to lower power pulse-skip mode and vice versa is seamless without dramatic effects on the output voltage.

In the adopted pulse-skip scheme, the device generates a single switching pulse to ramp up the inductor current and recharge the output capacitor, followed by a non-switching (pause) period where most of the internal circuits are shutdown to achieve a lowest quiescent current. During this time, the load current is supported by the output capacitor. The duration of the pause period depends on the load current and the inductor peak current.

6.2 SW1 and SW2 detailed description

SW1 and SW2 are identical buck regulators designed to carry a nominal load current of 1.0 A. Detailed characteristics and features of SW1 and SW2 are described in this section. Being identical, reference is made only to SWx though the same specifications apply to SW1 and SW2.

6.2.1 SWx dynamic voltage scaling description

SWx integrates an optional DVS circuit that is enabled via OTP. To reduce overall power consumption, when DVS is enabled SWx output voltage can be varied depending on the mode or activity level of the processor.

• Normal operation:

The output voltage is selected by I^2C bits SWx_VOLT[5:0]. A voltage transition initiated by I^2C is governed by the SWx_DVSSPEED I^2C bit as shown in <u>Table 20</u>.

· Standby mode:

The output voltage can be selected by I^2C bits SWx_STBY_VOLT[5:0]. Voltage transitions initiated by a Standby event are governed by the SWx_DVSSPEED I^2C bit as shown in <u>Table 20</u>. This applies only when DVS is enabled.


• Sleep mode:

The output voltage can be higher or lower than in normal operation, but is typically selected to be the lowest state retention voltage of a given processor; it is selected by I^2C bits SWx_SLP_VOLT[5:0]. Voltage transitions initiated by a turn off event are governed by the SWx_DVSSPEED I^2C bit for SWx as shown in <u>Table 20</u>. This applies only when DVS is enabled.

As shown in Figure 5, during a falling DVS transition, dv/dt of the output voltage depends on the load current. Setting the SWx_FPWM_IN_DVS bit forces the regulator in the FPWM mode during the falling transition allowing it to accurately track the DVS reference removing the load dependency. The SWx_FPWM_IN_DVS bit is active only when OTP_SWx_DVS_SEL = 0.

 Table 20.
 SWx DVS setting selection

SWx_DVS speed	Function
0	12.5 mV step each 2.0 μs
1	12.5 mV step each 4.0 μs




PF1510 Product data sheet

24 / 108

6.2.2 SWx DVS and non-DVS operation

SWx has two distinct modes of operation selectable via OTP:

- DVS enabled: a DVS reference is activated and output accuracy of the regulator is tight at the cost of slightly higher quiescent current. See <u>Section 5.3 "Electrical</u> <u>characteristics"</u> for details. In <u>Figure 6</u>, **DVS FB** and **DVS REF** are enabled via OTP for this mode of operation.
- DVS disabled: the regulator operates as a traditional buck converter with a fixed reference and soft-start. The quiescent current in this mode is lower at the cost of output accuracy and transient response. See <u>Section 5.3 "Electrical characteristics"</u> for details. In <u>Figure 6</u>, VREF FB and VREF are enabled via OTP for this mode of operation.



6.2.3 Regulator control

To improve system efficiency, the buck regulators can operate in different switching/ bias modes. The changing between DCM (Discontinuous Conduction Mode)/CCM (Continuous Conduction Mode) takes place automatically based on detecting the load current level. It can be enforced by one of the following means: I²C programming, exiting/ entering the Standby mode, exiting/entering Sleep/Low-power mode.

Available modes for buck regulators are presented in <u>Table 21</u>. These switching modes are available with OTP_SWx_DVS_SEL = 0 and OTP_SWx_DVS_SEL = 1. <u>Table 22</u> shows the bit settings for operating the buck converter is these modes based on the PMIC operating state.

 Table 21. Buck regulator operating modes

Mode	Description
OFF	The regulator is switched off and the output voltage is discharged using an internal resistor.

Table 21. Buck regulator operating modes...continued

	Mode	Description				
		This is the default mode of operation of the buck regulator. In this mode, the regulator operates in a quasi- fixed frequency switching mode at moderate and high loads, with pulse skip (variable switching frequency) scheme at light load for optimized efficiency.				
	F-PWM	In this mode, the regulator is always in PWM mode operation regardless of load conditions.				
	Low-power	To further extend power savings when the load current is minimal, this mode cuts the quiescent current of the buck converter by reducing the bias to the comparator. The regulator is operated in low power modes (Standby and/or Sleep) with the proper I^2C setting. See <u>Table 22</u> .				

The following table shows actions to control different bits for SW1 and SW2.

Table 22. Buck mode control

PMIC state	SWx_EN	SWx_STBY	SWx_OMODE	SWx_LPWR	SWx_FPWM	SWx operating mode
Run/Standby /Sleep	0	X	Х	Х	Х	SW disabled
Run	1	Х	Х	0	0	SW enabled. Operates in DCM at light loads
Run	1	Х	Х	0	1	SW enabled. Forced PWM mode
Run	1	Х	Х	1	0	SW Enabled. Does not operate in Low-power mode.
Run	1	Х	Х	1	1	SW enabled. Forced PWM mode
Standby	1	0	Х	Х	Х	SW disabled
Standby	1	1	Х	0	0	SW enabled. Operates in DCM at light loads.
Standby	1	1	Х	0	1	SW enabled. Forced PWM mode.
Standby	1	1	Х	1	0	SW enabled. Operates in Low-power mode.
Standby	1	1	Х	1	1	SW enabled. Forced PWM mode
Sleep	1	Х	0	Х	Х	SW disabled
Sleep	1	Х	1	0	0	SW enabled. Operates in DCM at light loads.
Sleep	1	Х	1	0	1	SW enabled. Forced PWM mode.
Sleep	1	Х	1	1	0	SW enabled. Operates in Low-power mode.
Sleep	1	Х	1	1	1	SW enabled. Forced PWM mode

6.2.4 Current limit protection

SWx features high and low-side FET current limit. When current through the FETs goes above their respective thresholds, the FET is turned off to prevent further increase in current.

The protection is enabled in a cycle-by-cycle mode. Hitting either current limit sets the corresponding interrupt sense bits. If the faults persist for longer than the 8.0 ms debounce time, the interrupt status bit is set.

6.2.5 Output voltage setting in SWx

Output voltage of SWx is programmable via OTP. During startup (REGS_DISABLE mode to RUN mode), contents of the OTP_SWx_VOLT[5:0] are mapped into the SWx_VOLT[5:0], SWx_STBY_VOLT[5:0] and SWx_SLP_VOLT[5:0] register which set the regulator output voltage during Run, Standby and Sleep modes respectively.

In the DVS enabled mode (OTP_SWx_DVS_SEL = 0), values of SWx_VOLT[5:0], SWx_STBY[VOLT[5:0] and SWx_SLP_VOLT[5:0] can be changed via I^2C after the PMIC starts up (RESETBMCU is released).

In the DVS disabled mode (OTP_SWx_DVS_SEL = 1), value of SWx_VOLT[5:0], SWx_STBY[VOLT[5:0] and SWx_SLP_VOLT[5:0] are read-only and must not be written to.

Table 23. SW1 and SW2 output voltage setting

Set point	SWx_VOLT[5:0] SWx_STBY_VOLT[5:0] SWx_SLP_VOLT[5:0]	Output voltage with DVS enabled OTP_SWx_DVS_SEL = 0	Output voltage with DVS disabled OTP_SWx_DVS_SEL = 1
0	000000	0.6000	1.10
1	000001	0.6125	1.20
2	000010	0.6250	1.35
3	000011	0.6375	1.50
4	000100	0.6500	1.80
5	000101	0.6625	2.50
6	000110	0.6750	3.00
7	000111	0.6875	3.30
8	001000	0.7000	3.30
9	001001	0.7125	3.30
10	001010	0.7250	3.30
11	001011	0.7375	3.30
12	001100	0.7500	3.30
13	001101	0.7625	3.30
14	001110	0.7750	3.30
15	001111	0.7875	3.30
16	010000	0.8000	3.3
17	010001	0.8125	3.30
18	010010	0.8250	3.30
19	010011	0.8375	3.30
20	010100	0.8500	3.30
21	010101	0.8625	3.30
22	010110	0.8750	3.30
23	010111	0.8875	3.30
24	011000	0.9000	3.30
25	011001	0.9125	3.30
26	011010	0.9250	3.30
27	011011	0.9375	3.30
28	011100	0.9500	3.30

Table 23. SW1 and SW2 output voltage settingcontinued							
Set point	SWx_VOLT[5:0] SWx_STBY_VOLT[5:0] SWx_SLP_VOLT[5:0]	Output voltage with DVS enabled OTP_SWx_DVS_SEL = 0	Output voltage with DVS disabled OTP_SWx_DVS_SEL = 1				
29	011101	0.9625	3.30				
30	011110	0.9750	3.30				
31	011111	0.9875	3.30				
32	100000	1.0000	3.30				
33	100001	1.0125	3.30				
34	100010	1.0250	3.30				
35	100011	1.0375	3.30				
36	100100	1.0500	3.30				
37	100101	1.0625	3.30				
38	100110	1.0750	3.30				
39	100111	1.0875	3.30				
40	101000	1.1000	3.30				
41	101001	1.1125	3.30				
42	101010	1.125	3.30				
43	101011	1.1375	3.30				
44	101100	1.1500	3.30				
45	101101	1.1625	3.30				
46	101110	1.1750	3.30				
47	101111	1.1875	3.30				
48	110000	1.2000	3.30				
49	110001	1.2125	3.30				
50	110010	1.2250	3.30				
51	110011	1.2375	3.30				
52	110100	1.2500	3.30				
53	110101	1.2625	3.30				
54	110110	1.2750	3.30				
55	110111	1.2875	3.30				
56	111000	1.3000	3.30				
57	111001	1.3125	3.3				
58	111010	1.3250	3.30				
59	111011	1.3375	3.30				
60	111100	1.3500	3.30				
61	111101	1.3625	3.30				
62	111110	1.3750	3.30				
63	111111	1.3875	3.30				

Table 23. SW1 and SW2 output voltage setting...continued

PF1510 Product data sheet © NXP B.V. 2021. All rights reserved.

6.2.6 SWx external components

<u>Table 24</u> shows the combination of inductor and capacitor values that work with the SWx regulator.

The design is optimized for a 1.0 μ H inductor.

Table 24. Acceptable inductance and capacitance values

Inductance / capacitance	2 x 10 µF			
1.0 μΗ				

Table 25 and Table 26 show example inductor and capacitor part numbers respectively.

Table 25. Example inductor part numbers


Part number	Size (mm)	1.0 µH
DFE201610E	2.0 x 1.6	57 mΩ, 3.6 A
DFE201610P	2.0 x 1.6	70 mΩ, 3.1 A
DFE201210U	2.0 x 1.2	95 mΩ, 3.1 A
DFE160810S	1.6 x 0.8	120 mΩ, 2.0 A
DFE201208S	2.0 x 1.2	86 mΩ, 2.4 A
DFE160808S	1.6 x 0.8	144 mΩ, 1.9 A

Table 26. Example capacitor part numbers

Murata part number	Description		
GRM188R60J106ME47D	6.3 V, 10 μF, 0402, X5R		
GRM188D70J106MA73	6.3 V, 10 μF, 0402, X7R		
GRM188R61A106KE69	10 µF 10 V 10 % X5R 0603 .95 mm		
GRM219R61A106KE44	10 µF 10 V 10 % X5R 0805 .95 mm		

6.3 SW3 detailed description

SW3 is a buck regulator designed to carry a nominal load current of 1.0 A. The output voltage is programmable from 1.8 V to 3.3 V in 100 mV steps. Dynamic voltage scaling is not supported in this regulator.



6.3.1 Regulator control

To improve system efficiency the buck regulator can operate in different switching/ bias modes. The changing between DCM/CCM takes place automatically based on detecting the load current level. It can be enforced by one of the following means: I²C programming, exiting/entering the Standby mode, exiting/entering Sleep/ Low-power mode.

Available modes for buck regulators are presented in Table 27.

<u>Table 28</u> shows the bit settings for operating the buck converter in these modes based on the PMIC operating state.

Mode	Description
OFF	The regulator is switched off and the output voltage is discharged using an internal resistor.
Adaptive	This is the default mode of operation of the buck regulator. In this mode, the regulator operates in a quasi-fixed frequency switching mode at moderate and high loads, with pulse skip (variable switching frequency) scheme at light load for optimized efficiency.
F-PWM	In this mode, the regulator is always in PWM mode operation regardless of load conditions.
Low-power	To further extend power savings when the load current is minimal, this mode cuts the quiescent current of the buck converter by reducing the bias to the comparator. The regulator is operated in low power modes (Standby and/or Sleep) with the proper I^2C setting. See <u>Table 28</u> .

PMIC state	SW3_EN	SW3_STBY	SW3_OMODE	SW3_LPWR	SW3_FPWM	SW3 operating mode
Run/ Standby/ Sleep	0	Х	Х	Х	Х	SW disabled
Run	1	X	Х	0	0	SW enabled Operates in DCM at light loads
Run	1	Х	Х	0	1	SW enabled Forced PWM mode
Run	1	Х	Х	1	0	SW enabled Does not operate in Low- power mode
Run	1	Х	Х	1	1	SW enabled Forced PWM mode
Standby	1	0	Х	Х	Х	SW disabled
Standby	1	1	Х	0	0	SW enabled Operates in DCM at light loads
Standby	1	1	Х	0	1	SW enabled Forced PWM mode

Table 28. SW3 buck mode control

© NXP B.V. 2021. All rights reserved.

PMIC state	SW3_EN	SW3_STBY	SW3_OMODE	SW3_LPWR	SW3_FPWM	SW3 operating mode
Standby	1	1	Х	1	0	SW enabled perates in Low-power mode
Standby	1	1	Х	1	1	SW enabled Forced PWM mode
Sleep	1	Х	0	Х	Х	SW disabled
Sleep	1	X	1	0	0	SW enabled Operates in DCM at light loads
Sleep	1	Х	1	0	1	SW enabled Forced PWM mode
Sleep	1	X	1	1	0	SW enabled Operates in Low-power mode
Sleep	1	Х	1	1	1	SW enabled Forced PWM mode

 Table 28. SW3 buck mode control...continued

6.3.2 Current limit protection

SW3 features high and low-side FET current limit. When current through the FETs goes above their respective thresholds, the FET is turned off to prevent further increase in current.

The protection is enabled in a cycle-by-cycle mode. Hitting either current limit sets the corresponding interrupt sense bits. If the faults persist for longer than the 8.0 ms debounce time, the interrupt status bit is set.

6.3.3 Output voltage setting in SW3

Output voltage of SW3 is programmable via OTP. During start up (REGS_DISABLE mode to RUN mode), contents of the OTP_SW3_VOLT[5:0] are mapped into the SW3_VOLT[5:0], SW3_STBY_VOLT[5:0] and SW3_SLP_VOLT[5:0] register which set the regulator output voltage during Run, Standby and Sleep modes respectively.

Values of SW3_VOLT[5:0], SW3_STBY[VOLT[5:0] and SW3_SLP_VOLT[5:0] are readonly and cannot be written to.

Set point	SW3_VOLT[3:0] SW3_STBY_VOLT[3:0] SW3_SLP_VOLT[3:0]	Output voltage (V)	
0	0000	1.80	
1	0001	1.90	
2	0010	2.00	
3	0011	2.10	
4	0100	2.20	
5	0101	2.30	

Table 29. SW3 output voltage setting

Set point	SW3_VOLT[3:0] SW3_STBY_VOLT[3:0] SW3_SLP_VOLT[3:0]	Output voltage (V)
6	0110	2.40
7	0111	2.50
8	1000	2.60
9	1001	2.70
10	1010	2.80
11	1011	2.90
12	1100	3.00
13	1101	3.10
14	1110	3.20
15	1111	3.30

Table 29. SW3 output voltage setting...continued

6.3.4 SW3 external components

<u>Table 30</u> shows the combination of inductor and capacitor values that work with the SW3 regulator.

 Table 30. Acceptable inductance and capacitance values

Inductance / capacitance	2 x 10 µF		
1.0 µH			

Table 31 and Table 32 show example inductor and capacitor part numbers respectively.

 Table 31. Example inductor part numbers

Part number	Size (mm)	1.0 µH
DFE201610E	2.0 x 1.6	57 mΩ, 3.6 A
DFE201610P	2.0 x 1.6	70 mΩ, 3.1 A
DFE201210U	2.0 x 1.2	95 mΩ, 3.1 A
DFE160810S	1.6 x 0.8	120 mΩ, 2.0 A
DFE201208S	2.0 x 1.2	86 mΩ, 2.4 A
DFE160808S	1.6 x 0.8	144 mΩ, 1.9 A

 Table 32. Example capacitor part numbers

Murata part number	Description
GRM188R60J106ME47D	6.3 V, 10 μF, 0402, X5R
GRM188D70J106MA73	6.3 V, 10 μF, 0402, X7R
GRM188R61A106KE69	10 µF 10 V 10 % X5R 0603 .95 mm
GRM219R61A106KE44	10 µF 10 V 10 % X5R 0805 .95 mm

7 Low dropout linear regulators, VREFDDR and VSNVS

7.1 General description

This section describes the LDO regulators provided by the PF1510. All regulators use the main bandgap as reference.

When a regulator is disabled, the output is discharged by an internal pull-down.

VLDO1 and VLDO3 can be used as load switches by setting the corresponding load switch enable bit OTP_VLDOx_LS.

All general purpose LDOs have short-circuit protection capability. The Short-circuit Protection (SCP) system includes debounced fault condition detection, regulator shutdown, and processor interrupt generation, to contain failures and minimize the chance of product damage. If a short-circuit condition is detected and REGSCPEN bit is set, the LDO is disabled by resetting its VLDOxEN bit, while at the same time, an interrupt VLDOxFAULTI is generated to flag the fault to the system processor. The VLDOxFAULTI interrupt is maskable through the VLDOxFAULTM mask bit.

The SCP feature is enabled by setting the REGSCPEN bit. If this bit is not set, the regulators are not automatically disabled upon a short-circuit detection. However, the current limiter continues to limit the output current of the regulator. By default, the REGSCPEN is not set; therefore, at start up none of the regulators are disabled if an overloaded condition occurs. A fault interrupt, VLDOxFAULTI is generated in an overload condition regardless of the state of the REGSCPEN bit. Each LDO features a Low-power mode where the quiescent current consumed is significantly lower than in regulator operation. In the Low-power mode, load current of each regulator is limited to 10 mA.

7.2 LDO1 and LDO3 detailed description

LDO1 and LDO3 are identical 300 mA low dropout (LDO) regulators that provide output voltage with high accuracy and are programmable through I²C interface bits. Being identical, reference is made to these LDOs as LDOy.

To support this wide input range, LDOy circuit incorporates a PMOS pass FET as well as an NMOS pass FET. The LDO uses the main bandgap as its reference.

The regulator incorporates a soft-start circuit that ramps the internal reference in order to provide smooth output waveform with minimal overshooting during power up. When the regulator is disabled, the output is discharged by an internal pull-down resistor. Additionally, the LDO can be used as a load switch by setting the corresponding Load Switch enable bit OTP_LDOy_LS.


Moreover, LDOy includes current limit protection with the option to turn off the LDO when an overcurrent is detected.

7.2.1 Features summary

- Input range LDO from 1.0 V to 4.5 V
- Programmable output voltage between 0.75 V to 1.5 V (uses NMOS) or 1.8 V and 3.3 V (uses PMOS) with 2 % accuracy
- Soft-start ramp control during power up and discharge mechanism during power down
- Low quiescent current (~ 2.5 μA) at Low-power mode
- Current limit protection

• Configurable into load switch via OTP bit

7.2.2 LDOy block diagram



7.2.3 LDOy external components

Use a 4.7 μ F X5R/X7R capacitor from output to ground with a voltage rating at least 2 times the nominal output voltage.

7.2.4 LDOy output voltage setting

LDOy output voltage is programmed by setting the LDOy[4:0] bits as shown in Table 33.

Set point	LDOy[4:0]	LDOy output (V)	
0	00000	0.7500	
1	00001	0.8000	
2	00010	0.8500	
3	00011	0.9000	
4	00100	0.9500	
5	00101	1.0000	
6	00110	1.0500	
7	00111	1.1000	
8	01000	1.1500	
9	01001	1.2000	
10	01010	1.2500	
11	01011	1.3000	
12	01100	1.3500	
13	01101	1.4000	
14 01110		1.4500	

Table 33. LDOy output voltage setting

Set point	LDOy[4:0]	LDOy output (V)	
15	01111 1.5000		
16	10000	1.8000	
17	10001	1.9000	
18	10010	2.0000	
19	10011	2.1000	
20	10100	2.2000	
21	10101	2.3000	
22	10110	2.4000	
23	10111	2.5000	
24	11000	2.6000	
25	11001	2.7000	
26	11010	2.8000	
27	11011	2.9000	
28	11100	3.0000	
29	11101	3.1000	
30	11110 3.2000		
31	11111 3.3000		

 Table 33. LDOy output voltage setting...continued

7.2.5 LDOy low power mode operation

LDOy can operate in a Low-power mode with reduced quiescent current. The Low-power mode can be activated in Standby and Sleep modes by setting the LDOy_LPWR bit as shown in <u>Table 34</u>. Maximum load current is limited to 10 mA when operating in the Low-power mode.

Table 34. LDOy control bits

PMIC state	LDOy_EN	LDOy_STBY	LDOy_OMODE	LDOy_LPWR	LDOy operating mode
Run/Standby/Sleep	0	Х	Х	Х	LDO disabled
Run	1	Х	Х	Х	LDO enabled
Standby	1	0	Х	Х	LDO disabled
Standby	1	1	Х	0	LDO enabled
Standby	1	1	Х	1	LDO enabled in Low-power mode
Sleep	1	Х	0	Х	LDO disabled
Sleep	1	Х	1	0	LDO enabled
Sleep	1	Х	1	1	LDO enabled in Low-power mode

7.2.6 LDOy current limit protection

LDOy has built in current limit protection. When the load current exceeds the current limit threshold, the regulator goes from a voltage regulation mode to a current regulation mode that limits the available output current.

By setting the REGSCPEN bit, LDOy can be automatically disabled in the event of an over current situation. In the event of an over current, the LDO will be disabled by resetting its LDOy_EN bit, while at the same time an interrupt LDOy_FAULTI is generated to flag the fault to the system processor. The LDOy_FAULTI interrupt is maskable through the LDOy_FAULTM mask bit.

If REGSCPEN is not set, the regulator will not be automatically disabled, but will instead enter the current limit mode. By default, the REGSCPEN is not set; therefore, at startup none of the regulators will be disabled if an overloaded condition occurs. A fault interrupt, LDOy_FAULTI, is generated in an overload condition regardless of the state of the REGSCPEN bit.

Current limit is not active when LDOy is operated in the load switch mode.

7.2.7 LDOy load switch mode

The LDOy path can be turned into a switch by setting the OTP_LDOy_LS bit. Setting this bit fully turns on the LDO pass FET. This could be useful if power domain partitioning or additional isolation is needed on the system application. Soft-start is engaged during start up of the load switch to reduce inrush currents.

7.3 LDO2 detailed description

LDO2 is a 400 mA low dropout (LDO) regulator that provides output voltage with high accuracy and programmable through I^2C / interface bits. To support this wide input range the LDO circuit incorporates a PMOS pass FET. The LDO uses the main bandgap as its reference.


The regulator incorporates a soft-start circuit that ramps the internal reference in order to provide smooth output waveform with minimal overshooting during power up. When the regulator is disabled, the output is discharged by an internal pull-down resistor. The pull-down is also activated when RESETBMCU is low.

Moreover, LDO2 includes current limit protection with option to turn off the LDO when an overcurrent is detected.

7.3.1 LDO2 features summary

- Input range LDO from 2.8 V to 4.5 V
- Programmable output voltage between 1.8 V and 3.3 V with 2 % accuracy
- Soft-start ramp control during power up and discharge mechanism during power down
- Low quiescent current (~ 1.5 μA) at Low-power mode
- Current limit protection

7.3.2 LDO2 block diagram



7.3.3 LDO2 external components

Use a 10 μF X5R/X7R capacitor from output to ground with a voltage rating at least 2 times the nominal output voltage.

7.3.4 LDO2 output voltage setting

LDO2 output voltage is programmed by setting the VLDO2[3:0] bits as shown in Table 35.

 Table 35. LDO2 output voltage setting

Set point	VLDO2[3:0]	VLDO2 output (V)
0	0000	1.80
1	0001	1.90
2	0010	2.00
3	0011	2.10
4	0100	2.20
5	0101	2.30
6	0110	2.40
7	0111	2.50
8	1000	2.60
9	1001	2.70
10	1010	2.80
11	1011	2.90
12	1100	3.00
13	1101	3.10
14	1110	3.20
All informatio	n provided in this document is subject to legal disclaimers.	© NXP B.V. 2021. All rights reserved

Table 36 | DO2 control bits

Power management integrated circuit (PMIC) for low power application processors

Table 35. LDO2 output voltage setting...continued

Set point	VLDO2[3:0]	VLDO2 output (V)
15	1111	3.30

7.3.5 LDO2 Low-power mode operation

LDO2 can operate in a Low-power mode with reduced quiescent current. The low power mode can be activated in Standby and Sleep modes by setting the LDO2LPWR bit as shown in <u>Table 36</u>. Maximum load current is limited to 10 mA when operating in the Low-power mode.

PMIC state	LDO2EN	LDO2STBY	LDO2OMODE	LDO2LPWR	LDO2 operating mode
Run	0	Х	Х	Х	LDO disabled
Run	1	Х	Х	Х	LDO enabled
Standby	1	0	Х	Х	LDO disabled
Standby	1	1	Х	0	LDO enabled
Standby	1	1	Х	1	LDO enabled in Low-power mode
Sleep	1	Х	0	Х	LDO disabled
Sleep	1	Х	1	0	LDO enabled
Sleep	1	Х	1	1	LDO enabled in Low-power mode

7.3.6 LDO2 current limit protection

LDO2 has built in current limit protection. When the load current exceeds the current limit threshold, the regulator goes from a voltage regulation mode to a current regulation mode limiting the available output current.

By setting the REGSCPEN bit, LDO2 can be automatically disabled in the event of an over current situation. In the event of an over current, the LDO is disabled by resetting its VLDO2EN bit, while at the same time an interrupt VLDO2FAULTI is generated to flag the fault to the system processor. The VLDO2FAULTI interrupt is maskable through the VLDO2FAULTM mask bit.


If REGSCPEN is not set, the regulator will not be automatically disabled, but instead enter the current limit mode. By default, the REGSCPEN is not set; therefore, at startup none of the regulators will be disabled if an overloaded condition occurs. A fault interrupt, VLDO2FAULTI is generated in an overload condition regardless of the state of the REGSCPEN bit.

7.4 VREFDDR reference

VREFDDR is an internal NMOS half supply voltage follower capable of supplying up to 10 mA. The output voltage is at one half the input voltage. It is typically used as the reference voltage for DDR memories.

A filtered resistor divider is utilized to create a low frequency pole. This divider then utilizes a voltage follower to drive the load.


PF1510 Product data sheet



7.5 VSNVS LDO/Switch

VSNVS powers the low-power SNVS/RTC domain on the processor. It derives its power from either VSYS or a coin cell. When powered by both, VSYS powers VSNVS if VSYS > VTH threshold and LICELL powers VSNVS when VSYS < VTL. When powered by VSYS, VSNVS is an LDO capable of supplying 2.0 mA at 3.0 V. When powered by coin cell, VSNVS output tracks the coin cell voltage by means of a switch. In this case, the VSNVS voltage is simply the coin cell voltage minus the voltage drop across the switch.

Upon subsequent removal of VSYS, with the coin cell attached, VSNVS will change configuration from an LDO to a switch.




8 Front-end LDO description

The VIN operates from 4.0 V to 6.5 V with up to 22 V overvoltage protection.

The VIN current limit works by monitoring the current being drawn from the VIN and comparing it to the programmed current limit. The current limit should be set based on the current-handling capability of the input adaptor. Generally, this limit is chosen to optimally fulfill the system-power requirements. See <u>Table 40</u>.

The PMIC is powered from the VSYS node in the PF1510.

The VSYS voltage can be regulated to either 3.5 V, 3.7 V or 4.3 V. See <u>Table 38</u>.



8.1 Operating modes and behavioral description

Table 37. Front-end regulator register

	FRONT-END REGULATOR REGISTER								
ADDR:		0x8F							
	D7	D6	D5	D4	D3	D2	D1	D0	
BITS:	VSYS	SMIN	Reserved						
POR:	0	0	1	0	1	0	1	1	

PF1510 Product data sheet

Figure 12. Startup sequence

Table 37. Front-end regulator register...continued

FRONT-END REGULATOR REGISTER								
ACCESS:								

The VSYS_{MIN} value is programmable via OTP as per the table below.

Table 38. VSYS_{MIN} setting

VSYSMIN[1:0] setting	VSYS _{MIN} setting (V)
00	3.5
01	3.7
10	4.3
11	Reserved

The VSYS_{MIN} setting is the "normal" regulation point for VSYS. This parameter sets the point where the VSYS loop starts taking control and regulates the output. 4.3 V is the recommended setting to ensure that there is enough headroom before reaching UVDET (PMIC undervoltage detection, 2.9 V typ.).

Typically, the VSYS output range can go as low as 300 mV below the VSYS_{MIN} setting. Therefore, the recommended setting for the VSYS output should be between 4.0 V to 4.3 V.

Table 39. VIN current limit register

	VIN CURRENT LIMIT REGISTER									
ADDR:		0x94								
	D7	D6	D5	D4	D3	D2	D1	D0		
BITS:	VIN_ILIM						RESERVED			
POR:	0	1	1	0	1	0	0	0		
ACCESS:	R/W	R/W	R/W	R/W	R/W		_			

The table below shows valid VIN limit settings.

Table 40. VIN limit settings

VIN_ILIM[4:0] setting	VIN current limit (mA)
00000	10
00001	15
00010	20
00011	25
00100	30
00101	35
00110	40
00111	45
01000	50
01001	100
01010	150

PF1510 Product data sheet

42 / 108

VIN_ILIM[4:0] setting	VIN current limit (mA)
01011	200
01100	300
01101	400
01110	500
01111	600
10000	700
10001	800
10010	900
10011	1000
10100	1500
10101 to 11101	Reserved
11110	Reserved
11111	Reserved

9 Control and interface signals

The PF1510 PMIC is fully programmable via the l^2C interface. Additional communication is provided by direct logic interfacing including interrupt and reset pins as well as pins for power buttons.

9.1 PWRON

PWRON is an input signal to the IC that acts as an enable signal for the voltage regulators in the PF1510.

The PWRON pin can be configured as either a level sensitive input (OTP_PWRON_CFG = 0), or as an edge sensitive input (OTP PWRON CFG = 1).

As a level sensitive input, an active high signal turns on the part and an active low signal turns off the part, or puts it into Sleep mode.

As an edge sensitive input, such as when connected to a mechanical switch, a falling edge will turn on the part and if the switch is held low for greater than or equal to 4.0 seconds, the part turns off or enters Sleep mode.

Table 41. PWRON pin OTP configuration options	Table 41.	PWRON	pin OTP	configuration	options
---	-----------	-------	---------	---------------	---------

OTP_PWRON_CFG	Mode
0	PWRON pin HIGH = ON PWRON pin LOW = OFF or Sleep mode
1	PWRON pin pulled LOW momentarily = ON PWRON pin LOW for 4.0 seconds = OFF or Sleep mode

PF1510 Product data sheet

 Table 42.
 PWRON pin logic level

Pin name	Parameter	Load condition	Min	Max	Unit
PWRON	V _{IL}	—	0.0	0.4	V
	V _{IH}		1.4	3.6	V

When OTP_PWRON_CFG = 1, PWRON pin pulled low momentarily takes the system from REGS_DISABLE/SLEEP to RUN mode. There is no effect if PWRON is pulled low momentarily while in RUN or STANDBY modes. Only an interrupt is generated.

PWRON pin low for 4.0 seconds with PWRONRSTEN bit = 1: Enters REGS_DISABLE or Sleep mode.

See Section 10 "PF1510 state machine" for detailed description.

In this configuration, the PWRON input can be a mechanical switch debounced through a programmable de-bouncer, PWRONDBNC[1:0], to avoid a response to a very short key press. The interrupt is generated for both the falling and the rising edge of the PWRON pin. By default, a 31.25 ms interrupt debounce is applied to both falling and rising edges. The falling edge debounce timing can be extended with PWRONDBNC[1:0]. The interrupt is cleared by software, or when cycling through the REGS_DISABLE mode.

Table 43. PWRONDBNC settings

Bits	State	Turn on debounce (ms)	Falling edge INT debounce (ms)	Rising edge INT debounce (ms)
PWRONDBNC[1:0]	00	31.25	31.25	31.25
	01	31.25	31.25	31.25
	10	125	125	31.25
	11	750	750	31.25

9.2 STANDBY

STANDBY is an input signal to the IC. When it is asserted the part enters standby mode and when deasserted, the part exits standby mode. STANDBY can be configured as active high or active low using the STANDBYINV bit.

 Table 44. Standby pin polarity control

STANDBY (pin)	STANDBYINV (I ² C bit)	STANDBY control
0	0	Not in Standby mode
0	1	In Standby mode
1	0	In Standby mode
1	1	Not in Standby mode

Table 45. STANDBY pin logic level

Pin name	Parameter	Load condition	Min	Max	Unit
STANDBY	V _{IL}	—	0	0.4	V
	V _{IH}		1.4	3.6	V

Since STANDBY pin activity is driven asynchronously to the system, a finite time is required for the internal logic to qualify and respond to the pin level changes. A programmable delay is provided to hold off the system response to a Standby event. This allows the processor and peripherals some time after a standby instruction has been received to terminate processes to facilitate seamless entering into Standby mode. When enabled (STANDBYDLY = 01, 10, or 11), STANDBYDLY delays the Standby initiated response for the entire IC, until the STBYDLY counter expires. An allowance should be made for three additional 32 kHz cycles required to synchronize the Standby event.

9.3 RESETBMCU

RESETBMCU is an open-drain, active low output configurable via OTP for two modes of operation.

In its default mode, it is deasserted at the end of the start-up sequence. In this mode, the signal can be used to bring the processor out of reset (POR), or as an indicator that all supplies have been enabled; it is only asserted during a turn off event.

When configured for its fault mode, RESETBMCU is deasserted after the startup sequence is completed only if no faults occurred during start up. At any time, if a fault occurs and persists for 1.8 ms typically, RESETBMCU is asserted low.

The PF1510 is turned off if the fault persists for more than 100 ms typically. The PWRON signal restarts the part, though if the fault persists, the sequence described above is repeated. To enter the fault mode, set bit OTP_PWRGD_EN to 1.

The time from the last regulator in the start-up sequence to when RESETBMCU is deasserted is programmable between 2.0 ms and 1024 ms via OTP_POR_DLY[2:0] bits.

	moo pin logio				
Pin name	Parameter	Load condition	Min	Мах	Unit
RESETBMCU	V _{OL}	–2.0 mA	0	0.2 * VDDIO	V
	V _{OH}	Open Drain	0.8 * VDDIO	3.6 V	V

Table 46. RESETBMCU pin logic level

9.4 INTB

INTB is an open-drain, active low output. It is asserted when any interrupt occurs, provided that the interrupt is unmasked. INTB is deasserted after the fault interrupt is cleared by software, which requires writing a "1" to the interrupt bit.

Each interrupt can be masked by setting the corresponding mask bit to a 1. As a result, when a masked interrupt bit goes high, the INTB pin does not go low. A masked interrupt can still be read from the interrupt status register. This gives the processor the option of polling for status from the IC.

The IC powers up with all interrupts masked, so the processor must initially poll the device to determine if any interrupts are active. Alternatively, the processor can unmask the interrupt bits of interest. If a masked interrupt bit was already high, the INTB pin goes low after unmasking. The sense registers contain status and input sense bits so the system processor can poll the current state of interrupt sources. They are read only, and not latched or clearable.

Pin name	Parameter	Load condition	Min	Max	Unit
INTB	V _{OL}	–2.0 mA	0	0.2 * VDDIO	V
	All information provided in this do	cument is subject to legal disclaimers.	·	© NXP B.V. 2021. All ri	ights reserved.

Product data sheet

PF1510

Table 47. INTB pin logic level...continued

Pin name	Parameter	Load condition	Min	Max	Unit
	V _{OH}	Open Drain	0.8 * VDDIO	3.6 V	V

9.5 WDI

WDI is an input signal to the IC. It is typically connected to the watchdog output of the processor. When the WDI pin is pulled low, the PMIC enters the "REGS_DISABLE" mode where all the regulators are turned off. The WDI acts as a hard reset input from the processor.

During PMIC startup (REGS_DISABLE to RUN mode), the WDI pin is masked till RESETBMCU is deasserted.

Table 48	WDI	pin loaic	level
		P	

Pin name	Parameter	Load condition	Min	Max	Unit
WDI	V _{IL}	—	0	0.2 * VDDIO	V
	V _{IH}		0.8 * VDDIO	3.6	V

9.6 ONKEY

ONKEY is an input pin to the IC and is typically connected to a push-button switch. The ONKEY pin is pulled high when the switch is depressed, and is pulled low when the switch is pressed.

Pressing the switch generates interrupts which the processor uses to initiate PMIC state transitions. Pressing the ONKEY for longer than the delay programmed by OTP_TGRESET[1:0] (ranges from 4.0 s to 16 s), forces the PMIC into the REGS_DISABLE state.

Table 49. ONKEY pin logic level

Pin name	Parameter	Load condition	Min	Max	Unit
ONKEY	V _{IL}	—	0	0.4	V
	V _{IH}		1.4	4.8	V

Table 50. ONKEYDBNC settings

Bits	State	Turn On Debounce (ms)	Falling Edge INT Debounce (ms)	Rising Edge INT Debounce (ms)
ONKEYDBNC[1:0]	00	31.25	31.25	31.25
	01	31.25	31.25	31.25
	10	125	125	31.25
	11	750	750	31.25

The ONKEY input can be a mechanical switch debounced through a programmable debouncer, ONKEYDBNC[1:0], to avoid a response to a very short (unintentional) key press. The interrupt is generated during the rising edge of the ONKEY pin.

The falling edge debounce timing can be extended with ONKEYDBNC[1:0] as defined <u>Table 50</u>. The interrupt is cleared by software, or when cycling through the REGS_DISABLE mode.

See <u>Section 12 "Register map"</u> for detailed description of the ONKEY interrupt registers.

9.7 Control interface I²C block description

The PF1510 contains an I^2C interface port which allows access by a processor, or any I^2C master, to the register set. Via these registers, the resources of the IC can be controlled. The registers also provide status information about how the IC is operating.

The SCL and SDA lines should be routed away from noisy signals and planes to minimize noise pick up. To prevent reflections in the SCL and SDA traces from creating false pulses, the rise and fall times of the SCL and SDA signals must be greater than 20 ns. This can be accomplished by reducing the drive strength of the I²C master via software.

9.7.1 I²C device ID

 I^2C interface protocol requires a device ID for addressing the target IC on a multi-device bus. The PF1510 I^2C device address is 0x08.


9.7.2 I²C operation

The I²C mode of the interface is implemented generally following the fast mode definition which supports up to 400 kbits/s operation (exceptions to the standard are noted to be 7-bit only addressing and no support for general call addressing). Timing diagrams, electrical specifications, and further details can be found in the I²C specification, which is available for download at:

http://www.nxp.com/acrobat_download/literature/9398/39340011.pdf

I²C read operations are also performed in byte increments separated by an ACK. Read operations also begin with the MSB and each byte is sent out unless a STOP command or NACK is received prior to completion.

The following examples show how to write and read data to and from the IC. The host initiates and terminates all communication. The host sends a master command packet after driving the start condition. The device responds to the host if the master command packet contains the corresponding slave address. In the following examples, the device is shown always responding with an ACK to transmissions from the host. If at any time a NACK is received, the host should terminate the current transaction and retry the transaction.




10 PF1510 state machine

The PMIC part of the PF1510 can operate in a number of states as shown in Figure 14.

The states can be split into two categories:

- 1. "System On" that includes the RUN, STANDBY and SLEEP modes
- 2. "System Off" that includes the REGS_DISABLE and CORE_OFF modes



In the "System On" modes, some or all of the PMIC regulators are powered and in general the system processor is powered.

In the "System Off" modes, all (or all regulators except VSNVS) are powered off. In general the system processor is powered off during these states. In the REGS_DISABLE and CORE_OFF modes, the VSNVS supply remains enabled keeping the system RTC running.

The only way to transition from "System Off" to "System On" and vice versa is through the REGS_DISABLE mode. From the REGS_DISABLE mode, the only exit into a "System On" state is into the "Run" mode. Transition from the REGS_DISABLE mode to the Run mode requires a Turn On event. See <u>Section 10.3 "Turn on events"</u>.

Transition from any of the "System On" modes to the REGS_DISABLE state is allowed. This transition is referred to as a Turn Off event. See <u>Section 10.4 "Turn off events"</u>.

10.1 System ON states

10.1.1 Run state

In this state, the PMIC regulators are enabled and the system is powered up. RESETBMCU is de-asserted in this state.

This mode can be entered in several ways:

- 1. From REGS_DISABLE through a Turn On Event: During this transition, the PMIC regulators are powered up as per their programmed start-up sequence. After all the regulators are powered, the RESETBMCU pin is de-asserted.
- 2. From STANDBY by using the STANDBY pin
- 3. From SLEEP mode by using the PWRON pin: Typically, some of the regulators are turned off in the SLEEP mode compared to the RUN mode. In the SLEEP mode, some of the buck regulator output voltages are set lower than those in the RUN mode. While transitioning from the SLEEP to the RUN mode, regulators that were turned off in the SLEEP mode are turned back on in the RUN mode following the same sequence as the programmed OTP sequence. Output voltage transitions during transition from the SLEEP to the RUN mode also occurs at the same OTP sequence time slot. RESETBMCU is de-asserted through this state transition.

10.1.2 STANDBY state

This state is entered by controlling the logic level of the STANDBY pin. It can be entered only from the RUN mode.

The STANDBY pin polarity is programmable through the STANDBYINV I^2C bit. By default, STANDBYINV = 0 and a logic high on the STANDBY pin moves the state machine from the RUN state to the STANDBY state. When STANDBYINV = 1, a logic low moves the state machine from the RUN state to the STANDBY state.

Regulator output voltage may be changed, or regulator outputs could be disabled while entering the STANDBY state and vice versa.

For details on the power-down sequence, see <u>Section 10.7 "Regulator power-down</u> <u>sequencer"</u>. While exiting STANDBY state into the RUN mode, regulator output voltage changes and regulator enables follow the power-up sequence.

It is possible to exit STANDBY state and enter the SLEEP state. SLEEP state is generally a lower power system state compared to the STANDBY state. Exiting STANDBY into the SLEEP state follows the power-down sequence.

RESETBMCU is de-asserted in the STANDBY state.

10.1.3 SLEEP state

This state is entered from either the RUN state or the STANDBY state by controlling the PWRON pin. The exact condition required for this transition depends on the OTP configuration of the PWRON pin. For details see <u>Section 9.1 "PWRON"</u>.

The power-down sequence is followed while entering this state and the power-up sequence is followed while exiting this state into the RUN state.

RESETBMCU is de-asserted in the SLEEP state.

10.2 System OFF states

RESETBMCU is asserted (low) in all the System Off states.

10.2.1 REGS_DISABLE

This state can be considered the 'home state' for the state machine. In this state, the state machine waits for appropriate commands to proceed to other states.

REGS_DISABLE can be entered from one of the "System On" state through a turn off event.

REGS_DISABLE can be entered from the CORE_OFF by pressing the ONKEY button for more than 1000 ms or by applying the Vin.

In the REGS_DISABLE state, the PMIC core circuitry is active. VSNVS is a best-ofsupply output of VSYS and LICELL.

10.2.2 CORE_OFF

This state is entered in two ways:

- From the REGS_DISABLE mode by pressing and holding the ONKEY button low > T_{greset}
- 2. From the REGS_DISABLE mode if the GOTO_CORE_OFF bit is set

This state cannot be entered if Vin is applied.

In this state, the internal core of the PMIC is turned off to reduce quiescent current. VSNVS is the only regulator that is supplied to external loads.

10.3 Turn on events

A turn on event takes the PMIC from the REGS_DISABLE state to the RUN state (transition H in Figure 14).

The turn on events are:

- 1. PWRON logic high with PWRON_CFG = 0
- 2. PWRON H -> L with PWRON_CFG = 1

VSYS > UVDET_{rising} and $T_J < T_{SHDN fall}$ are preconditions for a turn on event to occur.

The turn on is said to be complete after the RESETBMCU pin is deasserted. The WDI pin is masked till the RESETBMCU pin is deasserted.

10.4 Turn off events

A turn off event takes the PMIC state machine from one of the "System On" states (RUN, STANDBY or SLEEP) to the REGS_DISABLE state. The power-down sequence is followed during all of the turn off events.

The turn off events are:

- 1. Thermal Shutdown ($T_J > T_{SHDN_rise}$)
- 2. PWRON logic low with OTP_PWRON_CFG = 0
- 3. PWRON low > 4.0 s with OTP_PWRON_CFG = 1 && PWRONRSTEN = 1

PF1510

- 4. WDI = 0. This occurs when the processor watchdog expires and pulls the WDI pin low to create a hard reset.
- 5. ONKEY pressed low > T_{greset} && ONKEYRST_EN = 1. This facilitates creating a hard reset when pressing the ONKEY button without processor intervention.

10.5 State diagram and transition conditions

Table 51. State transition tabl

Transition	Description	PWRON_CFG = 0 (Level sensitive)	PWRON_CFG = 1 (Edge sensitive)
A	Standby to Run	(STANDBY pin = 0 && STANDBYINV bit = 0) OR (STANDBY pin = 1 && STANDBYINV bit = 1)	(STANDBY pin = 0 && STANDBYINV bit = 0) OR (STANDBY pin = 1 && STANDBYINV bit = 1)
В	Run to Standby	(STANDBY pin = 1 && STANDBYINV bit = 0) OR (STANDBY pin = 0 && STANDBYINV bit = 1)	(STANDBY pin = 1 && STANDBYINV bit = 0) OR (STANDBY pin = 0 && STANDBYINV bit = 1)
С	Standby to Sleep	(PWRON = 0) && (Any SWxOMODE = 1 Any LDOxOMODE = 1)	(PWRON High to Low and PWRON = 0 > 4s) && (PWRONRSTEN = 1) && (Any SWxOMODE = 1 Any LDOxOMODE = 1)
E	Sleep to Run	PWRON = 1	PWRON High to Low to High ^[1]
F	Run to Sleep	(PWRON = 0) && (Any SWxOMODE = 1 Any LDOxOMODE = 1)	(PWRON High to Low and PWRON = 0 > 4s) && (PWRONRSTEN = 1) && (Any SWxOMODE = 1 Any LDOxOMODE = 1)
G	Run/Standby/Sleep to REGS_DISABLE	(Thermal shutdown) OR (PWRON = 0 && All SWxOMODE = 0 && All LDOxOMODE = 0) OR (WDI = 0) ^[2] OR (ONKEY High to Low and ONKEY = 0 > Tgreset && ONKEY_RST_EN = 1) OR (VSYS < UVDET_Fall) ^[3]	$ \begin{array}{l} (Thermal shutdown) \\ OR \\ (PWRON = 0 > 4s & PWRONRSTEN = 1 & All \\ SWxOMODE = 0 & All LD0xOMODE = 0) \\ OR \\ (PWRON High to Low and PWRON = 0 > 4s when in \\ Sleep state) \\ OR \\ (WDI = 0) \\ \left[\begin{array}{c} 2 \\ 1 \\ 2 \\ 2 \\ 1 \\ 2 \\ 1 \\ 2 \\ 1 \\ 2 \\ 1 \\ 2 \\ 2$
Η	$\begin{array}{l} \text{REGS_DISABLE to Run} \\ \text{(Only if VSYS > UVDET} \\ \text{and } T_J < T_{SHDN_fall} \end{array}$	PWRON = 1	(PWRON High to Low) OR (If entered REGS_DISABLE via long press on PWRON && RESTARTEN = 1 && PWRON stays Low > 1.0 s) OR (Vin applied) [4] [5]
I	REGS_DISABLE to CORE_OFF (Only if VIN_INVALID = 1)	(GOTO_CORE_OFF = 1 && ONKEY = 1) OR (ONKEY High to Low and ONKEY = 0 > Tgreset && ONKEY_RST_EN = 1) ^{[6][7]}	(GOTO_CORE_OFF = 1 && ONKEY = 1) OR (ONKEY High to Low and ONKEY = 0 > Tgreset && ONKEY_RST_EN = 1) ^{[6][8]}
К	CORE_OFF to REGS_ DISABLE	(ONKEY High to Low and ONKEY = 0 > 1000 ms) OR (Vin applied)	(ONKEY High to Low and ONKEY = 0 > 1000 ms) OR (Vin applied)

[1] This low period is < 4.0 s. If it is longer than 4.0 s, it transitions to G

[2] PWRON pin is pulled low by processor after WDI = 0.

[3] [4] Follows regulator power-down sequence for this transition

WDI pin is masked till RESETBMCU is deasserted.

Debounce on PWRON programmable via PWRONDBNC[1:0] [5]

[6]

PWRON pin is pulled low by processor after ONKEY = 0 > Tgreset. GOTO_CORE_OFF is set by user when system is ON. For other products, a secondary processor is used to set this bit while in REGS_DISABLE GOTO_CORE_OFF must be set by user when system is ON [7]

[8]

10.6 Regulator power-up sequencer

Start-up sequence of all the switching and linear regulators in the PF1510 is programmable. VSNVS's sequence is not programmable but is always the first regulator to power up when the PF1510 is powered up via a cold start (from no input to valid input). When SYS is first applied to the PF1510, VSNVS comes up first.

The switching and linear regulators power up based on their programmed OTP sequence using the respective OTP_XX_SEQ[2:0] when transitioning from REGS_DISABLE to the RUN state.

RESETBMCU is pulled low from VCOREDIG POR till the end of the power-up sequencer.

RESETBMCU is pulled high 2.0 ms to 1024 ms after the last regulator powers up. This delay is OTP programmable through the OTP_POR_DLY[2:0] bits.

When transitioning from STANDBY mode to RUN mode, the power-up sequencer is activated only if any of the regulators turn back on during this transition.

The power-up sequencer ends as soon as the last regulator powers up, rather than waiting for a fixed time.

The power-up sequencer is always activated when transitioning from Sleep to Run modes. The sequencer ends as soon as the last regulator powers up, rather than waiting for a fixed time.

The PWRUP_I interrupt is set to indicate completion of transition from STANDBY to RUN and SLEEP to RUN.

The PWRUP_I interrupt is set while transitioning from STANDBY to RUN even if the sequencers were not used. This is used to indicate that the transition is complete.

10.7 Regulator power-down sequencer

The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0], VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence.

The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0].

When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default power-down is a mirror of the power-up sequence.

In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequencer is bypassed and all the regulators are turned off at once. During transition from Run to Standby, the power-down sequencer is activated if any of the regulators are turned off during this transition.

If regulators are not turned off during this transition, the power-down sequencer is bypassed and the transition happens at once (any associated DVS transitions still take time).

During transition from Run to Sleep, the power-down sequencer is always activated. However, if all XXX PWRDN SEQ[2:0] = 0, the transition happens immediately.

The PWRDN_I interrupt is set during transition from Run to Sleep and Run to Standby even if regulators are not turned off during these transitions.

11 Device start up

11.1 Startup timing diagram

The startup timing of the regulators is programmable through OTP, <u>Figure 15</u> shows the startup timing of the regulators as determined by their OTP A4 sequence.




Figure 15. A4 startup and power down sequence

 Table 52. A4 startup and power down sequence timing

Parameter	Description ^[1]		Min	Тур	Мах	Unit
t _{D1}	Turn-on delay of VSNVS		—	0.6	—	ms
t _{R1}	Rise time of VSNVS		_	0.1		ms
t _{D2}	User determined delay		_	_	_	ms
t _{R2}	Rise time of PWRON		_	[2]	—	ms
t _{D3}	Power up delay between regulators OTP_SEQ_CLK_SPEED = 0 OTP_SEQ_CLK_SPEED = 1 	[3]	_	0.5 2.0	_	ms
t _{R3}	Rise time of regulators	[4]	_	0.2		ms
t _{D4}	Turn-on delay of RESETBMCU		_	2.0		ms
t _{R4}	Rise time of RESETBMCU		_	0.2		ms
t _{D5}	Power down delay between regulators		_	2.0	_	ms

[1] All regulators avoid drop-out mode at startup

- [2] Depends on the external signal driving PWRON
 - A4 configuration
- [3] [4] Rise time is a function of slew rate of regulators and nominal voltage selected.

11.2 Device start up configuration

Table 53. PF1510 start up configuration

	Pre-programmed OTP configuration							
Registers	A1	A2	A3	A4	A5	A6	A7	
Default I ² C Address	0x08	0x08	0x08	0x08	0x08	0x08	0x08	
OTP_VSNVS_VOLT[2:0]	3.0 V	3.0 V	3.0 V	3.0 V	3.0 V	3.0 V	3.0 V	
OTP_SW1_VOLT[5:0]	1.1 V	1.0V	1.3875 V	1.1 V	1.3875 V	1.275 V	1.3875 V	
OTP_SW1_PWRUP_SEQ[2:0]	1	5	3	4	3	3	3	
OTP_SW2_VOLT[5:0]	1.1 V	1.2V	1.35 V	1.2 V	1.5 V	1.35 V	1.2 V	
OTP_SW2_PWRUP_SEQ[2:0]	2	5	3	3	3	3	3	
OTP_SW3_VOLT[5:0]	1.8 V	1.8V	3.3 V	1.8 V	3.3 V	3.3 V	1.8 V	
OTP_SW3_PWRUP_SEQ[2:0]	3	1	3	2	3	3	3	
OTP_LDO1_VOLT[4:0]	1.0 V	1.8 V	1.8 V	3.3 V	1.8 V	1.8 V	3.3 V	
OTP_LDO1_PWRUP_SEQ[2:0]	4	1	3	1	3	3	3	
OTP_LDO2_VOLT[3:0]	2.5 V	3.3 V	3.3 V	3.3 V	3.3 V	3.3 V	3.3 V	
OTP_LDO2_PWRUP_SEQ[2:0]	4	1	2	2	2	2	2	
OTP_LDO3_VOLT[4:0]	1.0 V	1.8 V	3.3 V	1.8 V	3.3 V	3.3 V	3.3 V	
OTP_LDO3_PWRUP_SEQ[2:0]	5	1	3	1	3	3	3	
OTP_VREFDDR_PWRUP_ SEQ[2:0]	5	5	3	3	3	3	3	
OTP_SW1_DVS_SEL	Non-DVS mode	B DVS mode						
OTP_SW2_DVS_SEL	DVS mode	Non-D	VS mode	DVS mode	N	on-DVS mod	de	
OTP_LDO1_LS_EN				LDO mode	1		-	
OTP_LDO3_LS_EN	LS mode			LDO	mode			
OTP_SW1_RDIS_ENB				Enabled				
OTP_SW2_RDIS_ENB				Enabled				
OTP_SW3_RDIS_ENB				Enabled				
OTP_SW1_DVSSPEED			12.5 n	nV step each	4.0 µs		-	
OTP_SW2_DVSSPEED	12.5 mV step each 2.0 μs	2.5 mV 12.5 mV step each 4.0 μs						
OTP_SWx_EN_AND_STBY_EN		SW1	, SW2, SW3	enabled in RI	UN and STA	NDBY		
OTP_LDOx_EN_AND_STBY_EN	L	DO1, LDO2	2, LDO3, VRE	FDDR enabl	ed in RUN a	nd STANDB	Ý	
OTP_PWRON_CFG			l	_evel sensitiv	e			
OTP_SEQ_CLK_SPEED	0.5 ms time slots			2 ms tin	ne slots			

Table 53. PF1510 start up configuration...continued

		Pre-programmed OTP configuration						
Registers	A1	A2	A3	A4	A5	A6	A7	
OTP_TGRESET[1:0]			4 sec	s global rese	t timer			
OTP_POR_DLY[2:0]			2 ms RESE	TBMCU pow	/er-up delay			
OTP_UVDET[1:0]			Rising	3.0 V; falling	g 2.9 V			
OTP_I2C_DEGLITCH_EN		I ² C deglitch filter disabled						
OTP_VSYSMIN[1:0]		VSYSMIN = 4.3 V VSYSMIN VSY = 3.7 V = 4						
OTP_VIN_ILIM[4:0]	VIN ILIM = 500 mA			VIN ILIM =	= 1500 mA		1	
OTP_USBPHYLDO	USBPHY LDO disabled	LDO						
OTP_USBPHY		USBPHY = 3.3 V						
OTP_ACTDISPHY	USBPHY active discharge disabled	USBPHY USBPHY active discharge enabled active discharge						

12 Register map

12.1 Specific PMIC Registers (Offset is 0x00)

The following pages contain description of the various registers in the PF1510.

Name	Bit	R/W	Default	Description
DEVICE_ID	2 to 0	R	100	Loaded from fuses 000 — Future use 001 — Future use 010 — Future use
				 011 — Future use 100 — PF1510 101 — Future use 110 — Future use 111 — Future use
FAMILY	7 to 3	R	01111	Identifies PMIC 01111 — 0b0_1111 for "15" used to denote the "PF1510"

Table 54. Register DEVICE ID - ADDR 0x00

Table 55. Register OTP_FLAVOR - ADDR 0x01

Name	Bit	R/W	Default	Description
UNUSED	7 to 0	R	0x00	Blown by ATE to indicate flavor of OTP used 0x00 — OTP not burned 0x01 — A1 0x02 — A2 0x03 — A3 continues

Table 56. Register SILICON_REV - ADDR 0x02

Name	Bit	R/W	Default	Description
METAL_LAYER_REV	2 to 0	R	000	Unused
FULL_LAYER_REV	5 to 3	R	001	Unused
FAB_FIN	7 to 6	R	00	Unused

Table 57. Register INT_CATEGORY - ADDR 0x06

Name	Bit	R/W	Default	Description
VIN_INT	0	R	0	This bit is set high if the VIN_I interrupt bit is set 0 — No interrupt bit is set, cleared, or did not occur 1 — "OR" function of all interrupt status bit
SW1_INT	1	R	0	This bit is set high if any of the Buck 1 interrupt status bits are set 0 — SW1 interrupts cleared or did not occur 1 — Any of the SW1 interrupt status bits are set
SW2_INT	2	R	0	 This bit is set high if any of the Buck 2 interrupt status bits are set 0 — SW2 interrupts cleared or did not occur 1 — Any of the SW2 interrupt status bits are set
SW3_INT	3	R	0	This bit is set high if any of the Buck 3 interrupt status bits are set 0 — SW3 interrupts cleared or did not occur 1 — any of the SW3 interrupt status bits are set
LDO_INT	4	R	0	 This bit is set high if any of the LDO interrupt status bits are set. This includes LDO1, LDO2 and LDO3. 0 — LDO interrupts cleared or did not occur 1 — Any of the LDO interrupt status bits are set
ONKEY_INT	5	R	0	 This bit is set high if any of the interrupts associated with ONKEY push button are set. 0 — ONKEY related interrupts cleared or did not occur 1 — Any of the ONKEY interrupt status bits are set
TEMP_INT	6	R	0	 This bit is set if any of the interrupts associated with the die temperature monitor are set 0 — PMIC junction temperature related interrupts cleared or did not occur 1 — any of the PMIC junction temperature interrupts status bits are set

Table 57. Register INT_CATEGORY - ADDR 0x06...continued

Name	Bit	R/W	Default	Description
MISC_INT	7	R	0	 This bit is set if interrupts not covered by the above mentioned categories occur 0 — Other interrupts (not covered by categories above) cleared, or did not occur 1 — Status bit of other interrupts (not covered by categories above) is set

Table 58. Register SW_INT_STAT0 - ADDR 0x08

Name	Bit	R/W	Default	Description
SW1_LS_I	0	RW1C ^[1]	0	 SW1 low-side current limit interrupt status. This bit is set if the current limit fault persists for longer than the debounce time. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
SW2_LS_I	1	RW1C	0	 SW2 low-side current limit interrupt status. This bit is set if the current limit fault persists for longer than the debounce time. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
SW3_LS_I	2	RW1C	0	 SW3 low-side current limit interrupt status. This bit is set if the current limit fault persists for longer than the debounce time. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	7 to 3	—		Unused

[1] Read or Write 1 to clear the bit

Table 59. Register SW_INT_MASK0 - ADDR 0x09

Name	Bit	R/W	Default	Description
SW1_LS_M	0	RW	1	 SW1 low-side current limit interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
SW2_LS_M	1	RW	1	 SW2 low-side current limit interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
SW3_LS_M	2	RW	1	 SW3 low-side current limit interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
UNUSED	7 to 3	—	_	Unused

Name	Bit	R/W	Default	Description
SW1_LS_S	0	R	0	 SW1 low-side current limit interrupt sense. Sense is high as long as fault persists (post-debounce). 0 — Fault removed 1 — Fault exists
SW2_LS_S	1	R	0	 SW2 low-side current limit interrupt sense. Sense is high as long as fault persists (post-debounce). 0 — Fault removed 1 — Fault exists
SW3_LS_S	2	R	0	 SW3 low-side current limit interrupt sense. Sense is high as long as fault persists (post-debounce) 0 — Fault removed 1 — Fault exists
UNUSED	7 to 3		_	Unused

Table 60. Register SW_INT_SENSE0 - ADDR 0x0A

Table 61. Register SW_INT_STAT1 - ADDR 0x0B

Name	Bit	R/W	Default	Description
SW1_HS_I	0	RW1C ^[1]	0	SW1 high-side current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
SW2_HS_I	1	RW1C	0	SW2 high-side current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
SW3_HS_I	2	RW1C	0	 SW3 high-side current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	7 to 3			Unused

[1] Read or Write 1 to clear the bit

Table 62. Register SW_INT_MASK1 - ADDR 0x0C

Name	Bit	R/W	Default	Description
SW1_HS_M	0	RW	1	 SW1 high-side current limit interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
SW2_HS_M	1	RW	1	 SW2 high-side current limit interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.

PF1510 Product data sheet © NXP B.V. 2021. All rights reserved.

Table 02. Register 0W_INT_MADRT - ADDR 0X00comminded						
Name	Bit	R/W	Default	Description		
SW3_HS_M	2	RW	1	SW3 high-side current limit interrupt mask		
				0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set.		
				 Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set. 		
UNUSED	7 to 3		—	Unused		

Table 62. Register SW_INT_MASK1 - ADDR 0x0C...continued

Table 63. Register SW_INT_SENSE1 - ADDR 0x0D

Name	Bit	R/W	Default	Description
SW1_HS_S	0	R	0	 SW1 high-side current limit interrupt sense. This bit should not toggle within a switching cycle (at buck switching frequency), but report the sense status within the switching cycle. 0 — Fault removed 1 — Fault exists
SW2_HS_S	1	R	0	 SW2 high-side current limit interrupt sense. This bit should not toggle within a switching cycle (at buck switching frequency), but report the sense status within the switching cycle. 0 — Fault removed 1 — Fault exists
SW3_HS_S	2	R	0	 SW3 high-side current limit interrupt sense. This bit should not toggle within a switching cycle (at buck switching frequency), but report the sense status within the switching cycle. 0 — Fault removed 1 — Fault exists
UNUSED	7 to 3		_	Unused

Table 64. Register SW_INT_STAT2 - ADDR 0x0E

Name	Bit	R/W	Default	Description
SW1_DVS_DONE_I	0	RW1C ^[1]	0	Interrupt to indicate SW1 DVS complete. This interrupt should occur every time regulator output voltage is changed (either via I^2C within a given state, or if there is change in voltage when transitioning states, Run to Standby, for example). 0 — DVS not complete and/or bit cleared 1 — DVS complete
SW2_DVS_DONE_I	1	RW1C	0	Interrupt to indicate SW2 DVS complete. This interrupt should occur every time regulator output voltage is changed (either via I^2C within a given state, or if there is change in voltage when transitioning states, Run to Standby, for example). 0 — DVS not complete and/or bit cleared 1 — DVS complete
UNUSED	7 to 2			Unused

[1] Read or Write 1 to clear the bit

Name	Bit	R/W	Default	Description
SW1_DVS_DONE_M	0	RW	1	 Mask for interrupt that indicates SW1 DVS complete 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
SW2_DVS_DONE_M	1	RW	1	 Mask for interrupt that indicates SW2 DVS complete 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
UNUSED	7 to 2			Unused

Table 65. Register SW_INT_MASK2 - ADDR 0x0F

Table 66. Register SW_INT_SENSE2 - ADDR 0x10

Name	Bit	R/W	Default	Description
SW1_DVS_S	0	R	0	Indicates DVS in progress for SW1 0 — DVS not in progress 1 — DVS in progress
SW2_DVS_S	1	R	0	Indicates DVS in progress for SW2 0 — DVS not in progress 1 — DVS in progress
UNUSED	7 to 2		—	Unused

Table 67. Register LDO_INT_STAT0 - ADDR 0x18

Name	Bit	R/W	Default	Description
LDO1_FAULTI	0	RW1C ^[1]	0	LDO1 current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
LDO2_FAULTI	1	RW1C	0	LDO2 current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
LDO3_FAULTI	2	RW1C	0	LDO3 current limit interrupt 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	7 to 3	_	_	Unused

[1] Read or Write 1 to clear the bit

PF1510 Product data sheet

Name	Bit	R/W	Default	Description
LDO1_FAULTM	0	RW	1	 LDO1 current limit fault interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
LDO2_FAULTM	1	RW	1	 LDO2 current limit fault interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
LDO3_FAULTM	2	RW	1	 LDO3 current limit fault interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
UNUSED	7 to 3			Unused

Table 68. Register LDO_INT_MASK0 - ADDR 0x19

Table 69. Register LDO_INT_SENSE0 - ADDR 0x1A

Name	Bit	R/W	Default	Description
LDO1_FAULTS	0	R	0	LDO1 fault interrupt sense 0 — Fault removed 1 — Fault exists
LDO2_FAULTS	1	R	0	LDO2 fault interrupt sense 0 — Fault removed 1 — Fault exists
LDO3_FAULTS	2	R	0	LDO3 fault interrupt sense 0 — Fault removed 1 — Fault exists
UNUSED	7 to 3	—		Unused

Table 70. Register TEMP_INT_STAT0 - ADDR 0x20

Name	Bit	R/W	Default	Description
THERM110I	0	RW1C ^[1]	0	 Die temperature crosses 110 °C interrupt. Bidirectional interrupt. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	1	—	—	Unused
THERM125I	2	RW1C	0	 Die temperature crosses 125 °C interrupt. Bidirectional interrupt. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	7 to 3			Unused

[1] Read or Write 1 to clear the bit

Name	Bit	R/W	Default	Description
THERM110M	0	RW	1	 Die temperature crosses 110 °C interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
UNUSED	1			Unused
THERM125M	2	RW	1	 Die temperature crosses 125 °C interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
UNUSED	7 to 3		—	Unused

Table 71. Register TEMP_INT_MASK0 - ADDR 0x21

Table 72. Register TEMP_INT_SENSE0 - ADDR 0x22

Name	Bit	R/W	Default	Description		
THERM110S	0	R	0	110 °C interrupt sense		
				0 — Die temperature below 110 °C		
				1 — Die temperature above 110 °C		
UNUSED	1	—	—	Unused		
THERM125S	2	R	0	125 °C interrupt sense		
				0 — Die temperature below 125 °C		
				1 — Die temperature above 125 °C		
UNUSED	7 to 3	—		Unused		

Table 73. Register ONKEY_INT_STAT0 - ADDR 0x24

Name	Bit	R/W	Default	Description
ONKEY_PUSHI	0	RW1C ^[1]	0	 Interrupt to indicate a push of the ONKEY button. Goes high after debounce. 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared. Interrupt occurs whenever ONKEY button is pushed low for longer than the falling edge debounce setting. Interrupt also occurs whenever ONKEY button is released high for longer than the rising edge debounce setting, provided it went past the falling edge debounce time. In other words, this interrupt occurs whenever a change in status of the ONKEY_PUSHS sense bit occurs.
ONKEY_1SI	1	RW1C	0	Interrupt after ONKEY pressed for > 1 s 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
ONKEY_2SI	2	RW1C	0	Interrupt after ONKEY pressed for > 2 s 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared

Name	Bit	R/W	Default	Description
ONKEY_3SI	3	RW1C	0	Interrupt after ONKEY pressed for > 3 s 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
ONKEY_4SI	4	RW1C	0	Interrupt after ONKEY pressed for > 4 s 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
ONKEY_8SI	5	RW1C	0	Interrupt after ONKEY pressed for > 8 s 0 — Interrupt cleared or did not occur 1 — Interrupt occurred and/or not cleared
UNUSED	7 to 6		—	Unused

Table 73. Register ONKEY_INT_STAT0 - ADDR 0x24...continued

[1] Read or Write 1 to clear the bit

Table 74. Register ONKEY_INT_MASK0 - ADDR 0x25

Name	Bit	R/W	Default	Description
ONKEY_PUSHM	0	RW	1	Interrupt mask for ONKEY_PUSH_I 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
ONKEY_1SM	1	RW	1	Interrupt mask for ONKEY_1SI 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
ONKEY_2SM	2	RW	1	Interrupt mask for ONKEY_2SI 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is NOT pulled low if corresponding interrupt status bit is set.
ONKEY_3SM	3	RW	1	Interrupt mask for ONKEY_3SI 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
ONKEY_4SM	4	RW	1	Interrupt mask for ONKEY_4SI 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
ONKEY_8SM	5	RW	1	Interrupt mask for ONKEY_8SI 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.

Table 74. Register ONKEY_INT_MASK0 - ADDR 0x25...continued

Name	Bit	R/W	Default	Description
UNUSED	7 to 6		—	Unused

Table 75. Register ONKEY_INT_SENSE0 - ADDR 0x26

Name	Bit	R/W	Default	Description
ONKEY_PUSHS	0	R	0	 Push interrupt sense 0 — ONKEY not pushed low. This bit follows debounced version of the ONKEY button being released. 1 — ONKEY pushed low. This follows the ONKEY button after the debounce circuit (debounce is programmable).
ONKEY_1SS	1	R	0	 1 s interrupt sense or cleared after ONKEY button is released 0 — ONKEY not pushed low for >1 s or cleared after ONKEY button is released. 1 — ONKEY pushed and being held low > 1 s. This bit is cleared when ONKEY_PUSHS goes back to 0 when the push button is released.
ONKEY_2SS	2	R	0	 2 s interrupt sense or cleared after ONKEY button is released 0 — ONKEY not pushed low for >1 s or cleared after ONKEY button is released. 1 — ONKEY pushed and being held low > 1 s. This bit is cleared when ONKEY_PUSHS goes back to 0 when the push button is released.
ONKEY_3SS	3	R	0	 3 s interrupt sense or cleared after ONKEY button is released 0 — ONKEY not pushed low for >1 s or cleared after ONKEY button is released 1 — ONKEY pushed and being held low > 1 s. This bit is cleared when ONKEY_PUSHS goes back to 0 when the push button is released.
ONKEY_4SS	4	R	0	 4 s interrupt sense or cleared after ONKEY button is released 0 — ONKEY not pushed low for >1 s or cleared after ONKEY button is released. 1 — ONKEY pushed and being held low > 1 s. This bit is cleared when ONKEY_PUSHS goes back to 0 when the push button is released.
ONKEY_8SS	5	R	0	 8 s interrupt sense or cleared after ONKEY button is released 0 — ONKEY not pushed low for >1 s or cleared after ONKEY button is released. 1 — ONKEY pushed and being held low > 1 s. This bit is cleared when ONKEY_PUSHS goes back to 0 when the push button is released.
UNUSED	7 to 6			Unused

Name	Bit	R/W	Default	Description
PWRUP_I	0	RW1C ^[1]	0	Interrupt to indicate completion of transition from STANDBY to RUN and from SLEEP to RUN 0 — Interrupt cleared or has not occurred 1 — Interrupt has occurred
PWRDN_I	1	RW1C	0	Interrupt to indicate completion of transition from RUN to STANDBY and from RUN to SLEEP 0 — Interrupt cleared or has not occurred 1 — Interrupt has occurred
PWRON_I	2	RW1C	0	Power on button event interrupt 0 — Interrupt cleared or has not occurred 1 — Interrupt has occurred
LOW_SYS_WARN_I	3	RW1C	0	LOW_SYS_WARN threshold crossed interrupt 0 — Interrupt cleared or has not occurred 1 — Interrupt has occurred
SYS_OVLO_I	4	RW1C	0	 SYS_OVLO threshold crossed interrupt 0 — Interrupt cleared or has not occurred 1 — Interrupt has occurred
UNUSED	7 to 5	—	—	Unused

Table 76. Register MISC_INT_STAT0 - ADDR 0x28

[1] Read or Write 1 to clear the bit

Table 77. Register MISC_INT_MASK0- ADDR 0x29

Name	Bit	R/W	Default	Description
PWRUP_M	0	RW ^[1]	1	 Mask for interrupt to indicate completion on transition from STANDBY to RUN and from SLEEP to RUN 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
PWRDN_M	1	RW	1	 Mask for interrupt to indicate completion on transition from RUN to STANDBY and from RUN to SLEEP 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
PWRON_M	2	RW	1	 Power on button event interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.
LOW_SYS_WARN_M	3	RW	1	 LOW_SYS_WARN threshold crossed interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding interrupt status bit is set.

Name	Bit	R/W	Default	Description		
SYS_OVLO_M	4	RW	1	 SYS_OVLO threshold crossed interrupt mask 0 — Mask removed. INTB pin is pulled low if corresponding interrupt status bit is set. 1 — Mask enabled. INTB pin is not pulled low if corresponding 		
				interrupt status bit is set.		
UNUSED	7 to 5			Unused		

Table 77. Register MISC_INT_MASK0- ADDR 0x29...continued

[1] Asynchronous Set, Read and Write

Name	Bit	R/W	Default	Description
PWRUP_S	0	R	0	 Sense for interrupt to indicate completion on transition from STANDBY to RUN and from SLEEP to RUN 0 — Transition not in progress 1 — Transition in progress
PWRDN_S	1	R	0	Interrupt to indicate completion on transition from RUN to STANDBY and from RUN to SLEEP 0 — Transition not in progress 1 — Transition in progress
PWRON_S	2	R	0	Power on button event interrupt sense 0 — PWRON low 1 — PWRON high
LOW_SYS_WARN_S	3	R	0	LOW_SYS_WARN threshold crossed interrupt sense 0 — SYS > LOW_SYS_WARN 1 — SYS < LOW_SYS_WARN
SYS_OVLO_S	4	R	0	SYS_OVLO threshold crossed interrupt sense 0 — SYS < SYS_OVLO 1 — SYS > SYS_OVLO
UNUSED	7 to 5		_	Unused

Table 78. Register MISC_INT_SENSE0 - ADDR 0x2A

Table 79. Register COINCELL_CONTROL - ADDR 0x30

Name	Bit	R/W	Default	Description		
VCOIN	3 to 0	RW	0000	Coin cell charger charging voltage 0000 — 1.8 V 0111 — 3.3 V (goes up in 100 mV step per LSB)		
COINCHEN	4	RW	0	Coin cell charger enable 0 — Charger disabled 1 — Charger enabled		
UNUSED	7 to 5			Unused		

PF1510 Product data sheet

Name	Bit	R/W	Default	Description
SW1_VOLT	5 to 0	RW1S ^[1]		SW1 voltage setting register (Run mode) 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings Reset condition — POR
UNUSED	7 to 5			Unused

[1] Load from OTP fuse, Read and Write

Table 81. Register SW1_STBY_VOLT - ADDR 0x33

Name	Bit	R/W	Default	Description
SW1_STBY_VOLT	5 to 0	RW1S ^[1]		 SW1 output voltage setting register (Standby mode). The default value here should be identical to SW1_VOLT[5:0] register. 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings
UNUSED	7 to 6			Unused

[1] Load from OTP fuse, Read and Write

Table 82. Register SW1_SLP_VOLT - ADDR 0x34

Name	Bit	R/W	Default	Description	
SW1_SLP_VOLT	5 to 0	RW1S ^[1]		 SW1 output voltage setting register (Sleep mode). The default value here should be identical to SW1_VOLT[5:0] register. 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings 	
UNUSED	7 to 6		_	Unused	

[1] Load from OTP fuse, Read and Write

Table 83. Register SW1_CTRL - ADDR 0x35

Name	Bit	R/W	Default	Description
SW1_EN	0	RW1S ^[1]	0	 Enables buck regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Run mode 1 — Regulator enabled in Run mode
SW1_STBY_EN	1	RW1S	0	 Enables buck regulator in Standby mode. User can turn regulator off by clearing this bit. The default value of this bit should be equal to the SW1_EN bit (based on OTP). 0 — Regulator disabled in Standby mode 1 — Regulator enabled in Standby mode
SW1_OMODE	2	RW ^[2]	0	 Enables buck regulator in Sleep mode. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Sleep mode 1 — Regulator enabled in Sleep mode

Name	Bit	R/W	Default	Description
SW1_LPWR	3	RW	0	Enables the buck to enter Low-power mode during Standby and Sleep 0 — Regulator not in Low-power mode 1 — Regulator in Low-power mode during Standby or Sleep modes
SW1_DVSSPEED	4	RW1S	0	Controls slew rate of DVS transitions. Loaded from OTP and changeable by user after boot up. Not used when OTP_SW1_ DVS_SEL = 1. 0 — DVS rate at 12.5 mV/2 μs 1 — DVS rate at 12.5 mV/4 μs
SW1_FPWM_IN_DVS	5	RW	0	 Enables CCM operation during DVS down 0 — does not force FPWM during DVS 1 — forces regulator to track the DVS reference while it is falling rather than relying on the load current to pull the voltage low
SW1_FPWM	6	RW	0	Forces buck to go into CCM mode 0 — Not in FPWM mode 1 — Forced in PWM mode irrespective of load current
SW1_RDIS_ENB	7	RW1S	0	 Controls discharge resistor on output when regulator disabled 0 — Enables discharge resistor on output when regulator disabled. Resistor connected at FB pin when regulator disabled to force capacitor discharge. 1 — Disables discharge resistor on output when regulator disabled. Resistor not connected at FB pin when regulator disabled. Relies on leakage/residue load to discharge output capacitor.

Table 83. Register SW1_CTRL - ADDR 0x35...continued

[1] Load from OTP fuse, Read and Write

[2] Asynchronous Set, Read and Writ

Table 84. Register SW1_SLP_VOLT - ADDR 0x36

Name	Bit	R/W	Default	Description
SW1_ILIM	1 to 0	RW1S ^[1]	00	Sets current limit of SW1 regulator 00 — Typical current limit of 1.0 A 01 — Typical current limit of 1.2 A 10 — Typical current limit of 1.5 A 11 — Typical current limit of 2.0 A
UNUSED	3 to 2	_	—	Unused
SW1_TMODE_SEL	4	RW	0	0 — TON control 1 — TOFF control
UNUSED	7 to 5		—	Unused

[1] Load from OTP fuse, Read and Write

NXP Semiconductors

Power management integrated circuit (PMIC) for low power application processors

Table 05. Register SW2_VOLT - ADDR 0X50					
Name	Bit	R/W	Default	Description	
SW2_VOLT	5 to 0	RW1S ^[1]		SW2 voltage setting register (Run mode) 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings	
UNUSED	7 to 6	—	—	Unused	

Table 85. Register SW2_VOLT - ADDR 0x38

[1] Load from OTP fuse, Read and Write

Table 86. Register SW2_STBY_VOLT - ADDR 0x39

Name	Bit	R/W	Default	Description	
SW2_STBY_VOLT	5 to 0	RW1S ^[1]		 SW2 output voltage setting register (Standby mode). The default value here should be identical to SW2_VOLT[5:0] register. 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings 	
UNUSED	7 to 6	—		Unused	

[1] Load from OTP fuse, Read and Write

Table 87. Register SW2_SLP_VOLT - ADDR 0x3A

Name	Bit	R/W	Default	Description
SW2_SLP_VOLT	5 to 0	RW1S ^[1]	_	SW2 output voltage setting register (Sleep mode). The default value here should be identical to SW2_VOLT[5:0] register. 000000 — See <u>Table 23</u> for voltage settings 111111 — See <u>Table 23</u> for voltage settings
UNUSED	7 to 6			Unused

[1] Load from OTP fuse, Read and Write

Table 88. Register SW2_CTRL - ADDR 0x3B

Name	Bit	R/W	Default	Description
SW2_EN	0	RW1S ^[1]	0	 Enables buck regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Run mode 1 — Regulator enabled in Run mode
SW2_STBY_EN	1	RW1S	0	Enables buck regulator in Standby mode. User can turn regulator off by clearing this bit. The default value of this bit should be equal to the SW1_EN bit (based on OTP). 0 — Regulator disabled in Standby mode 1 — Regulator enabled in Standby mode
SW2_OMODE	2	RW	0	 Enables buck regulator in Sleep mode. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Sleep mode 1 — Regulator enabled in Sleep mode

Name	Bit	R/W	Default	Description
SW2_LPWR	3	RW	0	Enables the buck to enter Low-power mode during Standby and Sleep modes 0 — Regulator not in Low-power mode 1 — Regulator in Low-power mode during Standby or Sleep
SW2_DVSSPEED	4	RW1S	0	Controls slew rate of DVS transitions. Loaded from OTP and changeable by user after boot up. Not used when OTP_SW2_DVS_SEL = 1. 0 - DVS rate at 12.5 mV/2 µs 1 - DVS rate at 12.5 mV/4 µs
SW2_FPWM_IN_DVS	5	RW	0	Enables CCM operation during DVS down 0 — does not force FPWM during DVS 1 — forces regulator to track the DVS reference while it is falling rather than relying on the load current to pull the voltage low
SW2_FPWM	6	RW	0	Forces buck to go into CCM mode 0 — Not in FPWM mode 1 — Forced in PWM mode irrespective of load current.
SW2_RDIS_ENB	7	RW1S	0	 Controls discharge resistor on output when regulator disabled 0 — Enables discharge resistor on output when regulator disabled. Resistor connected at FB pin when regulator disabled to force capacitor discharge. 1 — Disables discharge resistor on output when regulator disabled. Resistor not connected at FB pin when regulator disabled. Relies on leakage/residue load to discharge output capacitor.

Table 88. Register SW2	_CTRL - ADDR	0x3Bcontinued
------------------------	--------------	---------------

[1] Load from OTP fuse, Read and Write

Table 89. Register SW2_CTRL1 - ADDR 0x3C

Name	Bit	R/W	Default	Description
SW2_ILIM	1 to 0	RW1S	00	Sets current limit of SW2 regulator 00 — Typical current limit of 1.0 A 01 — Typical current limit of 1.2 A 10 — Typical current limit of 1.5 A 11 — Typical current limit of 2.0 A
UNUSED	3 to 2	_	—	Unused
SW2_TMODE_SEL	4	RW	0	0 — TON control 1 — TOFF control
UNUSED	7 to 5			Unused

Table 90. Register SW3_VOLT - ADDR 0x3E

Name	Bit	R/W	Default	Description
SW3_VOLT	3 to 0	RW1S		 SW3 voltage setting register (Run mode). Loaded from fuses. Read only because DVS is not supported in this regulator. 0000 — See <u>Table 29</u> for voltage settings 1111 — See <u>Table 29</u> for voltage settings
UNUSED	7 to 4		—	Unused

Table 91. Register SW3_STBY_VOLT - ADDR 0x3F

Name	Bit	R/W	Default	Description		
SW3_STBY_VOLT	3 to 0	RW1S		 SW3 voltage setting register (Standby mode). Loaded from fuses. Read only because DVS is not supported in this regulator. 0000 — See <u>Table 29</u> for voltage settings 1111 — See <u>Table 29</u> for voltage settings 		
UNUSED	7 to 4		—	Unused		

Table 92. Register SW3_SLP_VOLT - ADDR 0x40

Name	Bit	R/W	Default	Description	
SW3_SLP_VOLT	3 to 0	RW1S		 SW3 voltage setting register (Sleep mode). Loaded from fuses. Read only because DVS is not supported in this regulator. 0000 — See <u>Table 29</u> for voltage settings 1111 — See <u>Table 29</u> for voltage settings 	
UNUSED	7 to 4		—	Unused	

Table 93. Register SW3_CTRL - ADDR 0x41

Name	Bit	R/W	Default	Description
SW3_EN	0	RW1S	0	Enables buck regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Run mode 1 — Regulator enabled in Run mode
SW3_STBY_EN	1	RW1S	0	Enables buck regulator in Standby mode. User can turn regulator off by clearing this bit. The default value of this bit should be equal to the SW1_EN bit (based on OTP). 0 — Regulator disabled in Standby mode 1 — Regulator enabled in Standby mode
SW3_OMODE	2	RW	0	 Enables buck regulator in Sleep mode. User can turn regulator off by clearing this bit. 0 — Regulator disabled in Sleep mode 1 — Regulator enabled in Sleep mode
SW3_LPWR	3	RW	0	Enables the buck to enter Low-power mode during Standby and Sleep modes 0 — Regulator not in Low-power mode 1 — Regulator in Low-power mode while in Standby or Sleep

Name	Bit	R/W	Default	Description
UNUSED	4	—	—	Unused
UNUSED	5		—	Unused
SW3_FPWM	6	RW	0	Forces buck to go into CCM mode 0 — Not in FPWM mode 1 — Forced in PWM mode irrespective of load current
SW3_RDIS_ENB	7	RW1S	0	 Controls discharge resistor on output when regulator is disabled 0 — Enables discharge resistor on output when regulator disabled. Resistor connected at FB pin when regulator disabled to force capacitor discharge. 1 — Disables discharge resistor on output when regulator disabled. Resistor not connected at FB pin when regulator disabled. Relies on leakage/residue load to discharge output capacitor.

Table 93. Register SW3_CTRL - ADDR 0x41...continued

Table 94. Register SW3_CTRL1 - ADDR 0x42

Name	Bit	R/W	Default	Description
SW3_ILIM	1 to 0	RW1S	00	Sets current limit of SW3 regulator 00 — Typical current limit of 1.0 A 01 — Typical current limit of 1.2 A 10 — Typical current limit of 1.5 A 11 — Typical current limit of 2.0 A
UNUSED	3 to 2	_	—	Unused
SW3_TMODE_SEL	4	RW	0	0 — TON control 1 — TOFF control
UNUSED	7 to 5			Unused

Table 95. Register VSNVS_CTRL - ADDR 0x48

Name	Bit	R/W	Default	Description
VSNVS_VOLT	2 to 0	RW1S	000	Not used in PF1510. Placeholder for future products.
CLKPULSE	3	RW	0	Optional bit used for evaluation. Refer to IP block
FORCEBOS	4	RW	0	Optional bit for evaluation 0 — BOS circuit activated only when VSYS < UVDET 1 — Forces best of supply circuit irrespective of UVDET
LIBGDIS	5	RW	0	Use to reduce quiescent current in coin cell mode 0 — VSNVS local bandgap enabled in coin cell mode 1 — VSNVS local bandgap disabled in coin cell mode to save quiescent current
UNUSED	7 to 6		—	Unused

PF1510 Product data sheet

Name	Bit	R/W	Default	Description
VREFDDR_EN	0	RW1S	0	 0 — Disables VREFDDR regulator 1 — Enables VREFDDR regulator. This is set by the OTP sequence.
VREFDDR_STBY_EN	1	RW1S	0	The default value for this should be same as VREFDDREN 0 — Disables VREFDDR regulator in Standby mode 1 — Enables VREFDDR regulator in Standby mode if VREFDDREN = 1
VREFDDR_OMODE	2	RW	0	 0 — Keeps VREFDDR off in Off mode 1 — Enables VREFDDR in Sleep mode if VREFDDREN = 1
VREFDDR_LPWR	3	RW	0	 0 — Disables VREFDDR Low-power mode 1 — Enables VREFDDR Low-power mode
UNUSED	7 to 4		_	Unused

Table 96. Register VREFDDR_CTRL - ADDR 0x4A

Table 97. Register LDO1_VOLT - ADDR 0x4C

Name	Bit	R/W	Default	Description	
LDO1_VOLT	4 to 0	RW1S		LDO1 output voltage setting register. Loaded from OTP. 00000 — See <u>Table 33</u> for voltage settings 11111 — See <u>Table 33</u> for voltage settings	
UNUSED	7 to 5			Unused	

Table 98. Register LDO1_CTRL - ADDR 0x4D

Name	Bit	R/W	Default	Description
VLDO1_EN	0	RW1S	0	 Enables LDO regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Disables regulator 1 — Enables regulator
VLDO1_STBY_EN	1	RW1S	0	Enables LDO in Standby mode. Default value of this bit should be same as VLDO1_EN. 0 — Disables regulator 1 — Enables regulator
VLDO1_OMODE	2	RW	0	Enables LDO in Sleep mode 0 — Disables regulator 1 — Enables regulator
VLDO1_LPWR	3	RW	0	 Forces LDO to Low-power mode in Sleep and Standby modes 0 — Not in Low-power mode during Standby and Sleep 1 — Regulator in Low-power mode during Standby and Sleep
LDO1_LS_EN	4	RW1S	0	 This is loaded from OTP_LDOy_LS_EN and changeable from 0 to 1 on power up. Changing from 1 to 0 is not allowed. 0 — Sets LDOy in LDO mode 1 — Sets LDOy to a load switch (fully on) mode
UNUSED	7 to 5			Unused

Table 99. Register LDO2_VOLT - ADDR 0x4F

Name	Bit	R/W	Default	Description
LDO2_VOLT	3 to 0	RW1S		LDO2 output voltage setting register. Loaded from OTP. 0000 — See <u>Table 35</u> for voltage settings 1111 — See <u>Table 35</u> for voltage settings
UNUSED	7 to 4			Unused

Table 100. Register LDO2_CTRL - ADDR 0x50

Name	Bit	R/W	Default	Description
VLDO2_EN	0	RW1S	0	 Enables LDO regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Disables regulator 1 — Enables regulator
VLDO2_STBY_EN	1	RW1S	0	Enables LDO in Standby mode. Default value of this bit should be same as VLDO1_EN. 0 — Disables regulator 1 — Enables regulator
VLDO2_OMODE	2	RW	0	Enables LDO in Sleep mode 0 — Disables regulator 1 — Enables regulator
VLDO2_LPWR	3	RW	0	 Forces LDO to Low-power mode in Sleep and Standby modes 0 — Not in Low-power mode during Standby and Sleep 1 — Regulator in Low-power mode during Standby and Sleep
UNUSED	7 to 4			Unused

Table 101. Register LDO3_VOLT - ADDR 0x52

Name	Bit	R/W	Default	Description		
LDO3_VOLT	4 to 0	RW1S		LDO3 output voltage setting register. Loaded from OTP. 00000 — See <u>Table 33</u> for voltage settings 11111 — See <u>Table 33</u> for voltage settings		
UNUSED	7 to 5	_	—	Unused		

Table 102. Register LDO3_CTRL - ADDR 0x53

Name	Bit	R/W	Default	Description
VLDO3_EN	0	RW1S	0	 Enables LDO regulator. Loaded from OTP based on the sequence settings. User can turn regulator off by clearing this bit. 0 — Disables regulator 1 — Enables regulator
VLDO3_STBY_EN	1	RW1S	0	Enables LDO in Standby mode. Default value of this bit should be same as VLDO1_EN. 0 — Disables regulator 1 — Enables regulator

74 / 108

Name	Bit	R/W	Default	Description
VLDO3_OMODE	2	RW	0	Enables LDO in Sleep mode 0 — Disables regulator 1 — Enables regulator
VLDO3_LPWR	3	RW	0	 Forces LDO to Low-power mode in Sleep and Standby modes 0 — Not in Low-power mode during Standby and Sleep 1 — Regulator in Low-power mode during Standby and Sleep
LDO3_LS_EN	4	RW1S	0	 This is loaded from OTP_LDOy_LS_EN and changeable from 0 to 1 on power up. Changing from 1 to 0 is not allowed. 0 — Sets LDOy in LDO mode 1 — Sets LDOy to a load switch (fully on) mode
UNUSED	7 to 5		—	Unused

Table 102. Register LDO3_CTRL - ADDR 0x53...continued

Table 103. Register PWRCTRL0 - ADDR 0x58

Name	Bit	R/W	Default	Description
STANDBYDLY	1 to 0	RW	01	Controls delay of Standby pin after synchronization 0 — No additional delay 1 — 32 kHz cycle additional delay 2 — 32 kHz cycle additional delay 3 — 32 kHz cycle additional delay
STANDBYINV	2	RW	0	Controls polarity of STANDBY pin 0 — Standby pin input active high 1 — Standby pin input active low
POR_DLY	5 to 3	RW1S	000	Controls delay of RESETBMCU pin after power up (loaded from OTP) 000 — RESETBMCU goes high 2 ms after last regulator 010 — RESETBMCU goes high 4 ms after last regulator 011 — RESETBMCU goes high 8 ms after last regulator 100 — RESETBMCU goes high 16 ms after last regulator 101 — RESETBMCU goes high 128 ms after last regulator 101 — RESETBMCU goes high 256 ms after last regulator 111 — RESETBMCU goes high 256 ms after last regulator
TGRESET	7 to 6	RW1S	00	Controls duration for which ONKEY has to be pushed low for a global reset (part goes to REGS_DISABLE) 00 - 4 s 01 - 8 s 10 - 12 s 11 - 16 s

Name	Bit	R/W	Default	Description
PWRONDBNC	1 to 0	RW	00	Controls debounce of PWRON when in push button mode (PWRON_CFG = 1) 00 — 31.25 ms falling edge; 31.25 ms rising edge 01 — 31.25 ms falling edge; 31.25 ms rising edge 10 — 125 ms falling edge; 31.25 ms rising edge 11 — 750 ms falling edge; 31.25 ms rising edge
ONKEYDBNC	3 to 2	RW	00	Controls debounce of ONKEY push button 00 — 31.25 ms falling edge; 31.25 ms rising edge 01 — 31.25 ms falling edge; 31.25 ms rising edge 10 — 125 ms falling edge; 31.25 ms rising edge 11 — 750 ms falling edge; 31.25 ms rising edge
PWRONRSTEN	4	RW	0	Enables going to REGS_DISABLE or Sleep mode when PWRON_CFG = 1. See <u>Section 10 "PF1510 state machine"</u> for details. 0 — Long press on PWRON button does not take state to REGS_DISABLE or Sleep 1 — Long press on PWRON button takes state to REGS_DISABLE or Sleep
RESTARTEN	5	RW	0	Enables restart of system when PWRON push button is held low for 5 s 0 — No impact 1 — When going to REGS_DISABLE via a long press of PWRON button, holding it low for 1 more second takes state back to RUN (equally, a 5 second push restarts the system)
REGSCPEN	6	RW	0	 Shuts down LDO if it enters a current limit fault. Controls LDO1, LDO2 and LDO3. 0 — LDO does not shutdown in the event of a current limit fault. Continues to limit current. 1 — LDO is turned off when it encounters a current limit fault
ONKEY_RST_EN	7	RW	1	 Enables turning off of system via ONKEY. See <u>Section 10</u> "PF1510 state machine" for details. 0 — ONKEY cannot be used to turn off or restart system 1 — ONKEY can be used to turn off or restart system

Table 104. Register PWRCTRL1 - ADDR 0x59

Table 105. Register PWRCTRL2 - ADDR 0x5A

Name	Bit	R/W	Default	Description
UVDET	1 to 0	RW1S	00	Sets UVDET threshold 00 — Rising 2.65 V; falling 2.55 V 01 — Rising 2.8 V; falling 2.7 V 10 — Rising 3.0 V; falling 2.9 V 11 — Rising 3.1 V; falling 3.0 V
LOW_SYS_WARN	3 to 2	RW	00	Sets LOW_SYS_WARN threshold 00 — Rising 3.3 V; falling 3.1 V 01 — Rising 3.5 V; falling 3.3 V 10 — Rising 3.7 V; falling 3.5 V 11 — Rising 3.9 V; falling 3.7 V

PF1510

Table 105. Register PWRCTRL2 - ADDR 0x5A...continued

Name	Bit	R/W	Default	Description
UNUSED	7 to 4			Unused

Table 106. Register PWRCTRL3 - ADDR 0x5B

Name	Bit	R/W	Default	Description
UNUSED	0	RW	0	Unused
GOTO_CORE_OFF	1	RW	0	Set this bit to go to CORE_OFF mode once in REGS_DISABLE state 0 — No impact 1 — PF1510 gracefully enters CORE_OFF mode when in REGS_DISABLE state
UNUSED	7 to 2			Unused

Table 107. Register SW1_PWRDN_SEQ - ADDR 0x5F

Name	Bit	R/W	Default	Description
SW1_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequencer is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3	—	—	Unused

Name	Bit	R/W	Default	Description
SW2_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequence is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequence is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3			Unused

Table 108. Register SW2_PWRDN_SEQ - ADDR 0x60

Table 109. Register SW2_PWRDN_SEQ - ADDR 0x61

Name	Bit	R/W	Default	Description
SW3_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], SW3_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequencer is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3	_		Unused

Name	Bit	R/W	Default	Description
LDO1_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], SW3_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequence is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3			Unused

Table 110.	Register LDO	1_PWRD	N_SEQ - /	ADDR 0x62

Table 111. Register LDO2_PWRDN_SEQ - ADDR 0x63

Name	Bit	R/W	Default	Description
LDO2_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], SW3_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequencer is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3			Unused

Name	Bit	R/W	Default	Description
LDO3_PWRDN_SEQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], SW3_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequence is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3	_	_	Unused

Table 112. Register LDO3_PWRDN_SEQ - ADDR 0x64

Table 113. Register VREFDDR_PWRDN_SEQ - ADDR 0x65

Name	Bit	R/W	Default	Description
VREFDDR_PWRDN_S EQ	2 to 0	RW1S	000	This contains same value as power-up sequence value by default. Power-up sequence is in mirror registers. xxx = The power-down sequencer performs the functional opposite to the power-up sequencer. Each regulator has an associated register setting (SW1_PWRDN_SEQ[2:0], SW2_PWRDN_SEQ[2:0], LDO1_PWRDN_SEQ[2:0], LDO2_PWRDN_SEQ[2:0], LDO3_PWRDN_SEQ[2:0]. VREFDDR_PWRDN_SEQ[2:0]) that sets its power-down sequence. The default setting of the above registers is equal to the corresponding power-up sequence setting. For example, SW1_PWRDN_SEQ[2:0] = OTP_SW1_PWRUP_SEQ[2:0]. When the power-down sequencer is activated, regulators are turned off one by one in the descending order of the XXX_PWRDN_SEQ[2:0] setting. This way, by default, power-down is a mirror of the power-up sequence. In one of the "System On" states, the processor can change the values of the XXX_PWRDN_SEQ[2:0] registers. The power-up sequence is fixed by OTP (or TBB). If all XXX_PWRDN_SEQ[2:0] = 0x00, the power-down sequence is bypassed and all the regulators are turned off at once.
UNUSED	7 to 3			Unused

Table 114. Register STATE_INFO - ADDR 0X67							
Name	Bit	R/W	Default	Description			
STATE	5 to 0	R	000000	Indicates machine state 000000 — Wait state 001100 — Run state 001101 — Standby state 001110 — Sleep/LPSR state 101011 — REGS_DISABLE state Other bits are reserved			
UNUSED	7 to 6			Unused			

Table 114. Register STATE_INFO - ADDR 0x67

Table 115. Register I2C_ADDR - ADDR 0x68

Name	Bit	R/W	Default	Description
I2C_SLAVE_ADDR_L SBS	2 to 0	R	000	Loaded from fuses. But read only in functional space. 000 — Slave Address: 0x08 001 — Slave Address: 0x09 010 — Slave Address: 0x0A 011 — Slave Address: 0x0B 100 — Slave Address: 0x0C 101 — Slave Address: 0x0D 110 — Slave Address: 0x0E 111 — Slave Address: 0x0F
USE_DEFAULT_ADD R	7	RW	0	DEFAULT ADDR

Table 116. Register RC_16MHZ - ADDR 0x6B

Name	Bit	R/W	Default	Description
REQ_16MHZ	0	RW	0	Enables 16 MHz clock 0 — 16 MHz clock enable controlled by state machine 1 — 16 MHz clock always enabled
REQ_ACORE_ON	1	RW	0	Controls Analog core enable 0 — Analog core enable controlled by state machine 1 — Analog core always on
REQ_ACORE_HIPWR	2	RW	0	Controls Low-power mode of the analog core 0 — Analog core Low-power mode controlled by state machine 1 — Analog core never in Low-power mode
UNUSED	7 to 3		—	Unused

Table 117. Register KEY1 - ADDR 0x6B

Name	Bit	R/W	Default	Description
KEY1	7 to 0	RW	0x00	Unused

PF1510 Product data sheet

12.2 Specific Registers (Offset is 0x80)

Table 118. Register INT - ADDR 0x00

Name	Bit	R/W	Default	Description
RSVD0	0			
RSVD1	1			
RSVD2	2	RW1S ^[1]	0	Unused
RSVD3	3			
RSVD4	4			
VIN_I	5	RW1S	0	VIN interrupt 0 — The VIN_OK interrupt has not occurred or been cleared 1 — The VIN_OK interrupt has occurred Reset condition — VCOREDIG_RSTB
RSVD6	6	RW1S	0	Unused
RSVD7	7	RW1S	0	Unused

[1] Load from OTP fuse, Read and Write

Table 119. Register INT_MASK - ADDR 0x02

Name	Bit	R/W	Default	Description
RSVD0	0			
RSVD1	1			
RSVD2	2	RW	1	Unused
RSVD3	3			
RSVD4	4			
VIN_M	5	RW	1	VIN interrupt mask 0 — Unmasked 1 — Masked Reset condition — VCOREDIG_RSTB
RSVD6	6	RW	1	Unused
RSVD7	7	RW	1	Unused

Table 120. Register INT_OK - ADDR 0x04

Name	Bit	R/W	Default	Description
RSVD0	0		0	
RSVD1	1		0	
RSVD2	2	R	1	Unused
RSVD3	3		0	
RSVD4	4		0	

PF1510 Product data sheet

Name	Bit	R/W	Default	Description
VIN_OK	5	R	0	Single bit VIN status indicator. See VIN_SNS for more information. 0 — The VIN input is invalid. For example, VIN_VALID = 0. 1 — The VIN input is valid. For example, VIN_VALID = 1. Reset condition — VCOREDIG_RSTB
RSVS6	6	R	0	Unused
RSVD7	7	R	1	Unused

Table 120. Register INT_OK - ADDR 0x04...continued

Table 121. Register VIN_SNS - ADDR 0x06

Name	Bit	R/W	Default	Description
RSVD[1:0]	1 to 0	R	00	Unused
VIN_UVLO_SNS	2	R	1	0 — VIN > VIN_UVLO 1 — VIN < VIN_UVLO or when VIN is detached
VIN2SYS_SNS	3	R	1	0 — VIN > VSYS + VIN2SYS 1 — VIN < VSYS + VIN2SYS
VIN_OVLO_SNS	4	R	0	0 — VIN < VIN_OVLO 1 — VIN > VIN_OVLO
VIN_VALID	5	R	0	0 — VIN is not valid 1 — VIN is valid, VIN > VIN_UVLO, VIN > VSYS + VIN2SYS, VIN < VIN_OVLO Reset condition — VCOREDIG_RSTB
RSVD6	6	R	0	Unused
RSVD7	7	R	0	Unused

Table 122. Register FRONT_END_OPER- ADDR 0x09

Name	Bit	R/W	Default	Description
FRONT_END_ON	1 to 0	RW1S ^[1]	01	Front-end LDO operation configuration 0 — Front-end LDO is OFF 1 — Front-end LDO is ON 2 — Reserved 3 — Reserved Reset condition — VCOREDIG_RSTB
RSVD2	2		0	
RSVD3	3	RW	0	Unused
RSVD4	4		0	Onuseu
RSVD[7:5]	7 to 5		000	

[1] Load from OTP fuse, Read and Write

PF1510 Product data sheet

Table 123. Register FRONT	_END_REG - ADDR 0x0F
---------------------------	----------------------

Name	Bit	R/W	Default	Description
RSVD[5:0]	5 to 0	RW1S	101011	Unused
VSYSMIN	7 to 6	RW1S	00	Minimum system regulation voltage (VSYS _{MIN}) $0 - 3.5 \vee$ $1 - 3.7 \vee$ $2 - 4.3 \vee$ 3 - Reserved Reset condition - VCOREDIG_RSTB

Table 124. Register VIN_INLIM_CNFG - ADDR 0x14

Name	Bit	R/W	Default	Description
RSVD[2:0]	2 to 0	RW	000	Unused
VIN_ILIM	7 to 3	RW1S	01101	Maximum input current limit selection. 5 bit adjustment from 10 mA to 1500 mA.
				0 — 10 mA
				1 — 15 mA
				2 — 20 mA
				3 — 25 mA
				4 — 30 mA
				5 — 35 mA
				6 — 40 mA
				7 — 45 mA
				8 — 50 mA
				9 — 100 mA
				10 — 150 mA
				11 — 200 mA
				12 — 300 mA
				13 — 400 mA
				14 — 500 mA
				15 — 600 mA
				16 — 700 mA
				17 — 800 mA
				18 — 900 mA
				19 — 1000 mA
				20 — 1500 mA
				21 — Reserved
				22 — Reserved
				23 — Reserved
				24 — Reserved
				25 — Reserved
				26 — Reserved
				27 — Reserved
				28 — Reserved
				29 — Reserved
				30 — Reserved
				31 — Reserved
				Reset condition — CHGPOK_RSTB

Name	Bit	R/W	Default	Description
RSVD0	0	RW1S	1	Unused
USBPHY	1	RW1S	0	USBPHY voltage setting register 0 — 3.3 V 1 — 4.9 V Reset condition — VCOREDIG_RSTB
USBPHYLDO	2	RW1S	0	USBPHY LDO enable 0 — Disabled 1 — Enabled Reset condition — VCOREDIG_RSTB
RSVD3	3		0	
RSVD[5:4]	5 to 4	RW	00	Unused
RSVD[7:6]	7 to 6		00	

Table 125. Register USB_PHY_LDO_CNFG - ADDR 0x16

Table 126. Register DBNC_DELAY_TIME - ADDR 0x18

Name	Bit	R/W	Default	Description
VIN_OV_TDB	1 to 0	RW1S	00	VIN overvoltage debounce delay 0 — 10 μs (reserved) 1 — 100 μs 2 — 1 ms 3 — 10 ms Reset condition — VCOREDIG_RSTB
USB_PHY_TDB	3 to 2	RW1S	00	USBPHY debounce timer - not used in PF1510 0 — 0 ms 1 — 16 ms 2 — 32 ms 3 — Not used Reset condition — VCOREDIG_RSTB
SYS_WKUP_DLY	5 to 4	RW1S	00	System wake-up time 0 — 8.0 ms 1 — 16 ms 2 — 32 ms 3 — 100 ms Reset condition — VCOREDIG_RSTB
RSVD[7:6]	7 to 6	RW	00	Unused

Name	Bit	R/W	Default	Description
VIN2SYS_TDB	1 to 0	RW1S	00	VIN to VSYS comparator debounce time 0 — Reserved 1 — 100 μs 2 — 1 ms 3 — 10 ms Reset condition — VCOREDIG_RSTB
VIN2SYS_THRSH	2	RW1S	0	VIN to VSYS comparator threshold setting 0 — 50 mV 1 — 175 mV Reset condition — VCOREDIG_RSTB
RSVD[7:3]	7 to 3	RW	00000	Unused

Table 127. Register VIN2SYS_CNFG - ADDR 0x1B

12.3 Register PMIC bitmap

VCO	REDIG	PORB ^[1]

PS_END_RSTB^[2]

REGS_DISABLE_TOG_RSTB^[3]

[1]

Bits reset by invalid VCOREDIG Bits reset by PORB or RESETBMCU Bits reset by pulse to REGS_DISABLE mode [2] [3]

Address	Register name						BITS[7:0]			
			7	6	5	4	3	2	1	0
0x00	DEVICE_ID	Name			FAMILY[3:	7]			DEVICE_ID[2:0]	
		Reset	0	1	1	1	1	1	0	0
		Туре	R	R	R	R	R	R	R	R
0x01	OTP_FLAVOR	Name	_	_			OTP_F	LAVOR[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	_	-	R	R	R	R	R	R
0x02	SILICON_REV	Name	FAB_	FIN[7:6]	F	JLL_LAYER_REV[5:3]	ME	TAL_LAYER_REV	([2:0]
		Reset	0	0	0	0	1	0	0	0
		Туре	R	R	R	R	R	R	R	R
0x06	INT_CATEGORY	Name	MISC_INT	TEMP_INT	ONKEY_INT	LDO_INT	SW3_INT	SW2_INT	SW1_INT	VIN_INT
		Reset	0	0	0	0	0	0	0	0
		Туре	R	R	R	R	R	R	R	R
0x08	SW_INT_STAT0	Name	_	-	_	-	-	SW3_LS_I	SW2_LS_I	SW1_LS_I
		Reset	0	0	0	0	0	0	0	0
		Туре	_	-	_	-	-	RW1C	RW1C	RW1C
0x09	SW_INT_MASK0	Name	_	-	_	_	-	SW3_LS_M	SW2_LS_M	SW1_LS_M
		Reset	0	0	0	0	0	1	1	1
		Туре	_	-	_	_	-	RW	RW	RW
0x0A	SW_INT_SENSE0	Name	_	-	_	_	-	SW3_LS_S	SW2_LS_S	SW1_LS_S
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	_	-	_	R	R	R
0x0B	SW_INT_STAT1	Name	_	_	_	-	_	SW3_HS_I	SW2_HS_I	SW1_HS_I
		Reset	0	0	0	0	0	0	0	0

Table 128. Register PMIC bitmap

Product data sheet

PF1510

© NXP B.V. 2021. All rights reserved.

Table 128.	Register	PMIC	bitmapcontinued
------------	----------	------	-----------------

	-	nistor namo											
Address	Register name					1	BITS[7:0]						
		1	7	6	5	4	3	2	1	0			
		Туре	-	_		-	-	RW1C	RW1C	RW1C			
0x0C	SW_INT_MASK1	Name	-	_	-	-	-	SW3_HS_M	SW2_HS_M	SW1_HS_M			
		Reset	0	0	0	0	0	1	1	1			
		Туре			-		-	RW	RW	RW			
0x0D	SW_INT_SENSE1	Name			-		-	SW3_HS_S	SW2_HS_S	SW1_HS_S			
		Reset	0	0	0	0	0	0	0	0			
		Туре	-	_	-	-	-	R	R	R			
0x0E	SW_INT_STAT2	Name	_	—	_	-	_	_	SW2_DVS_ DONE_I	SW1_DVS_ DONE_I			
		Reset	0	0	0	0	0	0	0	0			
		Туре	_		_	_	_	_	RW1C	RW1C			
0x0F	DF SW_INT_MASK2	Name	-	_	_	-	_	-	SW2_DVS_ DONE_M	SW1_DVS_ DONE_M			
		Reset	0	0	0	0	0	0	1	1			
		Туре	_		_	_	_	_	RW	RW			
0x10	SW_INT_SENSE2	Name	_	_	_	_	-	_	SW2_DVS_S	SW1_DVS_S			
		Reset	0	0	0	0	0	0	0	0			
		Туре	_		_	_	_	_	R	R			
0x18	LDO_INT_STAT0	Name	_	_	_	_	_	LDO3_FAULTI	LDO2_FAULTI	LDO1_FAULTI			
		Reset	0	0	0	0	0	0	0	0			
		Туре	_	_		_	_	RW1C	RW1C	RW1C			
0x19	LDO_INT_MASK0	Name	_	_	_	_	_	LDO3_FAULTM	LDO2_FAULTM	LDO1_FAULTM			
		Reset	0	0	0	0	0	1	1	1			
		Туре	_		_		_	RW	RW	RW			
0x1A LD	LDO_INT_SENSE0	Name	_		_	_	_	LDO3 FAULTS	LDO2_FAULTS	LDO1_FAULTS			
		Reset	0	0	0	0	0	0	0	0			
		Туре	_		_	_	_	R	R	R			
0x20	TEMP_INT_STAT0	Name	_		_	_	_	THERM125I		THERM110I			
		Reset	0	0	0	0	0	0	0	0			
		Туре	_		_	_	_	RW1C	_	RW1C			
0x21	TEMP_INT_MASK0	Name			_	_	_	THERM125M	_	THERM110M			
		Reset	0	0	0	0	1	1	1	1			
		Туре	_		_	_	_	RW		RW			
0x22	TEMP_INT_SENSE0	Name				_	_	THERM125S	_	THERM110S			
UNEL		Reset	0	0	0	0	0	0	0	0			
		Туре	_				_	R		R			
0x24	ONKEY_INT_STAT0	Name			ONKEY_8SI	ONKEY_4SI	ONKEY_3SI	ONKEY_2SI	ONKEY_1SI	ONKEY_PUSHI			
UNL-		Reset	0	0	0	0	0	0	0	0			
		Туре			RW1C	RW1C	RW1C	RW1C	RW1C	RW1C			
0x25	ONKEY_INT_MASK0	Name	_	_	ONKEY_8SM	ONKEY_4SM	ONKEY_3SM	ONKEY_2SM	ONKEY_1SM	ONKEY_ PUSHM			
		Reset	0	0	1	1	1	1	1	1			
		Туре	_		RW	RW	RW	RW	RW	RW			
0x26	ONKEY_INT_SENSE0	Name			ONKEY_8SS	ONKEY_4SS	ONKEY_3SS	ONKEY_2SS	ONKEY_1SS	ONKEY_ PUSHS			
		Reset	0	0	0	0	0	0	0	0			
		Туре			R	R	R	R	R	R			
						SYS_OVLO_I	LOW_SYS_	PWRON_I	PWRDN_I	PWRUP_I			
0x28	MISC_INT_STAT0	Name	_	_	_	010_0120_1			_				
0x28	MISC_INT_STAT0	Name Reset	0	0	0	0	WARN_I	0	0	0			

PF1510 Product data sheet © NXP B.V. 2021. All rights reserved.

Table 128.	Register	PMIC	bitmapcontinued
------------	----------	------	-----------------

Address	Register name			r	1		BITS[7:0]	1	1	1
				6	5	4	3	2	1	0
0x29	MISC_INT_MASK0	Name	_	_	_	SYS_OVLO_M	LOW_SYS_ WARN_M	PWRON_M	PWRDN_M	PWRUP_M
		Reset	0	0	0	1	1	1	1	1
		Туре	_	_	_	RW	RW	RW	RW	RW
0x2A	MISC_INT_SENSE0	Name	_	_	_	SYS_OVLO_S	LOW_SYS_ WARN_S	PWRON_S	PWRDN_S	PWRUP_S
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	_	R	R	R	R	R
0x30	COINCELL_CONTROL	Name				COINCHEN		VCC	DIN[3:0]	
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	_	RW	RW	RW	RW	RW
0x32	SW1_VOLT	Name	_	_			SW1_	VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	_	-	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x33	SW1_STBY_VOLT	Name	_	-			SW1_STI	BY_VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	_	-	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x34	SW1_SLP_VOLT	Name	_	_			SW1_SL	P_VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x35	SW1_CTRL	Name	SW1_ RDIS_ENB	SW1_FPWM	SW1_FPWM_ IN_DVS	SW1_ DVSSPEED	SW1_LPWR	SW1_OMODE	SW1_STBY_EN	SW1_EN
		Reset	0	0	0	0	0	0	0	0
		Туре	RW1S	RW	RW	RW1S	RW	RW	RW1S	RW1S
0x36	SW1_CTRL1	Name	_	_	_	SW1_TMODE_ SEL	-	-	SW1_I	LIM[1:0]
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	_	RW	_	_	RW1S	RW1S
0x38	SW2_VOLT	Name	_	_			SW2_	VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x39	SW2_STBY_VOLT	Name	_	-			SW2_STI	BY_VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	-	_	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x3A	SW2_SLP_VOLT	Name	-	-			SW2_SL	.P_VOLT[5:0]		
		Reset	0	0	0	0	0	0	0	0
		Туре	-	—	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S
0x3B	SW2_CTRL	Name	SW2_ RDIS_ENB	SW2_FPWM	SW2_FPWM_ IN_DVS	SW2_ DVSSPEED	SW2_LPWR	SW2_OMODE	SW2_STBY_EN	SW2_EN
		Reset	0	0	0	0	0	0	0	0
		Туре	RW1S	RW	RW	RW1S	RW	RW	RW1S	RW1S
0x3C	SW2_CTRL1	Name	_	_	—	SW2_TMODE_ SEL	-	-	SW2_I	LIM[1:0]
		Reset	0	0	0	0	0	0	0	0
		Туре	-	_	_	RW	—	-	RW1S	RW1S
0x3E	SW3_VOLT	Name	-	—	_	-		SW3_	VOLT[3:0]	
		Reset	0	0	0	0	0	0	0	0
		Туре	-	—	_	-	RW1S	RW1S	RW1S	RW1S
0x3F	SW3_STBY_VOLT	Name	-	—	_	-		SW3_STE	BY_VOLT[3:0]	
		Reset	0	0	0	0	0	0	0	0
		Туре	_	_	_	-	RW1S	RW1S	RW1S	RW1S
0x40	SW3_SLP_VOLT	Name	_	-	_	_		SW3_SL	P_VOLT[3:0]	

PF1510

Table 128.	Register	PMIC	bitmapcontinued
------------	----------	------	-----------------

Register name	Reset Type Name	7 0	6 0	5	4	BITS[7:0] 3	2	1	0
SW3_CTRL	Туре	0							0
SW3_CTRL	Туре		0	0	0				
SW3_CTRL		_		-	0	0	0	0	0
SW3_CTRL	Name	-	-		—	RW1S	RW1S	RW1S	RW1S
		SW3_ RDIS_ENB	SW3_FPWM	—	SW3_ DVSSPEED	SW3_LPWR	SW3_OMODE	SW3_STBY_EN	SW3_EN
	Reset	0	0	0	0	0	0	0	0
	Туре	RW1S	RW	_	RW1S	RW	RW	RW1S	RW1S
SW3_CTRL1	Name	_	_	_	SW3_TMODE_ SEL	_	-	SW3_I	_IM[1:0]
	Reset	0	0	0	0	0	0	0	0
	Туре	-	—	—	RW	-	—	RW1S	RW1S
VSNVS_CTRL	Name	-	—	LIBGDIS	FORCEBOS	CLKPULSE		VSNVS_VOLT[2:0]	Ī
	Reset	0	0	0	0	0	0	0	0
	Туре	-	—	RW	RW	RW	RW1S	RW1S	RW1S
VREFDDR_CTRL	Name	-	-	_	-	VREFDDR_ LPWR	VREFDDR_ OMODE	VREFDDR_ STBY_EN	VREFDDR_EN
	Reset	0	0	0	0	0	0	0	0
	Туре	-	-	_	_	RW	RW	RW1S	RW1S
LDO1_VOLT	Name	-	_	_			LDO1_VOLT[4:0]	l	
	Reset	0	0	0	0	0	0	0	0
	Туре	-	—	—	RW1S	RW1S	RW1S	RW1S	RW1S
LDO1_CTRL	Name	_	_	—	LDO1_LS_EN	LDO1_LPWR	LDO1_OMODE	LDO1_STB Y_ EN	VLDO1_EN
	Reset	0	0	0	0	0	0	0	0
	Туре	-	-	_	RW1S	RW	RW	RW1S	RW1S
LDO2_VOLT	Name	-	-	_	_		LDO2_	VOLT[3:0]	
	Reset	0	0	0	0	0	0	0	0
	Туре	-	-	_	_	RW1S	RW1S	RW1S	RW1S
LDO2_CTRL	Name	-	_	_	-	LDO2_LPWR	LDO2_OMODE	LDO2_STB Y_ EN	VLDO2_EN
	Reset	0	0	0	0	0	0	0	0
	Туре	-	-	_	-	RW		RW1S	RW1S
LDO3_VOLT	Name	-	-	_		-			
	Reset	0	0	0	0	0			0
	Туре	-	-	_					RW1S
LDO3_CTRL	Name	-	-	—	LDO3_LS_EN	LDO3_LPWR	LDO3_OMODE	LDO3_STB Y_ EN	VLDO3_EN
	Reset	0	0	0	0	0	0	0	0
	Туре	—	-	—	RW1S	RW	RW	RW1S	RW1S
PWRCTRL0	-		1			1			
									1
									RW
PWRCTRL1		RST_EN							
	Reset								0
									RW
PWRCTRL2		-	-	-	-				
									0
	Туре	-	_	_	-	RW	RW		RW1S
PWRCTRL3					-	1	7	OFF	—
	Reset								0
	Туре	RW	RW	RW	RW	RW	RW	RW	RW
	/REFDDR_CTRL _DO1_VOLT _DO1_CTRL _DO2_VOLT _DO2_CTRL _DO3_VOLT	Reset Type Reset Type Reset Type DO1_VOLT Reset Type DO1_CTRL Name Reset Type DO1_CTRL Name DO2_VOLT Name DO2_VOLT Reset Type Name DO2_VOLT Name DO3_VOLT Name DO3_VOLT Name DO3_CTRL Name DO3_CTRL Name PWRCTRL0 Reset Type Type DWRCTRL1 Name PWRCTRL2 Name PWRCTRL2 Name PWRCTRL3 Name	Reset 0 Type	Reset00TypeVREFDDR_CTRLNameReset00TypeDO1_VOLTNameReset00TypeRoset00TypeDO1_VOLTNameReset00TypeDO1_CTRLNameReset00TypeDO2_VOLTNameReset00TypeDO2_CTRLNameReset00TypeDO3_VOLTNameReset00TypeDO3_CTRLNameReset00TypeDO3_CTRLNameTGRESET[7:6]Reset00TypeDO3_CTRLNameRW1SPWRCTRL0Reset10TypeRW1SRW1SPWRCTRL1NameReset00TypePWRCTRL2NameReset00TypePWRCTRL3NamePWRCTRL3NameReset00Type<	Reset00TypeRWVREFDDR_CTRLNameRWReset000TypeTypeDO1_VOLTNameReset000TypeDO1_CTRLNameReset000TypeDO2_VOLTNameReset000TypeDO2_VOLTNameReset000TypeDO2_VOLTNameReset000TypeDO3_VOLTNameReset000TypeDO3_TRLNameReset000TypeDO3_CTRLNameTGE<	Reset0000TypeRWRW/REFDDR_CTRLNameReset0000TypeD01_VOLTReset000Reset0000TypeRW1SD01_VOLTReset000Reset0000TypeRW1SD01_CTRLNameReset0000TypeReset0000TypeReset0000TypeD02_VOLTReset000Reset0000TypeD03_VOLTNameReset0000TypeD03_VOLTNameReset0000TypeD03_VOLTNameReset0000TypeReset000TypeReset000Reset000 <td< td=""><td>Reset00000TypeRWRWRWVREFDDR_CTRL Reset0000TypeRWDO1_VOLTNameRW1SReset00000TypeRW1SRW1SDO1_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO1_CTRL ResetNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SReset00000<td>Reset000000TypeRWRWRWRW15YREFDDR_CTRLNameRWRWRW16Reset0000000TypeRWRWRWDO1_VOLTReset000000TypeRW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000DO3_VOLTReset000000DO3_VOLTReset000000Reset00000000DO3_VOLTReset000000Reset00000000<td>Reset00000000TypeRWRWRWRWRWSRWSRWSREFDDR_CTRLNameRWRWRWRWSRWSSTSY_ENReset000000000TypeRWRWRWSRWSRWSLD01_VOLTNameRWRWSRWSRWSLD1_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD01_CTRLNameRWSRWSRWSRWSReset00000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000LD02_VOLTReset00000</td></td></td></td<>	Reset00000TypeRWRWRWVREFDDR_CTRL Reset0000TypeRWDO1_VOLTNameRW1SReset00000TypeRW1SRW1SDO1_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO1_CTRL ResetNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO2_VOLTNameRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SDO3_VOLTNameRW1SRW1SReset00000TypeRW1SRW1SReset00000 <td>Reset000000TypeRWRWRWRW15YREFDDR_CTRLNameRWRWRW16Reset0000000TypeRWRWRWDO1_VOLTReset000000TypeRW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000DO3_VOLTReset000000DO3_VOLTReset000000Reset00000000DO3_VOLTReset000000Reset00000000<td>Reset00000000TypeRWRWRWRWRWSRWSRWSREFDDR_CTRLNameRWRWRWRWSRWSSTSY_ENReset000000000TypeRWRWRWSRWSRWSLD01_VOLTNameRWRWSRWSRWSLD1_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD01_CTRLNameRWSRWSRWSRWSReset00000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000LD02_VOLTReset00000</td></td>	Reset000000TypeRWRWRWRW15YREFDDR_CTRLNameRWRWRW16Reset0000000TypeRWRWRWDO1_VOLTReset000000TypeRW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO1_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000TypeRW15RW15RW15RW15DO2_VOLTReset000000DO3_VOLTReset000000DO3_VOLTReset000000Reset00000000DO3_VOLTReset000000Reset00000000 <td>Reset00000000TypeRWRWRWRWRWSRWSRWSREFDDR_CTRLNameRWRWRWRWSRWSSTSY_ENReset000000000TypeRWRWRWSRWSRWSLD01_VOLTNameRWRWSRWSRWSLD1_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD01_CTRLNameRWSRWSRWSRWSReset00000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000LD02_VOLTReset00000</td>	Reset00000000TypeRWRWRWRWRWSRWSRWSREFDDR_CTRLNameRWRWRWRWSRWSSTSY_ENReset000000000TypeRWRWRWSRWSRWSLD01_VOLTNameRWRWSRWSRWSLD1_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD01_CTRLNameRWSRWSRWSRWSReset00000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSLD02_VOLTReset0000000TypeRWSRWSRWSRWSRWSLD02_VOLTReset0000000LD02_VOLTReset00000

PF1510

Product data sheet

89 / 108

© NXP B.V. 2021. All rights reserved.

Address	Register name			BITS[7:0]								
			7	6	5	4	3	2	1	0		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	-	RW1S	RW1S	RW1S		
0x60	SW2_PWRDN_SEQ	Name	_	_	_	_	-	SV	V2_PWRDN_SEQ[[2:0]		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	-	RW1S	RW1S	RW1S		
0x61	SW3_PWRDN_SEQ	Name	_	_	_	_	_	SV	V3_PWRDN_SEQ[[2:0]		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	_	RW1S	RW1S	RW1S		
0x62	LDO1_PWRDN_SEQ	Name	_	_	_	_	_	LD	01_PWRDN_SEQ	[2:0]		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	-	RW1S	RW1S	RW1S		
0x63	LDO2_PWRDN_SEQ	Name	_	_	_	_	-	LDO2_PWRDN_SEQ		[2:0]		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	-	RW1S	RW1S	RW1S		
0x64	LDO3_PWRDN_SEQ	Name	_	_	_	_	_	LD	O3_PWRDN_SEQ	[2:0]		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	_	RW1S	RW1S	RW1S		
0x65	VREFDDR_PWRDN_	Name	_	_	_	_	_	VREF		EQ[2:0]		
	SEQ	Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	_	_	_	RW1S	RW1S	RW1S		
0x67	STATE_INFO	Name	_	_			ST	ATE[5:0]				
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	R	R	R	R	R	R		
0x68	I2C_ADDR	Name	USE_ DEFAULT_ ADDR	—	_	_	-	I2C_SLAVE_ADDR_LSBS[2:0]				
		Reset	0	0	0	0	0	0	0	0		
		Туре	RW	_	_	_	-	R	R	R		
0x69	IO_DRV0	Name	_	_	_	_	-	_	_	-		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	—	_	-	-	-	-		
0x6A	IO_DRV1	Name	_	_	—	_	-	-	-	-		
		Reset	0	0	0	0	0	0	0	0		
		Туре	_	_	-	_	-	_	_	_		
0x6B	RC_16MHZ	Name	-	-	-	_	-	REQ_ACORE_ HIPWR	REQ_ACORE_ ON	REQ_16MHZ		
		Reset	0	0	0	0	0	0	0	0		
		Туре	-	_	_	_	-	RW	RW	RW		
0x6F	KEY1	Name				ł	KEY1[7:0]	·	·			
		Reset	0	0	0	0	0	0	0	0		
		Туре	RW	RW	RW	RW	RW	RW	RW	RW		

12.4 Additional register bitmap

CHGPOK_RSTB^[1]

VCOREDIG_RSTB^[2]

[1] Bits reset by invalid VIN

[2] Bits reset by invalid VCOREDIG

Table 129. Additional register bitmap


Address	Register name	BITS[7:0]									
			7	6	5	4	3	2	1	0	
0x00	INT	Name	RSVD7	RSVD6	VIN_I	RSVD4	RSVD3	RSVD2	RSVD1	RSVD0	
		Reset	0	0	0	0	0	0	0	0	
		Туре	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	RW1C	
0x02	INT_MASK	Name	RSVD7	RSVD6	VIN_M	RSVD4	RSVD3	RSVD2	RSVD1	RSVD0	
		Reset	1	1	1	1	1	1	1	1	
		Туре	RW	RW	RW	RW	RW	RW	RW	RW	
0x04	INT_OK	Name	RSVD7	RSVD6	VIN_OK	RSVD4	RSVD3	RSVD2	RSVD1	RSVD0	
		Reset	1	0	0	0	0	1	0	0	
		Туре	R	R	R	R	R	R	R	R	
0x06 VIN_SNS	VIN_SNS	Name	RSVD7	RSVD6	VIN2SYS_ SNS	VIN_OVLO_ SNS	VIN_IN2SYS_ SNS	VIN_UVLO_ SNS	RSVD	[1:0]	
		Reset	0	0	0	0	1	1	0	0	
		Туре	R	R	R	R	R	R	R	R	
0x09	FRONT_END_	Name		RSVD[7:5]	,	RSVD4	RSVD3	RSVD2	FRONT_EN	D_ON[1:0]	
	OPER	Reset	0	0	0	0	0	0	0	1	
		Туре	RW	RW	RW	RW	RW	RW	RW1S	RW1S	
0x0F	FRONT_END_REG	Name	VSYS	SMIN[7:6]		[5:0]					
		Reset	0	0	1	0	1	0	1	1	
		Туре	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	
0x14	VIN_INLIM_CNFG	Name			VIN_ILIM[7	[:3]		RSVD[2:0]			
		Reset	0	1	1	0	1	0	0	0	
		Туре	RW1S	RW1S	RW1S	RW1S	RW1S	RW	RW	RW	
0x16	USB_PHY_LDO_	Name	RS	VD[7:6]	RSVI	D[5:4]	RSVD3	USBPHYLDO	USBPHY	RSVD0	
	CNFG	Reset	0	0	0	0	0	0	0	1	
		Туре	RW	RW	RW	RW	RW	RW1S	RW1S	RW1S	
0x18	DBNC_DELAY_	Name	RS	VD[7:6]	SYS_WKU	P_DLY[5:4]	USB_PH	(_TDB[3:2]	VIN_OV_1	FDB[1:0]	
	TIME	Reset	0	0	0	0	0	0	0	0	
		Туре	RW	RW	RW1S	RW1S	RW1S	RW1S	RW1S	RW1S	
0x1B	VIN2SYS_CNFG	Name			RSVD[7:3	3]		VIN2SYS_ THRSH	VIN2SYS_	TDB[1:0]	
		Reset	0	0	0	0	0	0	0	0	
		Туре	RW	RW	RW	RW	RW	RW1S	RW1S	RW1S	

13 Application details

13.1 Example schematic

Figure 16 shows a typical schematic of the PF1510 with key external components.





13.2 Bill of materials

The table below shows an example bill of materials to be used with the PF1510.

Table 130. Bill of materials

Block	Function	Description	Qty
VCORE	Analog IC supply	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
VDIG	Digital IC supply	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
LDO2P7	Analog supply	CAP CER 2.2 µF 6.3 V 20% X5R 0201	1
USBPHY	USB PHY output capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
VIN	VIN bypass capacitor	CAP CER 2.2 µF 25 V 20 % X5R 0402	1
VSYS	VSYS capacitor	22 µF, 10 V, MLCC, X5R	2
VDDIO	VDDIO bypass capacitor	CAP CER 0.1 uF 6.3 V 20 % X5R 0201	1
Buck 1	BUCK1 inductor	1.0 μH, +/-20 %, 120 mOhm typ, 1700 mA	1
	BUCK1 input capacitor	4.7 μF, 6.3 V, MLCC, X5R	1
	BUCK1 output capacitor	10 µF, 6.3 V, MLCC, X5R	2
Buck 2	BUCK2 inductor	1.0 μH, +/-20 %, 120 mOhm typ, 1700 mA	1
	BUCK2 input capacitor	4.7 μF, 6.3 V, MLCC, X5R	1
	BUCK2 output capacitor	10 µF, 6.3V, MLCC, X5R	2
Buck 3	BUCK3 inductor	1.0 μH, +/-20 %, 120 mOhm typ, 1700 mA	1
	BUCK3 input capacitor	4.7 μF, 6.3 V, MLCC, X5R	1
	BUCK3 output capacitor	10 µF, 6.3 V, MLCC, X5R	2
LDO1	LDO1 input capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
	LDO1 output capacitor	4.7 μF, 6.3 V, MLCC, X5R	1
LDO2	LDO2 input capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
	LDO2 output capacitor	10 µF, 6.3 V, MLCC, X5R	1
LDO3	LDO3 input capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
	LDO3 output capacitor	4.7 μF, 6.3 V, MLCC, X5R	1
VREFDDR	VREFDDR input capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
	VREFDDR output capacitor	CAP CER 1.0 µF 6.3 V 20 % X5R 0201	1
VSNVS	VSNVS output capacitor	CAP CER 0.47 µF 6.3 V 20 % X5R 0201	1
LICELL	LICELL bypass capacitor	CAP CER 0.1 µF 6.3 V 20 % X5R 0201	1

13.3 PF1510 layout guidelines

13.3.1 General board recommendations

- It is recommended to use an eight layer board stack-up arranged as follows:
 - High current signal
 - GND
 - Signal
 - Power
 - Power
 - Signal
 - GND

- Allocate TOP and BOTTOM PCB layers for POWER ROUTING (high current signals), copper-pour the unused area.
- Use internal layers sandwiched between two GND planes for the SIGNAL routing.

13.3.2 Component placement


It is desirable to keep all component related to the power stage as close to the PMIC as possible, specially decoupling input and output capacitors.

13.3.3 General routing requirements

- Some recommended things to keep in mind for manufacturability:
 - Via in pads require a 4.5 mil minimum annular ring. Pad must be 9.0 mils larger than the hole
 - Maximum copper thickness for lines less than 5.0 mils wide is 0.6 oz copper
 - Minimum allowed spacing between line and hole pad is 3.5 mils
 - Minimum allowed spacing between line and line is 3.0 mils
- Care must be taken with SWxFB pins traces. These signals are susceptible to noise and must be routed far away from power, clock, or high power signals, like the ones on the SWxIN, SWxLX. They could be also shielded.
- Shield feedback traces of the regulators and keep them as short as possible (trace them on the bottom so the ground and power planes shield these traces).
- Avoid coupling traces between important signal/low noise supplies (like VCORE, VDIG) from any switching node (for example, SW1LX, SW2LX, SW3LX).
- Make sure that all components related to a specific block are referenced to the corresponding ground.


13.3.4 Parallel routing requirements

- I²C signal routing
 - CLK is the fastest signal of the system, so it must be given special care.
 - To avoid contamination of these delicate signals by nearby high power or high frequency signals, it is a good practice to shield them with ground planes placed on adjacent layers. Make sure the ground plane is uniform throughout the whole signal trace length.
 - These signals can be placed on an outer layer of the board to reduce their capacitance with respect to the ground plane.
 - Care must be taken with these signals not to contaminate analog signals, as they are high frequency signals. Another good practice is to trace them perpendicularly on different layers, so there is a minimum area of proximity between signals.




13.3.5 Switching regulator layout recommendations

- Per design, the switching regulators in PF1510 are designed to operate with only one input bulk capacitor. However, it is recommended to add a high frequency filter input capacitor (CIN_hf), to filter out any noise at the regulator input. This capacitor should be in the range of 100 nF and should be placed right next to or under the IC, closest to the IC pins.
- Make high-current ripple traces low-inductance (short, high W/L ratio).
- Make high-current traces wide or copper islands.







13.4 Thermal information

13.4.1 Rating data

The thermal rating data of the packages has been simulated with the results listed in Table 3 .

Junction to Ambient Thermal Resistance Nomenclature: the JEDEC specification reserves the symbol R_{0JA} or 0JA (Theta-JA) strictly for junction-to-ambient thermal resistance on a 1s test board in natural convection environment. R_{0JMA} or 0JMA (Theta-JMA) is used for both junction-to-ambient on a 2s2p test board in natural convection and for junction-to-ambient with forced convection on both 1s and 2s2p test boards. It is anticipated that the generic name, Theta-JA, continues to be commonly used.

The JEDEC standards can be consulted at <u>http://www.jedec.org/</u>.

13.4.2 Estimation of junction temperature

An estimation of the chip junction temperature T_J can be obtained from the equation: T_J = T_A + ($R_{\theta JA} \times P_D$) with:

 T_A = Ambient temperature for the package in °C

 $R_{\theta JA}$ = Junction to ambient thermal resistance in °C/W

 P_D = Power dissipation in the package in W

The junction to ambient thermal resistance is an industry standard value that provides a quick and easy estimation of thermal performance. Unfortunately, there are two values in common usage: the value determined on a single layer board $R_{\theta JA}$ and the value obtained on a four layer board $R_{\theta JMA}$. Actual application PCBs show a performance close to the simulated four layer board value although this may be somewhat degraded in case of significant power dissipated by other components placed close to the device.

At a known board temperature, the junction temperature T_J is estimated using the following equation T_J = T_B + ($R_{\theta JB}x P_D$) with

 T_B = Board temperature at the package perimeter in °C

 $R_{\theta JB}$ = Junction to board thermal resistance in °C/W


 P_D = Power dissipation in the package in W


14 Packaging information

The PF1510 uses a 40 QFN 5.0 mm x 5.0 mm with exposed pad, case number 98ASA00913D.

14.1 Packaging description

This drawing is available for download at <u>http://www.nxp.com</u>. Consult the most recently issued drawing before initiating or completing a design.





PF1510

H-PQFN-40 I/O 5 X 5 X 0.85 PKG, 0.4 PITCH			SOT1369-4
NOTES:			
1. ALL DIMENSIONS ARE IN MILLIM	ETERS.		
2. DIMENSIONING AND TOLERANCIN	IG PER ASME Y14.5M-1994	L.	
3. THIS IS A NON-JEDEC REGISTE	RED PACKAGE.		
4. COPLANARITY APPLIES TO LEAD	DS, DIE ATTACH FLAG.		
5. MIN. METAL GAP SHOULD BE 0			
© NXP B.V.	ALL RIGHTS RESERVED	T	DATE: 15 OCT 2020
MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:
PRINT VERSION NOT TO SCALE	NON JEDEC	98ASA00913D	D

15 Revision history

Table 131. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes		
PF1510 v.4.0	20210305	Product	PCN 202012012F01	PF1510 v.3.0		
Modifications	• <u>Section 14.1</u> : ac drawings	Ided "Optional Deta	ail G with 0.15 mm lead edge	package option" to package outline		
PF1510 v.3.0	20200407	Product	CIN 2020040011	PF1510 v.2.0		
Modifications	• <u>Table 1</u> : added	MC32PF1510A0EP	and MC34PF1510A0EP (no	(non-programmed parts)		
PF1510 v.2.0	20190524	Product	CIN 201904034I	PF1510 v.1.0		
	 µF capacitor Changed Reccapacitor to g Section 7.5 Changed "It of "It derives its Changed "Up VSNVS" to Table 45 Changed V_{IL} Changed V_{IL} Changed V_{IH} Added Table 46 Added Table 49 Changed V_{IL} Ch	to ground mandator commended connec round mandatory" lerives its power fro power from either \ on subsequent rem "Upon subsequent max from "0.2 * VS min from "0.2 * VS min from "0.2 * VS si to "4.8" p-down from VSYS changed capacitor v	ry" ction when not used from "Lea om either VSYS or a coin cell /SYS or a coin cell." hoval of VSYS, with the coin of removal of VSYS, with the coin NVS" to "0.4" NVS" to "1.4" YS" to "0.4" YS" to "1.4"			
PF1510 v.1.0	20180523	Advance	_	_		

16 Legal information

16.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

16.2 Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

16.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without

notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

 $\ensuremath{\mathsf{Applications}}$ — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

NXP Semiconductors

Power management integrated circuit (PMIC) for low power application processors

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever

customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Tables

Tab. 1.	Orderable part variations		Tab. 54.	Register
Tab. 2.	Pin description		Tab. 55.	Register
Tab. 3.	Thermal ratings		Tab. 56.	Register
Tab. 4.	Maximum ratings	10	Tab. 57.	Register
Tab. 5.	Front-end LDO	12	Tab. 58.	Register
Tab. 6.	Input currents	12	Tab. 59.	Register
Tab. 7.	Switch impedances and leakage currents	13	Tab. 60.	Register
Tab. 8.	Watchdog timer		Tab. 61.	Register
Tab. 9.	Internal 2.7 V Regulator (LDO2P7)		Tab. 62.	Register
Tab. 10.	USBPHY LDO		Tab. 63.	Register
Tab. 11.	SW1 and SW2 electrical characteristics		Tab. 64.	Register
Tab. 12.	SW3 electrical characteristics		Tab. 65.	Register
Tab. 12.	LDO1 electrical characteristics		Tab. 66.	Register
Tab. 14.	LDO2 electrical characteristics		Tab. 67.	Register
Tab. 1 4 . Tab. 15.	LDO2 electrical characteristics		Tab. 68.	
Tab. 15. Tab. 16.				Register
	VREFDDR electrical characteristics		Tab. 69.	Register
Tab. 17.	VSNVS electrical characteristics		Tab. 70.	Register
Tab. 18.	IC level electrical characteristics		Tab. 71.	Register
Tab. 19.	Voltage regulators		Tab. 72.	Register
Tab. 20.	SWx DVS setting selection			0x22
Tab. 21.	Buck regulator operating modes		Tab. 73.	Register
Tab. 22.	Buck mode control			0x24
Tab. 23.	SW1 and SW2 output voltage setting	27	Tab. 74.	Register
Tab. 24.	Acceptable inductance and capacitance			0x25
	values		Tab. 75.	Register
Tab. 25.	Example inductor part numbers			0x26
Tab. 26.	Example capacitor part numbers		Tab. 76.	Register
Tab. 27.	SW3 buck regulator operating modes		Tab. 77.	Register
Tab. 28.	SW3 buck mode control	30	Tab. 78.	Register
Tab. 29.	SW3 output voltage setting	31		0x2A
Tab. 30.	Acceptable inductance and capacitance		Tab. 79.	Register
	values	32		0x30
Tab. 31.	Example inductor part numbers	32	Tab. 80.	Register
Tab. 32.	Example capacitor part numbers	32	Tab. 81.	Register
Tab. 33.	LDOy output voltage setting	34	Tab. 82.	Register
Tab. 34.	LDOy control bits		Tab. 83.	Register
Tab. 35.	LDO2 output voltage setting		Tab. 84.	Register
Tab. 36.	LDO2 control bits		Tab. 85.	Register
Tab. 37.	Front-end regulator register		Tab. 86.	Register
Tab. 38.	VSYSMIN setting		Tab. 87.	Register
Tab. 39.	VIN current limit register		Tab. 88.	Register
Tab. 40.	VIN limit settings		Tab. 89.	Register
Tab. 41.	PWRON pin OTP configuration options		Tab. 90.	Register
Tab. 42.	PWRON pin logic level		Tab. 91.	Register
Tab. 43.	PWRONDBNC settings		Tab. 92.	Register
Tab. 44.	Standby pin polarity control		Tab. 92.	Register
Tab. 45.	STANDBY pin logic level		Tab. 94.	Register
Tab. 46.	RESETBMCU pin logic level		Tab. 95.	Register
Tab. 40. Tab. 47.	INTB pin logic level		Tab. 95. Tab. 96.	
Tab. 47. Tab. 48.	WDI pin logic level		Tab. 90. Tab. 97.	Register
Tab. 40. Tab. 49.				Register
	ONKEY pin logic level		Tab. 98.	Register
Tab. 50.	ONKEYDBNC settings		Tab. 99.	Register
Tab. 51.	State transition table	51	Tab. 100.	- 0
Tab. 52.	A4 startup and power down sequence	50	Tab. 101.	0
T-6 50	timing		Tab. 102.	0
Tab. 53.	PF1510 start up configuration	54	Tab. 103.	Register
PF1510	All information provid	ed in this docum	nent is subject to lega	al disclaimers.

Tab. 54.	Register DEVICE ID - ADDR 0x00	55
Tab. 55.	Register OTP_FLAVOR - ADDR 0x01	
Tab. 56.	Register SILICON_REV - ADDR 0x02	
Tab. 57.	Register INT_CATEGORY - ADDR 0x06	56
Tab. 58.	Register SW INT STAT0 - ADDR 0x08	57
	Register SW INT MASK0 - ADDR 0x08	
Tab. 59.		
Tab. 60.	Register SW_INT_SENSE0 - ADDR 0x0A	58
Tab. 61.	Register SW_INT_STAT1 - ADDR 0x0B	58
Tab. 62.	Register SW_INT_MASK1 - ADDR 0x0C	58
Tab. 63.	Register SW_INT_SENSE1 - ADDR 0x0D	59
Tab. 64.	Register SW_INT_STAT2 - ADDR 0x0E	
Tab. 65.	Register SW_INT_MASK2 - ADDR 0x0F	
Tab. 66.	Register SW_INT_SENSE2 - ADDR 0x10	60
Tab. 67.	Register LDO_INT_STAT0 - ADDR 0x18	60
Tab. 68.	Register LDO INT MASK0 - ADDR 0x19	61
Tab. 69.	Register LDO INT SENSE0 - ADDR 0x1A (61
Tab. 70.	Register TEMP_INT_STAT0 - ADDR 0x20	
Tab. 71.	Register TEMP_INT_MASK0 - ADDR 0x21	62
Tab. 72.	Register TEMP_INT_MASK0 - ADDR 0x21 (Register TEMP_INT_SENSE0 - ADDR	02
100.72.	0x22	62
Tab. 73.	Degister ONIZEV INT STATE ADDD	02
Tab. 75.	Register ONKEY_INT_STAT0 - ADDR	<u></u>
T 1 74		62
Tab. 74.	Register ONKEY_INT_MASK0 - ADDR	
	0x25	63
Tab. 75.	Register ONKEY_INT_SENSE0 - ADDR	
	0x26	
Tab. 76.	Register MISC_INT_STAT0 - ADDR 0x28	65
Tab. 77.	Register MISC INT MASKA ADDR 0v20	65
Tap. 11.		~ ~
Tab. 77. Tab. 78.	Register MISC_INT_SENSE0 - ADDR	
	Register MISC_INT_MASK0- ADDR 0x29 Register MISC_INT_SENSE0 - ADDR 0x2A	66
	0x2A	66
Tab. 78.	0x2A	66
Tab. 78. Tab. 79.	0x2A Register COINCELL_CONTROL - ADDR 0x30	66 66
Tab. 78. Tab. 79. Tab. 80.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32	66 66 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33	66 66 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34	66 66 67 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83.	0x2A	66 67 67 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36	66 67 67 67 67 68
 Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. 	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38	66 67 67 67 67 68 68
 Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. 	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38	66 67 67 67 67 68 69 69
 Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. 	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38	66 66 67 67 67 68 69 69 69
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_SLP_VOLT - ADDR 0x38	66 66 67 67 67 67 68 69 69 69
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38	66 66 67 67 67 67 68 69 69 69 69 69
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38	66 67 67 67 67 67 68 69 69 69 69 70 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38	66 67 67 67 67 67 68 69 69 69 69 70 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38	66 67 67 67 67 68 69 69 69 69 69 70 71 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 89. Tab. 90. Tab. 91.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_VOLT - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x36	66 67 67 67 67 67 68 69 69 69 70 71 71 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_STBY_VOLT - ADDR 0x36 Register SW3_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x37 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x41	66 67 67 67 67 67 68 69 69 69 69 70 71 71 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 88. Tab. 89. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW1_SLP_VOLT - ADDR 0x35 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_SLP_VOLT - ADDR 0x36 Register SW3_SLP_VOLT - ADDR 0x40 Register SW3_CTRL - ADDR 0x41	66 67 67 67 67 68 69 69 69 69 71 71 71 71 71
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94. Tab. 95.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_STBY_VOLT - ADDR 0x36 Register SW3_CTRL1 - ADDR 0x37 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_STBY_VOLT - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL1 - ADDR 0x42 Register SW3_CTRL - ADDR 0x48	66 67 67 67 67 68 69 69 69 69 71 71 71 71 71 72 72
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 95. Tab. 96.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL1 - ADDR 0x38 Register SW3_CTRL1 - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x48 Register SW3_CTRL - ADDR 0x48	66 667 677 67 67 67 67 67 69 69 69 71 71 71 71 71 72 73
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 95. Tab. 96. Tab. 97.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_CTRL - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x48 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44	66 667 677 67 67 67 67 67 67 67 67 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94. Tab. 95. Tab. 96. Tab. 97. Tab. 98.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x39 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_CTRL - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x44 Register VSNVS_CTRL - ADDR 0x48 Register VSNVS_CTRL - ADDR 0x44 Register VREFDDR_CTRL - ADDR 0x44 Register VREFDDR_CTRL - ADDR 0x44	66 667 677 67 67 67 67 67 67 67 67 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94. Tab. 95. Tab. 96. Tab. 97. Tab. 98. Tab. 99.	0x2ARegister COINCELL_CONTROL - ADDR0x30Register SW1_VOLT - ADDR 0x32Register SW1_STBY_VOLT - ADDR 0x33Register SW1_SLP_VOLT - ADDR 0x34Register SW1_SLP_VOLT - ADDR 0x35Register SW1_SLP_VOLT - ADDR 0x36Register SW1_SLP_VOLT - ADDR 0x36Register SW2_VOLT - ADDR 0x38Register SW2_VOLT - ADDR 0x38Register SW2_STBY_VOLT - ADDR 0x39Register SW2_SLP_VOLT - ADDR 0x38Register SW2_CTRL - ADDR 0x38Register SW2_CTRL - ADDR 0x38Register SW3_VOLT - ADDR 0x38Register SW3_VOLT - ADDR 0x38Register SW3_CTRL1 - ADDR 0x36Register SW3_STBY_VOLT - ADDR 0x37Register SW3_STBY_VOLT - ADDR 0x40Register SW3_CTRL - ADDR 0x41Register SW3_CTRL - ADDR 0x44Register SW3_CTRL - ADDR 0x44Register SW3_CTRL - ADDR 0x44Register VSNVS_CTRL - ADDR 0x44Register UD1_VOLT - ADDR 0x44Register LD01_VOLT - ADDR 0x44Register LD01_VOLT - ADDR 0x44	66 667 677 67 67 67 67 67 67 67 67 67 67
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 93. Tab. 94. Tab. 95. Tab. 96. Tab. 97. Tab. 98. Tab. 99. Tab. 100.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x39 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_VOLT - ADDR 0x36 Register SW3_VOLT - ADDR 0x38 Register SW3_CTRL - ADDR 0x37 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x44 Register VSNVS_CTRL - ADDR 0x44 Register VREFDDR_CTRL - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_CTRL - ADDR 0x45 Register LDO1_CTRL - ADDR 0x45	66 667 677 6767 6768 699 699 711 712 737 737 747
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94. Tab. 95. Tab. 95. Tab. 96. Tab. 97. Tab. 98. Tab. 99. Tab. 100. Tab. 101.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x39 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_VOLT - ADDR 0x38 Register SW3_VOLT - ADDR 0x36 Register SW3_CTRL1 - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x42 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_CTRL - ADDR 0x44 Register LDO2_VOLT - ADDR 0x45 Register LDO2_VOLT - ADDR 0x45 Register LDO2_VOLT - ADDR 0x45 Register LDO2_CTRL - ADDR 0x45	66 667 677 689 699 699 771 712 733 74 74 74
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 93. Tab. 94. Tab. 95. Tab. 96. Tab. 95. Tab. 96. Tab. 97. Tab. 98. Tab. 99. Tab. 100. Tab. 101. Tab. 102.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x39 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_VOLT - ADDR 0x38 Register SW3_VOLT - ADDR 0x38 Register SW3_CTRL1 - ADDR 0x38 Register SW3_VOLT - ADDR 0x38 Register SW3_CTRL1 - ADDR 0x40 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL1 - ADDR 0x41 Register SW3_CTRL - ADDR 0x42 Register SW3_CTRL1 - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x45 Register LDO1_VOLT - ADDR 0x45 Register LDO1_CTRL - ADDR 0x45 Register LDO2_VOLT - ADDR 0x45 Register LDO3_VOLT - ADDR 0x50	66 667 677 6768 699 699 699 711 712 733 734 74 74 74 74
Tab. 78. Tab. 79. Tab. 80. Tab. 81. Tab. 82. Tab. 83. Tab. 83. Tab. 84. Tab. 85. Tab. 86. Tab. 87. Tab. 88. Tab. 89. Tab. 90. Tab. 91. Tab. 92. Tab. 93. Tab. 94. Tab. 95. Tab. 95. Tab. 96. Tab. 97. Tab. 98. Tab. 99. Tab. 100. Tab. 101.	0x2A Register COINCELL_CONTROL - ADDR 0x30 Register SW1_VOLT - ADDR 0x32 Register SW1_STBY_VOLT - ADDR 0x33 Register SW1_SLP_VOLT - ADDR 0x34 Register SW1_SLP_VOLT - ADDR 0x35 Register SW1_CTRL - ADDR 0x35 Register SW1_SLP_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x36 Register SW2_VOLT - ADDR 0x38 Register SW2_STBY_VOLT - ADDR 0x39 Register SW2_SLP_VOLT - ADDR 0x38 Register SW2_CTRL - ADDR 0x38 Register SW3_VOLT - ADDR 0x38 Register SW3_VOLT - ADDR 0x36 Register SW3_CTRL1 - ADDR 0x36 Register SW3_STBY_VOLT - ADDR 0x37 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x40 Register SW3_CTRL - ADDR 0x41 Register SW3_CTRL - ADDR 0x42 Register SW3_CTRL - ADDR 0x44 Register SW3_CTRL - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_VOLT - ADDR 0x44 Register LDO1_CTRL - ADDR 0x44 Register LDO2_VOLT - ADDR 0x45 Register LDO2_VOLT - ADDR 0x45 Register LDO2_VOLT - ADDR 0x45 Register LDO2_CTRL - ADDR 0x45	66 667 677 6768 699 699 699 711 712 733 734 74 74 74 74

© NXP B.V. 2021. All rights reserved.

Tab. 104.	Register PWRCTRL1 - ADDR 0x59	76
Tab. 105.	Register PWRCTRL2 - ADDR 0x5A	76
Tab. 106.	Register PWRCTRL3 - ADDR 0x5B	77
Tab. 107.	Register SW1_PWRDN_SEQ - ADDR	
	0x5F	77
Tab. 108.	Register SW2_PWRDN_SEQ - ADDR	
	0x60	78
Tab. 109.	Register SW2_PWRDN_SEQ - ADDR	
	0x61	78
Tab. 110.	Register LDO1_PWRDN_SEQ - ADDR	
	0x62	79
Tab. 111.	Register LDO2_PWRDN_SEQ - ADDR	
	0x63	79
Tab. 112.	Register LDO3_PWRDN_SEQ - ADDR	
	0x64	80
Tab. 113.	Register VREFDDR_PWRDN_SEQ -	
	ADDR 0x65	80
Tab. 114.	Register STATE_INFO - ADDR 0x67	81
Tab. 115.	Register I2C_ADDR - ADDR 0x68	81

Figures

Fig. 1.	Application diagram	
Fig. 2.	Functional block diagram	4
Fig. 3.	Internal block diagram	5
Fig. 4.	Pinout diagram	
Fig. 5.	SWx DVS transitions	24
Fig. 6.	SWx DVS and non-DVS selection	25
Fig. 7.	SW3 block diagram	29
Fig. 8.	LDOy Block Diagram	34
Fig. 9.	LDO2 block diagram	
Fig. 10.	VREFDDR block diagram	39
Fig. 11.	VSNVS block diagram	
Fig. 12.	Startup sequence	41
Fig. 13.	I2C sequence	48

Tab. 116.	Register RC_16MHZ - ADDR 0x6B 81
Tab. 117.	Register KEY1 - ADDR 0x6B81
Tab. 118.	Register INT - ADDR 0x0082
Tab. 119.	Register INT_MASK - ADDR 0x0282
Tab. 120.	Register INT_OK - ADDR 0x0482
Tab. 121.	Register VIN_SNS - ADDR 0x0683
Tab. 122.	Register FRONT_END_OPER- ADDR
	0x0983
	Register FRONT_END_REG - ADDR 0x0F 84
Tab. 124.	Register VIN_INLIM_CNFG - ADDR 0x14 84
Tab. 125.	Register USB_PHY_LDO_CNFG - ADDR
	0x1685
Tab. 126.	Register DBNC_DELAY_TIME - ADDR
	0x1885
Tab. 127.	Register VIN2SYS_CNFG - ADDR 0x1B 86
Tab. 128.	Register PMIC bitmap86
Tab. 129.	Additional register bitmap91
Tab. 130.	Bill of materials94
Tab. 131.	Revision history102

Fig. 14.	PMIC state machine48
Fig. 15.	A4 startup and power down sequence53
Fig. 16.	Typical schematic93
Fig. 17.	Recommended shielding for critical signals96
Fig. 18.	Generic buck regulator architecture
Fig. 19.	Layout example for buck regulators
Fig. 20.	Package outline for HVQFN40
	(SOT1369-4)99
Fig. 21.	Package outline detail for HVQFN40
•	(SOT1369-4)100
Fig. 22.	Package outline notes for HVQFN40
0	(SOT1369-4)101

Contents

1	General description1	
1.1	Features and benefits1	
1.2	Applications2	
2	Application diagram3	
2.1	Functional block diagram4	
2.2	Internal block diagram5	
3	Orderable parts5	
4	Pinning information7	
4.1	Pinning7	
4.2	Pin definitions8	
5	General product characteristics9	
5.1	Thermal characteristics9	
5.2	Absolute maximum ratings10	
5.3	Electrical characteristics12	
5.3.1	Electrical characteristics – Front-end LDO12	
5.3.2	Electrical characteristics – SW1 and SW2 14	
5.3.3	Electrical characteristics – SW3 16	
5.3.4	Electrical characteristics – LDO117	
5.3.5	Electrical characteristics – LDO2	
5.3.6	Electrical characteristics – LDO3	
5.3.7	Electrical characteristics – VREFDDR20	
5.3.8	Electrical characteristics – VSNVS	
5.3.9	Electrical characteristics – IC level bias	
-	currents	
6	Detailed description	
6.1	Buck regulators	
6.2	SW1 and SW2 detailed description24	
6.2.1	SWx dynamic voltage scaling description24	
6.2.2	SWx DVS and non-DVS operation25	
6.2.3	Regulator control	
6.2.4 6.2.5	Current limit protection	
6.2.5 6.2.6	Output voltage setting in SWx	
6.3	SWX external components29 SW3 detailed description	
6.3.1	Regulator control	
6.3.2	Current limit protection	
6.3.3	Output voltage setting in SW3	
6.3.4	SW3 external components	
7 7	Low dropout linear regulators, VREFDDR	
'	and VSNVS	
7.1	General description	
7.2	LDO1 and LDO3 detailed description	
7.2.1	Features summary	
7.2.2	LDOy block diagram	
7.2.3	LDOy external components	
7.2.4	LDOy output voltage setting	
7.2.5	LDOy low power mode operation	
7.2.6	LDOy current limit protection	
7.2.7	LDOy load switch mode	
7.3	LDO2 detailed description	
7.3.1	LDO2 features summary	
7.3.2	LDO2 block diagram	
7.3.3	LDO2 external components	
7.3.4	LDO2 output voltage setting	
7.3.5	LDO2 Low-power mode operation	
7.3.6	LDO2 current limit protection	

7.4	VREFDDR reference	38
7.5	VSNVS LDO/Switch	
8	Front-end LDO description	
8.1	Operating modes and behavioral	
-	description	41
9	Control and interface signals	
9.1	PWRON	
9.2	STANDBY	
9.3	RESETBMCU	
9.4	INTB	
9.5	WDI	
9.6	ONKEY	
9.7	Control interface I2C block description	
9.7.1	I2C device ID	47
9.7.2	I2C operation	47
10	PF1510 state machine	
10.1	System ON states	49
10.1.1	Run state	
10.1.2	STANDBY state	49
10.1.3	SLEEP state	49
10.2	System OFF states	50
10.2.1	REGS_DISABLE	50
10.2.2	CORE_OFF	50
10.3	Turn on events	50
10.4	Turn off events	
10.5	State diagram and transition conditions	
10.6	Regulator power-up sequencer	
10.7	Regulator power-down sequencer	
11	Device start up	
11.1	Startup timing diagram	
11.2	Device start up configuration	
12	Register map	
12.1	Specific PMIC Registers (Offset is 0x00)	
12.2	Specific Registers (Offset is 0x80)	
12.3	Register PMIC bitmap	
12.4	Additional register bitmap	
13	Application details	
13.1 13.2	Example schematic	
13.2 13.3	Bill of materials PF1510 layout guidelines	
13.3.1	General board recommendations	94
13.3.2	Component placement	
13.3.3	General routing requirements	
13.3.4	Parallel routing requirements	
13.3.5	Switching regulator layout	
10.0.0	recommendations	96
13.4	Thermal information	
13.4.1	Rating data	
13.4.2	Estimation of junction temperature	
14	Packaging information	
14.1	Packaging description	
15	Revision history	
16	Legal information	

PF1510

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2021.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 5 March 2021 Document identifier: PF1510