

TDA8026

Multiple smart card slot interface IC

Rev. 1.1 — 30 June 2016

Product data sheet

1. General description

The TDA8026 is a cost-effective, analog interface for addressing multiple smart card slots in a Point Of Sales (POS) terminal. It can address up to two main cards (synchronous or asynchronous smart cards supported) and up to four Security Access Modules (SAMs). Its packaging supports the latest payment terminal security requirements.

2. Features and benefits

- I²C-bus controlled IC card interface in a TFBGA64 package
- Supply voltage between 2.7 V and 5.5 V
- Dedicated microcontroller interface supply voltage (V_{DD(INTF)})
- Shutdown mode ensures very low power consumption when the TDA8026 is inactive
- Programmable power reduction modes triggered when the card slots are inactive
- V_{CC(n)} generation via DC-to-DC converter: two card slots can be fully loaded, the three others in reduced consumption mode
- Two clock input pins: CLKIN1 for card slot 1 and CLKIN2 for card slots 2 to 5
- Two transparent I/O lines on microcontroller side, one for card slot 1 and the other for card slots 2 to 5
- Five protected, half-duplex, bidirectional, buffered I/O lines with current limitation at ± 15 mA and a maximum frequency 1 MHz
- Two I²C-bus controlled auxiliary I/O lines
- $V_{CC(n)}$ regulation on all card slots at $I_{CC} \le 55$ mA:
 - ◆ 5 V, 3 V or 1.8 V ± 5 %
 - Current spikes of 40 nAs up to 20 MHz for 5 V cards with controlled rise and fall times
 - Current limitation of approximately 100 mA
- Thermal protection and short-circuit protection on all card contacts
- Automatic activation and deactivation sequences initiated by the software or hardware in the event of a short-circuit, card take-off or voltage drop-out for V_{DD(INTF)}, V_{DD} or V_{UP}
- Enhanced ElectroStatic Discharge (ESD) protection on the card-side up to 6 kV
- 20 MHz clock input
- Card clock generation up to 20 MHz and dividable by 1, 2, 4 or 5 with synchronous frequency changes:
 - Stop, HIGH or LOW
 - Clock frequency between 1 MHz and 2.2 MHz in card low-power mode
 - Current limitation on pin CLK_(n)



Multiple smart card slot interface IC

- RST_(n) signal lines with current limitation at 20 mA, controlled by an embedded programmable clock pulse counter on asynchronous cards or by a register on synchronous cards
- ISO 7816-3 and EMV 4.3¹ payment systems compatibility
- V_{DD(INTF)} supply voltage supervisor ensures correct communication between microcontroller and circuit; threshold internally fixed or set using an external resistor bridge
- V_{DD} supply voltage supervisor for spike suppression during power-on and emergency deactivation at power-off; threshold internally fixed
- Card presence input with a 17.8 ms (typical) built-in debouncing system on card slots 1 and 2
- One interrupt signal (IRQN)

3. Applications

- Point Of Sale terminals
- Multiple SAM contact readers

4. Quick reference data

Table 1. Quick reference data

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|-----------------------|--------------------------|--|------------|------|-----|-----|------|
| Supply | | | | | | | |
| V_{DD} | supply voltage | on pin V _{DD} ; DC-to-DC converter on | [1] | 2.7 | - | 5.5 | V |
| | | on pin V_{DD} ; DC-to-DC converter off and $V_{CC(n)}$ pin = 5 V | [1] | 5.25 | - | 5.5 | V |
| I_{DD} | supply current | shutdown mode | | - | 25 | 40 | μΑ |
| | Standby mode | | - | 300 | 450 | μΑ | |
| | | clock-stop mode; all card slots in this mode; $f_{clk(ext)}$ stopped on pins $CLK_{(n)}$; pins $CLKIN1$ and $CLKIN2$ either stopped, $HIGH$ -level or LOW -level | | - | 3.7 | - | mA |
| | | active mode; all $V_{CC(n)}$ pins = 5 V; $f_{Clk(ext)}$ on pins $CLK_{(n)}$ = 5 MHz; $I_{CC(1)}$ = $I_{CC(2)}$ = 55 mA; $I_{CC(3)}$ = $I_{CC(4)}$ = $I_{CC(5)}$ = 2 mA | [2] [3] | - | 210 | 260 | mA |
| $V_{DD(INTF)}$ | interface supply voltage | on pin V _{DD(INTF)} | | 1.6 | - | 3.6 | V |
| I _{DD(INTF)} | interface supply current | shutdown mode | | - | 10 | 15 | μΑ |
| | | active mode; all $V_{CC(n)}$ pins = 5 V; $f_{Clk(ext)}$ on pins $CLK_{(n)}$ = 5 MHz | | - | 35 | - | μΑ |

TDA8026_1

for C3 version

Multiple smart card slot interface IC

Table 1. Quick reference data ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{Clk(ext)} = 10 \text{ MHz; GND} = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|--------------------------|--|---|------------|------|------|------|------|
| Card supp | ly voltage pins: V _{CC(1)} to | V _{CC(5)} [4] | | | | | |
| V _{CC} | supply voltage | active mode; $2.7 \text{ V} < \text{V}_{DD} < 5.5 \text{ V}$ | <u>[5]</u> | | | | |
| | | 5 V card; DC I _{CC(n)} ≤ 55 mA | | 4.75 | 5 | 5.25 | V |
| | | 3 V card; DC I _{CC(n)} ≤ 55 mA | | 2.85 | 3 | 3.15 | V |
| | | 1.8 V card; DC $I_{CC(n)} \le 35 \text{ mA}$ | | 1.71 | 1.8 | 1.89 | V |
| | | active mode; AC current pulses with I < 200 mA, t < 400 ns and f < 20 MHz | [5] | | | | |
| | | 5 V card; current spikes of 40 nAs | | 4.65 | - | 5.35 | V |
| | | 3 V card; current spikes of 17.5 nAs | | 2.76 | - | 3.24 | V |
| | | 1.8 V card; current spikes of 11.1 nAs | | 1.62 | - | 1.98 | V |
| V _{ripple(p-p)} | peak-to-peak ripple voltage | 20 kHz to 200 MHz with default Register6 (Slew Rate register) settings | | - | - | 350 | mV |
| I _{CC} | supply current | V _{CC(n)} = 5 V | | - | - | 55 | mA |
| | | V _{CC} (n) = 3 V | | - | - | 55 | mA |
| | | V _{CC} (n) = 1.8 V | | - | - | 35 | mA |
| | | sum of all card supply currents on pins $V_{CC(n)}$; active mode; All V_{CC} pins = 5 V; $f_{clk(ext)}$ on pins $CLK_{(n)}$ = 5 MHz; $I_{CC(1)} = I_{CC(2)} = 55$ mA; $I_{CC(3)} = I_{CC(4)} = I_{CC(5)} = 2$ mA | [3] | - | 116 | 125 | mA |
| General | | | · | | | | |
| t _{deact} | deactivation time | total sequence | [6] | 60 | 80 | 100 | μS |
| t _{deb} | debounce time | | | - | 17.8 | 23.8 | ms |
| P _{tot} | total power dissipation | $T_{amb} = -25 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$ | | - | 455 | 665 | mW |
| T _{amb} | ambient temperature | | | -25 | +25 | +85 | °C |

- [1] Refer to Section 8.6 for further information about the DC-to-DC converter operation.
- [2] Typical value measurement based on a 85 % DC-to-DC converter and inductance efficiency; depends on PCB layout and external component quality (inductor, capacitor).
- [3] Maximum value measurement based on a 125 mA (sum of all card supply currents on pins V_{CC(n)}) current load and a 75 % DC-to-DC converter and inductance efficiency; depends on PCB layout and external component quality (inductor, capacitor).
- [4] Two ceramic multilayer 100 nF (minimum) capacitors with a low Equivalent Series Resistance (ESR) should be used to meet these specifications.
- [5] Output voltage to the card including ripple.
- [6] Refer to Section 8.8.3 for further information.

Multiple smart card slot interface IC

5. Ordering information


The TDA8026 is available in 2 versions. All version have the same functionality. The C3 version is compliant with EMVC0 4.3

Table 2. Ordering information

| Type number | Package | Package | | | | | | | | |
|--------------|---------|---|-----------|--|--|--|--|--|--|--|
| | Name | Description | Version | | | | | | | |
| TDA8026ET/C2 | TFBGA64 | plastic thin fine-pitch ball grid array package; 64 balls | SOT1073-1 | | | | | | | |
| TDA8026ET/C3 | TFBGA64 | plastic thin fine-pitch ball grid array package; 64 balls | SOT1073-1 | | | | | | | |

Multiple smart card slot interface IC

6. Block diagram



Multiple smart card slot interface IC

7. Pinning information

7.1 Pinning




Table 3. TDA8026 ball map

| Ва | II positio | า <u>[1][2]</u> | | | | | | |
|----|-------------------|---------------------|---------------------|----------------|--------------------|--------------------------|--------------------|---------------------|
| | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 |
| Α | TST2 | TST1 | TESTMODE | $V_{DD(INTF)}$ | SDWNN | V _{DD(INTREGD)} | V_{DD} | PORADJ |
| В | STAP3 | SCL | CLKIN2 | GND1 | V _{CC(5)} | RST ₍₅₎ | CLK ₍₅₎ | DCDC_OFF |
| С | STAP4 | SDA | CLKIN1 | I/OUC1 | I/OUC2 | CLK ₍₄₎ | I/O ₍₅₎ | GNDS |
| D | STAP5 | INTAUXN | GND2 | GND3 | GND4 | RST ₍₄₎ | I/O ₍₄₎ | V _{CC(4)} |
| Ε | A0 | IRQN | I/O ₍₁₎ | GND5 | GND6 | CLK ₍₃₎ | I/O ₍₃₎ | V _{CC(3)} |
| F | C8 ₍₁₎ | CLK ₍₁₎ | GND7 | GND8 | GND9 | RST ₍₃₎ | I/O ₍₂₎ | PRES ₍₂₎ |
| G | C4 ₍₁₎ | RST ₍₁₎ | V _{CC(1)} | GNDP | V _{CC(2)} | RST ₍₂₎ | CLK ₍₂₎ | GNDC ₍₂₎ |
| Н | SPRES | PRES ₍₁₎ | GNDC ₍₁₎ | LX | V_{UP} | n.c. | INHIB | GND10 |

^[1] The numbers in subscript and between brackets "(n)" indicate the relevant card slot.

^[2] The ball positions are those when the TDA8026 is viewed from the top.

Multiple smart card slot interface IC

7.2 Pin description

Table 4. Pin description

| Symbol | Pin | Type[1] | Type[1] Supply Description | | | | | |
|---------------------|-----|------------|----------------------------|--|--|--|--|--|
| Oymboi | • | туреш | power | Description | | | | |
| IRQN | E2 | 0 | $V_{DD(INTF)}$ | microcontroller interrupt; active LOW; open-drain | | | | |
| INTAUXN | D2 | Į | $V_{DD(INTF)}$ | auxiliary interrupt line input: | | | | |
| | | | | auxiliary contact reader front end not connected: connect INTAUXN pad to supply voltage $V_{\mathrm{DD(INTF)}}$ | | | | |
| | | | | auxiliary contact reader front end connected: connect INTAUXN pad to an external 10 k Ω pull-up resistor; active LOW | | | | |
| SDWNN | A5 | <u>[3]</u> | $V_{DD(INTF)}$ | shutdown and reset input; active LOW | | | | |
| $V_{DD(INTF)}$ | A4 | Р | $V_{DD(INTF)}$ | microcontroller interface supply voltage | | | | |
| SDA | C2 | I/O | V _{DD(INTF)} | serial data line to and from the I ² C-bus master; open-drain | | | | |
| SCL | B2 | I | $V_{DD(INTF)}$ | serial clock line from the I ² C-bus master | | | | |
| A0 | E1 | С | $V_{DD(INTF)}$ | I ² C-bus address configuration and selection | | | | |
| SPRES | H1 | С | $V_{DD(INTF)}$ | PRES mode configuration and selection | | | | |
| CLKIN1 | C3 | I | V _{DD(INTF)} | card slot 1 external clock input; connect external clock (f _{clk(ext)}) to generate the CLK ₍₁₎ frequency | | | | |
| CLKIN2 | B3 | I | V _{DD(INTF)} | card slots 2 to 5 external clock input; connect external clock ($f_{clk(ext)}$) to generate the $CLK_{(2)}$ to $CLK_{(5)}$ frequency | | | | |
| GND1 | B4 | G | - | ground connection | | | | |
| I/OUC1 | C4 | I/O[3] | $V_{DD(INTF)}$ | card slot 1 microcontroller data input and output | | | | |
| I/OUC2 | C5 | I/O[3] | $V_{DD(INTF)}$ | card slots 2 to 5 microcontroller data input and output | | | | |
| V _{CC(1)} | G3 | Р | V _{CC(1)} | card slot 1 card supply; position C1 | | | | |
| RST ₍₁₎ | G2 | 0 | V _{CC(1)} | card slot 1 card reset output; position C2 | | | | |
| CLK ₍₁₎ | F2 | 0 | V _{CC(1)} | card slot 1 card clock output; provides f _{CLK} ; position C3 | | | | |
| C4 ₍₁₎ | G1 | I/O[4] | V _{CC(1)} | card slot 1 auxiliary input and output; position C4 | | | | |
| C8 ₍₁₎ | F1 | I/O[4] | V _{CC(1)} | card slot 1 auxiliary input and output; position C8 | | | | |
| I/O ₍₁₎ | E3 | I/O[4] | V _{CC(1)} | card slot 1 card input and output; position C7 | | | | |
| GNDC ₍₁₎ | НЗ | G | - | card slot 1 card ground signal; position C5 | | | | |
| PRES ₍₁₎ | H2 | I | $V_{DD(INTF)}$ | card slot 1 card presence input | | | | |
| V _{CC(2)} | G5 | Р | V _{CC(2)} | card slot 2 card supply; position C1 | | | | |
| RST ₍₂₎ | G6 | 0 | V _{CC(2)} | card slot 2 card reset; position C2 | | | | |
| CLK ₍₂₎ | G7 | 0 | V _{CC(2)} | card slot 2 card clock output; provides f _{CLK} ; position C3 | | | | |
| I/O ₍₂₎ | F7 | I/O[4] | V _{CC(2)} | card slot 2 card input and output; position C7 | | | | |
| GNDC ₍₂₎ | G8 | G | - | card slot 2 card signal ground; position C5 | | | | |
| PRES ₍₂₎ | F8 | I | $V_{DD(INTF)}$ | card slot 2 card presence input | | | | |
| GNDS | C8 | G | - | card slots 3 to 5 card signal ground; position C5 | | | | |
| V _{CC(3)} | E8 | Р | V _{CC(3)} | card slot 3 card supply; position C1 | | | | |
| RST ₍₃₎ | F6 | 0 | V _{CC(3)} | card slot 3 card reset output; position C2 | | | | |
| CLK ₍₃₎ | E6 | 0 | V _{CC(3)} | card slot 3 card clock output; provides f _{CLK} ; position C3 | | | | |
| I/O ₍₃₎ | E7 | I/O[4] | V _{CC(3)} | card slot 3 card input and output; position C7 | | | | |

Multiple smart card slot interface IC

 Table 4.
 Pin description ...continued

| Symbol | Pin | Type ^[1] | Supply power | Description | | |
|--------------------|-----|---------------------|--------------------|--|--|--|
| V _{CC(4)} | D8 | Р | V _{CC(4)} | card slot 4 card supply; position C1 | | |
| RST ₍₄₎ | D6 | 0 | V _{CC(4)} | card slot 4 card reset output; position C2 | | |
| CLK ₍₄₎ | C6 | 0 | V _{CC(4)} | card slot 4 card clock output; provides f _{CLK} ; position C3 | | |
| I/O ₍₄₎ | D7 | I/O[4] | V _{CC(4)} | card slot 4 card input and output; position C7 | | |
| V _{CC(5)} | B5 | Р | V _{CC(5)} | card slot 5 card supply; position C1 | | |
| RST ₍₅₎ | B6 | 0 | V _{CC(5)} | card slot 5 card reset output; position C2 | | |
| CLK ₍₅₎ | B7 | 0 | V _{CC(5)} | card slot 5 card clock output; provides f _{CLK} ; position C3 | | |
| I/O ₍₅₎ | C7 | I/O[4] | V _{CC(5)} | card slot 5 card input and output; position C7 | | |
| TST1 | A2 | С | $V_{DD(INTF)}$ | test pin; connect to ground | | |
| TST2 | A1 | С | $V_{DD(INTF)}$ | test pin; connect to ground | | |
| STAP3 | B1 | I | $V_{DD(INTF)}$ | card slot 3 presence status input[5] | | |
| STAP4 | C1 | I | $V_{DD(INTF)}$ | card slot 4 presence status input[5] | | |
| STAP5 | D1 | I | $V_{DD(INTF)}$ | card slot 5 status presence input[5] | | |
| n.c. | H6 | - | - | not connected | | |
| PORADJ | A8 | I | $V_{DD(INTF)}$ | power-on reset threshold input for V _{DD(INTF)} : | | |
| | | | | threshold used: connect pin PORADJ using an external resistor bridge | | |
| | | | | threshold not used: connect to V _{DD(INTF)} | | |
| V_{DD} | A7 | Р | V_{DD} | main supply voltage | | |
| V_{UP} | H5 | 0 | V_{UP} | DC-to-DC converter output | | |
| LX | H4 | I | LX | DC-to-DC converter power supply input | | |
| GNDP | G4 | G | - | DC-to-DC converter ground | | |
| $V_{DD(INTREGD)}$ | A6 | 0 | V_{DD} | internal voltage regulator output | | |
| DCDC_OFF | B8 | С | $V_{DD(INTF)}$ | DC-to-DC converter on/off control; active HIGH | | |
| INHIB | H7 | С | $V_{DD(INTF)}$ | connect to ground | | |
| TESTMODE | А3 | С | $V_{DD(INTF)}$ | connect to ground | | |
| GND2 | D3 | G | - | ground | | |
| GND3 | D4 | G | - | ground | | |
| GND4 | D5 | G | - | ground | | |
| GND5 | E4 | G | - | ground | | |
| GND6 | E5 | G | - | ground | | |
| GND7 | F3 | G | - | ground | | |
| GND8 | F4 | G | - | ground | | |
| GND9 | F5 | G | - | ground | | |
| GND10 | H8 | G | - | ground | | |

- [1] I = Input, O = Output, P = Power, G = Ground, C = Configuration.
- [2] Refer to the Application note AN10724 for further information.
- [3] Integrated pull-up to V_{DD(INTF)} value.
- [4] Integrated pull-up to the related $V_{\text{CC}(n)}$ value.
- [5] In Shutdown mode, set to LOW.

Multiple smart card slot interface IC

8. Functional description


Remark: Throughout this document ISO 7816-3 and EMV standard terminology conventions have been adhered to and it is assumed that the reader is familiar with these.

8.1 Power supplies

The TDA8026 supply pins are V_{DD} , $V_{DD(INTF)}$ and GND1 to GND10.

- V_{DD} must be between 2.7 V and 5.5 V
- V_{DD(INTF)} must be between 1.6 V and 3.6 V

The V_{DD} , $V_{DD(INTF)}$ supply voltages can be applied to the device at any time, in any sequence. All interface signals to the system controller are referenced to the $V_{DD(INTF)}$ supply voltage which can be lower or higher than V_{DD} . The integrated DC-to-DC converter generates the card supply voltage ($V_{CC(n)}$) of either 5 V , 3 V or 1.8 V (\pm 5 %). In addition, the internal voltage regulator delivers $V_{DD(INTREGD)}$ 3.3 V supply voltage.



8.2 Power modes

Three power modes are available for the TDA8026. These are:

- Standby mode
- · Active mode with a clock-stop sub-mode
- Shutdown mode

Multiple smart card slot interface IC

8.2.1 Standby mode

In Standby mode, both the supply voltages V_{DD} and $V_{DD(INTF)}$ are applied within the specification limits as described in <u>Table 40 on page 40</u>. In addition, the DC-to-DC converter is not running and the card slots are not activated.

8.2.2 Active mode

In active mode, both the V_{DD} and $V_{DD(INTF)}$ supply voltages are applied to the device within the specification limits as described in <u>Table 40 on page 40</u>. A minimum of one card slot is activated. All card slots can be activated at once and communication performed with up to two cards slots.

The DC-to-DC converter has been developed to handle a 116 mA (typical) DC load. This allows two active card slots to communicate with a load of 55 mA while the three remaining card slots are in clock-stop mode (see <u>Section 8.2.3</u> for information about this mode) with a 2 mA load.

The DC-to-DC converter overload protection is triggered when a higher current load than specified in <u>Table 40 on page 40</u> is supplied to the DC-to-DC converter (see <u>Section 8.11</u> for further information).

8.2.3 Clock-stop mode

Clock-stop mode is a low-power mode which is triggered when a card is activated without any communication. In this mode, a supply voltage with a low frequency clock is applied to cards that do not support the clock-stop feature.

8.2.4 Shutdown mode

Shutdown mode is the very low power consumption mode, typically 25 μ A. The TDA8026 enters this mode when the SDWNN pin is driven LOW. Only presence monitoring on card slot 1 remains enabled. When card insertion or removal is detected on card slot 1, an interrupt signal (IRQN) is sent to the microcontroller.

In shutdown mode, it is assumed that the $V_{DD(INTF)}$ and V_{DD} supply voltages are stable and the SDWNN pin is active LOW.

8.2.4.1 Entering shutdown mode

Shutdown mode is activated when the SDWNN pin is driven LOW. On entering this mode:

- 1. All card slots are automatically deactivated
- 2. The power consumption is reduced on completion of the deactivation sequence.


This causes the following:

- Digital module moves in to reset mode. However, card presence monitoring on slot 1 continues to operate normally
- All card slots are disabled and all card pins are forced to 0 V. Again, card presence monitoring on slot 1 continues to operate normally
- Thermal protection is disabled
- The DC-to-DC converter is bypassed
- All interface signal pull-up resistors are disconnected from their supply rail (except the pull-up resistor on the SDWNN pin)

TDA8026_1

Multiple smart card slot interface IC


• I/OUC1 and I/OUC2 are set to high-impedance.



8.2.4.2 Exiting shutdown mode

The TDA8026 performs the following steps when exiting shutdown mode:


- 1. Card insertion on card slot 1 is signalled by the IRQN pin signal being driven LOW.
- 2. Using the IRQN pin signal, the microcontroller detects the card insertion and drives the SDWNN pin HIGH to wake-up the TDA8026
- 3. When the SDWNN pin is HIGH, the IRQN pin is set to HIGH and the analog module is powered-up. A full power-up sequence is executed by the TDA8026
- 4. When the TDA8026 is ready, the IRQN pin is set to LOW
- 5. The microcontroller detects the device interrupt using the IRQN pin and services it which resets pin IRQN to HIGH



Multiple smart card slot interface IC

8.3 Voltage supervisors

8.3.1 Block diagram




8.3.2 Description


The voltage supervisor can be used to perform Power-On Resets (POR) and supply drop detection during a card session. The supervisors control the internal regulated supply voltage ($V_{DD(INTREGD)}$) and the microcontroller interface supply voltage ($V_{DD(INTF)}$) to ensure problem-free operation of the TDA8026. This block controls:

- V_{DD} using the internal voltage regulator's output (V_{DD(INTREGD)})
- the microcontroller interface supply voltage (V_{DD(INTF)}) using the voltage on the PORADJ pin (V_{PORADJ})

When an alarm occurs, the internal digital controller resets the TDA8026.



Multiple smart card slot interface IC



Remark: Refer to the Application note AN10724 for further information.

8.3.3 V_{DD(INTREGD)} voltage supervisor without external divider on PORADJ pin

An alarm signal is triggered and the analog controller resets the TDA8026 when:

- V_{DD(INTREGD)} is less than V_{th} on pin V_{DD(INTREGD)}
- Pin PORADJ monitoring V_{DD(INTF)} is less than V_{th}

The alarm is reset and the TDA8026 leaves reset mode 8 ms after V_{DD} and V_{PORADJ} are above their respective V_{th} + V_{hys} .

V_{th} on V_{DD(INTF)} is set as shown in Equation 1:

$$V_{th} = V_{bg} \left(1 + \frac{R2}{RI} \right) \tag{1}$$

Thus $V_{bg} = 1.21 \text{ V (see } \frac{\text{Figure 6}}{\text{Mode 6}}$).

In reset mode, the TDA8026 is inactive and does not respond to any external command lines.

Multiple smart card slot interface IC

8.4 I²C-bus description

Remark: Refer to the PC-bus specification for more information.

The I²C-bus interface in the TDA8026 is an I²C-bus slave operating either Standard mode (100 kHz) or Fast mode (400 kHz). In addition, it integrates shift register functions, shift timing generation and slave address recognition.

8.4.1 I²C-bus protocol

The I²C-bus protocol is based on bidirectional, 2-line communication between ICs or modules. The serial bus consists of two bidirectional lines: one for data signals (SDA) and one for clock signals (SCL). Both the SDA and SCL lines must be connected to the $V_{\text{DD(INTF)}}$ supply voltage using a pull-up resistor (refer to the I²C-bus specification for more details).

The I²C-bus protocol is defined as follows:

- Data transfer can only be initialized when the I²C-bus is not busy.
- During data transfer, the data line must remain stable when the clock line is HIGH.
 Changes in the data line while the clock line is HIGH are interpreted as control signals.

8.4.2 Bus conditions

The following bus conditions are defined.

Bus not busy — Both data and clock lines remain HIGH.

Start data transfer — The START condition is generated when the state of the data line changes from HIGH to LOW while the clock line is HIGH.

Stop data transfer — The STOP condition is generated when the state of the data line changes from LOW to HIGH while the clock line is HIGH.

Data valid — The data line state represents valid data, after a START condition with the data line stable for the duration of the clock signal HIGH period. There is one clock pulse per bit of data.

8.4.3 Data transfer

Each data transfer is triggered by a START condition and finished by a STOP condition (see Figure 13 for timing information).

Data transfers can be performed in Standard mode at 100 kHz or Fast mode at 400 kHz. Data transfer is performed on a byte for byte basis in both read or write modes. The information is transmitted in bytes and each receiver acknowledges with a 9th bit (acknowledge).

Each byte is followed by an acknowledge bit and the transmitter must release the SDA line during the acknowledge bit. The master generates an extra acknowledge related clock pulse. The addressed slave receiver must generate an acknowledge bit after receiving each byte. The master-receiver must generate an acknowledge bit after receiving each byte clocked out of the slave transmitter.

The acknowledging device must pull-down the SDA line during the acknowledge clock pulse to ensure the SDA line is stable LOW during the acknowledge related clock pulse HIGH period.

Multiple smart card slot interface IC

In addition, the set-up and hold times must be taken into account. The master-receiver must signal the end of the last data byte to the slave transmitter by not sending an acknowledge bit on the last byte that has been clocked out of the slave. The transmitter must ensure the data line is HIGH to enable the master to generate the STOP condition.

8.4.4 Device addressing

Three device addresses are needed to control the TDA8026.

- One high address: The high address enables selection of a bank page (Bank 0 or Bank 1) based on a configuration byte. A bank page relates to a card slot or general registers. See Table 7 for detailed information.
- Two low addresses: The microcontroller uses two low addresses to read and write into the selected bank page (see <u>Table 6 on page 15</u> to <u>Table 39 on page 38</u> for detailed information).

The addresses for the device are shown in Table 5 and Table 6.

Table 5. Base addressing

| Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 |
|-------|-------|-------|-------|-------|-------|-------|-------|
| 0 | 1 | 0 | 0 | 1 | A0 | 0 | R/W |

Bit 1 is the address bit which selects Register0 or Register1. Bit 0 defines either Read or Write mode.

- When bit 0 is set to logic 1, read mode is selected
- When bit 0 is set to logic 0, write mode is selected

Table 6. Write mode addresses

| | Bank 0 base register address (Hex) | Bank 1 Register0 address (Hex) | Bank 1 Register1 address (Hex) |
|---|------------------------------------|--------------------------------|-----------------------------------|
| 0 | 48h | 40h | 42h |
| 1 | 4Ch | 44h | 46h |

Bank 1 page selection is performed when the configuration byte (CSb[7:0]) is written to the high address representing bank 0 based on the A0 pin value.

Using pin A0, two TDA8026s can be used in parallel based on the selection made to the address selection pin A0. Pin A0 is externally hardwired to the pins $V_{DD(INTF)}$ or GND. The voltage on the A0 pin sets the bit 2 address bit

Multiple smart card slot interface IC

8.5 Banks and registers

The device registers enable the microcontroller to control the TDA8026. These registers are defined as banks:

- Bank 0 register is a read/write register which enables selection of the required card slot number and access to the corresponding registers Bank 1 registers. In addition, Bank 0 is used to write information about the interrupt status and the product version. The registers in bank 0 (CSb[7:0] = 1h to 5h) are similar to the registers of the TDA8023.
- Bank 1 provides access to the corresponding card slot registers. Bank 1 is composed
 of several pages which in turn contain registers related to each individual card slot or
 general registers. Typically, pages can contain two general registers or five card slot
 related registers.

Remark: The registers are organized in bank pages in order to keep compatibility with the TDA8023.

Bank 1 page selection is performed when the configuration byte (CSb[7:0]) is written to the high I²C-bus address representing bank 0 based on the A0 pin.

0111 0100

NXP Semiconductors

Table 7. Register overview

| Page number/ | Register | R/W | Bit definit | ion | | | | | | | Reset value |
|------------------------------------|--------------------------|----------------|--------------|--|----------------|-------------|----------|---------|-----------|---------|-------------|
| register Subaddress (Hex)[1] | name | | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 | (Binary) |
| Bank 0: Card s | ot selection, | produc | t version a | nd interrupt | registers (see | Table 8 and | Table 9) | | | | |
| -/48h | CSb | R/W | | | | CS | b[7:0] | | | | 0000 0001 |
| Bank 1: Card s | ot registers (s | see <u>Tak</u> | ole 11 throu | gh Table 33 |) | | | | | | <u>'</u> |
| Slot 1 | | | | | | | | | | | |
| 01h/40h | Register0 | R | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | PRESL | PRES | 0000 1000 |
| 01h/40h | Register0 | W | VCC1V8 | I/OEN | REC | G[1:0] | PDWN | 5V/3VN | WARM | START | 0000 0000 |
| 01h/42h | Register1[3] | R/W | <u>-[2]</u> | [2] RSTIN C81 C41 CLKPD[1:0] CLKDIV[1:0] | | | | | 0111 1111 | | |
| 01h/42h | Register14 | R/W | | D[7:0] | | | | | | | |
| 01h/42h | Register1 ^[5] | R/W | | C[15:8] | | | | | | | |
| 01h/42h | Register16 | R/W | | | | С | [7:0] | | | | 0111 0100 |
| Slot 2 | | | | | | | | | | | |
| 02h/40h | Register0 | R | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | PRESL | PRES | 0000 1000 |
| 02h/40h | Register0 | W | VCC1V8 | I/OEN | REC | G[1:0] | PDWN | 5V/3VN | WARM | START | 0000 0000 |
| 02h/42h | Register1[3] | R/W | CFGP2 | RSTIN | - | <u>[2]</u> | CLK | PD[1:0] | CLKD | IV[1:0] | 0100 1111 |
| 02h/42h | Register14 | R/W | | | | D | [7:0] | | | | 1010 1010 |
| 02h/42h | Register1 ^[5] | R/W | | | | C[| 15:8] | | | | 1010 0100 |
| 02h/42h | Register16 | R/W | | | | С | [7:0] | | | | 0111 0100 |
| Slot 3 | | | | | | | | | | | |
| 03h/40h | Register0 | R | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | _[2] | STAP3 | 0000 1000 |
| 03h/40h | Register0 | W | VCC1V8 | I/OEN | REC | G[1:0] | PDWN | 5V/3VN | WARM | START | 0000 0000 |
| 03h/42h | Register1[3] | R/W | <u>-[2]</u> | RSTIN | | [2] | CLK | PD[1:0] | CLKD | IV[1:0] | 0100 1111 |
| 03h/42h | Register1[4] | R/W | | • | | D | [7:0] | | | | 1010 1010 |
| 03h/42h | Register1 ^[5] | R/W | | | | C[| 15:8] | | | | 1010 0100 |
| | | | | | | | | | | | |

C[7:0]

03h/42h

Register16 R/W

Reset value

(Binary)

Table 7.

register

Page number/

| Subaddress (Hex)[1] | name | | Bit 7 | Bit 6 | Bit 5 | Bit 4 | Bit 3 | Bit 2 | Bit 1 | Bit 0 | (Billary) | |
|------------------------|---------------------|----------------|-------------|------------------------------|------------|--------|--------|----------|-------------|-----------|-----------|--|
| Slot 4 | | | | | | | | <u>'</u> | | | | |
| 04h/40h | Register0 | R | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | <u>[2]</u> | STAP4 | 0000 1000 | |
| 04h/40h | Register0 | W | VCC1V8 | I/OEN | RE | G[1:0] | PDWN | 5V/3VN | WARM | START | 0000 0000 | |
| 04h/42h | Register1[3] | R/W | <u>-[2]</u> | RSTIN | RSTIN -[2] | | | PD[1:0] | 0100 1111 | | | |
| 04h/42h | Register1[4] | R/W | | | , | | D[7:0] | | ' | | 1010 1010 | |
| 04h/42h | Register1 5 | R/W | | | | С | [15:8] | | | | 1010 0100 | |
| 04h/42h | Register16 | R/W | | | | (| C[7:0] | | | | 0111 0100 | |
| Slot 5 | | | | | | | | | | | | |
| 05h/40h | Register0 | R | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | <u>-[2]</u> | STAP5 | 0000 1000 | |
| 05h/40h | Register0 | W | VCC1V8 | I/OEN | RE | G[1:0] | PDWN | 5V/3VN | WARM | START | 0000 0000 | |
| 05h/42h | Register1[3] | R/W | <u>-[2]</u> | RSTIN | | _[2] | CLK | (PD[1:0] | CLKD | IV[1:0] | 0100 1111 | |
| 05h/42h | Register1[4] | R/W | | | , | | D[7:0] | | ' | | 1010 1010 | |
| 05h/42h | Register1 5 | R/W | | | | С | [15:8] | | | | 1010 0100 | |
| 05h/42h | Register16 | R/W | | | | (| C[7:0] | | | | 0111 0100 | |
| Bank 1: Gener | al registers (se | ee <u>Tabl</u> | e 34 throug | gh <u>Table 39</u>) | l | | | | | | | |
| 00h/42h | Product version | R | | | | Р | V[7:0] | | | | 1100 0010 | |
| 00h/42h | Interrupt status | R | | - <u>[2]</u> INTAUX INT[4:0] | | | | | | 0001 1111 | | |
| 06h/40h | Slew rate | R/W | CLK_ | CLK_SR[3:2] | | | | | | | | |

Bit 4

Bit 3

Bit 2

Bit 1

Bit 0

Register overview ...continued

R/W

Bit definition

Bit 6

Bit 5

Bit 7

Register

name

uctors N.V. 2016. All rights reserved

^[1] See <u>Table 8</u>, <u>Table 9</u> and <u>Table 11</u> through <u>Table 39</u> for detailed information.

^[2] Reserved bit position.

^[3] REG[1:0] = 00 depending on the setting for Bank1 CSb[7:0].

^[4] REG[1:0] = 01 depending on the setting for Bank1 CSb[7:0].

^[5] REG[1:0] = 10 depending on the setting for Bank1 CSb[7:0].

^[6] REG[1:0] = 11 depending on the setting for Bank1 CSb[7:0].

Multiple smart card slot interface IC

8.5.2 Bank 0 register description

The device registers enable the microcontroller to control the TDA8026. The registers are organized in bank pages to ensure compatibility with the TDA8023.

Bank 0 write register enables selection of the card slot number and access to the corresponding registers in bank 1. The card slot registers in bank 1 are accessed using the configuration byte (CSb[7:0]). The range 01h to 05h is used to select the specific card slot starting at card slot 1 (01h) and ending with card slot 5 (05h) in a similar way to the TDA8023 registers.

8.5.2.1 Bank 0 register (address: 48h) bit allocation

Table 8. Bank 0 register (address: 48h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | | |
|--------|---|----------|---|---|---|---|---|---|--|--|
| Symbol | | CSb[7:0] | | | | | | | | |
| Access | | R/W | | | | | | | | |

8.5.2.2 Bank 0 bit description

Table 9. Bank 0 bit description

| Bit | Symbol | Value | Description |
|--------|----------|-------|---|
| 7 to 0 | CSb[7:0] | | Bank 1 page selection: |
| | | 00h | selects product version and interrupts status register page |
| | | 01h | selects card slot 1 page |
| | | 02h | selects card slot 2 page |
| | 03h | | selects card slot 3 page |
| | | 04h | selects card slot 4 page |
| | | 05h | selects card slot 5 page |
| | | 06h | selects the clock frequency and I/O lines slew rate settings page |

8.5.3 Bank 1 card slots 1 and 2 register descriptions

8.5.3.1 Bank 1 CSb[7:0] Register0 (address 40h) card slot 1 and card slot 2 bit allocation

Table 10. Bank 1 CSb[7:0] Register0 (address 40h) card slot 1 and card slot 2 bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|---|---------------|-------|----------|------|------|--------|-------|-------|
| Card slot 1 (address 01h) and Card slot 2 (address 02h) | | | | | | | | |
| Symbol | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | PRESL | PRES |
| Access | [1]R | R | R | R | R | R | R | R |
| Symbol | VCC1V8 | I/OEN | REG[1:0] | | PDWN | 5V/3VN | WARM | START |
| Access | [<u>1]</u> W | W | W | W | W | W | W | W |

^[1] See <u>Table 11</u> for the read mode bits and <u>Table 12</u> for the write mode bits.

When at least one of the PRESL, SUPL, PROT, MUTE and EARLY bits is set to logic 1, IRQN pin is driven LOW until the status byte has been read. After power-on, the SUPL bit is set to logic 1 until the status byte has been read and the IRQN pin is LOW until the voltage supervisor is deactivated.

Multiple smart card slot interface IC

8.5.3.2 Bank 1 Register0 card slot 1 (address 01h) and card slot 2 (address 02h) read mode bit descriptions

Table 11. Bank 1 Register0 card slot 1 (address 01h) and card slot 2 (address 02h) read mode bit descriptions

| Bit | Symbol | Value | Description |
|-----|--------|-------|--|
| 7 | ACTIVE | 1 | set to logic 1: the card is active |
| | 0 | | set to logic 0: the card is inactive |
| 6 | EARLY | 1 | set to logic 1: during ATR, when the card answers too early |
| | | 0 | set to logic 0: after reading the byte |
| 5 | MUTE | 1 | set to logic 1: during ATR, when the card does not answer according to the ISO 7816 time period |
| | | | set to logic 0: after reading the byte |
| 4 | PROT | | set to logic 1: during a card session when an overload or overheating occurs |
| | | 0 | set to logic 0: after reading the byte |
| 3 | SUPL | 1 | set to logic 1: when the supervisor signals a fault |
| | | 0 | set to logic 0: after reading the byte |
| 2 | CLKSW | 1 | set to logic 1: when the card slot is in Power-down mode and the clock has switched to $f_{osc(int)}/2$ |
| | | | Remark: (f _{osc(int)} is the internal oscillator frequency) |
| | | 0 | set to logic 0: when exiting Power-down mode and when the clock is switched back to the f _{clk(ext)} frequency[1] |
| 1 | PRESL | 1 | set to logic 1: the card has been inserted or extracted |
| | | 0 | set to logic 0: after reading the byte |
| 0 | PRES | 1 | set to logic 1: the card is present |
| | | 0 | set to logic 0: the card is not present or has been removed |

^[1] $f_{clk(ext)}$ is the external clock frequency applied to pins CLKIN1 and CLKIN2.

Multiple smart card slot interface IC

8.5.3.3 Bank 1 Register0 card slot 1 (address 01h) and card slot 2 (address 02h) write mode bit descriptions

Table 12. Bank 1 Register0 card slot 1 (address 01h) and card slot 2 (address 02h) write mode bit descriptions

| Bit | Symbol | Value | Description | | | |
|--------|-----------|-------|--|--|--|--|
| 7 | VCC1V8[1] | | used together with the 5V/3VN bit | | | |
| | | 1 | set to logic 1: V _{CC(n)} = 1.8 V; ignores the 5V/3VN bit logic state | | | |
| | | 0 | set to logic 0: V _{CC(n)} is set using the 5V/3VN bit | | | |
| 6 | I/OEN[2] | 1 | set to logic 1: pins I/OUCn are switched to pins I/O _(n) | | | |
| | | 0 | set to logic 0: pins I/OUCn and I/O $_{(n)}$ are high-impedance with internal pull-up resistor | | | |
| 5 to 4 | REG[1:0] | - | See Table 13 "Bank 1 CSb[7:0] Register0 (address 42h) card slots 1 and card slots 2 bit allocation" on page 22 for detailed information | | | |
| 3 | 3 PWDN[3] | 1 | set to logic 1 to apply the CLKPD[1:0] bit clock settings to pin $CLK_{(n)}$ for the selected card slot | | | |
| | | 0 | set to logic 0 to apply the CLKDIV[1:0] bits clock options to pin $CLK_{(n)}$ for the selected card slot | | | |
| 2 | 5V/3VN[1] | 1 | used together with VCC1V8 bit. | | | |
| | | | set to logic 1 and the VCC1V8 bit is logic 0: $V_{CC(n)} = 5 \text{ V}$ | | | |
| | | 0 | set to logic 0 and the VCC1V8 bit is logic 0: $V_{CC(n)} = 3 \text{ V}$ | | | |
| 1 | WARM | 1 | set to logic 1: a warm reset procedure is started | | | |
| | | 0 | set to logic 0: by hardware when a START bit is detected or when MUTE bit is set to logic 1 | | | |
| 0 | START | 1 | set to logic 1: starts the activation sequence and cold reset procedure (only if the SUPL and PROT bits are logic 0 and the PRES bit is logic 1) | | | |
| | | 0 | set to logic 0: starts the deactivation sequence | | | |

^[1] This bit cannot be written when the START bit is logic 1.

[3] In synchronous mode, this bit cannot be written when START bit is logic 1.

^[2] It is a mandatory condition for card slots 2 to 5 that only one card slot I/O line is enabled at a time. When switching from one slot to another, the enabled I/O must be disabled before the I/O line for the required card slot is enabled.

Remark: If both pins I/OUC1 and I/OUC2 are connected at the same time, this mandatory condition also applies to card slot 1.

Multiple smart card slot interface IC

8.5.3.4 Bank 1 CSb[7:0] Register0 (address 42h) card slots 1 and card slot 2 bit allocation

Table 13. Bank 1 CSb[7:0] Register0 (address 42h) card slots 1 and card slots 2 bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | |
|------------------|---|-------------|-------------------|-----------|---------|------------------------------------|-------|--------------------------|--|
| Card slot 1 (add | Card slot 1 (address 01h) and Card slot 2 (address 02h) | | | | | | | | |
| Card Slot 1 Reg[| Card Slot 1 Reg[1:0] = 00; see <u>Table 14 on page 22</u> | | | | | | | | |
| Symbol | <u>-[1]</u> | RSTIN | C8(1) | C4(1) | CLKPE |)[1:0] <mark>^[2]</mark> | CLKDI | /[1:0] <mark>[3]</mark> | |
| Access | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | |
| Card Slot 2 Reg[| Card Slot 2 Reg[1:0] = 00; see <u>Table 14 on page 22</u> | | | | | | | | |
| Symbol | CFGP2 | RSTIN | -[| <u>1]</u> | CLKPE |)[1:0] <mark>^[2]</mark> | CLKDI | /[1:0 <mark>[3]</mark>] | |
| Access | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W | |
| Card Slot 1 and | card slot 2 R | eg[1:0] = 0 | 01; see <u>Ta</u> | ble 16 on | page 24 | | | | |
| Symbol | | | | D[7: | 0] | | | | |
| Access | | | | R/V | V | | | | |
| Card Slot 1 and | card slot 2 R | eg[1:0] = ' | 10; see <u>Ta</u> | ble 18 on | page 24 | | | | |
| Symbol | | | | C[15 | :8] | | | | |
| Access | | R/W | | | | | | | |
| Card Slot 1 and | card slot 2 R | eg[1:0] = ' | 11; see <u>Ta</u> | ble 20 on | page 24 | | | | |
| Symbol | | C[7:0] | | | | | | | |
| Access | | | | R/V | V | | | | |

^[1] Reserved bit position.

8.5.3.5 Bank 1 Register1 (REG[1:0] = 00) card slot 1 (address 01h) and card slot 2 (address 02h) read/write mode bit descriptions

Table 14. Bank 1 Register1 (REG[1:0] = 00) card slot 1 (address 01h) and card slot 2 (address 02h) Read/Write mode bit descriptions

| Bit | Symbol | Value | Description |
|-----|----------|-------|---|
| 7 | | | enables another type of card detection switch to be used on card socket 1 and card socket 2 |
| | | | if CFGP2 is logic 1, an interrupt is generated during each power-up because the reset value of CFGP2 is logic level 0. Refer to the <i>Application note AN10724</i> for further information |
| 0 | | | the reset value of CFGP2 is logic 0. Refer to the <i>Application</i> note AN10724 for further information |
| 6 | RSTIN | 1 | synchronous mode: when set to logic 1, pin $RST_{(n)}$ is set to HIGH |
| | | | asynchronous mode: RSTIN is controlled by hardware (ATR management) |
| | | 0 | set to logic 0: pin RST _(n) is LOW |
| 5 | C8(1)[2] | - | writing C8(1) bit writes the corresponding value on C8 ₍₁₎ pin |
| | | - | reading C8(1) bit reads the state of C8 ₍₁₎ pin |
| 4 | C4(1)[2] | - | writing C41 bit writes the corresponding value on C4 ₍₁₎ pin |
| | | - | reading C41 bit reads the state of C4 ₍₁₎ pin |

^[2] CLKPD[2] = bit 3 and <math>CLKPD[1] = bit 2.

^[3] CLKDIV[2] = bit 2 and CLKDIV[1] = bit 1.

Multiple smart card slot interface IC

Table 14. Bank 1 Register1 (REG[1:0] = 00) card slot 1 (address 01h) and card slot 2 (address 02h) Read/Write mode bit descriptions ...continued

| Bit | Symbol | Value | Description |
|--------|-------------|-------|--|
| 3 to 2 | CLKPD[1:0] | - | asynchronous mode: when PWDN bit is set to logic 1, the CLKPD[1] and CLKPD[2] bits define the card clock |
| | | - | synchronous mode: when the PWDN bit and the START bit are set to logic 1, the CLKPD[2] bit remains logic 0 and the clock frequency is controlled by the CLKPD[1] bit |
| | | 00 | asynchronous mode: the card clock is stopped and set to logic 0 |
| | | - | synchronous mode: the card clock is set to logic 0 |
| | | 01 | asynchronous mode: the card clock is stopped and set to logic 1 |
| | | - | synchronous mode: the card clock is set to logic 1 |
| | | 10 | asynchronous mode: the card clock = $f_{osc(int)}/2$ |
| | | | Remark: (f _{osc(int)} is the internal oscillator frequency) |
| | | 11 | asynchronous mode: the card clock frequency $(f_{(clk)})$ is set using the CLKDIV[1:0] bits. |
| 1 to 0 | CLKDIV[1:0] | | asynchronous mode: when the PWDN bit is set to logic 0 the CLKDIV[1:0] bits define the card clock frequency. |
| | | | synchronous mode: the CLKDIV[1:0] bits are logic 0 |
| | | 00 | [3] card slot 1 card clock frequency = f _{clk(ext)} on pin CLK ₍₁₎ |
| | | | card slot 2 card clock frequency = f _{clk(ext)} on pin CLK ₍₂₎ |
| | | 01 | card slot 1 card clock frequency = f _{clk(ext)} / 2 on pin CLK ₍₁₎ |
| | | | card slots 2 card clock frequency = f _{clk(ext)} / 2 on pin CLK ₍₂₎ |
| | | 10 | card slot 1 card clock frequency = f _{clk(ext)} / 4 on pin CLK ₍₁₎ |
| | | | card slot 2 card clock frequency = $f_{clk(ext)}$ / 4 on pin $CLK_{(2)}$ |
| | | 11 | card slot 1 card clock frequency = f _{clk(ext)} / 5 on pin CLK ₍₁₎ |
| | | | card slot 2 card clock frequency = f _{clk(ext)} / 5 on pin CLK ₍₂₎ |

^[1] Only for card slot 2 register.

8.5.3.6 Bank 1 Register1 (REG[1:0] = 01) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

Table 15. Bank 1 Register1 (REG[1:0] = 01) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|--------|---|--------|---|---|----|---|---|---|
| Symbol | | D[7:0] | | | | | | |
| Access | | | | R | /W | | | |

^[2] Only for card slot 1 register.

^[3] $f_{Clk(ext)}$ is the external clock frequency applied to pins CLKIN1 and CLKIN2.

Multiple smart card slot interface IC

8.5.3.7 Bank 1 Register1 (REG[1:0] = 01) card slot 1 (address 01h) and card slot 2 (address 02h) read/write mode bit descriptions

Table 16. Bank 1 Register1 (REG[1:0] = 01) card slot 1 (address 01h) and card slot 2 (address 02h) Read/Write mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|---|
| 7 to 0 | D[7:0] | programmable 8-bit clock counter. This value is applied to all slots. The reset value is AAh. See Section 8.9 "Answer to reset counters" on page 36 |

8.5.3.8 Bank 1 Register1 (REG[1:0] = 10) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

Table 17. Bank 1 Register1 (REG[1:0] = 10) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|--------|---|---------|---|---|----|---|---|---|
| Symbol | | C[15:8] | | | | | | |
| Access | | | | R | /W | | | |

8.5.3.9 Bank 1 Register1 (REG[1:0] = 10) card slot 1 (address 01h) and card slot 2 (address 02h) read/write mode bit descriptions

Table 18. Bank 1 Register1 (REG[1:0] = 10) card slot 1 (address 01h) and card slot 2 (address 02h) Read/Write mode bit descriptions

| Bit | Symbol | Description |
|--------|---------|---|
| 7 to 0 | C[15:8] | most significant byte of a programmable 16-bit clock counter. This value is applied to all slots. The reset value is A4h. See Section 8.9 "Answer to reset counters" on page 36 |

8.5.3.10 Bank 1 Register1 (REG[1:0] = 11) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

Table 19. Bank 1 Register1 (REG[1:0] = 11) card slot 1 (address 01h) and card slot 2 (address 02h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|--------|---|--------|---|---|---|---|---|---|
| Symbol | | C[7:0] | | | | | | |
| Access | | | | R | W | | | |

8.5.3.11 Bank 1 Register1 (REG[1:0] = 11) card slot 1 (address 01h) and card slot 2 (address 02h) read/write mode bit descriptions

Table 20. Bank 1 Register1 (REG[1:0] = 11) card slot 1 (address 01h) and card slot 2 (address 02h) read/write mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|---|
| 7 to 0 | C[7:0] | least significant byte of a programmable 16-bit clock counter. This value is applied to all slots. The reset value is 74h. See Section 8.9 "Answer to reset counters" on page 36. |

Multiple smart card slot interface IC

8.5.4 Card slots 3 to 5 register descriptions

8.5.4.1 Bank 1 CSb[7:0] Register0 (address 40h) card slots 3 to 5 bit allocation

Table 21. Bank 1 CSb[7:0] Register0 (address 40h) card slots 3 to 5 bit allocation

| | | • | • | • | | | | |
|--|--------|-------|----------|------|------|--------|-------------|-------|
| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
| Card slot 3 (address 03h), Card slot 4 (address 04h) and Card slot 5 (address 05h) | | | | | | | | |
| Symbol | ACTIVE | EARLY | MUTE | PROT | SUPL | CLKSW | <u>-[1]</u> | STAP |
| Access | R[2] | R | R | R | R | R | R | R |
| Symbol | VCC1V8 | I/OEN | REG[1:0] | | PDWN | 5V/3VN | WARM | START |
| Access | W[2] | W | W | W | W | W | W | W |

^[1] Reserved bit position.

8.5.4.2 Bank 1 Register0 card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read mode bit descriptions

Table 22. Bank 1 Register0 card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read mode bit descriptions

| Bit | Symbol | Value | Description |
|-----|--------|-------|--|
| 7 | ACTIVE | 1 | set to logic 1: the card is active |
| | | 0 | set to logic 0: the card is inactive |
| 6 | EARLY | 1 | set to logic 1: during ATR, when the card answers too early |
| | | 0 | set to logic 0: after reading the byte |
| 5 | MUTE | 1 | set to logic 1: during ATR, when the card does not answer according to the ISO 7816 time period |
| | | 0 | set to logic 0: after reading the byte |
| 4 | PROT | 1 | set to logic 1: during a card session when an overload or overheating occurs |
| | | 0 | set to logic 0: after reading the byte |
| 3 | SUPL | 1 | set to logic 1: the supervisor signaled a fault |
| | | 0 | set to logic 0: after reading the byte |
| 2 | CLKSW | 1 | set to logic 1: when the card slot is in Power-down mode and the clock has switched to $f_{osc(int)}/2$ |
| | | | Remark: (f _{osc(int)} is the internal oscillator frequency) |
| | | | set to logic 0: when exiting Power-down mode and when the clock is switched back to $f_{\text{clk}(\text{ext})}$ |
| 1 | - | - | reserved |
| 0 | STAP | - | gives the value of the corresponding STAPn pin when read |

When at least one of the SUPL, PROT, MUTE and EARLY bits are set to logic 1, the IRQN pin is driven LOW until the status byte has been read. After power-on, the SUPL bit is set to logic 1 until the status byte has been read and the IRQN pin is LOW until the voltage supervisor is deactivated.

^[2] See table Table 22 for more detailed information on read mode bits and Table 23 for more detailed information on write mode bits.

Multiple smart card slot interface IC

8.5.4.3 Bank 1 Register0 card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) write mode bit descriptions

Table 23. Bank 1 Register0 card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) write mode bit descriptions

| Bit | Symbol | Value | Description | | | | |
|--------|-----------|-------|---|--|--|--|--|
| 7 | VCC1V8[1] | | used together with the 5V/3VN bit | | | | |
| | | 1 | set to logic 1: V _{CC(n)} = 1.8 V; ignores the 5V/3VN bit logic state | | | | |
| | | 0 | if set to logic 0 V _{CC(n)} is set using the 5V/3VN bit | | | | |
| 6 | I/OEN[2] | 1 | set to logic 1: pins I/OUCn are switched to pins I/O _(n) | | | | |
| | | 0 | set to logic 0: pins I/OUCn and I/O $_{(n)}$ are high-impedance with internal pull-up resistor | | | | |
| 5 to 4 | REG[1:0] | - | see Table 24 "Bank 1 CSb[7:0] Register1 (address 42h) card slots 3 and 5 bit allocation" on page 27 for detailed information | | | | |
| 3 | PWDN[3] | | set to logic 1: to apply the CLKPD[1:0] bit clock settings to pin $CLK_{(n)}$ for the selected card slot | | | | |
| | | 0 | set to logic 0: to apply the CLKDIV[1:0] bits clock options to pin $\text{CLK}_{(n)}$ for the selected card slot | | | | |
| 2 | 5V/3VN[1] | | used together with VCC1V8 bit | | | | |
| | | 1 | set to logic 1: and the VCC1V8 bit is logic 0: $V_{CC(n)} = 5 \text{ V}$ | | | | |
| | | 0 | set to logic 0: and the VCC1V8 bit is logic 0: $V_{CC(n)} = 3 \text{ V}$ | | | | |
| 1 | WARM | 1 | set to logic 1: a warm reset procedure is started | | | | |
| | | 0 | set to logic 0: by the hardware: a START bit is detected or the MUTE bit is set to logic 1 | | | | |
| 0 | START 1 | | set to logic 1: when the SUPL and PROT bits are logic 0 and the PRES bit is logic 1, the activation sequence and cold reset procedure are started | | | | |
| | | 0 | set to logic 0: deactivation sequence starts | | | | |

^[1] This bit cannot be written when START bit is logic 1.

Remark: If both pins I/OUC1 and I/OUC2 are connected at the same time, this mandatory condition also applies to card slot 1.

[3] In synchronous mode, this bit cannot be written when START bit is logic 1.

^[2] It is a mandatory condition for card slots 2 to 5 that only one card slot I/O line is enabled at a time. When switching from one slot to another, the enabled I/O must be disabled before the I/O line for the required card slot is enabled.

Multiple smart card slot interface IC

8.5.4.4 Bank 1 CSb[7:0] Register1 (address 42h) card slots 3 and 5 bit allocation

Table 24. Bank 1 CSb[7:0] Register1 (address 42h) card slots 3 and 5 bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|------------------|-------------|-------------|---------|------------|------------|------------|---------------|-----|
| Card slot 3 (add | ress 03h), | card slot 4 | (addres | s 04h) an | d card slo | t 5 (addre | ess 05h) | |
| Reg[1:0] = 00 | | | | | | | | |
| Symbol | <u>-[1]</u> | RSTIN | - | <u>[1]</u> | CLKP | D[1:0][2] | CLKDIV[1:0[3] | |
| Access | R/W | R/W | R/W | R/W | R/W | R/W | R/W | R/W |
| Reg[1:0] = 01 | | | | | | ' | | |
| Symbol | | | | D[7: | :0] | | | |
| Access | | | | R/\ | V | | | |
| Reg[1:0] = 10 | | | | | | | | |
| Symbol | | | | C[15 | 5:8] | | | |
| Access | | | | R/\ | V | | | |
| Reg[1:0] = 11 | | | | | | | | |
| Symbol | | | | C[7: | :0] | | | |
| Access | | | | R/\ | V | | | |

^[1] Reserved bit position.

8.5.4.5 Bank 1 Register1 (REG[1:0] = 00) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode

Table 25. Bank 1 Register1 (REG[1:0] = 00) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode

| Bit | Symbol | Value | Description |
|--------|--------|-------|---|
| 7 | - | - | reserved |
| 6 | RSTIN | 1 | synchronous mode: when set to logic 1, pin $RST_{(n)}$ is set to HIGH asynchronous mode: RSTIN is controlled by the hardware (ATR management) |
| | | 0 | set to logic 0: RST _(n) is set LOW |
| 5 to 4 | - | - | reserved |

^[2] CLKPD[2] = bit 3 and <math>CLKPD[1] = bit 2.

^[3] CLKDIV[2] = bit 2 and CLKDIV[1] = bit 1.

Multiple smart card slot interface IC

Table 25. Bank 1 Register1 (REG[1:0] = 00) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode ...continued

| Bit | Symbol | Value | Description |
|--------|-------------|-------|--|
| 3 to 2 | CLKPD[1:0] | - | asynchronous mode: when PWDN bit is set to logic 1, the CLKPD[1] and CLKPD[2] bits define the card clock |
| | | - | synchronous mode: when the PWDN bit and the START bit are set to logic 1, the CLKPD[2] bit remains logic 0 and the clock frequency is controlled by the CLKPD[1] bit |
| | | 00 | asynchronous mode: the card clock is stopped and set to logic 0 |
| | | - | synchronous mode: the card clock is set to logic 0 |
| | | 01 | asynchronous mode: the card clock is stopped and set to logic 1 |
| | | - | synchronous mode: the card clock is set to logic 1 |
| | | 10 | asynchronous mode: the card clock = $f_{osc(int)}/2$ |
| | | | Remark: (f _{osc(int)} is the internal oscillator frequency) |
| | | 11 | asynchronous mode: the card clock frequency $(f_{(clk)})$ is set using the CLKDIV[1:0] bits. |
| 1 to 0 | CLKDIV[1:0] | | synchronous mode: the CLKDIV[1] and CLKDIV[2] bits are set to logic 0 by the hardware |
| | | | asynchronous mode: PWDN bit is logic 0, the CLKDIV[1] and CLKDIV[2] bits define the card clock as follows: |
| | | 00 | f _{clk(ext)} on pin CLKIN2 for card slots 2 to 5 |
| | | 01 | f _{clk(ext)} / 2 on pin CLKIN2 for card slots 2 to 5 |
| | | 10 | f _{clk(ext)} / 4 on pin CLKIN2 for card slots 2 to 5 |
| | | 11 | f _{clk(ext)} / 5 on pin CLKIN2 for card slots 2 to 5 |

8.5.4.6 Bank 1 Register1 (REG[1:0] = 01) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

Table 26. Bank 1 Register1 (REG[1:0] = 01) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | |
|--------|---|--------|---|---|----|---|---|---|--|
| Symbol | | D[7:0] | | | | | | | |
| Access | | | | R | /W | | | | |

8.5.4.7 Bank 1 Register1 (REG[1:0] = 01) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

Table 27. Bank 1 Register1 (REG[1:0] = 01) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|--|
| 7 to 0 | | programmable 8-bit clock counter. This value applies to all slots. The reset value is AAh. See Section 8.9 "Answer to reset counters" on page 36 |

Multiple smart card slot interface IC

8.5.4.8 Bank 1 Register1 (REG[1:0] = 10) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

Table 28. Bank 1 Register1 (REG[1:0] = 10) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | |
|--------|---|---------|---|---|----|---|---|---|--|
| Symbol | | C[15:8] | | | | | | | |
| Access | | | | R | /W | | | | |

8.5.4.9 Bank 1 Register1 (REG[1:0] = 10) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

Table 29. Bank 1 Register1 (REG[1:0] = 10) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|---|
| 7 to 0 | | most significant byte of a programmable 16-bit clock counter. This value applies to all slots. The reset value is A4h. See ATR Section 8.9 "Answer to reset counters" on page 36 |

8.5.4.10 Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

Table 30. Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 | |
|--------|---|--------|---|---|----|---|---|---|--|
| Symbol | | C[7:0] | | | | | | | |
| Access | | | | R | /W | | | | |

8.5.4.11 Bank 1: Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

Table 31. Bank 1: Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) and card slot 5 (address 05h) read/write mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|---|
| 7 to 0 | C[7:0] | least significant byte of a programmable 16-bit clock counter. This value |
| | | applies to all slots. The reset value is 74h. See Section 8.9 on page 36 |

8.5.5 Selection of asynchronous or synchronous mode

When the activation sequence starts, the selected card slot on the TDA8026 uses the RSTIN bit value to configure itself for use with asynchronous or synchronous cards. If the RSTIN bit is set to logic 1 at the activation sequence start (the START bit changes from LOW to HIGH), the TDA8026 will manage asynchronous cards.

In asynchronous mode, the card slot $RST_{(n)}$ pin is controlled by the corresponding ATR counter (see Section 8.9 on page 36).

In synchronous mode, the card slot $RST_{(n)}$ pin is controlled by the corresponding RSTIN bit. The card clock configuration is set by the PWDN bit value at the activation sequence start of the selected card slot (the START bit changed from LOW to HIGH).

Multiple smart card slot interface IC

If the PDWN bit is set to logic 0 at the start of the activation, the card clock value is the CLKIN1 pin frequency for card slot 1 and the CLKIN2 pin frequency for card slots 2 to 5. If CLKDIV[1:0] = 00, the first four clock cycles are not transferred to CLK_(n). When CLKDIV[1:0] = 01, 10 or 11, the first five clock cycles are not transferred to CLK_(n).

 If the PDWN bit is set to logic 1 at the start of the activation, the clock uses the CLKPD1 bit.

The card clock frequency and the stop state are configured using the CLKDIV[1:0] and CLKPD[1:0] bits. Refer to <u>Table 32</u> for the configuration in asynchronous mode and <u>Table 33</u> for synchronous mode.

Table 32. Asynchronous mode card clock settings

| PWDN bit | CLKDIV[1:0] bit | CLKPD[1:0] bit | Card clock (CLK) |
|----------|-----------------|----------------|---------------------------------------|
| 0 | 00 | - | f _{clk(ext)} |
| 0 | 01 | - | f _{clk(ext)} / 2 |
| 0 | 10 | - | f _{clk(ext)} / 4 |
| 0 | 11 | - | f _{clk(ext)} / 5 |
| 1 | - | 00 | logic 0 |
| 1 | - | 01 | logic 1 |
| 1 | - | 10 | $f_{osc(int)}/2$ |
| 1 | - | 11 | f _{clk(ext)} / x (no change) |

Table 33. Synchronous mode card clock settings

| PWDN bit | CLKDIV[1:0] bit | CLKPD[1:0] bit | Card clock (CLK) |
|---|-----------------|----------------|-----------------------|
| logic 1 at activation sequence start | - | x0 | logic 0 |
| logic 1 at activation sequence start | - | x1 | logic 1 |
| logic 0 at activation sequence start[1] | - | xx | f _{clk(ext)} |

^[1] If CLKDIV[1:0] = 00, the first four clock cycles are not transferred to $CLK_{(n)}$. When CLKDIV[1:0] is not 00, the first five clock cycles are not transferred to $CLK_{(n)}$.

 $f_{\text{clk(ext)}}$ is the clock input frequency on either pin CLKIN1 or pin CLKIN2 depending on the card slot number.

During transitions, no pulse is shorter than 45 % of the smallest period and both the first/last clock pulse around the change have the correct width; making the frequency change synchronous.

When changing the card clock frequency from one $f_{\text{clk(ext)}}$ frequency division to another, the modification is only active after the next rising clock edge.

Any change after switching the card clock frequency from an external $f_{clk(ext)}$ frequency division to the internal oscillator frequency ($f_{osc(int)}$) is not immediate. The change is indicated by the state of the CLKSW bit (see the register descriptions in <u>Table 11</u> and <u>Table 22</u>). In addition, it is assumed that the $f_{clk(ext)}$ / x frequency division is less than or equal to 6.25 MHz.

Multiple smart card slot interface IC

8.5.6 General registers

8.5.6.1 Bank 1 General registers (address: 40h, 42h; CSb[7:0] = 00h, 06h) bit allocation

Table 34. Bank 1 General registers (addresses: 40h, 42h; CSb[7:0] = 00h, 06h) bit allocation

| Bit | 7 | 6 | 5 | 4 | 3 | 2 | 1 | 0 |
|-----------|--------------|-------------|-------------------|-------------------------|-------|---------|------|--------|
| Address 4 | 0h; CSb[7: | 0] = 00h, s | ee <u>Table 3</u> | <u>5</u> | | | | |
| Symbol | PV[7:0] | | | | | | | |
| Access | R | | | | | | | |
| Address 4 | 0h; CSb[7: | 0] = 06h | | | | | | |
| Symbol | CLK_SI | R[3:2] | IO_SR[3:2] | | CLK_S | SR[1:0] | IO_S | R[1:0] |
| Access | R/V | V | R/W | | R | /W | R | /W |
| Address 4 | 2h; CSb[7: | 0] = 00h | 1 | | | | 1 | |
| Symbol | _ <u>[1]</u> | | INTAUX | INT[4:0] ^[2] | | | | |
| Access | R | | R | R | | | | |

^[1] Reserved bit position.

8.5.6.2 Bank 1 Product version register (address 40h; CSb[7:0] = 00h) read mode bit descriptions

Table 35. Bank 1 Product version register (address 40h; CSb[7:0] = 00h) read mode bit descriptions

| Bit | Symbol | Description |
|--------|--------|--|
| 7 to 0 | | reading this register returns the product version. The MSB nibble is C (commercial product) and the LSB nibble is 2 (release number) |

^[2] The INT numbers do not match the bit positions and are as follows: bit 4 = INT5, bit 3 = INT4, bit 2 = INT3, bit 1 = INT2 and bit 0 = INT1

Multiple smart card slot interface IC

8.5.6.3 Bank 1 Interrupt register (address 42h; CSb[7:0] = 00h) read mode bit descriptions

Table 36. Bank 1 Interrupt register (address 42h; CSb[7:0] = 00h) read mode bit descriptions

| Bit | Symbol | Value | Description |
|--------|-------------|-------|---|
| 7 to 6 | - | - | reserved |
| 5 | INTAUX | - | auxiliary interrupt line |
| 4 to 0 | INT[4:0][1] | | These interrupt bits remain at logic 1 until the interrupt SUPL, PROT, MUTE and EARLY bits have been read |
| | | | INT5: card slot 5 interrupt: |
| | | 1 | set to logic 1: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 1 |
| | | 0 | set to logic 0: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 0 when read |
| | | | INT4: card slot 4 interrupt: |
| | | 1 | set to logic 1: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 1 |
| | | 0 | set to logic 0: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 0 when read |
| | | | INT3: card slot 3 interrupt: |
| | | 1 | set to logic 1: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 1 |
| | | 0 | set to logic 0: when any of the bits SUPL, PROT, MUTE and EARLY are set to logic 0 when read |
| | | | INT2: card slot 2 interrupt: |
| | | 1 | set to logic 1: when any of the bits PRESL, SUPL, PROT, MUTE and EARLY are set to logic 1 |
| | | 0 | set to logic 0: when any of the bits PRESL, SUPL, PROT, MUTE and EARLY are set to logic 0 when read |
| | | | INT1: card slot 1 interrupt: |
| | | 1 | set to logic 1: when any of the bits PRESL, SUPL, PROT, MUTE and EARLY are set to logic 1 |
| | | 0 | set to logic 0: when any of the bits PRESL, SUPL, PROT, MUTE and EARLY are set to logic 0 when read |

^[1] The INTx numbers do not match the bit positions and are as follows: bit 4 = INT5, bit 3 = INT4, bit 2 = INT3, bit 1 = INT2 and bit 0 = INT1

8.5.6.4 Bank 1 Slew rate register (address 40h; CSb[7:0] = 06h) read/write mode bit descriptions

Table 37. Bank 1 Slew rate register (address 40h; CSb[7:0] = 06h) read/write mode bit descriptions

| Bit | Symbol | Description |
|--------|-------------|--|
| 7 to 6 | CLK_SR[3:2] | card slot 2 to 5 clock slew rate selection |
| 5 to 4 | IO_SR[3:2] | card slot 2 to 5 I/O slew rate selection |
| 3 to 2 | CLK_SR[1:0] | card slot 1 clock slew rate selection |
| 1 to 0 | IO_SR[1:0] | card slot 1 I/O slew rate selection |

Refer <u>Section 8.10 on page 38</u> for more detailed information.

Multiple smart card slot interface IC

8.6 DC-to-DC converter


The DC-to-DC converter has been designed to provide an average of 5.4 V to the programmable voltage regulators (5 V, 3 V and 1.8 V) for the card slots. It is capable of delivering a total DC current of 116 mA to the card slots.

If the total current from all card slots exceeds 170 mA, the overcurrent/overload protection deactivates the DC-to-DC converter. The addition of a 10 μ H external coil and Schottky diode ensures the DC-to-DC converter operates at an input voltage range between 2.7 V and 5.5 V.

When the DC-to-DC converter cannot act as a step-up converter, an overload alarm is sent to the digital module and all card slot interfaces are deactivated. This causes the IRQN line to be driven LOW and the Bank 1 Register 0 PROT bit is set to logic 1.

The DC-to-DC converter is deactivated when the TDA8026 is in shutdown mode.

The card slots can be directly supplied by the V_{DD} supply voltage, if it is always above 5.25 V, thus removing the need to use the DC-to-DC converter. In this situation, the supply voltage can be directly applied to the V_{UP} and LX pins as shown in Figure 9.



When DCDC_OFF is set to V_{DD(INTF)}, the DC-to-DC converter is shutdown:

- the output power transistors are switched OFF
- the DC-to-DC converter current consumption is 0 A.

8.7 V_{CC} buffer

The current on the V_{CC} buffer is internally limited to approximately 100 mA. When this limit is reached, the automatic deactivation sequence is performed. Each card slot has its own limitation and deactivation of one card slot does not affect the other card slots.

The $V_{CC(n)}$ voltage should be decoupled with two low ESR 100 nF (minimum) capacitors. One capacitor should be placed close to the V_{CC} pin of the device and the other close to the C1 pin of the card connector. See <u>Figure 14</u> for detailed information.

8.8 Sequencer and clock counter

Each card slot has a dedicated sequencer and clock counter.

The sequencer ensures that the activation and deactivation sequences meet the ISO 7816 and EMV 4.3 standards, even during an emergency deactivation caused by card removal during transaction, supply drop out or a hardware problem. The sequencer is clocked with an internal oscillator (fosc(int)).

Multiple smart card slot interface IC

Card slot 1 or card slot 2 can only be activated if a card is detected as present in the slot and if an alarm is not triggered by the voltage supervisor. When both of these parameters are met, the card slots can be activated by setting the Command register START bit. The activation sequence is described in Section 8.8.2.

Card slots 3 to 5 do not have presence monitoring. The corresponding STAP pin is used for card presence detection on these slots.

The deactivation is initiated by the system controller or automatically in the case of a hardware problem or a supply drop out. The deactivation sequence is described in Section 8.8.3.

Outside a session, the card contacts are forced to low-impedance with respect to the GNDC pin.

8.8.1 Standby mode

Standby mode is the default state after a power-on reset. This mode ensures the power consumption remains low until a card is inserted or the microcontroller starts a card session. When there is not an ongoing card session, the internal oscillator runs at its low frequency (t_{15}).

A debouncing time of 17.8 ms is applied to card slot 1 and card slot 2 to allow for card insertion (presence) detection.

8.8.2 Activation sequence

When the card is inactive, pins $V_{CC(n)}$, $CLK_{(n)}$, $RST_{(n)}$ and $I/O_{(n)}$ are LOW which is low-impedance with respect to pin $GNDC_{(n)}$ or pin GNDS depending of the card slot.


The sequencer is clocked by an internal oscillator. When everything is satisfactory (voltage supply, card presence, no hardware problem), the system controller can trigger the card present activation sequence by setting card slot's START bit to logic 1:

- The internal oscillator switches to its high frequency (t₀, see Figure 10).
- The DC-to-DC converter starts (t₁).
- V_{CC(n)} starts to rise from 0 V to 1.8 V, 3 V or 5 V during the controlled rise time (t₂).
- The voltage on the I/O_(n) pin rises to $V_{CC(n)}$, due to integrated 10 k Ω pull-ups for $V_{CC(n)}$ (t₃).
- CLK_(n) clock signal is sent to the card (t₄ = t_{act}) and the RST_(n) pin is enabled. The
 RST_(n) pin is managed by the ATR counter or the Register1 RSTIN bit depending on
 the card slot mode (asynchronous or synchronous).

The sequencer is clocked by $\frac{f_{osc(int)}}{64}$ which leads to a time interval T = 25 μs (typical).

Thus,
$$t_1=0$$
, $t_2=t_1+\frac{3T}{2}$, $t_3=t_1+\frac{7T}{2}$ and $t_4=t_1+4T$.

Multiple smart card slot interface IC



In <u>Figure 10</u> only one card slot is activated. If another card slot is active, the DC-to-DC converter remains active.

8.8.3 Deactivation sequence


When the session finishes, the microcontroller resets the START bit to logic 0 (Figure 11) and the following deactivation sequence is performed:

- Card reset: RST_(n) pin falls to 0 V (t₁₁).
- Pin CLK_(n) is stopped (t₁₂).
- Pin I/O_(n) falls to 0 V (t₁₃).
- Pin V_{CC(n)} falls to 0 V with a controlled slew rate (t₁₄).
- The DC-to-DC converter is stopped.
- Pins CLK_(n), RST_(n), V_{CC(n)} and I/O_(n) are driven to 0 V with a low-impedance switch attached to pin GNDS (t₁₅).
- The internal oscillator switches to its low frequency (t₁₅)

Thus,
$$t_{11} = 0$$
, $t_{12} = t_{11} + \frac{T}{2}$, $t_{13} = t_{11} + T$, $t_{14} = t_{11} + \frac{3T}{2}$ and $t_{15} = t_{11} + \frac{7T}{2}$.

The deactivation time t_{deact} is the time that $V_{CC(n)}$ needs to be driven below 0.4 V, counting from the moment START bit is reset.

Multiple smart card slot interface IC



In <u>Figure 11</u> only one card slot is active. If another card slot is active, the DC-to-DC converter is still active.

8.9 Answer to reset counters

Each TDA8026 card slot has its own sequencer. The sequencer controls the activation and deactivation sequences. In addition to these sequencers, there are two Answer To Reset (ATR) counters:

- ATR dedicated to card slot 1
- · ATR dedicated to the other slots

The operating mode (asynchronous or synchronous) has to be selected by the microcontroller. The ATR counters are used in asynchronous mode to manage the RST_(n) pin and to check the card's ATR. In synchronous mode, the RST pin is controlled by the microcontroller using the RSTIN bit (see the bit description in <u>Table 11 on page 20</u> and <u>Table 22 on page 25</u>) and the card's ATR is not checked.

The ATR counter module comprises two counters:

- EARLY answer counter: The early answer counter consists of a fixed part which
 counts up to 200 clock cycles. The secondary part counts up to the D[7:0] bits value of
 clock cycles (see the register descriptions in <u>Table 16 on page 24</u> and <u>Table 27 on
 page 28</u>). The default D[7:0] bits value is 170 which gives a total default count of
 370 clock cycles
- MUTE counter: The mute counter counts up to C[15:8] and C[7:0] bits value for the clock cycles (see the register descriptions in <u>Table 22 on page 25</u> and <u>Table 30 on page 29</u>). The default value of the C[15:0] bits is 42100 which gives a default count of 42100 clock cycles.

Both counters can be easily quickly reprogrammed, if for example, a card does not fully meet the EMVCo/ISO7816 standards or to enable the implementation of new and enhanced standards.


Multiple smart card slot interface IC

When operating, the microcontroller starts to configure the selected card slot (card supply voltage) and then triggers the activation sequence using the START bit. The sequencer then performs the activation sequence. The DC-to-DC converter is started, pin $V_{CC(n)}$ is set to the previously configured card supply voltage, pin $I/O_{(n)}$ is enabled and $CLK_{(n)}$ starts (see Section 8.8.2 on page 34 and Section 8.8.3 on page 35). Pin RST_(n) is set to LOW.

The ATR counter dedicated to the card slot makes the following checks and takes the steps required:

- START bits from a card detected on pin I/O_(n) during the first 200 clock cycles are ignored and the count continues.
- START bits from a card detected while pin RST_(n) is set to LOW, with the number of clock cycles between 200 and the C[15:0] bits value (default 42100), cause the EARLY and MUTE bits to be set to logic 1. Pin RST_(n) remains LOW and the microcontroller decides if it will accept the card.
- START bits detected after the number of clock cycles is equal to the C[15:0] bits value cause pin RST_(n) to be set to HIGH.
- START bits received from the card when the first number of clock cycles is equal to the D[7:0] bits value (default 370) and pin RST_(n) set to HIGH cause the EARLY bit to be set to logic 1.
- Cards not answering before 42100 clock cycles (or the C[15:0] bits value) with RST_(n) set to HIGH cause the MUTE bit to be set to logic 1.
- Cards answering within the correct time frame, stops the clock cycles count and the microcontroller can send commands to the card.

Figure 12 shows the timings checked by the ATR counters.



When the EARLY and MUTE bits are set to logic 1, they signal an interrupt (see the bit descriptions in <u>Table 12 on page 21</u>, <u>Table 22 on page 25</u> and <u>Table 36 on page 32</u>).

TDA8026_1

Multiple smart card slot interface IC

The sequence described in Section 8.9 relates to a cold reset. If the card is mute (has not answered), the microcontroller can start a warm reset by setting WARM bit to logic 1 (see the bit descriptions in Table 11 on page 20 and Table 22 on page 25). Then, the ATR counter set pin $RST_{(n)}$ to LOW and performs the same timing checks (see Figure 12).

Remark: It is assumed that two card activations will not take place simultaneously on card slots 2 to 5 because only one $I/O_{(n)}$ line is available for these four slots. There is no protection on the second ATR counter against starting an activation while a count is ongoing. The first ATR counter is dedicated to the slot 1. Consequently, it is mandatory to enable only one slot $I/O_{(n)}$ line at the same time for card slots 2 to 5. When switching from one slot to another one, it is mandatory to first disable the slot $I/O_{(n)}$ line in use before enabling the slot $I/O_{(n)}$ line required. During this transition, no $I/O_{(n)}$ lines are enabled for card slots 2 to 5. This allows the ATR counter to be reset between card slot switching actions. If both pins I/OUC1 and I/OUC2 are connected at the same time, this mandatory condition also applies to card slot 1.

8.10 Slew rate control

Slew rate control is embedded for the clock buffer and the $I/O_{(n)}$ line of each card slot. The rising and falling edge of the card clock signal can be configured using 2 bits in Register6 of bank 1. The settings based on a 30 pF load capacitance and a $V_{CC(n)} = 5$ V are shown in Table 38.

Table 38. Clock Slew rate

| CLK_SR ^[1] (high) | CLK_SR ^[2] (low) | Rise and fall time (ns) |
|------------------------------|-----------------------------|-------------------------|
| L | L | 10 |
| L | Н | 7 |
| Н | L | 6 |
| Н | Н | 5 |

^[1] The high slots are define by [1] (slot 1) and [3] (all other slots).

The rise and fall time is calculated from 10 % to 90 % and 90 % to 10 % (respectively) of the signal amplitude. The default setting for CLK_SR[1]/CLK_SR[3] (high) is LOW and CLK_SR[0]/CLK_SR[2] (low) is HIGH.

Only the falling edge of the card $I/O_{(n)}$ signal can be configured with the two programmable bits in Register6 of bank 1. The settings based on a 30 pF load capacitance and a $V_{CC(n)} = 5$ V are shown in Table 39 on page 38:

Table 39. I/O slew rate

| IO_SR[1] (high) | IO_SR ^[2] (low) | Fall time (ns) |
|-----------------|----------------------------|----------------|
| L | L | 67 |
| L | Н | 54 |
| Н | L | 35 |
| Н | Н | 17 |

^[1] The high slots are define by [1] (slot 1) and [3] (all other slots).

^[2] The low slots are define by [0] (slot 1) and [2] (all other slots).

^[2] The low slots are define by [0] (slot 1) and [2] (all other slots).

Multiple smart card slot interface IC

The fall time is calculated from 90 % to 10 % of the signal amplitude. The default setting for IO_SR[0]/IO_SR[2] (low) and IO_SR[1]/IO_SR[3] (high) is LOW (see table <u>Table 39 on page 38</u>).

8.11 Fault detection

The following fault conditions are monitored by the TDA8026.

- Overheating: All the card slots are automatically deactivated and the device is forced in to Standby mode when the detected temperature range is between 125 °C to 209 °C. The card slot PROT bit is set to logic 1. Above 209 °C the device is shutdown.
- Card removal during transaction: A deactivation sequence is performed in accordance with the EMV 4.2 standard.
- DC-to-DC converter overload: All card slots are automatically deactivated and the device is placed in Standby mode when the current supplied by the DC-to-DC converter exceeds 170 mA (I_{CC} parameter for V_{CC(n)}). The card slot PROT bit is set to logic 1
- Card slot current limitation and deactivation: A current level drawn by a card
 which exceeds 120 mA (I_{sd} parameter for V_{CC(n)}) triggers the deactivation sequence
 on the faulty card slot. During the deactivation, the current is limited to approximately
 110 mA. The card slot PROT bit is set to logic 1
- V_{DD} or V_{DD(INTF)} dropping: A voltage drop occurring on V_{DD} or V_{DD(iNTF)} generates card slot deactivation followed by a device reset. The completion of this phase is validated when the SUPL bits are set to logic 1.

Multiple smart card slot interface IC

9. Limiting values

Table 40. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | | Min | Max | Unit |
|-----------------------|--------------------------|--|-----|------|------|------|
| V_{DD} | supply voltage | on pin V _{DD} | | -0.5 | +6 | V |
| V _{DD(INTF)} | interface supply voltage | on pin V _{DD(INTF)} | | -0.5 | +4.6 | V |
| V _{IH} | HIGH-level input | on all card pins | | -0.5 | +6 | V |
| | voltage | on all other pins | | -0.5 | +4.6 | V |
| Vo | output voltage | on pin LX | [1] | -0.5 | +7.2 | V |
| Ü | | DC-to-DC converter output on pin V _{UP} | [1] | -0.5 | +7.2 | V |
| P _{tot} | total power dissipation | $T_{amb} = -25 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$ | | - | 665 | mW |
| T _{stg} | storage temperature | | | -55 | +150 | °C |
| V _{ESD} | electrostatic | НВМ | [2] | | | |
| | discharge voltage | on I/O _(n) , $V_{CC(n)}$, $CLK_{(n)}$, $GNDC_{(n)}$, PRES, $RST_{(n)}$, $C4_{(1)}$, $C8_{(1)}$ card pins | [3] | -7 | +7 | kV |
| | | on all other pins | | -2 | +2 | kV |
| | | MM | | | | |
| | | on all pins | | -200 | +200 | V |
| | | CDM | | | | |
| | | on all pins | | -500 | +500 | V |

^[1] The limiting values depend on the external inductor and V_{UP} decoupling capacitor used.

10. Thermal characteristics

Table 41. Thermal characteristics

| Symbol | Parameter | Conditions | | Тур | Unit |
|---------------|---|------------|-----|------|------|
| $R_{th(j-a)}$ | thermal resistance from junction to ambient | | [1] | 47.1 | K/W |

[1] With a 4-layer board

^[2] Every pin withstands the ESD test according to MIL-STD-883C class 3 for card contacts, class 2 for the remaining. Method 3015 (HBM; 1500 Ω ; 100 pF) defines three pulses positive and three pulses negative on each pin referenced to ground.

^[3] The 7 kV ESD test is performed in the typical application configuration as depicted in the *Application note AN10724* with two external capacitors connected to each V_{CC(n)} line.

Multiple smart card slot interface IC

11. Characteristics

Table 42. Supply

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; GND} = 0 \text{ V; inductor} = 10 \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \mu\text{F; } T_{amb} = 25 \text{ }^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|-----------------------|--------------------------|---|------------|------|------|------|------|
| V_{DD} | supply voltage | on pin V _{DD} ; DC-to-DC converter on | [2] | 2.7 | - | 5.5 | V |
| | | on pin V_{DD} ; DC-to-DC converter off; $V_{CC(n)}$ pins = 5 V | [2] | 5.25 | - | 5.5 | V |
| V _{hys} | hysteresis voltage | on pin V _{DD} | [3] | 50 | 100 | 150 | mV |
| $V_{DD(INTF)}$ | interface supply voltage | on pin V _{DD(INTF)} | | 1.6 | - | 3.6 | V |
| V_{th} | threshold voltage | decreasing voltage on pin V _{DD} | [3] | 2.35 | 2.45 | 2.55 | V |
| | | on pin V _{DD(INTF)} | | 1.19 | 1.26 | 1.32 | V |
| I _{DD} | supply current | shutdown mode | - 25 40 | 40 | μΑ | | |
| | | Standby mode | | - | 300 | 450 | μΑ |
| | | clock-stop mode; All card slots in this mode; f _{clk(ext)} = stopped on pins CLKIN1 and CLKIN2 | | - | 3.7 | - | mA |
| | | active mode; All $V_{CC(n)}$ pins = 5 V; $f_{clk(ext)}$ = 5 MHz; $I_{CC(1)}$ = $I_{CC(2)}$ = 55 mA; $I_{CC(3)}$ = $I_{CC(4)}$ = $I_{CC(5)}$ = 2 mA | [5] [6] | - | 210 | 260 | mA |
| I _{DD(INTF)} | interface supply | shutdown mode | | - | 10 | 15 | μΑ |
| | current | active mode; All $V_{CC(n)}$ pins = 5 V; $f_{clk(ext)}$ = 5 MHz; | | - | 35 | - | μΑ |
| | | increasing voltage on pin V _{DD} | [3] | 2.35 | 2.55 | 2.65 | V |
| t _{wake} | wake-up time | | | 5.8 | - | 11 | ms |

- [1] $f_{clk(ext)}$ is the external clock frequency applied to pins CLKIN1 and CLKIN2.
- [2] Refer to Section 8.6 for further information about DC-to-DC converter operation.
- [3] See Figure 6 "The voltage supervisor circuit" on page 12.
- [4] See Section 8.3.2 "Description" for a description of the voltage supervisor.
- [5] Typical value measurement based on a 85 % DC-to-DC converter and inductance efficiency; depends on PCB layout and external component quality (inductor, capacitor).
- [6] Maximum measurement value based on a 125 mA I_{CC} current load and a 75 % DC-to-DC converter and inductance efficiency; depends on PCB layout and external component quality (inductor, capacitor).

Table 43. Supply supervisor

 $V_{DD}=V_{DD(INTF)}=3.3~V;~f_{clk(ext)}=10~MHz;~GND=0~V;~inductor=10~\mu H;~decoupling~capacitors~on~pins~V_{DD}~and~V_{UP}=10~\mu F;~T_{amb}=25~^{\circ}C~unless~otherwise~specified.$

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|-----------------|--------------------------|------------|-----|-----|-----|------|
| PORADJ Pin | | | | | | |
| IL | leakage current | | -1 | - | +1 | μΑ |
| I _{IL} | LOW-level input current | | -1 | - | +1 | μΑ |
| I _{IH} | HIGH-level input current | | -1 | - | +1 | μА |

Multiple smart card slot interface IC

Table 44. DC-to-DC converter

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins V and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|-----------------------|-------------------------------|--|------|------|-----|------|
| f _{osc(int)} | internal oscillator frequency | | 2.1 | 2.8 | 3.5 | MHz |
| Vo | output voltage | from DC-to-DC converter; DC-to-DC converter on; not bypassed | 5.25 | 5.5 | - | V |
| Vi | input voltage | pin LX input voltage; DC-to-DC converter on; not bypassed | - | - | 7.2 | V |
| t _{on(DCDC)} | DC-to-DC converter | V _{DD} < 4.2 V | - | 1.4 | - | μS |
| | turn-on time | V _{DD} > 4.2 V | - | 0.35 | - | μμs |

Table 45. Card drivers

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|--------------------------|---|---|-----|------|-----|------|------|
| Card suppl | y voltage: V _{CC(1)} to V _{CC(1)} | 5) [1] | | 1 | | ' | • |
| V _{CC} | supply voltage | Standby mode | | | | | |
| | | no load | | -0.1 | - | +0.1 | V |
| | | I _o = 1 mA | | -0.1 | - | +0.3 | V |
| | | active mode; 2.7 V < V _{DD} < 5.5 V | [2] | | | | |
| | | 5 V card; DC I _{CC(n)} ≤ 55 mA | | 4.75 | 5 | 5.25 | V |
| | | 3 V card; DC $I_{CC(n)} \le 55$ mA | | 2.85 | 3 | 3.15 | V |
| | | 1.8 V card; DC $I_{CC(n)} \le 35 \text{ mA}$ | | 1.71 | 1.8 | 1.89 | V |
| | | active mode; AC current pulses with I < 200 mA, t < 400 ns and f < 20 MHz | [2] | | | | |
| | | 5 V card; 40 nAs current spikes | | 4.65 | - | 5.35 | V |
| | | 3 V card; 17.5 nAs current spikes | | 2.76 | - | 3.24 | V |
| | | 1.8 V card; 11.1 nAs current spikes | | 1.62 | - | 1.98 | V |
| V _{ripple(p-p)} | peak-to-peak ripple voltage | on pins V _{CC(n)} ; 20 kHz < card clock frequency < 200 MHz | | - | - | 350 | mV |

Multiple smart card slot interface IC

Table 45. Card drivers ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|------------------|---|---|-----|--------------------------|------|--------------------|------|
| I _{CC} | supply current | Standby mode and pin V _{CC(n)} grounded | | - | - | -1 | mA |
| | | active mode; 2.7 V < V _{DD} < 5.5 V | | | | | |
| | | 5 V card | | - | - | 55 | mA |
| | | 3 V card | | - | - | 55 | mA |
| | | 1.8 V card | | - | - | 35 | mA |
| | | sum of all card supply currents on pins $V_{CC(n)}$; active mode; All V_{CC} pins = 5 V; $f_{clk(ext)}$ on pins $CLK_{(n)}$ = 5 MHz; $I_{CC(1)}$ = $I_{CC(2)}$ = 55 mA; $I_{CC(3)}$ = $I_{CC(4)}$ = $I_{CC(5)}$ = 2 mA | [5] | - | 116 | 125 | mA |
| SR | slew rate | rising; maximum C _L = 200 nF; 5 V, 3 V and 1.8 V cards | | 0.06 | 0.16 | 0.27 | V/μs |
| C _{dec} | decoupling capacitance | connected to V _{CC(n)} ; 100 nF and 100 nF at 20 % | | 160 | 200 | 240 | nF |
| Card rese | et output pins: RST ₍₁₎ to R | ST ₍₅₎ | | | | | |
| V_o | output voltage | Standby mode | | | | | |
| | | no load | | 0 | - | 0.1 | V |
| | | I _o = 1 mA | | 0 | - | 0.3 | V |
| Io | output current | Standby mode and pin RST _(n) grounded | | 0 | - | -1 | mA |
| V_{OL} | LOW-level output voltage | $I_{OL} \le 200 \ \mu A$ - C2 version | | 0 | - | 0.3 | V |
| | | $I_{OL} \le 200~\mu\text{A}$ - C3 version | | 0 | - | 0.15 VCC(n) | V |
| | | $I_{OL} \le 20 \text{ mA}$ | | V _{CC(n)} - 0.4 | - | V _{CC(n)} | V |
| V _{OH} | HIGH-level output | $-200 \ \mu A \le I_{OH} \le 0$ | | V _{CC(n)} - 0.5 | - | V _{CC(n)} | V |
| | voltage | $-20 \text{ mA} \leq I_{OH} \leq 0$ | | 0 | - | 0.4 | V |
| t _r | rise time | C _L = 100 pF; 10 % to 90 % | | - | - | 0.1 | μS |
| t _f | fall time | C _L = 100 pF; 90 % to 10 % | | - | - | 0.1 | μS |
| Clock to c | card output pins: CLK ₍₁₎ to | CLK ₍₅₎ ; default register values | | | | | |
| V_o | output voltage | Standby mode | | | | | |
| | | no load | | 0 | - | 0.1 | V |
| | | $I_0 = 1 \text{ mA}$ | | 0 | - | 0.3 | V |
| Io | output current | Standby mode and CLK _(n) pin grounded | | 0 | - | -1 | mA |
| V_{OL} | LOW-level output | $I_{OL} \le 200~\mu\text{A}$ - C2 version | | 0 | - | 0.3 | V |
| | voltage | $I_{OL} \leq 200~\mu\text{A}$ - C3 version | | 0 | - | 0.15 VCC(n) | V |
| | | $I_{OL} \le 70 \text{ mA}$ | | $V_{CC(n)}-0.4$ | - | V _{CC(n)} | V |
| V_{OH} | HIGH-level output | $-200 \ \mu A \le I_{OH} \le 0$ | | $V_{CC(n)}-0.5$ | - | V _{CC(n)} | V |
| | voltage | $-70 \text{ mA} \le I_{OH} \le 0$ | | 0 | - | 0.4 | V |
| t _r | rise time | C _L = 30 pF; 10 % to 90 % | | - | - | 7 | ns |

Multiple smart card slot interface IC

Table 45. Card drivers ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|-----------------------|--|---|--------|--------------------------|-----|--------------------|------|
| t _f | fall time | C _L = 30 pF; 90 % to 10 % | | - | - | 7 | ns |
| f _{CLK} | frequency on pin CLK | all CLK _(n) pins; operating | | 0 | - | 20 | MHz |
| δ_{clk} | clock duty cycle | C _L = 30 pF | | 45 | - | 55 | % |
| SR | slew rate | rise and fall; C _L = 30 pF; 90 % to 10 % | | 0.2 | - | | V/ns |
| Data line | pins: I/O ₍₁₎ to I/O ₍₅₎ , C4 ₍₁₎ a | nd C8 ₍₁₎ | | | | | |
| Vo | output voltage | Standby mode | | | | | |
| | | no load | | 0 | - | 0.1 | V |
| | | I _o = 1 mA | | - | - | 0.3 | V |
| Io | output current | Standby mode and I/O _(n) , C4 ₍₁₎ or C8 ₍₁₎ pins grounded. | | 0 | - | -1 | mA |
| V_{OL} | LOW-level output | I _{OL} ≤ 1 mA - C2 version | | 0 | - | 0.3 | V |
| | voltage | I _{OL} ≤ 1 mA - C3 version | | 0 | - | 0.15 VCC(n) | V |
| | | $I_{OL} \le 15 \text{ mA}$ | | V _{CC(n)} - 0.4 | - | V _{CC(n)} | V |
| V _{OH} | HIGH-level output | no DC load | | 0.9V _{CC(n)} | - | $V_{CC(n)} + 0.1$ | V |
| | voltage | $-20 \mu A \le I_{OH} \le 0$ | | 0.8V _{CC(n)} | - | $V_{CC(n)} + 0.1$ | V |
| | | $-40 \mu A \le I_{OH} \le 0$ | | 0.7V _{CC(n)} | - | $V_{CC(n)} + 0.1$ | V |
| | | -15 mA ≤ I _{OH} ≤ 0 | | 0 | - | 0.4 | V |
| V_{IL} | LOW-level input voltage | All V _{CC(n)} - C2 version | | -0.3 | - | +0.8 | V |
| | | All V _{CC(n)} - C3 version | | -0.3 | - | 0.2 VCC | V |
| V_{IH} | HIGH-level input voltage | $V_{CC(n)} = 5 \text{ V} \text{ and } 3 \text{ V}$ | | 0.6V _{CC(n)} | - | V _{CC(n)} | V |
| | | V _{CC(n)} = 1.8 V - C2 version | | 0.7V _{CC(n)} | - | V _{CC(n)} | V |
| | | V _{CC(n)} = 1.8 V - C3 version | | 1.55 | - | V _{CC(n)} | V |
| V_{hys} | hysteresis voltage | on I/O _(n) | | - | 50 | - | mV |
| I _{IL} | LOW-level input current | 0 V applied to pin | [3] | - | - | 650 | μΑ |
| I _{LIH} | HIGH-level input leakage current | $V_{IH} = V_{CC(n)}$ | [3] | - | - | 10 | μΑ |
| I _{pu} | pull-up current | $V_{OH} = 0.9V_{CC(n)}$; $C_L = 30 \text{ pF}$ | [3] | 1 | - | - | mA |
| t _d | delay time | falling edge on pins I/O and I/Oµ _(n) or vice versa | [3][4] | | - | 400 | ns |
| t _{r(i)} | input rise time | $V_{\rm IL}$ minimum to $V_{\rm IH}$ maximum; 10 % to 90 % | | - | - | 1.2 | μS |
| t _{f(i)} | input fall time | V_{IL} maximum to V_{IH} minimum; 90 % to 10 % | | - | - | 1.2 | μS |
| $t_{r(o)}$ | output rise time | V_{IL} minimum to V_{IH} maximum; 10 % to 90 % | | - | - | 0.1 | μS |
| $t_{f(O)}$ | output fall time | $V_{\rm IL}$ maximum to $V_{\rm IH}$ minimum; 90 % to 10 % | | - | - | 0.1 | μS |
| C _i | input capacitance | | [3] | - | - | 10 | pF |
| R _{pu} | pull-up resistance | between pins $I/O_{(n)}$ or $C4_{(1)}$ or $C8_{(1)}$ and $V_{CC(n)}$ | [3] | 8 | 10 | 12 | kΩ |
| f _{max} | maximum frequency | input clock | [3] | - | - | 500 | kHz |

TDA8026_1

Multiple smart card slot interface IC

Table 45. Card drivers ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|------------------|----------------------------------|-------------------------------|--------|---------------------------|---------|----------------------------|------|
| Card pres | ence input: pin PRES; act | ive HIGH when SPRES pin = LO\ | N or a | ctive LOW wh | nen SPF | RES pin = HIGH | • |
| V_{IL} | LOW-level input voltage | | | -0.3 | - | +0.2 V _{DD(INTF)} | V |
| V_{IH} | HIGH-level input voltage | | | 0.8 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| I _{LIL} | LOW-level input leakage current | $V_i = 0.2V_{DD(INTF)}$ | | - | - | 70 | μΑ |
| I _{LIH} | HIGH-level input leakage current | $V_i = 0.8 V_{DD(INTF)}$ | | - | - | 5 | μΑ |
| t _{deb} | debounce time | | | - | 17.8 | 23.8 | ms |

- [1] Two ceramic multilayer capacitors of minimum 100 nF with low Equivalent Series Resistance (ESR) should be used in order to meet these specifications.
- [2] Output voltage towards the card, including ripple.
- [3] $I/O_{(n)}$ pin has an internal 10 k Ω pull-up resistor to $V_{CC(n)}$.
- [4] I/OUCn pin has an internal 11 k Ω pull-up resistor to $V_{DD(INTF)}$
- [5] Maximum value measurement based on a 125 mA (sum of all card supply currents on pins V_{CC(n)}) current load and a 75 % DC-to-DC converter and inductance efficiency; depends on PCB layout and external component quality (inductor, capacitor).

Table 46. Sequencer and clock counter

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V}; f_{clk(ext)} = 10 \text{ MHz}; GND = 0 \text{ V}; inductor = 10 \mu\text{H}; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \mu\text{F}; T_{amb} = 25 ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|--------------------|-------------------|----------------|-----|-----|-----|-----|------|
| t _{act} | activation time | total sequence | [1] | - | - | 135 | μS |
| t _{deact} | deactivation time | total sequence | [1] | 60 | 80 | 100 | μS |
| T _{clk} | clock period | sequencer | | - | 25 | - | μS |

^[1] Refer to Section 8.8.3 for further information.

Table 47. Interface signals to microcontroller

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Parameter | Conditions | | Min | Тур | Max | Unit |
|----------------------------------|---|---|--|---|---|---|
| pins: I/OUC1 and I/O | UC2[1] | | | | | |
| LOW-level output voltage | I _{OL} = 1 mA | (| 0 | - | 0.3 | V |
| HIGH-level output | no DC load | (| 0.9 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.2$ | V |
| voltage | $-10 \ \mu A \le I_{OH} \le 0$ | (| 0.75 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.2$ | V |
| LOW-level input voltage | | - | -0.3 | - | +0.25 V _{DD(INTF)} | V |
| HIGH-level input voltage | | (| 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| LOW-level input current | V _{IL} = 0 V | - | - | - | 600 | μΑ |
| hysteresis voltage | on I/OUC _(n) | | - | 0.19V _{DD(INTF)} | - | V |
| HIGH-level input leakage current | $V_{IH} = V_{DD(INTF)}$ | | - | - | 10 | μΑ |
| | pins: I/OUC1 and I/O LOW-level output voltage HIGH-level output voltage LOW-level input voltage HIGH-level input voltage LOW-level input voltage LOW-level input tourrent hysteresis voltage HIGH-level input | pins: I/OUC1 and I/OUC2[1] LOW-level output voltage HIGH-level output voltage LOW-level input voltage HIGH-level input voltage HIGH-level input voltage LOW-level input voltage LOW-level input voltage HIGH-level input $V_{IL} = 0 \ V$ current hysteresis voltage HIGH-level input $V_{IH} = V_{DD(INTF)}$ | pins: I/OUC1 and I/OUC2[1] LOW-level output voltage HIGH-level output voltage LOW-level input voltage HIGH-level input voltage HIGH-level input voltage LOW-level input voltage HIGH-level input voltage LOW-level input voltage LOW-level input voltage HIGH-level input V _{IL} = 0 V current hysteresis voltage on I/OUC(n) HIGH-level input V _{IH} = V _{DD(INTF)} | $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ | $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ | $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ |

TDA8026_1

All information provided in this document is subject to legal disclaimers.

© NXP Semiconductors N.V. 2016. All rights reserved.

Multiple smart card slot interface IC

 Table 47.
 Interface signals to microcontroller ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V}; f_{clk(ext)} = 10 \text{ MHz}; GND = 0 \text{ V}; inductor = 10 \mu\text{H}; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \mu\text{F}; T_{amb} = 25 ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|-----------------------|----------------------------------|--|-----|----------------------------|---------------------------|-----------------------------|------|
| t _{r(o)} | output rise time | V_{IL} minimum to V_{IH} maximum; 10 % to 90 % | | - | - | 0.1 | μS |
| $t_{r(i)}$ | input rise time | V_{IL} minimum to V_{IH} maximum; 10 % to 90 % | | - | - | 1.2 | μS |
| $t_{f(O)}$ | output fall time | V_{IL} maximum to V_{IH} minimum; 90 % to 10 % | | - | - | 0.1 | μS |
| $t_{f(i)}$ | input fall time | V_{IL} maximum to V_{IH} minimum; 90 % to 10 % | | - | - | 1.2 | μS |
| Ci | input capacitance | | [1] | - | - | 10 | pF |
| R _{pu(int)} | internal pull-up resistance | between pins I/OUC $_{(n)}$ and $V_{DD(INTF)}$ | | 9 | 11 | 13 | kΩ |
| I _{pu} | pull-up current | $V_{OH} = 0.9 V_{DD}, C_i = 30 pF$ | | -1 | - | - | mA |
| Clock in | put pins: CLKIN1 and | CLKIN2 | | | | | |
| f _{clk(ext)} | external clock frequency | on pins CLKIN1 and CLKIN2 | | 0 | - | 20 | MHz |
| V _{IL} | LOW-level input | V _{DD(INTF)} > 2 V | | 0 | - | 0.3 V _{DD(INTF)} | V |
| | voltage | $1.6 \text{ V} \leq V_{DD(INTF)} \leq 2 \text{ V}$ | | 0 | - | 0.15V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input | V _{DD(INTF)} > 2 V | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| | voltage | $1.6 \text{ V} \leq V_{DD(INTF)} \leq 2 \text{ V}$ | | 0.85 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| t _r | rise time | 10 % to 90 % | | - | - | 0.1 / f _{clk(ext)} | ns |
| t _f | fall time | 90 % to 10 % | | - | - | 0.1 / f _{clk(ext)} | ns |
| Logic in | put pins: A0, SPRES, | INHIB, DCDC_OFF and TESTM | IOD | E | | | |
| V _{IL} | LOW-level input voltage | | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input voltage | | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| I _{LIL} | LOW-level input leakage current | | | -1 | - | +1 | μΑ |
| V _{hys} | hysteresis voltage | on pin SPRES | | - | 0.14V _{DD(INTF)} | - | V |
| I _{LIH} | HIGH-level input leakage current | | | -1 | - | +1 | μΑ |
| C _i | input capacitance | | | - | - | 10 | pF |
| Logic in | put pin: SDWNN | | | | | | |
| V_{IL} | LOW-level input voltage | | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input voltage | | | 0.7 V _{DD(INTF)} | - | V _{DD(INTF)} + 0.3 | V |
| I _{LIH} | HIGH-level input leakage current | | | -1 | - | +1 | μΑ |
| C _i | input capacitance | | | - | - | 10 | pF |
| R _{pu(int)} | internal pull-up resistance | between pins SDWNN and V _{DD(INTF)} | | 2 | 2.5 | 3 | МΩ |

Multiple smart card slot interface IC

 Table 47.
 Interface signals to microcontroller ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V}; f_{clk(ext)} = 10 \text{ MHz}; GND = 0 \text{ V}; inductor = 10 \mu\text{H}; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \mu\text{F}; T_{amb} = 25 ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|------------------|----------------------------------|---|-----------------------------|------|----------------------------|------|
| Logic in | put pin: INTAUXN | | | | | |
| V _{IL} | LOW-level input voltage | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input voltage | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| I _{LIL} | LOW-level input leakage current | | -425 | -330 | -260 | μΑ |
| Ci | input capacitance | | - | - | 10 | pF |
| $R_{pu(int)}$ | internal pull-up resistance | between pins INTAUXN and $V_{DD(INTF)}$; SDWNN pin equal to pin $V_{DD(INTF)}$ | 8 | 10 | 12 | kΩ |
| Interrupt | line: IRQN pin; open- | drain, active LOW output | | | | |
| V _{OL} | LOW-level output voltage | I _{OL} = 2 mA | - | - | 0.3 | V |
| I _{LH} | current | | - | - | 10 | μΑ |
| Logic in | put/output pins: TST1 | , TST2, STAP3, STAP4, STAP5 | | | | |
| V _{IL} | LOW-level input voltage | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input voltage | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| V _{OL} | LOW-level output | $V_{DD(INTF)} = 3.3 \text{ V}; I_{OL} = 4 \text{ mA}$ | 0 | - | 0.4 | V |
| | voltage | $V_{DD(INTF)} = 1.8 \text{ V}; I_{OL} = 4 \text{ mA}$ | 0 | - | 0.4 | V |
| V _{OH} | HIGH-level output voltage | $V_{DD(INTF)} = 3.3 \text{ V};$ $I_{OH} = -4 \text{ mA}$ | V _{DD(INTF)} – 0.4 | - | V _{DD(INTF)} | V |
| | | $V_{DD(INTF)} = 1.8 \text{ V};$ $I_{OH} = -4 \text{ mA}$ | V _{DD(INTF)} – 0.4 | - | V _{DD(INTF)} | V |
| I _{OL} | LOW-level output current | $V_{DD(INTF)} = 3.3 \text{ V};$ $V_{OL} = 0.3 \text{ V}_{DD(INTF)}$ | 4 | - | - | mA |
| | | $V_{DD(INTF)} = 1.8 \text{ V};$ $V_{OL} = 0.3 \text{ V}_{DD(INTF)}$ | 2 | - | - | mA |
| I _{OH} | HIGH-level output current | $V_{DD(INTF)} = 3.3 \text{ V};$ $V_{OH} = 0.7 \text{ V}_{DD(INTF)}$ | -4 | - | - | mA |
| | | $V_{DD(INTF)} = 1.8 \text{ V};$ $V_{OH} = 0.7 \text{ V}_{DD(INTF)}$ | -2 | - | - | mA |
| I _{LIL} | LOW-level input leakage current | | -1 | - | +1 | μΑ |
| I _{LIH} | HIGH-level input leakage current | | -1 | - | +1 | μΑ |
| Ci | input capacitance | | - | - | 10 | pF |
| Co | output capacitance | | - | 30 | - | pF |

Multiple smart card slot interface IC

 Table 47.
 Interface signals to microcontroller ...continued

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \ \mu\text{H; decoupling capacitors on pins } V_{DD} \text{ and } V_{UP} = 10 \ \mu\text{F; } T_{amb} = 25 \ ^{\circ}\text{C} \text{ unless otherwise specified.}$

| Symbol | Parameter | Conditions | | Min | Тур | Max | Unit |
|----------------------|--|--|-----|---------------------------|-----|----------------------------|------|
| Serial da | ata input/output pin: SI | OA; open-drain | | | | | |
| V_{IL} | LOW-level input voltage | | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V_{IH} | HIGH-level input voltage | | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| V _{OL} | LOW-level output voltage | I _{OL} = 3 mA | | - | - | 0.3 | V |
| I _{LH} | HIGH-level leakage current | I/O | | - | - | 1 | μΑ |
| I _{LL} | LOW-level leakage current | depending on the pull-up resistance; input or output | | - | - | 1 | μΑ |
| Serial cl | ock input pin: SCL | | , | | | 1 | ' |
| V_{IL} | LOW-level input voltage | | | -0.3 | - | +0.3 V _{DD(INTF)} | V |
| V _{IH} | HIGH-level input voltage | | | 0.7 V _{DD(INTF)} | - | $V_{DD(INTF)} + 0.3$ | V |
| I _{LIH} | HIGH-level input leakage current | | | - | - | 1 | μΑ |
| I _{IL} | LOW-level input current | depends on the pull-up resistance | | - | - | 1 | μΑ |
| I ² C-bus | timing; see Figure 13 | | , | | | 1 | |
| f _{SCL} | SCL clock frequency | | | 0 | - | 400 | kHz |
| t _{BUF} | bus free time between a STOP and START condition | | | 1.3 | - | - | μS |
| t _{HD;STA} | hold time (repeated) START condition | hold time after which first clock pulse is generated | | 0.6 | - | - | μS |
| t_{LOW} | LOW period of the SCL clock | | | 1.3 | - | - | μS |
| t _{HIGH} | HIGH period of the SCL clock | | | 0.6 | - | - | μS |
| t _{SU;STA} | set-up time for a repeated START condition | | | 0.6 | - | - | μS |
| t _{HD;DAT} | data hold time | | [2] | 0 | - | - | ns |
| t _{SU;DAT} | data set-up time | | | 100 | - | - | ns |
| t _r | rise time | both SDA and SCL signals; 10 % to 90 % | | - | - | 300 | ns |
| t _f | fall time | both SDA and SCL signals; 90 % to 10 % | | - | - | 300 | ns |
| t _{SU;STO} | set-up time for STOP condition | | | 0.6 | - | - | μS |

^[1] I/OUCn pin has an internal 11 k Ω pull-up resistor to $V_{DD(INTF)}$.

TDA8026_1

All information provided in this document is subject to legal disclaimers.


^[2] The hold time required (not greater than 300 ns) to bridge the undefined region of the falling edge of SCL must be internally provided by a transmitter.

Multiple smart card slot interface IC

Table 48. Protections

 $V_{DD} = V_{DD(INTF)} = 3.3 \text{ V; } f_{Clk(ext)} = 10 \text{ MHz; } GND = 0 \text{ V; inductor} = 10 \text{ } \mu\text{H; decoupling capacitors on pin } V_{DD} \text{ and } V_{UP} = 10 \text{ } \mu\text{F; } T_{amb} = 25 \text{ °C unless otherwise specified.}$

| Symbol | Parameter | Conditions | Min | Тур | Max | Unit |
|-------------------|----------------------|---|-----|-----|------|------|
| T _{sd} | shutdown temperature | | 125 | 167 | 209 | °C |
| I _{sd} | shutdown current | all V _{CC(n)} pins | 80 | 120 | 150 | mA |
| I _{Olim} | output current limit | pins I/O _(n) | -15 | - | +15 | mA |
| | | pins CLK _(n) | -70 | - | +70 | mA |
| | | pins RST _(n) | -20 | - | +20 | mA |
| | | pins V _{CC(n)} | 80 | - | 150 | mA |
| T _{amb} | ambient temperature | | -25 | +25 | +85 | °C |
| Tj | junction temperature | | - | - | +125 | °C |
| I _{CC} | supply current | sum of all V _{CC(n)} signals on all card slots; active mode; DC-to-DC converter on | - | 170 | - | mA |



12. **Application information**




Fig 14. Application diagram: TDA8026 with one card and four SAMs

© NXP Semiconductors N.V. 2016. All rights reserved

Product data sheet

All information provided in this document is subject to legal disclaimers

Rev. 1.1 —

30 June 2016

Multiple smart card slot interface IC

13. Package outline




Fig 15. Package outline SOT1073-1 (TFBGA64)

Multiple smart card slot interface IC

14. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365* "Surface mount reflow soldering description".

14.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

14.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- · Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- · Lead-free soldering versus SnPb soldering

14.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

Multiple smart card slot interface IC

14.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 16</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 49 and 50

Table 49. SnPb eutectic process (from J-STD-020C)

| Package thickness (mm) | Package reflow temperature (°C) | | |
|------------------------|---------------------------------|-------|--|
| | Volume (mm³) | | |
| | < 350 | ≥ 350 | |
| < 2.5 | 235 | 220 | |
| ≥ 2.5 | 220 | 220 | |


Table 50. Lead-free process (from J-STD-020C)

| Package thickness (mm) | Package reflow temperature (°C) | | | | |
|------------------------|---------------------------------|-------------|--------|--|--|
| | Volume (mm³) | | | | |
| | < 350 | 350 to 2000 | > 2000 | | |
| < 1.6 | 260 | 260 | 260 | | |
| 1.6 to 2.5 | 260 | 250 | 245 | | |
| > 2.5 | 250 | 245 | 245 | | |

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 16.

Multiple smart card slot interface IC



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

15. Abbreviations

Table 51. Abbreviations and acronyms

| Acronym | Description |
|---------|------------------------------|
| ATR | Answer To Request |
| CDM | Charged Device Model |
| ESD | ElectroStatic Discharge |
| ESR | Equivalent Series Resistance |
| НВМ | Human Body Model |
| LSB | Least Significant Bit |
| MM | Machine Model |
| MSB | Most Significant Bit |
| PCB | Printed-Circuit Board |
| POR | Power-On Reset |
| POS | Point Of Sales |
| SAM | Security Access Module |

Multiple smart card slot interface IC

16. Revision history

Table 52. Revision history

| Document ID | Release date | Data sheet status | Change notice | Supersedes | |
|----------------|---|--------------------|---------------|-------------|--|
| TDA8026 v. 1.1 | 20160630 | Product data sheet | [1] | TDA8026 v.1 | |
| Modifications | ions • C3 version EMVC0 4.3 compliant added | | | | |
| | <u>Table 45 "Card drivers"</u> : updated | | | | |
| TDA8026 v.1 | 20100309 | Product data sheet | - | | |

^[1] Versions 1.0 to 1.2 have all been superseded by this version which includes changes to symbols, pin names and drawings.

Multiple smart card slot interface IC

17. Legal information

17.1 Data sheet status

| Document status[1][2] | Product status[3] | Definition |
|--------------------------------|-------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

17.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

17.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on a weakness or default in the customer application/use or the application/use of customer's third party customer(s) (hereinafter both referred to as "Application"). It is customer's sole responsibility to check whether the NXP Semiconductors product is suitable and fit for the Application planned. Customer has to do all necessary testing for the Application in order to avoid a default of the Application and the product. NXP Semiconductors does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

TDA8026 1

All information provided in this document is subject to legal disclaimers.

© NXP Semiconductors N.V. 2016. All rights reserved.

Multiple smart card slot interface IC

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

17.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

 I^2 C-bus — logo is a trademark of NXP B.V.

18. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

Multiple smart card slot interface IC

19. Tables

| Table 1. | Quick reference data2 | Table 27. | Bank 1 Register1 (REG[1:0] = 01) card slot 3 |
|-----------|--|-----------------|---|
| Table 2. | Ordering information4 | | (address 03h), card slot 4 (address 04h) and card |
| Table 3. | TDA8026 ball map | | slot 5 (address 05h) read/write mode bit |
| Table 4. | Pin description | | descriptions |
| Table 5. | Base addressing15 | Table 28. | Bank 1 Register1 (REG[1:0] = 10) card slot 3 |
| Table 6. | Write mode addresses15 | | (address 03h), card slot 4 (address 04h) and card |
| Table 7. | Register overview17 | | slot 5 (address 05h) bit allocation 29 |
| Table 8. | Bank 0 register (address: 48h) bit allocation19 | Table 29. | Bank 1 Register1 (REG[1:0] = 10) card slot 3 |
| Table 9. | Bank 0 bit description19 | | (address 03h), card slot 4 (address 04h) and card |
| | Bank 1 CSb[7:0] Register0 (address 40h) card slot | | slot 5 (address 05h) read/write mode bit |
| | 1 and card slot 2 bit allocation | | descriptions |
| Table 11. | Bank 1 Register0 card slot 1 (address 01h) and | Table 30. | Bank 1 Register1 (REG[1:0] = 11) card slot 3 |
| | card slot 2 (address 02h) read mode bit | | (address 03h), card slot 4 (address 04h) and card |
| | descriptions | | slot 5 (address 05h) bit allocation |
| Table 12 | Bank 1 Register0 card slot 1 (address 01h) and | Table 31 | Bank 1: Bank 1 Register1 (REG[1:0] = 11) card |
| Table 12. | card slot 2 (address 02h) write mode bit | Table 51. | slot 3 (address 03h), card slot 4 (address 04h) and |
| | descriptions21 | | card slot 5 (address 05h) read/write mode bit |
| Table 12 | | | descriptions |
| Table 13. | Bank 1 CSb[7:0] Register0 (address 42h) card | Toble 22 | Asynchronous mode card clock settings 30 |
| Table 44 | slots 1 and card slots 2 bit allocation | | • |
| Table 14. | Bank 1 Register1 (REG[1:0] = 00) card slot 1 | | Synchronous mode card clock settings 30 |
| | (address 01h) and card slot 2 (address 02h) | Table 34. | Bank 1 General registers (addresses: 40h, 42h; |
| T | Read/Write mode bit descriptions | T | CSb[7:0] = 00h, 06h) bit allocation |
| Table 15. | Bank 1 Register1 (REG[1:0] = 01) card slot 1 | Table 35. | Bank 1 Product version register (address 40h; |
| | (address 01h) and card slot 2 (address 02h) bit | T 00 | CSb[7:0] = 00h) read mode bit descriptions 31 |
| | allocation | Table 36. | Bank 1 Interrupt register (address 42h; |
| Table 16. | Bank 1 Register1 (REG[1:0] = 01) card slot 1 | | CSb[7:0] = 00h) read mode bit descriptions 32 |
| | (address 01h) and card slot 2 (address 02h) | Table 37. | Bank 1 Slew rate register (address 40h; |
| | Read/Write mode bit descriptions24 | | CSb[7:0] = 06h) read/write mode bit |
| Table 17. | Bank 1 Register1 (REG[1:0] = 10) card slot 1 | | descriptions |
| | (address 01h) and card slot 2 (address 02h) bit | | Clock Slew rate |
| | allocation24 | | I/O slew rate |
| Table 18. | Bank 1 Register1 (REG[1:0] = 10) card slot 1 | | Limiting values40 |
| | (address 01h) and card slot 2 (address 02h) | | Thermal characteristics 40 |
| | Read/Write mode bit descriptions24 | | Supply |
| Table 19. | Bank 1 Register1 (REG[1:0] = 11) card slot 1 | | Supply supervisor |
| | (address 01h) and card slot 2 (address 02h) bit | | DC-to-DC converter42 |
| | allocation24 | | Card drivers |
| Table 20. | Bank 1 Register1 (REG[1:0] = 11) card slot 1 | | Sequencer and clock counter 45 |
| | (address 01h) and card slot 2 (address 02h) | Table 47. | Interface signals to microcontroller 45 |
| | read/write mode bit descriptions24 | Table 48. | Protections |
| Table 21. | Bank 1 CSb[7:0] Register0 (address 40h) card | Table 49. | SnPb eutectic process (from J-STD-020C) 53 |
| | slots 3 to 5 bit allocation25 | Table 50. | Lead-free process (from J-STD-020C) 53 |
| Table 22. | Bank 1 Register0 card slot 3 (address 03h), card | Table 51. | Abbreviations and acronyms 54 |
| | slot 4 (address 04h) and card slot 5 (address 05h) | Table 52. | Revision history |
| | read mode bit descriptions25 | | |
| Table 23. | Bank 1 Register0 card slot 3 (address 03h), card | | |
| | slot 4 (address 04h) and card slot 5 (address 05h) | | |
| | write mode bit descriptions26 | | |
| Table 24. | Bank 1 CSb[7:0] Register1 (address 42h) card | | |
| | slots 3 and 5 bit allocation27 | | |
| Table 25. | Bank 1 Register1 (REG[1:0] = 00) card slot 3 | | |
| | (address 03h), card slot 4 (address 04h) and card | | |
| | slot 5 (address 05h) read/write mode27 | | |
| Table 26. | Bank 1 Register1 (REG[1:0] = 01) card slot 3 | | |
| | (address 03h), card slot 4 (address 04h) and card | | |
| | slot 5 (address 05h) bit allocation28 | | |
| | 1.1.1 (| | |

Multiple smart card slot interface IC

20. Figures

| Fig 1. | TDA8026 Block diagram |
|---------|--|
| Fig 2. | TDA8026 pin configuration for the TFBGA64 |
| | package |
| Fig 3. | TDA8026 Power diagram9 |
| Fig 4. | The enter shutdown sequence |
| Fig 5. | The exit shutdown sequence |
| Fig 6. | The voltage supervisor circuit |
| Fig 7. | V _{DD} voltage supervisor |
| Fig 8. | V _{DD(INTF)} voltage supervisor |
| Fig 9. | The DC-to-DC converter |
| Fig 10. | The card slot activation sequence |
| Fig 11. | Deactivation sequence36 |
| Fig 12. | ATR counter timing check |
| Fig 13. | Timing requirements for the I ² C-bus |
| Fig 14. | Application diagram: TDA8026 with one card |
| | and four SAMs50 |
| Fig 15. | Package outline SOT1073-1 (TFBGA64) 51 |
| Fig 16. | Temperature profiles for large and small |
| | components |

Multiple smart card slot interface IC

21. Contents

| 1 | General description 1 | 8.5.3.6 | Bank 1 Register1 (REG[1:0] = 01) card slot 1 |
|---------|---|----------|--|
| 2 | Features and benefits 1 | | (address 01h) and card slot 2 (address 02h) bit |
| 3 | Applications 2 | 0.5.0.7 | allocation |
| 4 | Quick reference data 2 | 8.5.3.7 | Bank 1 Register1 (REG[1:0] = 01) card slot 1 (address 01h) and card slot 2 (address 02h) |
| 5 | Ordering information 4 | | read/write mode bit descriptions 24 |
| 6 | Block diagram 5 | 8.5.3.8 | Bank 1 Register1 (REG[1:0] = 10) card slot 1 |
| 7 | Pinning information 6 | | (address 01h) and card slot 2 (address 02h) bit |
| 7.1 | Pinning 6 | | allocation |
| 7.2 | Pin description | 8.5.3.9 | Bank 1 Register1 (REG[1:0] = 10) card slot 1 |
| 8 | Functional description 9 | | (address 01h) and card slot 2 (address 02h) |
| 8.1 | Power supplies 9 | | read/write mode bit descriptions 24 |
| 8.2 | Power modes | 8.5.3.10 | Bank 1 Register1 (REG[1:0] = 11) card slot 1 |
| 8.2.1 | Standby mode | | (address 01h) and card slot 2 (address 02h) bit |
| 8.2.2 | Active mode | | allocation |
| 8.2.3 | Clock-stop mode | 8.5.3.11 | Bank 1 Register1 (REG[1:0] = 11) card slot 1 |
| 8.2.4 | Shutdown mode | | (address 01h) and card slot 2 (address 02h) |
| 8.2.4.1 | Entering shutdown mode | | read/write mode bit descriptions 24 |
| 8.2.4.2 | Exiting shutdown mode | 8.5.4 | Card slots 3 to 5 register descriptions 25 |
| 8.3 | Voltage supervisors | 8.5.4.1 | Bank 1 CSb[7:0] Register0 (address 40h) card |
| 8.3.1 | Block diagram | | slots 3 to 5 bit allocation |
| 8.3.2 | Description | 8.5.4.2 | Bank 1 Register0 card slot 3 (address 03h), card |
| 8.3.3 | V _{DD(INTREGD)} voltage supervisor without | | slot 4 (address 04h) and card slot 5 (address 05h) |
| | external divider on PORADJ pin | | read mode bit descriptions |
| 8.4 | I ² C-bus description | 8.5.4.3 | Bank 1 Register0 card slot 3 (address 03h), card |
| 8.4.1 | I ² C-bus protocol | | slot 4 (address 04h) and card slot 5 (address 05h) |
| 8.4.2 | Bus conditions | 0 = 4 4 | write mode bit descriptions |
| 8.4.3 | Data transfer | 8.5.4.4 | Bank 1 CSb[7:0] Register1 (address 42h) card |
| 8.4.4 | Device addressing | 0545 | slots 3 and 5 bit allocation |
| 8.5 | Banks and registers | 8.5.4.5 | Bank 1 Register1 (REG[1:0] = 00) card slot 3 |
| 8.5.1 | Register overview | | (address 03h), card slot 4 (address 04h) and card |
| 8.5.2 | Bank 0 register description 19 | 0.5.4.0 | slot 5 (address 05h) read/write mode 27 |
| 8.5.2.1 | Bank 0 register (address: 48h) bit allocation . 19 | 8.5.4.6 | Bank 1 Register1 (REG[1:0] = 01) card slot 3 |
| 8.5.2.2 | Bank 0 bit description 19 | | (address 03h), card slot 4 (address 04h) and card |
| 8.5.3 | Bank 1 card slots 1 and 2 register descriptions 19 | 0.5.4.7 | slot 5 (address 05h) bit allocation |
| 8.5.3.1 | Bank 1 CSb[7:0] Register0 (address 40h) card slot | 8.5.4.7 | Bank 1 Register1 (REG[1:0] = 01) card slot 3 |
| | 1 and card slot 2 bit allocation 19 | | (address 03h), card slot 4 (address 04h) and card |
| 8.5.3.2 | Bank 1 Register0 card slot 1 (address 01h) | | slot 5 (address 05h) read/write mode bit |
| | and card slot 2 (address 02h) read mode bit | 8.5.4.8 | descriptions |
| | descriptions 20 | 0.3.4.0 | (address 03h), card slot 4 (address 04h) and card |
| 8.5.3.3 | Bank 1 Register0 card slot 1 (address 01h) | | |
| | and card slot 2 (address 02h) write mode bit | 0 5 4 0 | slot 5 (address 05h) bit allocation |
| | descriptions | 8.5.4.9 | Bank 1 Register1 (REG[1:0] = 10) card slot 3 (address 03h), card slot 4 (address 04h) and card |
| 8.5.3.4 | Bank 1 CSb[7:0] Register0 (address 42h) card | | slot 5 (address 05h) read/write mode bit |
| | slots 1 and card slot 2 bit allocation 22 | | descriptions |
| 8.5.3.5 | Bank 1 Register1 (REG[1:0] = 00) card slot 1 | | uesunphons |
| | (address 01h) and card slot 2 (address 02h) | | |
| | read/write mode bit descriptions 22 | | |

continued >>

TDA8026 NXP Semiconductors

Multiple smart card slot interface IC

| 8.5.4.10 | Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) and caslot 5 (address 05h) bit allocation | |
|----------|---|----------|
| 8.5.4.11 | Bank 1: Bank 1 Register1 (REG[1:0] = 11) card slot 3 (address 03h), card slot 4 (address 04h) a card slot 5 (address 05h) read/write mode bit | d |
| | descriptions | 29 |
| 8.5.5 | Selection of asynchronous or synchronous | |
| | mode | 29 |
| 8.5.6 | General registers | 31 |
| 8.5.6.1 | Bank 1 General registers (address: 40h, 42h; | . |
| 0.5.0.0 | CSb[7:0] = 00h, 06h) bit allocation | 31 |
| 8.5.6.2 | Bank 1 Product version register (address 40h; | 04 |
| 0.5.0.0 | CSb[7:0] = 00h) read mode bit descriptions | 31 |
| 8.5.6.3 | Bank 1 Interrupt register (address 42h; CSb[7:0] = 00h) read mode bit descriptions | 22 |
| 8.5.6.4 | Bank 1 Slew rate register (address 40h; | 32 |
| 0.5.0.4 | CSb[7:0] = 06h) read/write mode bit | |
| | descriptions | 32 |
| 8.6 | DC-to-DC converter | 33 |
| 8.7 | V _{CC} buffer | 33 |
| 8.8 | Sequencer and clock counter | 33 |
| 8.8.1 | Standby mode | 34 |
| 8.8.2 | Activation sequence | 34 |
| 8.8.3 | Deactivation sequence | 35 |
| 8.9 | Answer to reset counters | 36 |
| 8.10 | Slew rate control | 38 |
| 8.11 | Fault detection | 39 |
| 9 | Limiting values | 40 |
| 10 | Thermal characteristics | 40 |
| 11 | Characteristics | 41 |
| 12 | Application information | 50 |
| 13 | Package outline | 51 |
| 14 | Soldering of SMD packages | 52 |
| 14.1 | Introduction to soldering | 52 |
| 14.2 | Wave and reflow soldering | 52 |
| 14.3 | Wave soldering | 52 |
| 14.4 | Reflow soldering | 53 |
| 15 | Abbreviations | 54 |
| 16 | Revision history | 55 |
| 17 | Legal information | 56 |
| 17.1 | Data sheet status | 56 |
| 17.1 | Definitions | 56 |
| 17.3 | Disclaimers | 56 |
| 17.4 | Trademarks | 57 |
| 18 | Contact information | 57 |
| 19 | Tables | 58 |
| 20 | Figures | 59 |
| | ga. vo | - |

| 21 | Contents | 60 |
|----|----------|----|
|----|----------|----|

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP Semiconductors N.V. 2016.

All rights reserved.