

| | | | | | |
|---|---|--|--|--|--|
|  <small>ASSOCIATION CONNECTING ELECTRONICS INDUSTRIES®</small> | Material Composition Declaration © Copyright 2005. IPC, Bannockburn, Illinois. All rights reserved under both international and Pan-American copyright conventions. | This document is a declaration of the substances within the manufacturer listed item. Note: if the item is an assembly with lower level parts, the declaration encompasses all lower level materials for which the manufacturer has engineering responsibility. <div style="text-align: right;">Adobe Reader version 7.0.5 is required to complete this declaration.</div> | | | |
| 1752-2 1.1 | IPC Web Site for Information on IPC-1752 Standard http://www.ipc.org/IPC-175x | Form Type * Request/Reply | Declaration Class * Class 1 - RoHS Yes/No | | |

| | | | | | | | | | | | | |
|------------------------------------|--------------------------|--|--|---------------------------------|--|---------------------------------|---------|--|-------------------------|---|-----|-----------|
| Requester Information | | | | | | | | | | <div>Lock Request Fields</div> | | |
| Company Name * | | Company Unique ID | | Unique ID Authority | | Request Date* | | Request Document ID | | Respond By Date | | |
| Contact Name * | | Contact Title | | Contact Phone * | | Contact Email * | | Requester Comments or URL for Additional Information | | | | |
| My supplier ID | | The File Type and Destination fields control how the form is submitted by the supplier. Consult your IT staff for configuration. | | | | File Type PDF | | Destination - URL or Email Address | | <input type="checkbox"/> Supplier provides Mfr Item Version & Manufacturing Site. | | |
| | Item Number * | Item Name | | Mfr Item Number * | | Mfr Item Name | | Mfr Item Version | | Manufacturing Site | | |
| | | | | | | | | | | | | |
| Supplier Information | | | | | | | | | | | | |
| Company Name * | | Company Unique ID | | Unique ID Authority | | Response Date * | | Response Document ID | | | | |
| Contact Name * | | Title - Contact | | Phone - Contact * | | Email - Contact * | | <div>Duplicate Contact -> Authorized Representative</div> | | | | |
| Authorized Representative * | | Title - Representative | | Phone - Representative * | | Email - Representative * | | Supplier Comments or URL for Additional Information | | | | |
| | Requester Item Number | Mfr Item Number | | Mfr Item Name | | Effective Date | Version | Manufacturing Site | | Weight * | UOM | Unit Type |
| | | | | | | | | | | | mg | Each |
| | Alternate Recommendation | | | | | | | | Alternate Item Comments | | | |

Manufacturing Information section intentionally omitted.

| | | | | | | | |
|--|--|--|--|--------------------------------------|---|---|---|
| Save the fields in this form to a file | <input type="button" value="Export Data"/> | Import fields from a file into this form | <input type="button" value="Import Data"/> | Clear all of the fields on this form | <input type="button" value="Reset Form"/> | Lock the fields on this form to prevent changes | <input type="button" value="Lock Supplier Fields"/> |
|--|--|--|--|--------------------------------------|---|---|---|

| | | | | |
|---|---|------------------------------|--|----------------------|
| RoHS Material Composition Declaration | | Declaration Type * | | <input type="text"/> |
| RoHS Directive 2002/95/EC | RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) in homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material for Cadmium | | | |
| <div></div> | | | | |
| RoHS Declaration * | | Supplier Acceptance * | | Accepted |
| Exemptions: If the declared item does not contain RoHS restricted substances per the definition above except for defined RoHS exemptions, then select the corresponding response in the RoHS Declaration above and choose all applicable exemptions. | | | | |

| | | |
|--|----------------------|----------------------|
| Declaration Signature | | |
| Instructions: Complete all of the required fields on all pages of this form. Select the "Accepted" on the Supplier Acceptance drop-down. This will display the signature area. Digitally sign the declaration (if required by the Requester) and click on Submit Form to have the form returned to the Requester. | | |
| Supplier Digital Signature | <input type="text"/> | <input type="text"/> |

JIG section intentionally omitted.