



26	4	Shunt	3M	929955-06
25	1	Resistor	Yageo	RC0603JR-070RL
24	1	Resistor	Yageo	RC0603JR-071KL
23	1	Resistor	Yageo	RC0603JR-071K2L
22	6	Resistor	Yageo	RC0603JR-0710KL
21	5	Resistor	Yageo	RC0603JR-0747KL
20	1	Resistor	Yageo	RC0603JR-0710RL
19	1	Ceramic Capacitor	Kemet	C0603C103K5RACTU
18	1	Ceramic Capacitor	Kemet	C0603C101J5GACTU
17	4	Ceramic Capacitor	AVX	C0603C104K3RACTU
16	1	Tantalum Capacitor	AVX	TAJB106M016R
15	3	Ceramic Capacitor	AVX	0603ZC224KAT2A
14	2	Ceramic Capacitor	Yageo	CX0603MRX7R6BB104
13	2	Ceramic Capacitor	Kemet	C0603C100J5GACTU
12	4	2X18 Socket	3M	929852-01-18-RA
11	1	2X3 Berg Header	Sullins	PBC03DAAN
10	1	1X3 Berg Header	Sullins	PBC03SAAN
9	3	1X2 Berg Header	Sullins	PBC02SAAN
8	4	2X18 Berg Header	Sullins	PBC18DAAN
7	1	IC Sensor	On Semi	MC34164DM-5R2G
6	1	IC Tri-State Buffer	On Semi	MC74AC125DTR2G
5	1	Tactile Switch	Omron	B3S-1002P
4	1	IC DIP Socket	Mill-Max	214-44-314-01-670800
3	1	8.0Mhz Crystal	ECS	ECS-80-18-5PX
2	1	ZIF Socket	Yamaichi	IC51-0804-711
1	1	PCB	Freescale Semi	CDC1369

ITEM	QTY	NAME	MATERIAL	DESCRIPTION
Parts List				
FILE NAME		LFSMPBS12DFM.DWG		
CONTRACT NO		-		
DRAWN		06/09/08 MJL		
CHECK		07/17/08 CJW		
APPR.				
ISSUED				
NOTE:		DIMENSIONS ARE IN MILLIMETERS DO NOT SCALE DRAWING		
SIZE		FSCM NO	DWG NO	REV
B		-	LFSMPBS12DFM	
SCALE		N/A	WEIGHT	SHEET 1 of 2



28125 Cabot Drive, Suite 100  
Novi MI 48377

MC9S12D Family QFP Programming Adapter  
80 PIN 0.65mm Pitch (Lead Free)