
SO & SOJ FOOTPRINT (REFLOW SOLDERING)



Reflow soldering

| PACKAGE | PHILIPS OUTLINE CODE | N | | PLACEMENT | | | | | | |
|---------|----------------------------|----|-------|-----------|------|------|------|-------|-------|----------|
| NAME | | | Α | В | С | D1 | D2 | F | G | ACCURACY |
| SO8 | SOT96-1 | 8 | 6.60 | 4.00 | 1.30 | 0.60 | 0.60 | 7.00 | 5.50 | ±0.25 |
| SO8 | SOT176-1 | 8 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 8.40 | ±0.25 |
| SO14 | SOT108-1 | 14 | 6.60 | 4.00 | 1.30 | 0.60 | 0.60 | 7.00 | 9.30 | ±0.25 |
| SO16 | SOT109-1 | 16 | 6.60 | 4.00 | 1.30 | 0.60 | 0.60 | 7.00 | 10.50 | ±0.25 |
| SO16 | SOT109-2 | 16 | 6.60 | 4.00 | 1.30 | 0.60 | 0.60 | 7.00 | 10.50 | ±0.25 |
| SO16 | SOT109-3 | 16 | 6.60 | 4.00 | 1.30 | 0.60 | 0.60 | 7.00 | 10.50 | ±0.25 |
| SO16 | SOT162-1 | 16 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 10.90 | ±0.25 |

| ┰ |
|--------------------------|
| Ť |
| <u>=</u> : |
| ₹. |
| \sim |
| O, |
| S |
| Œ, |
| |
| \supset |
| Ξ. |
| ö |
| \preceq |
| \overline{c} |
| \succeq |
| \succeq |
| 얽 |
| 0 |
| $\overline{\mathcal{L}}$ |
| 0, |

| PC | |
|----------|--|
| board | |
| footprir | |

PDF: 2001 Feb 19

| O20 | SOT163-1 | 20 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 13.40 | ±0.25 |
|-------|----------|----|-------|------|------|------|------|-------|-------|-------|
| SO24 | SOT137-1 | 24 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 16.00 | ±0.25 |
| SO28 | SOT136-1 | 28 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 18.50 | ±0.25 |
| SO32 | SOT287-1 | 32 | 11.00 | 8.00 | 1.50 | 0.60 | 0.60 | 11.40 | 21.20 | ±0.25 |
| SOJ40 | SOT449-1 | 40 | 12.10 | 7.30 | 2.40 | 0.70 | 0.85 | 12.35 | 26.50 | ±0.25 |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |
| | | | | | | | | | | |