



S12GC Automotive and Industrial Microcontrollers (MCUs)

S12GC

Last Updated: Jan 17, 2023

The MC9S12GC128 MCU is a 16-bit device composed of the top on-chip peripherals for your automotive designs.


An on-chip bandgap-based voltage regulator (Vreg) generates the internal digital supply voltage (VDD) for a 2.97 V to 5.5 V external supply range.

The MC9S12GC128 has full 16-bit data paths throughout.

The inclusion of a phase-lock loop (PLL) circuit allows power consumption and performance to be adjusted to suit operational requirements.

A total of 50 I/O port pins and two input pins are available in the 80-pin package version. Up to 12 I/O port bits are available with wake-up capability from STOP or WAIT mode.

S12GC Microcontroller Block Diagram Block Diagram



View additional information for [S12GC Automotive and Industrial Microcontrollers \(MCUs\)](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.