

P8xC591



CAN features of the 8xC591

- CAN 2.0B active controller, supporting 11-bit standard and 29-bit extended identifiers
- Up to 1 Mbit/s CAN bus speed at 8MHz clock
- 64-byte receive FIFO (can capture sequential data frames from the same source as required by the transport layer of higher protocols such as DeviceNet, CANopen and OSEK)
- 13-byte transmit buffer
- Enhanced PeliCAN core (CAN2.0B controller)
- Byte-oriented I²C master for external EEPROM store of device profiles

PeliCAN features

- Controlled by five SF-register (fast access, no MOVX required)
- Fully integrated in C51 architecture (bit addressable)
- Four independently configurable acceptance filters
- Each acceptance filter has two 32-bit specifiers: a 32-bit match and a 32-bit mask
- 32-bits of mask per acceptance filter allows unique group addressing per acceptance filter
- Higher layer protocols especially supported in standard CAN format with:
 - up to four 11-bit ID acceptance filters that also screen the first two data bytes i.e., data frames are screened by CAN ID and by data byte content
- Up to eight 11-bit ID acceptance filters half of which also screens the first data byte
- All acceptance filters are changeable “on the fly”
- Bus arbitration and reception without CPU involvement
- DMA-access of FIFO by C51-core and PeliCAN

CAN 2.0B microcontroller



Description

The P8xC591 is a single-chip 80C51 microcontroller with an on-chip CAN controller. It uses the powerful 80C51 instruction set and includes the successful PeliCAN functionality of the SJA1000 stand-alone CAN controller.

The fully static core provides extended power save provisions because the oscillator can be stopped and easily restarted without loss of data. A key feature of the P8xC591 is its six clock operation (per machine cycle), which doubles the performance of the conventional 80C51; this is 500 ns instruction cycle time at 12 MHz external clock rate. Or, by keeping the same throughput, the clock frequency can be reduced in half, thus dramatically reducing the electromagnetic interference. So, a 12 MHz P8xC591 becomes a 24 MHz equivalent at a substantially improved EMC.

The P8xC591 is designed for use in industrial control applications such as medical equipment, office equipment, large industrial equipment, and factory floor applications where reliability is a concern in a noisy environment. The 8xC591 incorporates all the functions of the Philips Rx+ core plus:

- CAN 2.0B controller (PeliCAN)
- PeliCAN features
- Six clocks for enhanced performance (500 ns at 12 MHz)
- Low active reset
- Six-input 10-bit ADC
- 32 I/Os
- Packaged in 44-pin PQFP or PLCC


PHILIPS

P8xC591

CAN 2.0B microcontroller



P8xC591 block diagram



Purchase of Philips I²C components conveys a license under the Philips' patent to use the components in the I²C system provided the system conforms to the I²C specification defined by Philips.

www.semiconductors.philips.com/microcontrollers



Philips Semiconductors

Philips Semiconductors is a worldwide company with over 100 sales offices in more than 50 countries. For a complete up-to-date list of our sales offices please e-mail sales.addresses@www.semiconductors.philips.com.

A complete list will be sent to you automatically. You can also visit our website <http://www.semiconductors.philips.com/sales>

© Koninklijke Philips Electronics N.V. 2003

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release: February 2003
document order number: 9397 750 11105

Published in U.S.A.