

The choice for embedded technologies

Our microcontroller offering combines the highest performance in Flash with the lowest power consumption in the smallest packages. A comprehensive portfolio of industry-leading performers includes the latest 32-bit LPC3000, LPC2000, LH7A, LH7, and 8-bit LPC900 families. We offer an easy migration path from 8-bit to 32-bit solutions.

LPC3000 series

The 32-bit LPC3000 series is based on the ARM926EJ core and is the only ARM9 microcontroller that provides a vector floating-point co-processor and integrated USB On-The-Go, as well as the ability to operate in ultra-low-power mode down to 0.9V. With speeds of up to 208 MHz, the NXP LPC3180 series supports Linux and WinCE and is ideal for a wide range of high-precision applications such as point-of-sale (POS) equipment, medical devices, and global positioning systems (GPS).

Type	Memory				Timers		Serial interfaces				ADC (10-bit) No. of channels	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	Instruction cache	Data cache	No. of timers*	PWM channels	USB	UART	I ² C	SPI										
LPC3180		64K	32K	32K	4	2	1	7	2	2	3	55	•	•	208	1.2V	3/1.8V	F	LFBGA320	90nm process, NAND Flash, SDRAM/DDR (1.8V), (1) USB 2.0 FS OTG, VFP unit, and SD card

LH7A series

To save time-to-market for applications that use an LCD screen, these ARM922T-based microcontrollers are equipped with an LCD controller. Supported by a comprehensive set of software and hardware design tools, the LH7A series makes it easy to create everything from cost-conscious consumer systems to advanced systems with media-rich environments.

Type	Memory				Timers		Serial interfaces				ADC (10-bit) No. of channels	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	Instruction cache	Data cache	No. of timers	PWM channels	USB	UART	I ² C	SPI										
LH7A400		80K Frame Buffer	8K	8K	5	0	1	3	0	1		60	•	•	245	1.8V	3.3V	F	BGA256 LFBGA256	Integrated LCD controller. IrDA. MMU. USB 2.0 Full Speed device. 32-bit external data bus. CompactFlash. SDRAM controller. MMC, PCMCIA, BMI.
LH7A404		80K Frame Buffer	8K	8K	5	2	1	3	0	1	10	64	•	•	266	1.8V	3.3V	F	LFBGA324	Integrated LCD controller. IrDA touchscreen interface. Touchscreen controller. MMU. USB 2.0 Full Speed Host/Device. 32-bit external data bus. CompactFlash. SDRAM controller. DMA controller. PCMCIA, BMI, PS/2, MMC/SD/SDIO.

LPC2000 and LH7 series

Based on an ARM7TDMI-S core operating at up to 84 MHz, these 32-bit microcontrollers deliver high performance and low power consumption in a cost-effective package. In addition to offering integrated LCD support, they offer a wide range of peripherals, including multiple serial interfaces, Ethernet, USB Host/OTG, CAN, and external bus options and are designed for use in general-purpose and specialty embedded applications such as industrial control, automotive, medical, and connectivity.

Type	Memory		Timers		Serial interfaces								Analog			SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S	ADC (10-bit) No. of channels	DAC (10-bit) No. of channels											
LPC2900 devices																									
LPC2919	768K	48K	5	24			2		2	3			16			108	•	•	80	1.8V	3.3V	F	LQFP144	ARM968E-S MCU with 2 LIN Master Controllers, 16 KB I-TCM, 16 KB D-TCM	
LPC2917	512K	48K	5	24			2		2	3			16			108	•	•	80	1.8V	3.3V	F	LQFP144	ARM968E-S MCU with 2 LIN Master Controllers, 16 KB I-TCM, 16 KB D-TCM	
LPC2915	512K	32K	5	24			2		2	3			16			76		•	80	1.8V	3.3V	F	LQFP100	ARM968E-S MCU with 16 KB I-TCM, 16 KB D-TCM	
LPC2800 devices																									
LPC2888	1M	64K	4			1 ⁽¹⁾	1 ⁽²⁾	1				1	5			•	85	•	•	60	1.8V	3.3V	F	TBGA180	⁽¹⁾ USB V2.0 high speed; ⁽²⁾ IrDA configurable; LCD interface logic
LPC2880		64K	4			1 ⁽¹⁾	1 ⁽²⁾	1				1	5			•	85	•	•	60	1.8V	3.3V	F	TBGA180	LPC2880 is the ROMless version of the LPC2888
LPC2400 devices																									
LPC2478	512K	98K	6	12 ⁽¹⁾	1	1 ⁽²⁾	4 ⁽³⁾	3	2	1	2	1	8	1		•	160	• ⁽⁴⁾	•	72		3.3V	F	LQFP208 TFBGA208	LPC2468 with QVGA LCD controller
LPC2470		98K	6	12 ⁽¹⁾	1	1 ⁽²⁾	4 ⁽³⁾	3	2	1	2	1	8	1		•	160	• ⁽⁴⁾	•	72		3.3V	F	LQFP208 TFBGA208	LPC2468 with QVGA LCD controller
LPC2468	512K	98K	6	12 ⁽¹⁾	1	1 ⁽²⁾	4 ⁽³⁾	3	2	1	2	1	8	1		•	160	• ⁽⁴⁾	•	72		3.3V	F	LQFP208 TFBGA208	On-chip 4MHz RC-Osc, GP DMA, RTC w/ 2K batt. RAM ⁽¹⁾ 2 PWM blocks; ⁽²⁾ USB 2.0 FS Host/OTG/device, DMA and 4K RAM; ⁽³⁾ UART 3 w/ IrDA; ⁽⁴⁾ 32-bit ext. bus
LH7 devices																									
LH75401		32K	5	3			3		1	1	1		8			76	•	•	84	1.8V	3.3V	F	LQFP144	Color LCD controller. Touchscreen interface. DMA controller. 5-V-tolerant I/O. 16-bit external data bus.	
LH75411		32K	5	3			3			1	1		8			76	•	•	84	1.8V	3.3V	F	LQFP144	Color LCD controller. Touchscreen interface. DMA controller. 5-V-tolerant I/O. 16-bit external data bus.	
LH79520		32K + 8K cache	6	2			3			1	1					64	•	•	77	1.8V	3.3V	F	LQFP176	ARM720T MCU with color LCD controller. IrDA. SDRAM controller. MMU. 32-bit external data bus.	
LH79524		16K + 8K cache	5	3	1	1	3	1		1	1	1	10			104	•	•	76	1.8V	3.3V	F	LFPGA208	ARM720T MCU with color LCD controller. Touchscreen interface. USB 2.0 device. IrDA. SDRAM controller. MMU. DMA. NAND Flash boot. 32-bit external data bus.	
LH79525		16K + 8K cache	5	3	1	1	3	1		1	1	1	10			86	•	•	76	1.8V	3.3V	F	LQFP176	ARM720T MCU with color LCD controller. Touchscreen interface. USB 2.0 device. IrDA. SDRAM controller. MMU. DMA. NAND Flash boot. 16-bit external data bus.	
LPC2300 devices																									
LPC2378	512K	58K	6	6	1	1 ⁽¹⁾	4 ⁽²⁾	3	2	1	2	1	8	1		•	104	• ⁽³⁾	•	72		3.3V	F	LQFP144	On-chip 4MHz RC-Osc, GP DMA, RTC w/ 2K batt. RAM ⁽¹⁾ USB 2.0 FS device w/ PHY, DMA and 4K RAM; ⁽²⁾ UART 3 w/ IrDA; ⁽³⁾ MiniBus (8-bit)
LPC2368	512K	58K	6	6	1	1 ⁽¹⁾	4 ⁽²⁾	3	2	1	2	1	6	1		•	70		•	72		3.3V	F	LQFP100	100-pin version of LPC2378, no external bus
LPC2366	256K	58K	6	6	1	1 ⁽¹⁾	4 ⁽²⁾	3	2	1	2	1	6	1			70		•	72		3.3V	F	LQFP100	256K Flash version of LPC2368, no SD/MMC
LPC2364	128K	34K	6	6	1	1 ⁽¹⁾	4 ⁽²⁾	3	2	1	2	1	6	1			70		•	72		3.3V	F	LQFP100	128K Flash / 34K RAM version of LPC2368, no SD/MMC
LPC2200 devices																									
LPC2294/01	256K	16K	5	6			2	1	4	2			8				112	•	•	60	1.8 V	3.3 V	H	LQFP144	LPC2214/01 upgrade with 4x CAN

Note: Reset active low. * Includes WatchDog timer and Real-time Clock. ** Using timers 0-3.

Continued next page

LPC2000 and LH7 series (continued)

Type	Memory		Timers		Serial interfaces							Analog		SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S	ADC (10-bit) No. of channels										
LPC2292/01	256K	16K	5	6			2	1	2	2			8		112	•	•	60	1.8 V	3.3 V	F	LQFP144, TFBGA144	LPC2214/01 upgrade with 2x CAN
LPC2290/01		64K	5	6			2	1	2	2			8		76	•	•	60	1.8 V	3.3 V	F	LQFP144	ROMless version of LPC2292/01
LPC2220		64K	5	6			2	1		2			8		76	•	•	75	1.8 V	3.3 V	F	LQFP144, TFBGA144	64K RAM version of LPC2210/01
LPC2214/01	256K	16K	5	6			2	1		2			8		112	•	•	60	1.8 V	3.3 V	F	LQFP144	External Bus, 4 Chip Selects, 10-bit SA ADC, 256K Flash
LPC2212/01	128K	16K	5	6			2	1		2			8		112	•	•	60	1.8 V	3.3 V	F	LQFP144	128K Flash version of LPC2214/01
LPC2210/01		16K	5	6			2	1		2			8		76	•	•	60	1.8 V	3.3 V	F	LQFP144	ROMless version of LPC2214/01
LPC2100 devices																							
LPC2194/01	256K	16K	5	6			2	1	4	2			4		46		•	60	1.8 V	3.3 V	H	LQFP64	LPC2124/01 upgrade with 4x CAN
LPC2158	512K	40K	5	6		1	2	1		1	1		8+6	1	32		•	60	3.3 V		F	LQFP64	LPC2148 with 32 x 4 LCD driver
LPC2157	512K	32K	5	6			2	1		1	1		2x8	1	32		•	60	3.3 V		F	LQFP64, HVQFN64	LPC2138/01 with 32 x 4 LCD driver
LPC2148	512K	40K	5	6		1	2	2		1	1		8+6	1	45		•	60	3.3 V		F	LQFP64	LPC2138 plus USB 2.0 full speed
LPC2146	256K	40K	5	6		1	2	2		1	1		8+6	1	45		•	60	3.3 V		F	LQFP64	LPC2136 plus USB 2.0 full speed
LPC2144	128K	16K	5	6		1	2	2		1	1		8+6	1	45		•	60	3.3 V		F	LQFP64	LPC2134 plus USB 2.0 full speed
LPC2142	64K	16K	5	6		1	2	2		1	1		6	1	45		•	60	3.3 V		F	LQFP64	LPC2132 plus USB 2.0 full speed
LPC2141	32K	8K	5	6		1	2	2		1	1		6		45		•	60	3.3 V		F	LQFP64	LPC2131 plus USB 2.0 full speed
LPC2138/01	512K	32K	5	6			2	2		1	1		2x8	1	47		•	60	3.3 V		F	LQFP64, HVQFN64	Dual 8-ch. 10-bit ADC, BOD, POR, 32-kHz XTAL input, VBAT, Fast I/O
LPC2136/01	256K	32K	5	6			2	2		1	1		2x8	1	47		•	60	3.3 V		F	LQFP64	256K Flash version of LPC2138/01
LPC2134/01	128K	16K	5	6			2	2		1	1		2x8	1	47		•	60	3.3 V		F	LQFP64	128K Flash, 16K RAM version of LPC2138/01
LPC2132/01	64K	16K	5	6			2	2		1	1		8	1	47		•	60	3.3 V		F	LQFP64, HVQFN64	64K Flash, 16K RAM version of LPC2138/01
LPC2131/01	32K	8K	5	6			2	2		1	1		8		47		•	60	3.3 V		F	LQFP64	32K Flash, 8K RAM version of LPC2138/01
LPC2129/01	256K	16K	5	6			2	1	2	2			4		46		•	60	1.8 V	3.3 V	F	LQFP64	LPC2124/01 upgrade with 2x CAN
LPC2119/01	128K	16K	5	6			2	1	2	2			4		46		•	60	1.8 V	3.3 V	F	LQFP64	LPC2114/01 upgrade with 2x CAN
LPC2109/01	64K	8K	5	6			2	1	1	2			4		46		•	60	1.8 V	3.3 V	F	LQFP64	LPC2119/01 with 64 KB Flash, 8 KB RAM, and 1x CAN
LPC2124/01	256K	16K	5	6			2	1		2			4		46		•	60	1.8 V	3.3 V	F	LQFP64	10-bit SA ADC, 2x SPI and 256K Flash
LPC2114/01	128K	16K	5	6			2	1		2			4		46		•	60	1.8 V	3.3 V	F	LQFP64	128K Flash version of the LPC2124/01
LPC2106	128K	64K	5	6			2	1		1					32		•	60	1.8 V	3.3 V	B, F	LQFP48	64K RAM, 128K Flash
LPC2105	128K	32K	5	6			2	1		1					32		•	60	1.8 V	3.3 V	B	LQFP48	32K RAM version of LPC2106
LPC2104	128K	16K	5	6			2	1		1					32		•	60	1.8 V	3.3 V	B	LQFP48	16K RAM version of LPC2106
LPC2103	32K	8K	6	14**			2	2		1	1		8		32		•	70	1.8 V	3.3 V	F	LQFP48	Lowest cost, lowest power, ADC
LPC2102	16K	4K	6	14**			2	2		1	1		8		32		•	70	1.8 V	3.3 V	F	LQFP48	16K Flash, 4K RAM version of LPC2103
LPC2101	8K	2K	6	14**			2	2		1	1		8		32		•	70	1.8 V	3.3 V	F	LQFP48	8K Flash, 2K RAM version of LPC2103

LPC900 series

Designed for applications that demand high integration and low cost over a wide range of performance requirements, these single-chip microcontrollers integrate a number of system-level functions.

Type	Memory			Timers			Serial interfaces			Analog			I/O pins	Frequency range (MHz) at 3 V	Temp. range options	Package	Comments / special features
	FLASH / EEPROM (program / data)	EEPROM (data)	RAM	Total no. of timers	PWM	RTC / system timer / WD	UART	I ² C	SPI	ADC channels resolution	DAC channels resolution	Comparators					
LPC95x devices																	
P89LPC954	16K		512 B	4	2 ch.	1	2	1	1	8/10b		2	40	0-18	F	PLCC44, LQFP44	LPC952 with 16 KB Flash
P89LPC952	8K		512 B	4	2 ch.	1	2	1	1	8/10b		2	40	0-18	F	PLCC44, LQFP44	LPC900 in 44/48-pin package; 2 UARTs; 2-wire debug interface
LPC940x devices																	
P89LPC9408	8K	512 B	768 B	5	CCU	1	1	1	1	8/10b		2	23	0-18	F	LQFP64	LPC938 with integrated PCF8576D universal LCD driver
P89LPC9401	8K		256 B	4	2 ch.	1	1	1	1			2	23	0-18	F	LQFP64	LPC931 with integrated PCF8576D universal LCD driver
LPC93x devices																	
P89LPC938	8K	512 B	768 B	5	CCU	1	1	1	1	8/10b		2	26	0-18	F	TSSOP28, HVQFN28, PLCC28	LPC935 with 10-bit ADC
P89LPC936	16K	512 B	768 B	5	CCU	1	1	1	1	2x4/8b	2x8b	2	26	0-18	F	TSSOP28	LPC935 with 16K Flash
P89LPC935	8K	512 B	768 B	5	CCU	1	1	1	1	2x4/8b	2x8b	2	26	0-18	F	TSSOP28, PLCC28, HVQFN28	LPC932A1 + two 4-ch 8-bit ADCs / two 8-bit DACs
P89LPC934	8K		256 B	4	2 ch.	1	1	1	1	4/8b	2x8b	2	26	0-18	F	TSSOP28	LPC930/931 + 4-ch 8-bit ADC / two 8-bit DACs
P89LPC933	4K		256 B	4	2 ch.	1	1	1	1	4/8b	2x8b	2	26	0-18	F	TSSOP28	LPC930/931 + 4-ch 8-bit ADC / two 8-bit DACs
P89LPC932A1	8K	512 B	768 B	5	CCU	1	1	1	1			2	26	0-18	F	TSSOP28, PLCC28, HVQFN28	LPC935 with ADCs and DACs
P89LPC9311	8K		256 B	4	2 ch.	1	1	1	1			2	26	0-18	F	TSSOP28	LPC931 with 8 high-drive pins (20 mA)
P89LPC931	8K		256 B	4	2 ch.	1	1	1	1			2	26	0-18	F	TSSOP28	4K / 8K Flash versions of LPC932A1 w/o EEPROM, w/o CCU, w/o XRAM
P89LPC930	4K		256 B	4	2 ch.	1	1	1	1			2	26	0-18	F	TSSOP28	4K / 8K Flash versions of LPC932A1 w/o EEPROM, w/o CCU, w/o XRAM
LPC92x devices																	
P89LPC925	8K		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	18	0-18	F	TSSOP20	LPC921/922 + 4-ch 8-bit ADC / 8-bit DAC; runs up to 18 MHz
P89LPC924	4K		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	18	0-18	F	TSSOP20	LPC921/922 + 4-ch 8-bit ADC / 8-bit DAC; runs up to 18 MHz
P89LPC9221	8K		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20, DIP20	LPC922 with 8 high-drive pins (20 mA)
P89LPC922	8K		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20, DIP20	20-pin versions of LPC930/931 w/o SPI; LPC76x pin-comp. upgrade
P89LPC921	4K		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20	20-pin versions of LPC930/931 w/o SPI; LPC76x pin-comp. upgrade
P89LPC920	2K		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20	2K Flash version of 921/922
LPC91x devices																	
P89LPC917	2K		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	14	0-18	F	TSSOP16	4-ch 8-bit ADC / 8-bit DAC; 2 serial channels; 2-ch 8-bit PWM
P89LPC916	2K		256 B	4	1 ch.	1	1	1	1	4/8b	1/8b	2	14	0-18	F	TSSOP16	4-ch 8-bit ADC / 8-bit DAC; 3 serial channels; 1-ch 8-bit PWM
P89LPC915	2K		256 B	4	1 ch.	1	1	1		4/8b	1/8b	2	12	0-18	F, H	TSSOP14, DIP14	4-ch 8-bit ADC / 8-bit DAC; 2 serial channels; 1-ch 8-bit PWM
P89LPC914	1K		128 B	4	1 ch.	1	1		1			2	12	0-IRC	F	TSSOP14	1-ch 8-bit PWM; UART; SPI; 12 I/O pins
P89LPC913	1K		128 B	4		1	1		1			2	12	0-18	F	TSSOP14	UART; SPI; 12 I/O pins; external crystal pins
P89LPC912	1K		128 B	4	1 ch.	1			1			2	12	0-18	F	TSSOP14	1-ch 8-bit PWM; SPI; 12 I/O pins; external crystal pins
LPC910x devices																	
P89LPC9107	1K		128 B	4	2 ch.	1	1			4/8b	1/8b	1	10	0-18	F	TSSOP14, DIP14	Clock doubler for internal RC OSC
P89LPC9103	1K		128 B	4		1	1			4/8b	1/8b	1	8	0-18	F	HVSON10	Smallest available package 3 x 3 mm ²
P89LPC9102	1K		128 B	4	2 ch.	1				4/8b	1/8b	1	8	0-18	F	HVSON10	Smallest available package 3 x 3 mm ²
LPC90x devices																	
P89LPC908	1K		128 B	4		1	1					1	6	0-IRC	F	SO8	UART; 6 I/O pins
P89LPC907	1K		128 B	4		1	1 ⁽¹⁾					1	6	0-IRC	F	SO8	UART ⁽¹⁾ (Transmit function only); 6 I/O pins
P89LPC906	1K		128 B	4	1 ch.	1						1	6	0-18	F	SO8	1-ch 8-bit PWM; 6 I/O pins; external crystal pins
P89LPC903	1K		128 B	4		1	1					2	6	0-IRC	F	SO8	Industry-standard pinout; 6 I/O pins; 2 analog comparators; UART
P89LPC902	1K		128 B	4		1						2	6	0-IRC	F	SO8, DIP8	Industry-standard pinout; 6 I/O pins; 2 analog comp. 5 ext. interrupt inputs
P89LPC901	1K		128 B	4	1 ch.	1						1	6	0-18	F	SO8, DIP8	Industry-standard pinout; 6 I/O pins; 1-ch 8-bit PWM; external crystal pins

Notes: (1) LPC900 FLASH EEPROM features: Program and data (byte) storage, block-/sector-/page-/byte-erasable, 2-ms erase, data read via MOVN instruction. (2) Auxiliary EEPROM features: Data (byte) storage, page-/byte-erasable, 2-ms erase. (3) Reset active low.

LPC700 series

Designed for applications that demand low voltage, high integration, and low cost, the LPC700 series uses a high-performance 6-clock 80C51 that executes instructions at twice the rate of the standard 80C51. To reduce component count, board space, and system cost, the devices combine a number of system supervisory functions, serial interfaces, and analog options in low-profile SO and TSSOP packages.

Type	Memory			Timers			Serial interfaces		Analog		I/O pins	Max. frequency (MHz)	Temp. range options	Package	Comments / special features
	OTP / ROM	RAM	ICP / PP	No. of timers	PWM	WD	UART	I ² C	ADC ch. / bits	Comparators					
LPC76x / LPC77x devices															
P87LPC779	8K	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	F	TSSOP20	LPC769 upgrade with 8K OTP; addtl 128 B of RAM not supported by emulators
P87LPC778	8K	128 B	ICP	2	•	•	1	1 (bit)	4/8	2	18	20	F	TSSOP20	LPC768 upgrade with 8K OTP; addtl 128 B of RAM not supported by emulators
P87LPC769	4K	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	H	SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC, 2ch 8-bit DAC
P87LPC768	4K	128 B	ICP	2	•	•	1	1 (bit)	4/8	2	18	20	B, F	DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC, PWM
P87LPC767	4K	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	B, F	DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC
P87LPC764	4K	128 B	ICP	2		•	1	1 (bit)		2	18	20	B, F, H	TSSOP20, DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 10% / ± 25%)
P87LPC762	2K	128 B	ICP	2		•	1	1 (bit)		2	18	20	B, F	TSSOP20, DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 10% / ± 25%)
P87LPC761	2K	128 B	ICP	2		•	1	1 (bit)		2	14	20	B	TSSOP16, DIP16	16-pin LPC derivative; ± 2.5% internal RC Oscillator (0-50 °C)
P87LPC760	1K	128 B	ICP	2		•	1	1 (bit)		2	12	20	B	TSSOP14, DIP14	14-pin LPC derivative; ± 2.5% internal RC Oscillator (0-50 °C)

80C51 family

Designed for real-time applications, these 8-bit microcontrollers are used in a wide variety of applications, from consumer products and computer peripherals to automotive systems. The NXP portfolio includes Flash, OTP (one-time programmable), ROM, and ROMless devices.

Type	Memory			Timers			Serial interfaces			I/O Pins	Max. freq. (MHz)	Temp. range options	Package	Comments / special features
	FLASH	OTP / ROM	RAM	No. of timers	PWM	WD	UART	I ² C	SPI					
66x devices														
P89V664	64K		2K	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
P89V662	32K		1K	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
P89V660	16K		512 B	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
66xX2 devices														
P87C661X2		16K	512 B	4	•	•	1	2		32	33	B	PLCC44, LQFP44	87C660X2 with two I ² C interfaces
P87C660X2		16K	512 B	4	•	•	1	1		32	33	B, F	PLCC44, LQFP44	OTP version of 89C660; 12-clk default, 6-clk option
Mx2 devices														
P87C51MC2/02		96K	3K	4	•	•	2		1	34	24	B	PLCC44	16 MB data/code addr. range; 2 UARTs, SPI, P4 I/O
P87C51MB2/02		64K	2K	4	•	•	2		1	34	24	B	PLCC44	16 MB data/code addr. range; 2 UARTs, SPI, P4 I/O

Continued next page

80C51 family (continued)

Type	Memory			Timers			Serial interfaces			I/O Pins	Max. freq. (MHz)	Temp. range options	Package	Comments / special features
	FLASH	OTP / ROM	RAM	No. of timers	PWM	WD	UART	I ² C	SPI					
Rx2 devices														
P89CV51RD2	64K		1K	4	•	•	1		1	32	33	B, F	PLCC44, TQFP44	
P89LV51RD2	64K		1K	4	•	•	1		1	32	33	B, F	DIP40, PLCC44, LQFP44	
P89LV51RC2	32K		1K	4	•	•	1		1	32	33	B, F	DIP40, PLCC44, LQFP44	
P89LV51RB2	16K		1K	4	•	•	1		1	32	33	B, F	PLCC44, LQFP44	
P89V51RD2	64K		1K	4	•	•	1		1	32	40	B, F	DIP40, PLCC44, LQFP44	
P89V51RC2	32K		1K	4	•	•	1		1	32	40	B, F	DIP40, PLCC44, LQFP44	
P89V51RB2	16K		1K	4	•	•	1		1	32	40	B, F	DIP40, PLCC44, LQFP44	
P89V52X2	8K		256 B	4	•		1			32	33	B, F	DIP40, PLCC44, TQFP44	192B EEPROM

Temperature Legend:

B	0 to +70 °C
F	-40 to +85 °C
H	-40 to +125 °C
J	-40 to +105 °C

Need devices, support, and development tools?

For a list of sales offices and distributors near you, please visit www.nxp.com/profile/sales/index.html

For general support, please visit www.nxp.com/microcontrollers

For tools, evaluation boards, and development support, please visit www.standardics.nxp.com/support/board

www.nxp.com



© 2007 NXP B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release: September 2007

Document order number: 9397 750 16132

Printed in the USA