

The choice for embedded technologies

Our microcontroller offering combines the highest performance in Flash with the lowest power consumption in the smallest packages. A comprehensive portfolio of industry-leading performers includes the latest 32-bit LPC3000, LPC2000, LPC1000, LH7A, LH7, and 8-bit LPC900, LPC700 and 80C51 families. We offer an easy migration path from 8-bit to 32-bit solutions.

LPC3000 series

The 32-bit LPC3000 series is based on the ARM926EJ core and is the only ARM9 microcontroller that provides a vector floating-point co-processor and integrated USB On-The-Go, as well as the ability to operate in ultra-low-power mode down to 0.9V. With speeds of up to 266 MHz, the NXP LPC3000 series supports Linux and WinCE and is ideal for a wide range of applications in consumer, medical, industrial, automotive and networking.

Type	Memory				Timers		Serial interfaces							Analog	LCD Controller	SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	Instruction cache	Data cache	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	SPI	SSP	I ² S	ADC (10-bit) No. of channels											
LPC3250	256 KB	32 KB	32 KB	32 KB	8	11	1	1	7	2	2	2	2	3	•	•	87	•	•	266/208	1.35/1.2 V	1.8/ 2.8/ 3.0 V	F	LFBGA296	VFP unit, NAND Flash, SRAM/SDRAM/DDR, USB 2.0 FS OTG/Host/Device, 24-bit Color LCD controller and Touch Screen controller, Keypad interface and 0.9v low power mode
LPC3240	256 KB	32 KB	32 KB	32 KB	8	11	1	1	7	2	2	2	2	3		•	87	•	•	266/208	1.35/1.2 V	1.8/ 2.8/ 3.0 V	F	LFBGA296	VFP unit, NAND Flash, SRAM/SDRAM/DDR, USB 2.0 FS OTG/Host/Device, Keypad interface and 0.9v low power mode
LPC3230	256 KB	32 KB	32 KB	32 KB	8	11		1	7	2	2	2	2	3	•	•	87	•	•	266/208	1.35/1.2 V	1.8/ 2.8/ 3.0 V	F	LFBGA296	VFP unit, NAND Flash, SRAM/SDRAM/DDR, USB 2.0 FS OTG/Host/Device, 24-bit Color LCD controller and Touch Screen controller, Keypad interface and 0.9v low power mode
LPC3220	128 KB	32 KB	32 KB	32 KB	8	11		1	7	2	2	2	2	3		•	87	•	•	266/208	1.35/1.2 V	1.8/ 2.8/ 3.0 V	F	LFBGA296	VFP unit, NAND Flash, SRAM/SDRAM/DDR, USB 2.0 FS OTG/Host/Device, Keypad interface and 0.9v low power mode
LPC3180/01	64 KB	32 KB	32 KB	32 KB	4	2		1	7	2	2		3		•	55	•	•	266/208	1.35/1.2 V	1.8/ 2.8/ 3.0 V	F	LFBGA320	VFP unit, NAND Flash, SDRAM/DDR, USB 2.0 FS OTG/Host/Device	

LH7A series

To save time-to-market for applications that use an LCD screen, these ARM922T-based microcontrollers are equipped with an LCD controller. Supported by a comprehensive set of software and hardware design tools, the LH7A series makes it easy to create everything from cost-conscious consumer systems to advanced systems with media-rich environments.

Type	Memory				Timers		Serial interfaces				Analog		LCD Controller	SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	Instruction cache	Data cache	No. of timers	PWM channels	USB	UART	I ² C	SPI	ADC (10-bit) No. of channels	No. of channels											
LH7A404	80 KB Frame Buffer	8 KB	8 KB	8 KB	5	2	1	3	0	1	10	•	•	64	•	•	266	1.8 V	3.3 V	F	LFBGA324	Integrated LCD controller. IrDA touchscreen interface. Touchscreen controller. MMU. USB 2.0 Full Speed Host/Device. 32-bit external data bus. CompactFlash. SDRAM controller. DMA controller. PCMCIA, BMI, PS/2, MMC/SD.	
LH7A400	80 KB Frame Buffer	8 KB	8 KB	8 KB	5	0	1	3	0	1		•	•	60	•	•	245	1.8 V	3.3 V	F	BGA256 LFBGA256	Integrated LCD controller. IrDA. MMU. USB 2.0 Full Speed device. 32-bit external data bus. CompactFlash. SDRAM controller. MMC, PCMCIA, BMI.	

LPC1000 series

Based on the ARM Cortex-M3 core operating at 80 MHz, these low power 32-bit microcontrollers feature a broad range of serial interfaces including Ethernet, USB Host/OTG/Device, and CAN, as well as a broad range of analog peripherals. The controllers are ideal for a broad range of applications, such as eMetering, Medical, POS, and Industrial networking.

Type	Memory		Timers		Serial interfaces								Analog		SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S	ADC (12-bit) No. of channels	DAC (10-bit) No. of channels										
LPC1766	256 KB	64 KB	6	6	1	1	4	3	2	1	2	1	8	1	70		•	80	3.3 V	F	LQFP100	USB Host/OTG/Device, GP DMA, 4 MHz RC Oscillator, Motor Controller, Available Q4 '08		
LPC1765	256 KB	64 KB	6	6		1	4	3	2	1	2	1	8	1	70		•	80	3.3 V	F	LQFP100	LPC1766 without Ethernet. Available Q4 '08		
LPC1764	128 KB	32 KB	6	6	1	1	4	3	2	1	2		8		70		•	80	3.3 V	F	LQFP100	LPC1766 with 128 KB Flash, 32 KB SRAM, and no I ² S & no DAC. Available Q4 '08		
LPC1754	128 KB	32 KB	6	6	1	1	4	3	2	1	2	1	6	1	54		•	80	3.3 V	F	LQFP80	80-pin version of LPC1766 with 128 KB Flash and 32 KB SRAM. Available Q4 '08		
LPC1753	128 KB	32 KB	6	6		1	4	3	1	1	2		6	1	54		•	80	3.3 V	F	LQFP80	LPC1754 without Ethernet and I ² S. Available Q4 '08		
LPC1752	64 KB	16 KB	6	6		1	4	3	1	1	2		6		54		•	80	3.3 V	F	LQFP80	LPC1753 with 64 KB Flash, 16 KB SRAM and no DAC. Available Q4 '08		
LPC1751	32 KB	8 KB	6	6		1	4	3	1	1	2		6		54		•	80	3.3 V	F	LQFP80	LPC1752 with 32 KB Flash and 16 KB SRAM. Available Q4 '08		

LPC2000 and LH7 series

Based on an ARM7TDMI-S core operating at up to 84 MHz, these 32-bit microcontrollers deliver high performance and low power consumption in a cost-effective package. In addition to offering integrated LCD support, they offer a wide range of peripherals, including multiple serial interfaces, Ethernet, USB Host/OTG, CAN, and external bus options and are designed for use in general-purpose and specialty embedded applications such as industrial control, automotive, medical, and connectivity.

Type	Memory		Timers			Serial interfaces						Analog		LCD Controller	SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	EEPROM (KB)	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S											
LPC2900 devices																								
LPC2939	768 KB	48 KB	16	5	24	1	4	2	2	3			24			160	•	•	100	1.8 V	3.3 V	F	LQFP208	ARM968E-S MCU with USB Host/OTG/Device, 32 KB I- & D- TCM, Motor Control, GP, DMA, 16 KB EEPROM. Available Q1 '09
LPC2930		48 KB	16	5	24	1	4	2	2	3			24			160	•	•	100	1.8 V	3.3 V	F	LQFP208	Flashless version of LPC2939. Available Q1 '09
LPC2929	768 KB	48 KB	16	5	24	1	4	2	2	3			24			108	•	•	100	1.8 V	3.3 V	F	LQFP144	LPC2939 with 144 pins without USB Host. Available Q4 '08
LPC2927	512 KB	48 KB	16	5	24	1	4	2	2	3			24			108	•	•	100	1.8 V	3.3 V	F	LQFP144	LPC2929 with 512 KB Flash. Available Q4 '08
LPC2925	512 KB	32 KB	16	5	24	1	4	2	2	3			16			76		•	100	1.8 V	3.3 V	F	LQFP100	LPC2927 with 100 pins, with 32 KB SRAM, 16 KB I- & D- TCM and 16 channels of ADC. No External Memory Interface. Available Q1 '09
LPC2923	256 KB	16 KB	16	5	24	1	4	2	2	3			16			76		•	100	1.8 V	3.3 V	F	LQFP100	LPC2925 with 256 KB Flash, 16 KB SRAM. Available Q1 09
LPC2921	128 KB	16 KB	16	5	24	1	4	2	2	3			16			76		•	100	1.8 V	3.3 V	F	LQFP100	LPC2923 with 128 KB Flash. Available Q1 09
LPC2919/01	768 KB	48 KB		5	24			2	2	2	3		16			108	•	•	80	1.8 V	3.3 V	F	LQFP144	ARM968E-S MCU with 2 LIN Master Controllers, 16 KB I-TCM, 16 KB D-TCM
LPC2917/01	512 KB	48 KB		5	24			2	2	2	3		16			108	•	•	80	1.8 V	3.3 V	F	LQFP144	ARM968E-S MCU with 2 LIN Master Controllers, 16 KB I-TCM, 16 KB D-TCM
LPC2800 devices																								
LPC2888	1M	64 KB		4		1	1	1				1	5			• 85	•	•	60	1.8 V	3.3 V	F	TBGA180	USB V2.0 high speed; IrDA configurable; LCD interface logic; /01 version for JTAG enabled (for development), /D1 version for JTAG disabled (for production)
LPC2880		64 KB		4		1	1	1				1	5			• 85	•	•	60	1.8 V	3.3 V	F	TBGA180	LPC2880 is the ROMless version of the LPC2888
LH7 devices																								
LH79525		16 KB + 8 KB cache		5	3	1	1	3	1		1	1	10			• 86	•	•	76	1.8 V	3.3 V	F	LQFP176	ARM720T MCU with color LCD controller. Touchscreen interface. USB 2.0 device. IrDA. SDRAM controller. MMU. DMA. NAND Flash boot. 16-bit external data bus.
LH79524		16 KB + 8 KB cache		5	3	1	1	3	1		1	1	10			• 104	•	•	76	1.8 V	3.3 V	F	LFPGA208	ARM720T MCU with color LCD controller. Touchscreen interface. USB 2.0 device. IrDA. SDRAM controller. MMU. DMA. NAND Flash boot. 32-bit external data bus.
LH79520		32 KB + 8 KB cache		6	2			3			1	1				• 64	•	•	77	1.8 V	3.3 V	F	LQFP176	ARM720T MCU with color LCD controller. IrDA. SDRAM controller. MMU. 32-bit external data bus.
LH75411		32 KB		5	3			3			1	1	8			• 76	•	•	84	1.8 V	3.3 V	F	LQFP144	Color LCD controller. Touchscreen interface. DMA controller. 5-V-tolerant I/O. 16-bit external data bus.
LH75401		32 KB		5	3			3			1	1	1	8		• 76	•	•	84	1.8 V	3.3 V	F	LQFP144	Color LCD controller. Touchscreen interface. DMA controller. 5-V-tolerant I/O. 16-bit external data bus.
LPC2400 devices																								
LPC2478	512 KB	98 KB		6	12	1	1	4	3	2	1	2	1	8	1	• 160	•	•	72	3.3 V		F	LQFP208 TFBGA208	LPC2468 with XGA LCD controller
LPC2470		98 KB		6	12	1	1	4	3	2	1	2	1	8	1	• 160	•	•	72	3.3 V		F	LQFP208 TFBGA208	LPC2460 with XGA LCD controller
LPC2468	512 KB	98 KB		6	12	1	1	4	3	2	1	2	1	8	1	• 160	•	•	72	3.3 V		F	LQFP208 TFBGA208	On-chip 4-MHz RC-Osc, GP DMA, RTC w/ 2 K batt. RAM 2 PWM blocks; USB 2.0 FS Host/OTG/device, DMA and 4 K RAM; UART 3 w/ IrDA; 32-bit ext. bus
LPC2460		98 KB		6	12	1	1	4	3	2	1	2	1	8	1	• 160	•	•	72	3.3 V		F	LQFP208, TFBGA208	Flashless LPC2468
LPC2458	512 KB	98 KB		6	12	1	1	4	3	2	1	2	1	8	1	• 136	•	•	72	3.3 V		F	TFBGA180	LPC2468 with 16-bit External Memory Interface
LPC2420		82 KB		6	12	1	4	3		1	2	1	8	1	• 160	•	•	72	3.3 V		F	LQFP208	Flashless USB Host/OTG/Device controller	

LPC2000 series

Type	Memory		Timers		Serial interfaces							Analog		LCD Controller	SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features		
	FLASH	RAM	EEPROM (KB)	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S												ADC (10-bit) No. of channels	DAC (10-bit) No. of channels
LPC2300 devices																										
LPC2388	512 KB	98 KB		6	6	1	1	4	3	2	1	2	1	8	1		•	104	•	•	72	3.3 V	F	LQFP144	LPC2378 with 98 K SRAM and USB Host/OTG	
LPC2387	512 KB	98 KB		6	6	1	1	4	3	2	1	2	1	6	1		•	70		•	72	3.3 V	F	LQFP100	LPC2368 with 98 K SRAM and USB Host/OTG	
LPC2378	512 KB	58 KB		6	6	1	1	4	3	2	1	2	1	8	1		•	104	•	•	72	3.3 V	F	LQFP144	On-chip 4MHz RC-Osc, GP DMA, RTC w/ 2 K batt. RAM USB 2.0 FS device w/ PHY, DMA and 4 K RAM; UART 3 w/ IrDA; MiniBus (8-bit)	
LPC2377	512 KB	58 KB		6	6	1		4	3		1	2	1	8	1		•	104	•	•	72	3.3 V	F	LQFP144	LPC2378 without USB or CAN	
LPC2368	512 KB	58 KB		6	6	1	1	4	3	2	1	2	1	6	1		•	70		•	72	3.3 V	F	LQFP100	100-pin version of LPC2378, no external bus	
LPC2367	512 KB	58 KB		6	6	1		4	3		1	2	1	6	1		•	70		•	72	3.3 V	F	LQFP100	LPC2368 without USB or CAN	
LPC2366	256 KB	58 KB		6	6	1	1	4	3	2	1	2	1	6	1			70		•	72	3.3 V	F	LQFP100	256 K Flash version of LPC2368, no SD/MMC	
LPC2365	256 KB	58 KB		6	6	1		4	3		1	2	1	6	1			70		•	72	3.3 V	F	LQFP100	LPC2366 without USB or CAN	
LPC2364	128 KB	34 KB		6	6	1	1	4	3	2	1	2	1	6	1			70		•	72	3.3 V	F	LQFP100	128 K Flash / 34 K RAM version of LPC2368, no SD/MMC	
LPC2362	128 KB	58 KB		6	6	1	1	4	3	2	1	2	1	6	1			70		•	72	3.3 V	F	LQFP100	LPC2364 with USB Host/OTG/Device and more RAM	
LPC2361	64 KB	34 KB		6	6		1	4	3	2	1	2	1	6	1			70		•	72	3.3 V	F	LQFP100	64 KB Flash, USB Host/OTG/Host and CAN controller	
LPC2200 devices																										
LPC2294/01	256 KB	16 KB		5	6			2	1	4	2			8				112	•	•	60	1.8 V	3.3 V	H	LQFP144	LPC2214/01 upgrade with 4x CAN
LPC2292/01	256 KB	16 KB		5	6			2	1	2	2			8				112	•	•	60	1.8 V	3.3 V	F	LQFP144, TFBGA144	LPC2214/01 upgrade with 2x CAN
LPC2290/01		64 KB		5	6			2	1	2	2			8				76	•	•	60	1.8 V	3.3 V	F	LQFP144	ROMless version of LPC2292/01
LPC2220		64 KB		5	6			2	1		2			8				76	•	•	75	1.8 V	3.3 V	F	LQFP144, TFBGA144	64 K RAM version of LPC2210/01
LPC2214/01	256 KB	16 KB		5	6			2	1		2			8				112	•	•	60	1.8 V	3.3 V	F	LQFP144	External Bus, 4 Chip Selects, 10-bit SA ADC, 256 K Flash
LPC2212/01	128 KB	16 KB		5	6			2	1		2			8				112	•	•	60	1.8 V	3.3 V	F	LQFP144	128 K Flash version of LPC2214/01
LPC2210/01		16 KB		5	6			2	1		2			8				76	•	•	60	1.8 V	3.3 V	F	LQFP144	ROMless version of LPC2214/01
LPC2100 devices																										
LPC2194/01	256 KB	16 KB		5	6			2	1	4	2			4				46		•	60	1.8 V	3.3 V	H	LQFP64	LPC2124/01 upgrade with 4x CAN
LPC2158	512 KB	40 KB		5	6		1	2	1		1	1		8+6	1	•		32		•	60	3.3 V		F	LQFP100	LPC2148 with 32 x 4 LCD driver
LPC2157	512 KB	32 KB		5	6			2	1		1	1		2x8	1	•		32		•	60	3.3 V		F	LQFP100	LPC2138/01 with 32 x 4 LCD driver
LPC2148	512 KB	40 KB		5	6		1	2	2		1	1		8+6	1			45		•	60	3.3 V		F	LQFP64	LPC2138 plus USB 2.0 full speed
LPC2146	256 KB	40 KB		5	6		1	2	2		1	1		8+6	1			45		•	60	3.3 V		F	LQFP64	LPC2136 plus USB 2.0 full speed
LPC2144	128 KB	16 KB		5	6		1	2	2		1	1		8+6	1			45		•	60	3.3 V		F	LQFP64	LPC2134 plus USB 2.0 full speed
LPC2142	64 KB	16 KB		5	6		1	2	2		1	1		6	1			45		•	60	3.3 V		F	LQFP64	LPC2132 plus USB 2.0 full speed
LPC2141	32 KB	8 KB		5	6		1	2	2		1	1		6				45		•	60	3.3 V		F	LQFP64	LPC2131 plus USB 2.0 full speed
LPC2138/01	512 KB	32 KB		5	6			2	2		1	1		2x8	1			47		•	60	3.3 V		F	LQFP64, HVQFN64	Dual 8-ch. 10-bit ADC, BOD, POR, 32-kHz XTAL input, VBAT, Fast I/O
LPC2136/01	256 KB	32 KB		5	6			2	2		1	1		2x8	1			47		•	60	3.3 V		F	LQFP64	256 K Flash version of LPC2138/01
LPC2134/01	128 KB	16 KB		5	6			2	2		1	1		2x8	1			47		•	60	3.3 V		F	LQFP64	128 K Flash, 16 K RAM version of LPC2138/01
LPC2132/01	64 KB	16 KB		5	6			2	2		1	1		8	1			47		•	60	3.3 V		F	LQFP64, HVQFN64	64 K Flash, 16 K RAM version of LPC2138/01
LPC2131/01	32 KB	8 KB		5	6			2	2		1	1		8				47		•	60	3.3 V		F	LQFP64	32 K Flash, 8 K RAM version of LPC2138/01
LPC2129/01	256 KB	16 KB		5	6			2	1	2	2			4				46		•	60	1.8 V	3.3 V	F	LQFP64	LPC2124/01 upgrade with 2x CAN
LPC2119/01	128 KB	16 KB		5	6			2	1	2	2			4				46		•	60	1.8 V	3.3 V	F	LQFP64	LPC2114/01 upgrade with 2x CAN

LPC2000 series

Type	Memory			Timers		Serial interfaces						Analog		LCD Controller	SD/MMC	I/O pins	External bus interface	PLL	Max. freq. (MHz)	CPU voltage	I/O voltage	Temp. range options	Package	Comments / special features
	FLASH	RAM	EEPROM (KB)	No. of timers*	PWM channels	Ethernet	USB	UART	I ² C	CAN	SPI	SSP	I ² S											
LPC2109/01	64 KB	8 KB		5	6			2	1	1	2			4					• 60	1.8 V	3.3 V	F	LQFP64	LPC2119/01 with 64 KB Flash, 8 KB RAM, and 1x CAN
LPC2124/01	256 KB	16 KB		5	6			2	1		2			4					• 60	1.8 V	3.3 V	F	LQFP64	10-bit SA ADC, 2x SPI and 256 K Flash
LPC2114/01	128 KB	16 KB		5	6			2	1		2			4					• 60	1.8 V	3.3 V	F	LQFP64	128 K Flash version of the LPC2124/01
LPC2106/01	128 KB	64 KB		5	6			2	1		1								• 60	1.8 V	3.3 V	B, F	LQFP48	64 K RAM, 128 K Flash
LPC2105/01	128 KB	32 KB		5	6			2	1		1								• 60	1.8 V	3.3 V	B	LQFP48	32 K RAM version of LPC2106/01
LPC2104/01	128 KB	16 KB		5	6			2	1		1								• 60	1.8 V	3.3 V	B	LQFP48	16 K RAM version of LPC2106/01
LPC2103	32 KB	8 KB		6	14**			2	2		1	1		8					• 70	1.8 V	3.3 V	F	LQFP48, HVQFN48	Lowest cost, lowest power, ADC
LPC2102	16 KB	4 KB		6	14**			2	2		1	1		8					• 70	1.8 V	3.3 V	F	LQFP48 HVQFN48	16 K Flash, 4 K RAM version of LPC2103
LPC2101	8 KB	2 KB		6	14**			2	2		1	1		8					• 70	1.8 V	3.3 V	F	LQFP48	8 K Flash, 2 K RAM version of LPC2103

Note: Reset active low. * Includes Watchdog timer and real-time clock. ** Using timers 0-3.

LPC900 series

Designed for applications that demand high integration and low cost over a wide range of performance requirements, these single-chip microcontrollers integrate a number of system-level functions.

Type	Memory			Timers			Serial interfaces			Analog			I/O pins	Frequency range (MHz) at 3 V	Temp. range options	Package	Comments / special features
	FLASH / EEPROM (program / data)	EEPROM (data)	RAM	Total no. of timers	PWM	RTC / system timer / WD	UART	I ² C	SPI	ADC channels resolution	DAC channels resolution	Comparators					
LPC95x devices																	
P89LPC954	16 KB		512 B	4	2 ch.	1	2	1	1	8/10b		2	40	0-18	F	PLCC44, LQFP44, LQFP48	LPC952 with 16 KB Flash
P89LPC952	8 KB		512 B	4	2 ch.	1	2	1	1	8/10b		2	40	0-18	F	PLCC44, LQFP44	LPC900 in 44/48-pin package; 2 UARTs; 2-wire debug interface
LPC940x devices																	
P89LPC9408	8 KB	512 B	768 B	5	CCU	1	1	1	1	8/10b		2	23	0-18	F	LQFP64	LPC938 with integrated PCF8576D universal LCD driver
P89LPC9401	8 KB		256 B	4	2 ch.	1	1	1	1			2	23	0-18	F	LQFP64	LPC931 with integrated PCF8576D universal LCD driver
LPC93x devices																	
P89LPC9351	8 KB	512 B	768 B	5	CCU	1	1	1	1	4x8b/1x8b	4x8b/1x8b	2	26	0-18	F	TSSOP28, PLCC28	LPC935 with 2 x PGAs, Temp Sensor and other enhanced features
P89LPC9321	8 KB	512 B	768 B	5	CCU	1	1	1	1			2	26	0-18	F	TSSOP28, PLCC28, PDIP28	LPC932 with PGA, Temp Sensor and other enhanced features
P89LPC9381	4 KB		256 B	4		1	1	1	1	8/10b		2	26	0-18	F	TSSOP28	4K flash version of LPC938
P89LPC938	8 KB	512 B	768 B	5	CCU	1	1	1	1	8/10b		2	26	0-18	F	TSSOP28, HVQFN28, PLCC28	LPC935 with 10-bit ADC
P89LPC936	16 KB	512 B	768 B	5	CCU	1	1	1	1	2x4/8b	2x8b	2	26	0-18	F	TSSOP28	LPC935 with 16K Flash
P89LPC935	8 KB	512 B	768 B	5	CCU	1	1	1	1	2x4/8b	2x8b	2	26	0-18	F	TSSOP28, PLCC28, HVQFN28	LPC932A1 + two 4-ch 8-bit ADCs / two 8-bit DACs
P89LPC934	8 KB		256 B	4	2 ch.	1	1	1	1	4/8b	1/ 8b	2	26	0-18	F	TSSOP28	LPC931 + 4-ch 8-bit ADC/ 1-ch 8-bit DAC

Continued next page

LPC900 series (continued)

Type	Memory			Timers			Serial interfaces			Analog			I/O pins	Frequency range (MHz) at 3 V	Temp. range options	Package	Comments / special features
	FLASH / EEPROM (program / data)	EEPROM (data)	RAM	Total no. of timers	PWM	RTC / system timer / WD	UART	I ² C	SPI	ADC channels resolution	DAC channels resolution	Comparators					
P89LPC933	4 KB		256 B	4	2 ch.	1	1	1	1	4/8b	1/ 8b	2	26	0-18	F, H	TSSOP28	LPC930 + 4-ch 8-bit ADC/ 1-ch 8-bit DAC
P89LPC932A1	8 KB	512 B	768 B	5	CCU	1	1	1	1			2	26	0-18	F	TSSOP28, PLCC28, HVQFN28, DIP28	LPC935 without ADC and DAC
P89LPC931	8 KB		256 B	4	2 ch.	1	1	1	1			2	26	0-18	F	TSSOP28	4K / 8K Flash versions of LPC932A1 w/o EEPROM, w/o CCU, w/o XRAM
P89LPC930	4 KB		256 B	4	2 ch.	1	1	1	1			2	26	0-18	F	TSSOP28	4K / 8K Flash versions of LPC932A1 w/o EEPROM, w/o CCU, w/o XRAM
LPC92x devices																	
P89LPC925	8 KB		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	18	0-18	F	TSSOP20	LPC921/922 + 4-ch 8-bit ADC / 8-bit DAC; runs up to 18 MHz
P89LPC924	4 KB		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	18	0-18	F	TSSOP20	LPC921/922 + 4-ch 8-bit ADC / 8-bit DAC; runs up to 18 MHz
P89LPC9221	8 KB		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20	LPC922 with 8 high-drive pins (20 mA)
P89LPC922	8 KB		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20, DIP20	20-pin versions of LPC930/931 w/o SPI; LPC76x pin-comp. upgrade
P89LPC921	4 KB		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20, DIP20	20-pin versions of LPC930/931 w/o SPI; LPC76x pin-comp. upgrade
P89LPC920	2 KB		256 B	4	2 ch.	1	1	1				2	18	0-18	F	TSSOP20	2K Flash version of 921/922
LPC91x devices																	
P89LPC917	2 KB		256 B	4	2 ch.	1	1	1		4/8b	1/8b	2	14	0-IRC	F	TSSOP16	4-ch 8-bit ADC / 8-bit DAC; 2 serial channels; 2-ch 8-bit PWM
P89LPC916	2 KB		256 B	4	1 ch.	1	1	1	1	4/8b	1/8b	2	14	0-IRC	F	TSSOP16	4-ch 8-bit ADC / 8-bit DAC; 3 serial channels; 1-ch 8-bit PWM
P89LPC915	2 KB		256 B	4	1 ch.	1	1	1		4/8b	1/8b	2	12	0-IRC	F, H	TSSOP14, DIP14	4-ch 8-bit ADC / 8-bit DAC; 2 serial channels; 1-ch 8-bit PWM
P89LPC913	1 KB		128 B	4		1	1		1			2	12	0-18	F	TSSOP14	UART; SPI; 12 I/O pins; external crystal pins
P89LPC912	1 KB		128 B	4	1 ch.	1			1			2	12	0-18	F, H	TSSOP14	1-ch 8-bit PWM; SPI; 12 I/O pins; external crystal pins
LPC910x devices																	
P89LPC9107	1 KB		128 B	4	2 ch.	1	1			4/8b	1/8b	1	10	0-18	F	TSSOP14, DIP14	Clock doubler for internal RC OSC
P89LPC9103	1 KB		128 B	4		1	1			4/8b	1/8b	1	8	0-18	F	HVSON10	Smallest available package 3 x 3 mm ²
LPC90x devices																	
P89LPC903	1 KB		128 B	4		1	1					2	6	0-IRC	F	SO8	Industry-standard pinout; 6 I/O pins; 2 analog comparators; UART
P89LPC902	1 KB		128 B	4		1						2	6	0-IRC	F	SO8, DIP8	Industry-standard pinout; 6 I/O pins; 2 analog comp. 5 ext. interrupt inputs
P89LPC901	1 KB		128 B	4	1 ch.	1						1	6	0-18	F	SO8, DIP8	Industry-standard pinout; 6 I/O pins; 1-ch 8-bit PWM; external crystal pins

Notes: (1) LPC900 FLASH EEPROM features: Program and data (byte) storage, block-/sector-/page-/byte-erasable, 2-ms erase, data read via MOVc instruction. (2) Auxiliary EEPROM features: Data (byte) storage, page-/byte-erasable, 2-ms erase. (3) Reset active low.

LPC700 series

Designed for applications that demand low voltage, high integration, and low cost, the LPC700 series uses a high-performance 6-clock 80C51 that executes instructions at twice the rate of the standard 80C51. To reduce component count, board space, and system cost, the devices combine a number of system supervisory functions, serial interfaces, and analog options in low-profile SO and TSSOP packages.

Type	Memory			Timers			Serial interfaces		Analog		I/O pins	Max. frequency (MHz)	Temp. range options	Package	Comments / special features
	OTP / ROM	RAM	ICP / PP	No. of timers	PWM	WD	UART	I ² C	ADC ch. / bits	Comparators					
LPC76x / LPC77x devices															
P87LPC779	8 KB	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	F	TSSOP20	LPC769 upgrade with 8K OTP; addtl 128 B of RAM not supported by emulators
P87LPC778	8 KB	128 B	ICP	2	•	•	1	1 (bit)	4/8	2	18	20	F	TSSOP20	LPC768 upgrade with 8K OTP; addtl 128 B of RAM not supported by emulators
P87LPC769	4 KB	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	H	SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC, 2ch 8-bit DAC
P87LPC768	4 KB	128 B	ICP	2	•	•	1	1 (bit)	4/8	2	18	20	B, F	DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC, PWM
P87LPC767	4 KB	128 B	ICP	2		•	1	1 (bit)	4/8	2	18	20	B, F	DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 25%), 4ch 8-bit ADC
P87LPC764	4 KB	128 B	ICP	2		•	1	1 (bit)		2	18	20	B, F, H	TSSOP20, DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 10% / ± 25%)
P87LPC762	2 KB	128 B	ICP	2		•	1	1 (bit)		2	18	20	B, F	TSSOP20, DIP20, SO20	2 AC, BOD, POR, 8 KBIs, IRC (6 MHz ± 10% / ± 25%)
P87LPC761	2 KB	128 B	ICP	2		•	1	1 (bit)		2	14	20	B	TSSOP16, DIP16	16-pin LPC derivative; ± 2.5% internal RC Oscillator (0-50 °C)
P87LPC760	1 KB	128 B	ICP	2		•	1	1 (bit)		2	12	20	B	TSSOP14, DIP14	14-pin LPC derivative; ± 2.5% internal RC Oscillator (0-50 °C)

80C51 family

Designed for real-time applications, these 8-bit microcontrollers are used in a wide variety of applications, from consumer products and computer peripherals to automotive systems. The NXP portfolio includes Flash, OTP (one-time programmable), ROM, and ROMless devices.

Type	Memory			Timers			Serial interfaces			I/O Pins	Max. freq. (MHz)	Temp. range options	Package	Comments / special features
	FLASH	OTP / ROM	RAM	No. of timers	PWM	WD	UART	I ² C	SPI					
66x devices														
P89V664	64 KB		2 KB	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
P89V662	32 KB		1 KB	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
P89V660	16 KB		512 B	4	•	•	1	2	1	36	40	F	PLCC44, LQFP44	Fast erase times and more I/O
66xX2 devices														
P87C660X2		16 KB	512 B	4	•	•	1	1		32	33	B, F	PLCC44, LQFP44	OTP version of 89C660; 12-clk default, 6-clk option
Mx2 devices														
P87C51MC2/02		96 KB	3 KB	4	•	•	2		1	34	24	B	PLCC44	16 MB data/code addr. range; 2 UARTs, SPI, P4 I/O
P87C51MB2/02		64 KB	2 KB	4	•	•	2		1	34	24	B	PLCC44	16 MB data/code addr. range; 2 UARTs, SPI, P4 I/O

Continued next page

80C51 family (continued)

Type	Memory			Timers			Serial interfaces			I/O Pins	Max. freq. (MHz)	Temp. range options	Package	Comments / special features
	FLASH	OTP / ROM	RAM	No. of timers	PWM	WD	UART	I ² C	SPI					
Rx2 devices														
P89CV51RD2	64 KB		1 KB	4	•	•	1		1	32	33	B, F	PLCC44, TQFP44	
P89CV51RC2	32 KB		1 KB	4	•	•	1		1	32	33	B, F	PLCC44, TQFP44	
P89CV51RB2	16 KB		1 KB	4	•	•	1		1	32	33	B, F	PLCC44, TQFP44	
P89LV51RD2	64 KB		1 KB	4	•	•	1		1	32	33	B, F	DIP40, PLCC44, TQFP44	
P89LV51RC2	32 KB		1 KB	4	•	•	1		1	32	33	F	PLCC44, TQFP44	
P89LV51RB2	16 KB		1 KB	4	•	•	1		1	32	33	B	PLCC44	
P89V51RD2	64 KB		1 KB	4	•	•	1		1	32	40	B, F	DIP40, PLCC44, TQFP44	
P89V51RC2	32 KB		1 KB	4	•	•	1		1	32	40	F	DIP40, PLCC44, TQFP44	
P89V51RB2	16 KB		1 KB	4	•	•	1		1	32	40	B, F	DIP40, PLCC44, TQFP44	
P89V52X2	8 KB		256 B	4	•		1			32	33	F	DIP40, PLCC44, LQFP44	192B EEPROM

Temperature Legend:

B	0 to +70 °C
F	-40 to +85 °C
H	-40 to +125 °C
J	-40 to +105 °C

Need devices, support, and development tools?

For a list of sales offices and distributors near you, please visit www.nxp.com/profile/sales/index.html

For general support, please visit www.nxp.com/microcontrollers

For tools, evaluation boards, and development support, please visit <http://www.standardics.nxp.com/support/tools/microcontrollers/>

www.nxp.com

founded by

PHILIPS

© 2008 NXP B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Date of release: August 2008

Document order number: 9397 750 16617

Printed in the USA