




# Scalable Mainstream 32-bit Microcontroller (MCU) based on Arm® Cortex®-M3 Core

## LPC1758FBD80

Last Updated: Jul 31, 2023

The LPC1758 is a Cortex-M3 microcontroller for embedded applications featuring a high level of integration and low power consumption at frequencies of 100 MHz. Features include 512 kB of flash memory, 64 kB of data memory, USB Device/Host/OTG, Ethernet, 8-channel DMA controller, 4 UARTs, 2 CAN channels, 2 SSP, 1 SPI, 2 I2C, I2S, 8-channel 12-bit ADC, DAC, motor control PWM, Quadrature Encoder interface, 4 general purpose timers, 6-output general purpose PWM, ultra-low power Real-Time Clock with separate battery supply, and up to 52 general purpose I/O pins.

# Block diagram: LPC1751FBD80, LPC1752FBD80, LPC1754FBD80, LPC1756FBD80, LPC1758FBD80 Block Diagram



**Note:** The information on this document is subject to change without notice.

---

**[www.nxp.com](http://www.nxp.com)**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.