



# TEA2376xT, Digital Configurable Interleaved PFC Controllers

## TEA2376

Last Updated: Jan 10, 2024


The TEA2376 is a digital configurable two-phase interleaved PFC controller for high-efficiency power supplies. The PFC operates in discontinuous conduction mode or quasi-resonant mode with valley switching to optimize efficiency.

The TEA2376 is suitable for TV, computing, server and industrial power supplies. For low-load operation with good efficiency, phase shedding and burst mode operation are included.


The TEA2376 supports a high power factor and a low THD and contains many protections which can be configured independently by a GUI.

The TEA2376 allows an easy to design, highly efficient, reliable interleaved PFC with a low external component count for power levels up to typically 1000 W.

## TEA2376DT Block Diagram Block Diagram



## TEA2376AT and TEA2376BT Block Diagram Block Diagram



View additional information for [TEA2376xT, Digital Configurable Interleaved PFC Controllers](#).

**Note:** The information on this document is subject to change without notice.

---

**[www.nxp.com](http://www.nxp.com)**

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.