



MC33197A

Advance Information

Automotive Wash Wiper Timer

The MC33197A is a standard wiper timer control device designed for harsh automotive applications. The device can perform the intermittent, after wash, and continuous wiper timer functions. It is designed to directly drive a wiper motor relay. The MC33197A requires very few external components for full system implementation. The intermittent control pin can be switched to ground or Vbat to meet a large variety of possible applications. The intermittent timing can be fixed or adjustable via an external resistor. The MC33197A is built using bipolar technology and parametrically specified over the automotive ambient temperature range and 8.0 to 16 V supply voltage. The MC33197A can operate in both front and rear wiper applications.

- Adjustable Time Interval of Less Than 500 ms to More Than 30 s
- Intermittent Control Pin Can Be Switched to Ground or Vbat
- Adjustable After Wipe Time
- Priority to Continuous Wipe
- Minimum Number of Timing Components
- Integrated Relay Driver With Free Wheeling Protection Diode
- Operating Voltage Range From 8.0 to 16 V
- For Front Wiper and Rear Wiper Window Applications

ORDERING INFORMATION

Device	Operating Temperature Range	Package
MC33197AD	$T_A = -40^{\circ} \text{ to } +105^{\circ}\text{C}$	SO-8
MC33197AP	$T_A = -40^{\circ} \text{ to } +125^{\circ}\text{C}$	DIP-8

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Continuous Supply Voltage (VPin 6)	Vcc	16	V
Storage Temperature	T _{stg}	-55 to +150	°C
Thermal Resistance (Junction-to-Ambient) DIP-8 Package SO-8 Package	R _θ JA	100 145	°C/W
Operating Ambient Temperature Range DIP–8 Package SO–8 Package	ТД	-40 to +125 -40 to +105	°C
Operating Junction Temperature Range	TJ	-40 to +150	°C
Maximum Junction Temperature	T _{J(max)}	150	°C

NOTE: ESD data available upon request.

AUTOMOTIVE WASH WIPER TIMER

SEMICONDUCTOR TECHNICAL DATA




P SUFFIX PLASTIC PACKAGE **CASE 626**



D SUFFIX PLASTIC PACKAGE **CASE 751** (SO-8)


PIN CONNECTIONS



Osc1 1 7 INT CONT 2 W/W 3 6 Out VCC 5 Gnd (Top View)



Representative Block Diagram



This device contains 390 active transistors.

 $\textbf{ELECTRICAL CHARACTERISTICS} \ (-40^{\circ}C \leq T_{\mbox{A}} \leq +125^{\circ}C, \ 8.0 \ \mbox{V} \leq \mbox{V}_{\mbox{CC}} \leq 16 \ \mbox{V}, \ \mbox{unless otherwise noted}. \ \mbox{Typical values reflect}$ approximate mean at $T_A = 25^{\circ}$ C with $V_{CC} = 14$ V at the time of initial device characterization.)

Characteristic	Symbol	Min	Тур	Max	Unit
Functional Supply Voltage Range	VCCF	8.0	-	18	V
Operating Supply Voltage Range	VCCOP	8.0	-	16	V
Standby Supply Current (V _{CC} = 16 V, R2 = 68 k)	Icc	-	4.0	5.2	mA
Supply Current INT Active (R3 = 2.5 k)	Icc	-	7.0	8.4	mA
Supply Current Relay "On" (R2 = 68 k)	Icc	-	7.5	11.2	mA
Supply Current INT and Relay "On" (R2 = 68 k, R3 = 2.5 k)	Icc	-	10	14.5	mA
Oscillator Variations with Supply Voltage and Temperature (excluding external component tolerances, C2 = 100 nF polyester capacitor) (Notes 1 & 2)	K _{osc}				%
$10 \text{ V} \le \text{V}_{bb} \le 16 \text{ V}$ $8.0 \text{ V} \le \text{V}_{bb} \le 16 \text{ V}$		- -	10 15	- -	
Relay Resistance	RL	60	_	_	Ω
Output Voltage (I _{OUt} = 200 mA)	V _{out}	-	0.9	1.5	V
Output Clamp Voltage (I _{OUt} = 20 mA)	V _{Cl}	19.5	_	22	V
Oscillator Period Coefficient ($T_A = 25^{\circ}C$) $V_{bb} = 13 \text{ V (Note 3)}$ $V_{bb} = 13 \text{ V (INT Connected to Gnd) (Note 4)}$ $V_{bb} = 13 \text{ V (INT Connected to V}_{bat}, R1 = 220 \Omega) (Note 4)$	^t b1 ^t b2g ^t b2v	0.98 15.1 11.5	1.0 15.5 12.1	1.03 15.9 12.7	-
CONT Threshold (V _{CC} = 13 V)	Vih	6.0	_	8.5	٧
CONT Threshold (V _{CC} = 16 V)	V _{ih}	-	V _{CC} /2	-	V

NOTES: 1. The oscillator frequency is defined by the current flowing through the external resistor R2. The voltage at the INT pin is $(V_{CC}/2 - V_{be})$ and hence the current flowing through R3 is different if R3 is connected to V_{bb} or to Gnd because of the voltage drop across resistor R1. This voltage drop causes the oscillator coefficient for tb2 to be different for the two cases of INT terminated to Gnd or to V_{bb}. Because of this, the oscillator coefficient is speci– fied with a specific value of R1 whenever INT is connected to Vbb. If R1 is changed, the coefficient will change. Also, any extra current through the resistor R1 other than the current used by the device will cause timing deviations in th2 timings (as in the case where two devices are sharing a


^{2.} The oscillator stability with temperature is dependent on the temperature coefficients of the external components. If the capacitance value of the external capacitor varies more than 5% over the parametric temperature range, the figures quoted for oscillator variation are not valid.

^{3.} The t_{b1} duration is given by coefficient 4 x R2 x C2 (t_{b1} duration = t_{b1} x 4 x R2 x C2). 4. The t_{b2} duration is given by coefficient x R3 x C2 (t_{b2} duration = t_{b2} x R3 x C2).

NXP

Freescale Semieonductor, Inc.

Figure 1. Intermittent Wash Wiper Typical Application



This application shows the MC33197A with the external wirings and two speed wiper motor. This application has the Intermittent and Wash Wiper functions.

INTRODUCTION

The MC33197A is a wiper timer control device designed for use in harsh automotive applications. The device can perform the intermittent, after wash, and continuous wiper timer functions.

The MC33197A is designed to directly drive a wiper motor relay. The MC33197A is suitable for both front and rear wiper applications. The MC33197A connects directly to the vehicle's battery voltage (V_{bat}) through a 220 Ω resistor used with a 47 μ F de–coupling filter capacitor. The device has an internal oscillator controlled by one of two external resistors (R2 and R3) in addition to one external capacitor (C2), dependent on the application function required. The values of C2 and R2 determine the t_{b1} time base. T_{b1} is used to generate the relay wiper activation during the INT function (T3) and the after wash timing (T2) during the wash wipe mode. The values C2 and R3 determine the t_{b2} time base. The t_{b2} time base is used to generate the pause or intermittent time (T4).

The intermittent wiper function can generate intermittent timing (T4) from less than 500 ms to more than 30 seconds. The intermittent function of the device can be activated by the INT input connected to either ground or V_{bat}. The intermittent timing is externally adjustable by changing the value of resistor R3.

The wash wiper timer function detects the water pump motor's operation. When the pump motor activation is detected, the MC33197A turns the wiper on for the entire duration of the pump motor's activation. When the motor is turned off, it generates an after wash timing (T2) to maintain the wiping action. The W/W pin is connected to the water pump motor through a protection resistor (R4).

The MC33197A also has a continuous function, which activates the wiper relay whenever the CONT input is activated. The CONT input is connected to a switch through a protection resistor (R5). The CONT input comparator has an input threshold of $V_{bb}/2$ with hysteresis.

The device has internal debounce circuitry, based on the oscillator period. This provides filtering of the intermittent (INT) and wash wipe (W/W) input signals (see T1 Debounce Timing paragraph that follows). The device directly drives the wiper motor relay. It internally incorporates a 20 V free wheeling zener diode to protect the device against overvoltage spikes produced when relay is switched off.

Intermittent Operation


Conditions:

- W/W not connected or connected to ground.
- CONT not connected or connected to ground.
- INT connected to V_{bb} or to ground.



In this configuration, the circuit will respond to the switching of INT to either V_{bb} or ground after a time T1 (see T1 Debounce Timing). If INT is disconnected before the end of T1; no action will be taken. After a time T1, the output will be switched on for a duration, T3 = 16 x 4 x t_{b1} and then switched off for a duration, T4 = 144 x 4 x t_{b2} . This sequence will continue to repeat so long as INT is disconnected from V_{bb} or ground for a time duration greater than T1. If INT is disconnected during the time T3; the output will remain on for the remainder of T3. This is illustrated in the diagram on Figure 2.

Figure 2. Switching Waveform INT Timing




Wash Wipe Operation

Conditions:

- INT disconnected.
- CONT disconnected or connected to ground.

In this condition, the circuit will respond to the switching of W/W to V_{bb} after a time T1 (see T1 Debounce Timing). If W/W is disconnected or connected to ground before the end of T1; no action will be taken. After a time T1; the circuit will perform as shown on Figure 3. The output will turn on and remain on for the duration of W/W. When W/W becomes inactive, the output will remain on for T2 = 96 x 4 x t_{b1}.

Figure 3. Switching Waveform W/W Timing




Continuous Operation

In this condition, the circuit responds to the switching of CONT to V_{bb} . If CONT is connected to V_{bb} , the output will turn on regardless of the state of any other input and remain on so long as CONT is active. This command operates directly on the relay output and does not interfere with any other timing. Therefore, the circuit will not be reset to a defined state.

Wash Wiper and Intermittent Operation

If W/W is activated during the time INT is also activated, the circuit will respond to W/W after a time T1 (see T1 Debounce Timing). The output will turn on after T1, and stay on for a time T2 + T3 after W/W is deactivated. Following this, normal operation of INT will occur. This is shown on Figure 4.

Figure 4. Switching Waveform W/W and INT Active



T1 Debounce Timing

The criteria for an input signal to be detected is that it should be active at two successive negative internal clock edges. The inputs are sampled on the negative edge of the internal clock. If two consecutive samples are the same, the input is detected as being in that state. Hence the time T1 from a signal becoming active to the time that the circuit responds can be anytime from $4 \times t_{b1}$ to $2 \times 4 \times t_{b1}$ (due to synchronizing the input to the oscillator period) when the oscillator is oscillating with a time base of t_{b1} and $4 \times t_{b2}$ to $2 \times 4 \times t_{b2}$, when the oscillator is oscillating with a time base of t_{b2} .

The following table summarizes all T1 debounce timings:

Condition	Debounce Time	
INT Active	4 x t _{b1} to 2 x 4 x t _{b1}	
INT Inactive	4 x t _{b1} to 2 x 4 x t _{b1}	
W/W Active When INT Inactive	4 x t _{b1} to 2 x 4 x t _{b1}	
W/W Active When INT Active During T3	4 x t _{b1} to 2 x 4 x t _{b1}	
W/W Active When INT Active During T4	4 x t _{b2} to 2 x 4 x t _{b2}	

Two MC33197A Devices Using One Decoupling Resistor and Capacitor

Two devices may be connected to the power source using a common R1 resistor for protection against overvoltages. If this is done it should be noted that the current flowing through R1 is increased and hence the voltage drop across R1 is increased.



Overvoltage Protection

In reference to the Block Diagram and Typical Application, all of the foregoing operational cases require:

R1 \geq 100 Ω , C1 \geq 47 μ F

 $R3 \ge 1.0 \text{ k}\Omega, R4 \ge 4.7 \text{ k}\Omega, R5 \ge 4.7 \text{ k}\Omega$

The circuit will not operate during the transient conditions. By using the above component values, the circuit will be able to sustain the following overvoltages on V_{bb} without permanent damage:

- 1. +28 V for 5 minutes
- 2. -15 V for 5 minutes
- 3. -16 V cycled off for 1.0 minute
- 4. +80 V pulse decaying exponentially to 8.0 V in 400 ms repeated 3 times at 1.0 minute intervals.
- 5. \pm 300 V pulse decaying exponentially to 30 V in 300 ms with a maximum energy of 1.0 Joule.
 - 6. ±100 V pulse decaying exponentially to 10 V in 2 ms.

Recommended External Component Values

Below are the recommended component values to ensure the device will operate properly, and that all specified parameters will stay within their tolerances.

R1 should be greater than 100 Ω ; recommended value of 220 Ω . R1 can be up to 500 Ω , but in this case the t_{b2V} parameter could be out of it's specified value (see Electrical Characteristics and Note 1). Also, the minimum operating voltage range should be greater than 8.0 V. The following values should be adhered to:

 $\begin{array}{l} 10 \text{ k}\Omega \leq R2 \leq 68 \text{ k}\Omega \\ 1.5 \text{ k}\Omega \leq R3 \leq 47 \text{ k}\Omega \\ R4 \geq 4.7 \text{ k}\Omega \\ R5 \geq 4.7 \text{ k}\Omega \\ C1 \geq 47 \text{ uF} \\ 47 \text{ nF} \leq C2 \leq 470 \text{ nF} \end{array}$

Application Information

The following is an example of timing calculations using the following external components values:

 $R2 = 22 \text{ k}\Omega$, $R3 = 2.2 \text{ k}\Omega$, C2 = 100 nF (Referring to Block Diagram and Typical Application).

Oscillator Time Base Calculation:

 t_{b1} duration = $t_{b1} \times 4 \times R2 \times C2 = 1 \times 4 \times 27e3 \times 100e-9 = 10.8 ms$

 t_{b2} duration_g (INT to Gnd) = t_{b2g} x R3 x C2 = 15.5 x 2.2e3 x 100e-9 = 3.41 ms

 t_{b2} duration_v (INT to V_{bb}) = t_{b2v} x R3 x C2 = 12.1 x 2.2e3 x 100e-9 = 2.66 ms

Intermittent timing calculation:

T3 = 16 x 4 x t_{b1} duration = 16 x 4 x 10.8 ms = 691 ms T4 = 144 x 4 x t_{b2} duration_g = 144 x 4 x 3.41 ms = 1.96 s (INT connected to Gnd)

 $T4 = 144 \times 4 \times t_{b2} \text{ duration} \text{_v} = 144 \times 4 \times 2.66 \text{ ms} = 1.53 \text{ s}$ (INT connected to V_{bb})

Wash wipe timing calculation:

 $T2 = 96 \times 4 \times t_{b1} = 96 \times 4 \times 10.8 \text{ ms} = 4.15 \text{ s}$

T1 Debounce Time Calculation (see T1 Debounce Timing)

When oscillator is oscillating at tb1:

T1 minimum = $4 \times t_{b1} = 4 \times 10.8 \text{ ms} = 43.2 \text{ ms}$

T1 maximum = $2 \times 4 \times t_{b1} = 2 \times 4 \times 10.8 \text{ ms} = 86.4 \text{ ms}$

When oscillator is oscillating at th2:


T1 minimum (INT connected to Gnd, t_{b2g}) = 4 x t_{b2} = 4 x 3.41 ms = 13.6 ms

T1 maximum (INT connected to Gnd, t_{b2g}) = 2 x 4 x t_{b2} = 2 x 4 x 3.41 ms = 27.3 ms



OUTLINE DIMENSIONS





- NOTES:
 1. DIMENSION L TO CENTER OF LEAD WHEN
- FORMED PARALLEL.

 2. PACKAGE CONTOUR OPTIONAL (ROUND OR SQUARE CORNERS).

 3. DIMENSIONING AND TOLERANCING PER ANSI


	MILLIN	METERS	INC	HES
DIM	MIN	MAX	MIN	MAX
Α	9.40	10.16	0.370	0.400
В	6.10	6.60	0.240	0.260
С	3.94	4.45	0.155	0.175
D	0.38	0.51	0.015	0.020
F	1.02	1.78	0.040	0.070
G	2.54 BSC		0.100 BSC	
Н	0.76	1.27	0.030	0.050
J	0.20	0.30	0.008	0.012
K	2.92	3.43	0.115	0.135
L	7.62 BSC		0.300	BSC
M		10°		10°
N	0.76	1.01	0.030	0.040

TYLE 1:
PIN 1. AC IN
2. DC + IN
3. DC - IN
4. AC IN
5. GROUND
6. OUTPUT
7. AUXILIARY

8. V_{CC}



PLASTIC PACKAGE CASE 751-05 (SO-8) ISSUE N



NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: MILLIMETER.
 3. DIMENSIONS A AND B DO NOT INCLUDE
- MOLD PROTRUSION.

 4. MAXIMUM MOLD PROTRUSION 0.15 (0.006)
- 4. MAXIMUM MOLL PROTRUSION 0.15 (0.006) PER SIDE.
 5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.

	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
Α	4.80	5.00	0.189	0.196
В	3.80	4.00	0.150	0.157
С	1.35	1.75	0.054	0.068
D	0.35	0.49	0.014	0.019
F	0.40	1.25	0.016	0.049
G	1.27 BSC		0.050 BSC	
J	0.18	0.25	0.007	0.009
K	0.10	0.25	0.004	0.009
М	0 °	7 °	0 °	7°
Р	5.80	6.20	0.229	0.244
R	0.25	0.50	0.010	0.019



Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Motorola data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and any are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.



How to reach us:

USA/EUROPE/Locations Not Listed: Motorola Literature Distribution; P.O. Box 20912; Phoenix, Arizona 85036. 1–800–441–2447 or 602–303–5454

ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; 8B Tai Ping Industrial Park, I51 Ting Kok Road, Tai Po, N.T., Hong Kong. 852–26629298

JAPAN: Nippon Motorola Ltd.; Tatsumi–SPD–JLDC, 6F Seibu–Butsuryu–Center, 3–14–2 Tatsumi Koto–Ku, Tokyo 135, Japan. 03–81–3521–8315

