

Freescale Semiconductor

Application Note

AN2908/D Rev. 0, 02/2005

Using the M9328MXLADS for i.MXS Development MC9328MXS

by: David Babin

1 Abstract

The MC9328MXS (i.MXS) is backward-compatible to the MC9328MXL (i.MXL). Therefore, the i.MXL ADS (Application Development System) can be used for i.MXS hardware and software development.

This paper is a guideline for how to properly use the i.MXL ADS for i.MXS development purposes.

2 Introduction

To reduce cost, certain i.MXL circuit blocks are not available on the i.MXS. These include the following.

- Camera Interface or CMOS Sensor Interface (CSI)
- Memory Stick[®] Host Controller (MSHC)
- Multimedia Card Controller (MMC)
- Multimedia Accelerator (MMA)

Both devices use an ARM920T core. However, the i.MXS is limited to a maximum core speed of 100 MHz.

Contents

1	Abstract	1
2	Introduction	1
3	Comparison of the Two Processors	2
4	Programming the CPU Speed	3
5	Kit Contents	3





© Freescale Semiconductor, Inc., 2005. All rights reserved.



Comparison of the Two Processors

The ADS includes an i.MXL device in a 256-contact MAP BGA. Due to the reduced feature set, the production package for the i.MXS is a 225 MAP BGA.

3 Comparison of the Two Processors

Table 1 lists the features of the two processors. The differences are highlighted. When using the ADS documentation, simply ignore references to those modules which are not contained in the i.MXS device.

Attribute	i.MXL	i.MXS		
CPU Speed	150/200 MHz	100 MHz		
System Speed	96 MHz	96 MHz		
I Cache / D Cache	16 KB / 16 KB	16 KB / 16 KB		
Package	225 and 256 MAP BGA	225 MAP BGA only		
DMA	11 Channels	11 Channels		
UART	2	2		
General-Purpose Timer	2	2		
Watchdog Timer	1	1		
RTC	1	1		
PWM	1	1		
SSI / 12S	1	1		
I2C	1	1		
CSI	1	0		
USB Device	Client	Client		
MMC/SDHC	1	0		
MSHC	1	0		
PCMCIA	External logic required	External logic required		
SPI	2 (1 configurable)	1 (configurable)		
IrDA (Infrared)	v1.0 via UART	v1.0 via UART		
LCD Controller	STN, CSTN, TFT	STN, CSTN, TFT		
Bluetooth Support	via UART	via UART		
MMA	1	0		
SDRAM Support	Yes	Yes		
NOR Flash Support	Yes	Yes		
Flash boot	Yes	Yes		
JTAG	Yes	Yes		

Table 1. Comparison of the Processors

Using the M9328MXLADS for i.MXS Development Application Note, Rev. 0



4 Programming the CPU Speed

Per the *i.MXS Reference Manual*, the recommended setting for the MCU PLL, which produces the least amount of jitter, is shown in Table 2. PD, MFD, MFI, and MFN are bits in MCU PLL Control Register 0. A 32 kHz crystal is installed on the ADS board.

Table 2.	Sample	Frequency	Table

Premultiplier Input (Crystal Frequency)	PLL Input Frequency (Premultiplier Output)	PD	MFD	MFI	MFN	PLL Output Frequency
32 kHz	16.384 MHz	0	63	5	55	192 MHz

The i.MXS processor can run at 100 MHz maximum. Therefore, the PRESC bit in the Clock Source Control Register must be set to 1. This programs the ARM920T core's FCLK signal to 96 MHz. Note that if the PRESC bit is 0, FCLK is 192 MHz which exceeds the guaranteed frequency of the i.MXS processor. (Refer to the Clock Controller Module block diagram in the Phase-Locked Loop and Clock Controller chapter of the *i.MXS Reference Manual*.)

5 Kit Contents

The M9328MXLADS/B kit includes a populated circuit board, cables, power supply, styluses, earphones, and software. An LCD board is included that attaches to the main board with a ribbon cable.

A CMOS sensor camera is included but is not applicable to i.MXS evaluation because the CMOS Sensor Interface is not available on the i.MXS processor.

1 References

The following documents provide a complete description of the i.MXS processor and are necessary to design properly with the device. The following documents are helpful when used in conjunction with this application note.

MC9328MXS Data Sheet (order number MC9328MXS/D) MC9328MXS Reference Manual (order number MC9328MXSRM/D) M9328MX1_L_ADS_V2_0 ADS Schematics and Orcad File

Bill of Materials B11021_I, Bill of material for the MC9328MXL

M9328MXLADS Application Development System

The Freescale documents are available on the Freescale Semiconductor Web site at http://www.freescale.com/imx. These documents may be downloaded directly from the Freescale Web site, or printed versions may be ordered.



How to Reach Us:

Home Page: www.freescale.com

E-mail: support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064, Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405 Denver, Colorado 80217 1-800-521-6274 or 303-675-2140 Fax: 303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com

AN2908/D Rev. 0 02/2005 Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale[™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. ARM and the ARM Powered Logo are registered trademarks of ARM Limited. ARM920T is a trademark of ARM Limited. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2005. All rights reserved.

