

Freescale Semiconductor Reference Design Data Sheet

MCF51EM256220RDDS Rev. 0, 10/2009

MCF51EM256-based Poly Phase Energy Meter Reference Design 220V Technical Specifications

Electrical

Connection type Direct connected (Whole current)
Wiring configuration 3 phase 4 wire & 1 phase 2 wire

Voltage rating 230V +/-10% (L-N)

Current range 10-60 A
Accuracy Class 0.5
Frequency range 47Hz to 53Hz

Pulse constant 800 impulses/kWh & 800 impulses/kVArh

Standard compliance IEC 62053-11, IEC 62053-22, IEC 62053-23 & IEC62056-21

Mechanical

Dimensions (WxHxD) 168 x 242 x 84 mm

Weight 1.675 kg

Enclosure Plastic (PC/ABS blends)
Sealing Sealing screws provision

© Freescale Semiconductor, Inc., 2009. All rights reserved.





Environmental

Compliance IEC 60529

Ingress protection IP 51 (Indoor type meter)

Operating Temperature -25°C to +55°C Storage Temperature -25°C to +70°C

Humidity 95%

Features

Measurement parameters Voltage, Current, Frequency kWh, kVArh, kW, kVAr, Power factor

Tamper Recording Missing potential and current, current and voltage unbalance, cover

open tamper detection. LED indication for tamper

Load profile Load profile interval period: 5, 10, 15, 30, 60 minutes and 1 day.

Maximum demand Programmable MD interval period of 30 minutes and 60 minutes

MD can be reset by using Reset key

Display Custom built metering specific LCD with backlight. Eight digits 7

segment display for parameters with symbol identifiers.

Auto scroll

Manual scroll using UP and DOWN keys

Communication Optical port as per standard IEC 62056-22

RS 232 port and BDM port for programming

Data security Data storage in non-volatile memory; two levels of password for

programming configuration and for auto calibration

Output device LED pulses proportional to kWh, kVArh

LED for Power on indication



How to Reach Us:

Home Page:

www.freescale.com

Web Support:

http://www.freescale.com/support

USA/Europe or Locations Not Listed:

Freescale Semiconductor, Inc.
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
+1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd.
Headquarters
ARCO Tower 15F
1-8-1, Shimo-Meguro, Meguro-ku,
Tokyo 153-0064
Japan
0120 191014 or +81 3 5437 9125
support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor China Ltd.
Exchange Building 23F
No. 118 Jianguo Road
Chaoyang District
Beijing 100022
China
+86 10 5879 8000
support.asia@freescale.com

For Literature Requests Only: Freescale Semiconductor Literature Distribution Center 1-800-441-2447 or 303-675-2140 Fax: 303-675-2150

LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics as their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

 $\label{eq:Freescale} \textbf{Freescale} \ \textbf{Improve} \ \textbf{and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.}$

© Freescale Semiconductor, Inc. 2009. All rights reserved.

MCF51EM256220RDDS Rev. 0 10/2009