

Document Number:AN4851 Rev. 0, Dec 2013

Using the High Resolution Timer and PWM in the S12ZVC

by: Luis Olea

1 Introduction

The <u>S12ZVC family</u> is a member of the S12 MagniV product line integrating a battery level (12 V) voltage regulator, supply voltage monitoring, high voltage inputs and a Controller Area Network (CAN) physical interface. These and other features make this device ideal for CAN node applications such as sensors, switch panels, or small actuators.

This document intends to explain the functions and advantages of the special high resolution timers and PWM available in the MC9S12VC devices and their role in advanced timing applications.

2 High resolution timer

The TIM16B8CV3 module consists of a 16-bit software programmable counter driven by a flexible programmable prescaler.

This timer can be used for many purposes, including input waveform measurements while simultaneously generating an output waveform. Pulse widths can vary from microseconds to many seconds.

Contents

1	Introduction	1
2	High resolution timer	1
3	High resolution PWM	2
4	Use case examples	3
5	Attachments	3





rugu resolution PWM

2.1 Features

The following features are found in the TIM16B8CV3 module:

- 16-bit counter
- Up to 8 input capture/output compare channels
- 16-bit pulse accumulator available on channel 7
- Selectable trigger transition edge for captures
- Clock prescaling

2.2 Initialization

To use the timer module the application can follow the steps shown below:

- Configure the prescaler (TSCR2[PR]).
- Configure needed channels as Input Capture (TIOS[IOSx]=0) or Output Compare (TIOS[IOSx]=1).
- Enable interrupts if needed in the timer interrupt enable register (TIE).
- Set the timer enable bit (TSCR1[TEN]).

3 High resolution PWM

The S12PWM8B8CV2 module is a channel scalable PWM with the flexibility to select one of four clock sources per channel.

3.1 Features

The S12PWM8B8CV2 module has the following distinctive features:

- Up to eight 8-bit or four 16-bit independent PWM channels
- Programmable period and duty cycle for each channel
- Dedicated counter for each channel
- Programmable PWM enable/disable for each channel
- Selectable pulse polarity for each channel
- Double buffered period and duty cycle registers
- Left or center aligned output configurable independently on each channel
- Four clock sources

3.2 Initialization

To configure PWM the application can follow the steps shown below:

- 1. Select 8 bit (CONxx=0) or 16 bit (CONxx=1) operation.
- 2. Select the clock source (PWMCLK register).
- 3. Configure prescaler (PWMPRCLK register).
- 4. Configure duty (PWMDTYx) and period (PWMPERx).
- 5. Select the PWM polarity (PWMPOL).
- 6. Select left aligned (CAEx=0) or center aligned (CAEx=1) output.
- 7. Enable the needed channels (PWMEx=1).
- 8. Change the duty cycle and period of a given channel at any time by writing to the desired channel period and duty registers (Period and duty cycle registers are double buffered. Change takes place when the end of the effective period is reached or when the channel is disabled).

Using the High Resolution Timer and PWM in the S12ZVC, Rev. 0, Dec 2013





4 Use case examples

The following use cases illustrate how to take advantage of the advanced features of the S12ZVC in two example automotive applications.

4.1 Ultrasonic level sensor

In this application the signal runtime of ultrasonic response has to be measured. Sensor output can be connected to any ADC channel. The analog comparator is then used to compare the sensor output voltage with a reference voltage provided by the DAC module. The output of the analog comparator is finally connected to the high resolution timer to measure the signal runtime.

4.2 Waveform measurement and generation

The 16-bit counter of the timer module together with the 7 input capture or output compare channels can be configured to measure a waveform while simultaneously generating an output waveform.

Configuring a channel to function as input capture will help measure an input waveform by capturing the 16-bit value of the timer when an input event occurs. Input capture channels can be configured to detect rising edges, falling edges, or any edge. Furthermore channel 7 of the timer module has a 16-bit pulse accumulator that can count how many of these events have occurred. Software can read the capture registers and calculate input waveform features such as low time, high time, period, etc.

Using the timer channels as output compare can help generate an output waveform by changing the state of a pin when the timer counter reaches the value programmed in the output compare register of any given channel. Channels can be configured to just trigger an interrupt on a successful output compare, toggle the output line, clear the output line to zero, or set the output line to one thus helping generate an output waveform without CPU intervention.

5 Attachments

For your reference please download companion software AN4851SW.zip from freescale.com to find the code and CodeWarrior project for configuring the timer and PWM modules in the S12ZVC device.



How to Reach Us:

Home Page: www.freescale.com

Web Support: http://www.freescale.com/support

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, EL516 2100 East Elliot Road Tempe, Arizona 85284 +1-800-521-6274 or +1-480-768-2130 www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor China Ltd. Exchange Building 23F No. 118 Jianguo Road Chaoyang District Beijing 100022 China +86 10 5879 8000 support.asia@freescale.com Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductors products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claims alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics as their non-RoHS-complaint and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

 $\label{eq:FreescaleTM} Freescale TM and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.$

© 2013 Freescale Semiconductor, Inc.



Document Number: AN4851 Rev. 0, Dec 2013