


MC9S12D64

Target Applications

- > Automotive applications
- > Industrial control

Overview

Freescale Semiconductor's HCS12 Family of microcontrollers (MCUs) is the next generation of the highly successful 68HC12 architecture. Using Freescale's industry-leading 0.25 µs Flash, the MC9S12D64 is part of a pin-compatible family that scales from 32 KB to 512 KB of Flash memory. The MC9S12D64 provides an upward migration path from Freescale's 68HC08, 68HC11 and 68HC12 architectures for applications that need larger memory, more peripherals and higher performance. Also, with the increasing number of CAN-based electronic control units (ECUs), its multiple network modules support this environment by enabling highly efficient communications between different network buses.



Features	Benefits
High-Performance 16-bit HCS12 CPU Core	
> 25 MHz bus operation at 5V for 40 ns	> Object code compatible 68HC12
minimum instruction cycle time	> Assembly source code compatible with the 68HC11
	> C-optimized architecture produces extremely compact code
On-Chip Debug Interface	
> Dedicated serial debug interface > On-chip breakpoints	 Real-time in-circuit emulation and debug without expensive and cumbersome box emulators
	> Read/write memory and registers while runn at full speed
Network Modules	
> One msCAN module implementing the CAN	> Programmable bit rate up to 1 Mbps
2.0 A/B protocol • Five receive buffers per module with FIFO storage scheme	> FIFO receive approach superior for event-driven networks
Three transmit buffers per module with internal prioritization	
Integrated Third-Generation Flash Memory	
> In-application reprogrammable	> Flexibility to change code in the field
> Self-timed, fast programming	> Efficient end-of-line programming
 Fast Flash page erase—20 ms (512 bytes) 	> Total program time for 256 KB code is less than 10 seconds
 Can program 16 bits in 20 μs while in burst mode 	> Reduces production programming cost through ultra-fast programming
> 5V Flash program/erase/read	> No external high voltage or charge
> Flash granularity—512 byte Flash erase/2 byte Flash program	pump required > Virtual EEPROM implementation, Flash arr usable for EE extension
> Flexible block protection and security	
1 KB Integrated EEPROM	
> Flexible protection scheme for protection against accidental program or erase	> Can erase 4 bytes at a time and program 2 bytes at a time for calibration, security,
> EEPROM can be programmed in 46 µs	personality and diagnostic information





Features	Benefits		
10-bit Analog-to-Digital Converter (ADC)			
 > Two 8-channel ADCs > 7 μs, 10-bit single conversion time, scan mode available 	> Fast, easy conversion from analog inputs like position sensors, analog meters and photovoltaic cells to digital values for CPU processing		
	> Can effectively have 3.5 μs conversion time by sampling same signal with both ADCs		
Clock Generation Module with Phase-Lock Loop (PLL)			
Clock monitor with self clock mode in case of no external clock	> Reliable, robust operation		
> Programmable clock frequency with 1024 options ranging from divide by 16 to multiply	> Provides high performance using low-cost reference crystals		
by 64 from base oscillator	> Reduces generated noise		
> Real-time interrupt	> Reduces power consumption		
> Watchdog	> Easily able to implement real-time clock		
Enhanced Capture Timer			
> 8-channel, 16-bit with input capture, output compare and pulse accumulator	> Flexible, programmable timer system		
> 16-bit modulus down counter			
8-bit or 16-bit Pulse-Wide Modulation (PWM)			
8-channel, 8-bit or 4-channel, 16-bit PWMPWM supports center aligned operation	> Efficiently implement motor control, battery charging or digital-to-analog (DAC) functions		
Two Serial Communications Interfaces			
> 8192 prescaler options	> Asynchronous communication between the		
> 0192 prescaler options	MCU and a terminal, computer or a network of MCUs		
	> Exact baud rate matching		
One Serial Peripheral Interface			
> Up to 12.5 Mbps	 High-speed synchronous communication between multiple MCUs or between MCU and serial peripherals 		
Inter IC (I ² C) Bus			
> 256 clock rate options	> Provides a simple, efficient method of data exchange between devices		
	> Minimizes the need for large numbers of connections between devices and eliminates the need for an address decoder		
Up to 91 Input/Output (I/O) Lines			
> Programmable pull-ups/pull-downs	> Reduce system cost		
> Dual drive capability	> Able to tailor application for minimum EMC or high current loads		

Data Sheets	
9S12DJ64DGV1	MC9S12A64 Device Guide
S12BDMV4	HCS12 Background Debug (BDM) Block Guide
S12BKVD1	HCS12 Breakpoint (BKP) Block Guide
S12CPUV2	HCS12 CPU Reference Manual
S12MSCANV2	HCS12 Motorola Scalable Controller Area Network Block Guide
S12ATD10B8CV2	HCS12 10-bit 8-channel Analog to Digital Block Guide
S12CRGV3	HCS12 Clock Reset Generator Block Guide
S12ECT16B8CV1	HCS12 16-bit 8-channel Enhanced Capture Timer Block Guide
S12EETS4KV2	HCS12 4K EEPROM Block Guide
S12FTS256KV2	HCS12 256K Flash Block Guide
S12IICV2	HCS12 I ² C Block Guide
S12INTV1	HCS12 Interrupt (INT) Block Guide
S12MEBIV3	HCS12 Multiplexed External Bus Interface (MEBI) Block Guide
S12MMCV4	HCS12 Module Mapping Control (MMC) Block Guide
S12PWM8B8CV1	HCS12 8-bit 8-channel Pulse-Width Modulator Block Guide
S12SCIV2	HCS12 Serial Communications Interface Block Guide
S12SPIV2	HCS12 Serial Peripheral Interface Block Guide
S12VREGV1	HCS12 Voltage Regulator Block Guide

Cost-Effective Development Tools

For more information on development tools, please refer to the Freescale Development Tool Selector Guide (SG1011).

M68KIT912DP256

\$495*

Evaluation kit for development and evaluation of HCS12 application

code that includes the M68EVB912DP256 and USBMULTILINKBDM

M68CYCLONEPRO \$499*

HC08/HCS08/HC12/HCS12 stand-alone Flash programmer or in-circuit emulator, debugger, Flash programmer; USB, serial or Ethernet

interface options

\$99*

USBMULTILINKBDM Universal HCS08/HCS12 in-circuit emulator, debugger, and Flash programmer; USB PC interface

CWX-H12-SE

Free*

CodeWarrior™ Special Edition for HCS12 MCUs; includes integrated development environment (IDE), linker, debugger, unlimited assembler, Processor Expert™ auto-code generator, full-chip simulation and limited C compiler

Temp. Range

-40°C to +85°C

-40°C to +105°C

-40°C to +125°C

Application Notes and Engineering Bulletins


Approacion reces and Engineering Lancounc		
AN1284	Transporting M68HC11 Code to M68HC12 Devices	
AN1716	Using M68HC12 Indexed Indirect Addressing	
AN1775	Expanding Digital Input with an A/D Converter	
AN1783	Determining MCU Oscillator Start-Up Parameters	
AN2104	Using Background Debug Mode for the M68HC12 Family	
AN2204	Fast NVM Programming for the MC9S12DP256	
AN2216	MC9S12DP256 Software Development Using Metrowerks CodeWarrior™	
AN2318	Using the I ² C Bus with HCS12 Microcontrollers	
BCANPSV2.0	Bosch Controller Area Network (CAN) Version 2.0 Protocol Standard	
EB396	Use of OSC2/XTAL as a Clock Output on Motorola Microcontrollers	

Learn More: For more information about Freescale products, please visit www.freescale.com.

Package Options

Part Number Package MC9S12D64CFU 80 QFP MC9S12D64VFU 80 QFP 80 QFP MC9S12D64MFU MC9S12D64CPV 112 LQFP -40°C to +85°C MC9S12D64VPV 112 LQFP -40°C to +105°C MC9S12D64MPV 80-Lead QFP дишишищ

112 LQFP -40°C to +125°C



*Price indicated is MSRP.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. This product incorporates SuperFlash® technology licensed from SST. © Freescale Semiconductor, Inc. 2005

Document Number: MC9S12D64FS

RFV 0

