




NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETER	
	MIN	MAX	MIN	MAX
A	0.965	0.985	24.52	25.01
B	0.355	0.375	9.02	9.52
C	0.230	0.260	5.85	6.60
D	0.115	0.125	2.93	3.17
E	0.102	0.114	2.59	2.90
F	0.075	0.085	1.91	2.15
H	0.160	0.170	4.07	4.31
J	0.004	0.006	0.11	0.15
K	0.090	0.110	2.29	2.79
L	0.725 BSC		18.42 BSC	
N	0.225	0.241	5.72	6.12
Q	0.125	0.135	3.18	3.42

STYLE 1:
PIN 1. BASE (COMMON)
2. EMITTER (INPUT)
3. BASE (COMMON)
4. BASE (COMMON)
5. COLLECTOR (OUTPUT)
6. BASE (COMMON)

STYLE 2:
PIN 1. EMITTER (COMMON)
2. BASE (INPUT)
3. EMITTER (COMMON)
4. EMITTER (COMMON)
5. COLLECTOR (OUTPUT)
6. EMITTER (COMMON)

STYLE 3:
PIN 1. SOURCE (COMMON)
2. GATE (INPUT)
3. SOURCE (COMMON)
4. SOURCE (COMMON)
5. DRAIN (OUTPUT)
6. SOURCE (COMMON)