



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	15.11	16.00	0.595	0.630
B	13.06	13.56	0.514	0.534
C	5.08	5.59	0.200	0.220
D	0.41	0.51	0.016	0.020
F	1.22	1.63	0.048	0.064
G	2.54 BSC		0.100 BSC	
J	0.36	0.40	0.014	0.016
L	17.65	18.42	0.695	0.725
M	30° NOM		30° NOM	
N	12.07	12.57	0.475	0.495
R	10.92	11.43	0.430	0.450
Y	1.22	1.32	0.048	0.052
Z	2.68	3.00	0.106	0.118

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION A IS INCLUSIVE OF THE MOLD STOP RING NOT TO EXCEED 16.00 (0.630)
4. 344-01 THRU -4 OBSOLETE.
5. 344-05 THRU -11 OBSOLETE, NEW STANDARD 344-15.

STYLE 1:

- PIN 1. GROUND
 2. + OUTPUT
 3. + SUPPLY
 4. - OUTPUT

STYLE 2:

- PIN 1. VCC
 2. - SUPPLY
 3. + SUPPLY
 4. GROUND

STYLE 3:

- PIN 1. GROUND
 2. - VOUT
 3. VS
 4. + VOUT

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: UNIBODY A & D	DOCUMENT NO: 98ASB42280B	REV: AD
	STANDARD: NON-JEDEC	
	SOT1772-1	02 FEB 2016