

Freescale Semiconductor

Product Brief

Document Number: MC9S08JM60PB Rev. 1, 11/2007

> This document contains preview information on a new product that may be in a design phase or under development. Freescale reserves the right to change or discontinue this product without notice.

MC9S08JM60 Series MCUs Product Brief

8-bit Low-Cost, Low-Power, High-Performance HCS08 MCU Covers MC9S08JM60 and MC9S08JM32

1 2

3 4

The 8-bit MC9S08JM devices feature a full-speed USB 2.0 device with internal USB transceiver, 3.3V regulator and USBDP pull-up resister along with best in class module performance, system integration features, and software support. This family also has up to 60K bytes embedded flash, 4K Bytes RAM, and several serial peripherals such as IIC, SCI and SPI. In addition, these MCUs feature a 12ch 12bit ADC, independently clocked timers and peripherals, and up to 51 GPIO. These devices operate on a 48MHz HCS08 core with a 24MHz bus frequency and have an operating voltage range is from 2.7V to 5.5 V. This JM family is offered in 44LQFP, 48QFN, 64QFP, and 64LQFP packages.

Table of Contents

	Appli	ication Examples 2					
	Featu	ures					
	2.1	MC9S08JM60 Series Family Comparison 2					
	2.2	Block Diagram					
	2.3	Operating Parameters	4				
	2.4	Packages	4				
	2.5	Chip-Level Features					
	2.6	Module Features	5				
		2.6.1 8-Bit HCS08 Central Processor Unit (CPU).	5				
		2.6.2 On-Chip Memory	5				
		2.6.3 Power-Saving Modes	5				
		2.6.4 Clock Source Options	5				
		2.6.5 System Protection	5				
		2.6.6 USB Device Controller	6				
		2.6.7 Analog-to-Digital Converter (ADC)	6				
		2.6.8 Analog Comparator (ACMP)	6				
		2.6.9 Serial Communications Interface (SCI)	6				
		2.6.10 Serial Peripheral Interface (SPI)	6				
		2.6.11 Inter-Integrated Circuit (IIC)	6				
		2.6.12 Timer/Pulse-Width Modulator (TPM)	6				
		2.6.13 Keyboard Interrupt Module (KBI)	7				
		2.6.14 Real-Time Counter (RTC)	7				
		2.6.15 Input/Output	7				
		2.6.16 Debug	7				
Developer Environment							
Document Revision History							

This document contains information on a new product under development. Freescale Semiconductor reserves the right to change or discontinue this product without notice.



© Freescale Semiconductor, Inc., 2007. All rights reserved.



Application Examples

1 Application Examples

MC9S08JM60 series MCUs are general-purpose devices suitable for a wide range of applications, including:

- Uninterrupted power supplies
- Touch panels
- Gamepads
- Label printers
- Remote controls
- I/O modules
- Industrial networking products
- Stationary barcode scanners
- Barcode printers
- Utility meters

- Industrial printers
- Data loggers
- Automatic drug dispensers
- PC peripherals
- Motion controllers
- Laboratory equipment
- Lighting control systems
- Security control panels
- Cash register printers
- Measurement equipment

2 Features

2.1 MC9S08JM60 Series Family Comparison

Table 1 provides a summary of the different members of MC9S08JM60 series MCUs and their proposed features.

Table 1. Devices in the MC9S08JM60 Series

Footuro	Device					
realure	MC9S08JM60			MC9S08JM32		
Package	64-pin	48-pin	44-pin	64-pin	48-pin	44-pin
Flash	60,912			32,768		
RAM	4096			2048		
USB RAM	256			256		
ACMP		yes			yes	
ADC	12-ch	8-ch	8-ch	12-ch	8-ch	8-ch
IIC	yes			yes		
IRQ	yes			yes		
KBI	8	7	7	8	7	7



Feetuwe	Device						
reature	MC9S08JM60			MC9S08JM32			
Package	64-pin	48-pin	44-pin	64-pin	48-pin	44-pin	
SCI1		yes			yes		
SCI2		yes			yes		
SPI1	yes			yes			
SPI2		yes			yes		
TPM1	6-ch	4-ch	4-ch	6-ch	4-ch	4-ch	
TPM2		2-ch			2-ch		
USB	yes			yes			
I/O pins	51	37	33	51	37	33	
Package types	64 QFP 64LQFP	48 QFN	44 LQFP	64 QFP 64LQFP	48 QFN	44 LQFP	

Table 1. Devices in the MC9S08JM60 Series (continued)

2.2 Block Diagram

Figure 1 shows a top-level block diagram for the MC9S08JM60 series.



Figure 1. MC9SJM60 Block Diagram

MC9S08JM60 Series MCUs Product Brief, Rev. 1



2.3 **Operating Parameters**

Parameter		Min	Мах
Operating Voltage	V _{DD}	2.7 V	5.5 V
Operating Temperature	T _A	−40 °C	85 °C
Bus Frequency V _{DD} > 2.7 V	f _{Bus}	DC	24 MHz

Table 3 shows the design targets for supply currents. These are preliminary targets and are subject to change after the actual devices have been characterized.

Parameter	V _{DD} (V)	Typical ¹	Unit	
Run supply current ² measured at	5	1.1	m۸	
(CPU clock = 2 MHz, f _{Bus} = 1 MHz, BLPE mode)	3	0.8	шА	
Run supply current ² measured at	5	4.9	m۸	
(CPU clock = 8 MHz, f _{Bus} = 4 MHz, FBE mode)	3	4.3	3 MA	
Run supply current ² measured at	5	23	mΔ	
(CPU clock = 48 MHz, f _{Bus} = 24 MHz, FBE mode)	3	22	IIIA	
Stop2 mode supply current	5	0.8	μA	
	3	0.8		
Stop3 mode supply current	5	0.9	ıΔ	
	3	0.9	μΛ	
BTC adder to stop2 or stop 3^3	5	300	nΔ	
	3	300		
IVD adder to stop3 (IVDE – IVDSE – 1)	5	110	ıΔ	
	3	90	μΛ	
USB module enable current ⁴	5	1.5	mA	
USB suspend current ⁵	5	270	μA	

Table 3. Supply Current Characteristics

NOTES:

¹ Typicals are measured at 25°C unless otherwise stated.

- ² Measured at the following conditions: all modules except USB and ADC are active, Oscillator disabled (ERCLKEN = 0), using external clock resource for input, and no DC loads are applied on port pins.
- $^{3}\,$ Auto-wakeup from stop2 or stop3 can be used instead of the higher current wait mode.
- ⁴ Here USB module is enabled and clocked at 48 MHz (USBEN = 1, USBVREN =1, USBPHYEN = 1 and USBPU = 1), and D+ and D- pull down by two 15.1kΩ resisters independently. The current consumption may be much higher when the packets are being transmitted through the attached cable.
- ⁵ MCU enters into Stop3 mode, USB bus in idle state. The USB suspend current will be dominated by the D+ pull up resister.

2.4 Packages

MC9S08JM60 series devices are offered in the following packages:

- 64-pin quad flat package (QFP)
- 64-pin low-profile quad flat package (LQFP)



- 48-pin quad flat no-lead (QFN)
- 44-pin low-profile quad flat package (LQFP)

2.5 Chip-Level Features

- New high speed S08 platform, HCS08 core can run under 48 MHz
- On-chip USB transceiver, 3.3V regualtor and USBDP pull-up resister
- Ideal for USB applications that also require fast speed ADC

2.6 Module Features

2.6.1 8-Bit HCS08 Central Processor Unit (CPU)

- 48 MHz HCS08 CPU (central processor unit)
- 24 MHz internal bus frequency
- HC08 instruction set with added BGND instruction
- Support for up to 32 interrupt/reset sources
- Background debugging system
- Breakpoint capability to allow single breakpoint setting during in-circuit debugging (plus two more breakpoints in on-chip debug module)

2.6.2 On-Chip Memory

- Up to 60 KB of on-chip in-circuit programmable flash memory with block protection and security options
- Up to 4 KB of on-chip RAM
- 256 bytes of USB RAM

2.6.3 Power-Saving Modes

• Wait plus two stops

2.6.4 Clock Source Options

- Clock source options include crystal, resonator, external clock
- MCG (multi-purpose clock generator) supports PLL and FLL modes
- Internal reference clock with trim adjustment

2.6.5 System Protection

- Optional computer operating properly (COP) reset with option to run from independent 1 kHz internal clock source or the bus clock
- · Low-voltage detection with reset or interrupt

MC9S08JM60 Series MCUs Product Brief, Rev. 1



Features

- Illegal opcode detection with reset
- Illegal address detection with reset

2.6.6 USB Device Controller

- USB 2.0 full-speed (12 Mbps) with dedicated on-chip USB transceiver, 3.3V regulator and USBDP pull-up resister
- Supports control, interrupt, isochronous, and bulk transfers
- Supports endpoint 0 and up to 6 additional endpoints
- Endpoints 5 and 6 can be combined to provide double buffering capability

2.6.7 Analog-to-Digital Converter (ADC)

• 12-channel, 12-bit analog-to-digital converter with automatic compare function

2.6.8 Analog Comparator (ACMP)

- Analog comparator with option to compare to internal reference
- Operation in stop3 mode

2.6.9 Serial Communications Interface (SCI)

• Two serial communications interface modules with optional 13-bit break LIN extensions

2.6.10 Serial Peripheral Interface (SPI)

• Two 8- or 16-bit selectable serial peripheral interface modules with a receive data buffer hardware match function

2.6.11 Inter-Integrated Circuit (IIC)

- Inter-integrated circuit bus module to operate at up to 100 kbps with maximum bus loading
- Multi-master operation
- Programmable slave address, 10-bit addressing & broadcast modes support
- Interrupt-driven byte-by-byte data transfer

2.6.12 Timer/Pulse-Width Modulator (TPM)

- One 2-channel and one 6-channel 16-bit timer/pulse-width modulator (TPM) module
- Selectable input capture, output compare, and edge-aligned PWM capability on each channel
- Each timer module may be configured for buffered, centered PWM (CPWM) on all channels



2.6.13 Keyboard Interrupt Module (KBI)

• 8-pin keyboard interrupt module

2.6.14 Real-Time Counter (RTC)

• Real-time counter with binary- or decimal-based prescaler

2.6.15 Input/Output

- Up to 51 general-purpose input/output pins
- Software selectable pullups on ports when used as inputs
- Software selectable slew rate control on ports when used as outputs
- Software selectable drive strength on ports when used as outputs
- Master reset pin and power-on reset (POR)
- Internal pullup on RESET, IRQ, and BKGD/MS pins to reduce customer system cost

2.6.16 Debug

- Single-wire background debug interface
- Breakpoint capability to allow single breakpoint setting during in-circuit debugging (plus two more breakpoints in on-chip debug module)
- On-chip in-circuit emulator (ICE) debug module containing three comparators and nine trigger modes; eight deep FIFO for storing change-of-flow addresses and event-only data; debug module supports both tag and force breakpoints

3 Developer Environment

- Cost-effective demostration kit featuring the daughter cards with built-in USB-BDM circuitry
- CodeWarriorTM Development Studio for Microcontrollers 6.1 supports software development
- Freescale USB-LITE stack by CMX supports HID and CDC class

4 Document Revision History

Table 4. Revision History

Revision	Substantive Change(s)
1	Initial release



THIS PAGE IS INTENTIONALLY BLANK



THIS PAGE IS INTENTIONALLY BLANK



How to Reach Us:

Home Page: www.freescale.com

Web Support: http://www.freescale.com/support

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, EL516 2100 East Elliot Road Tempe, Arizona 85284 +1-800-521-6274 or +1-480-768-2130 www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405 Denver, Colorado 80217 1-800-441-2447 or 303-675-2140 Fax: 303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com

Document Number: MC9S08JM60PB Rev. 1 11/2007 Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale[™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. The PowerPC name is a trademark of IBM Corp. and is used under license. The described product contains a PowerPC processor core. The PowerPC name is a trademark of IBM Corp. and used under license. The described product is a PowerPC microprocessor. The PowerPC name is a trademark of IBM Corp. and is used under license. The described product is a PowerPC microprocessor core. The PowerPC name is a trademark of IBM Corp. and is used under license.

© Freescale Semiconductor, Inc. 2007. All rights reserved.

