

PART INFORMATION

Mfg Item Number	MC9328MXLCVM15
Mfg Item Name	MAPBGA 256 14*14*1.6P0.8

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-04-10
Response Document ID	5296K10862D054A1.22
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	

MANUFACTURING

Mfg Item Number	MC9328MXLCVM15
Mfg Item Name	MAPBGA 256 14*14*1.6P0.8
Version	ALL
Weight	0.504300
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.0665						g				
Solder Balls - Lead Free		Metals	Aluminum, metal	7429-90-5		0.0000206	g	31	0.0031	4	0.0004
Solder Balls - Lead Free		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0		0.00000831	g	125	0.0125	16	0.0016
Solder Balls - Lead Free		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000492	g	74	0.0074	9	0.0009
Solder Balls - Lead Free		Bismuth/Bismuth Compounds	Bismuth	7440-69-9		0.00001244	g	187	0.0187	24	0.0024
Solder Balls - Lead Free		Cadmium/Cadmium Compounds	Cadmium	7440-43-8		0.0000008	g	12	0.0012	1	0.0001
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8		0.0003321	g	4994	0.4994	658	0.0658
Solder Balls - Lead Free		Metals	Gold, metal	7440-57-5		0.00000412	g	62	0.0062	8	0.0008
Solder Balls - Lead Free		Metals	Iron, metal	7439-89-6		0.00000831	g	125	0.0125	16	0.0016
Solder Balls - Lead Free		Lead/Lead Compounds	Lead	7439-92-1		0.00002494	g	375	0.0375	49	0.0049
Solder Balls - Lead Free		Nickel (external applications only)	Nickel	7440-02-0		0.00000206	g	31	0.0031	4	0.0004
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4		0.00265687	g	39953	3.9953	5268	0.5268
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5		0.0634331	g	953881	95.3881	125784	12.5784
Solder Balls - Lead Free		Metals	Zinc, metal	7440-66-6		0.00000126	g	19	0.0019	2	0.0002
Solder Balls - Lead Free		Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances.	-		0.00000871	g	131	0.0131	17	0.0017
Non-Conductive Epoxy/Adhesive	0.0026						g				
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.000195	g	75000	7.5	386	0.0386
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5		0.00052	g	200000	20	1031	0.1031
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-		0.000195	g	75000	7.5	386	0.0386
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-		0.00052	g	200000	20	1031	0.1031
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	80676-86-0		0.00117	g	450000	45	2320	0.232
Silicon Semiconductor Die	0.0341						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.000682	g	20000	2	1352	0.1352
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.033418	g	980000	98	66266	6.6266
Die Encapsulant, Halogen-free	0.2667						g				
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-		0.008001	g	30000	3	15865	1.5865
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.002667	g	10000	1	5288	0.5288
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.008001	g	30000	3	15865	1.5865
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-		0.008001	g	30000	3	15865	1.5865
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	80676-86-0		0.226695	g	850000	85	449542	44.9542
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-		0.013335	g	50000	5	26442	2.6442
Bonding Wire, PoCu	0.0058						g				
Bonding Wire, PoCu		Metals	Copper, metal	7440-50-8		0.00564337	g	972995	97.2995	11190	1.119
Bonding Wire, PoCu		Metals	Palladium, metal	7440-05-3		0.00015663	g	27005	2.7005	310	0.031
Substrate	0.1286						g				
Substrate		Metals	Barium sulfate	7727-43-7		0.00696896	g	54191	5.4191	13819	1.3819
Substrate		Metals	Copper, metal	7440-50-8		0.02369198	g	184230	18.423	46979	4.6979
Substrate		Plastics/polymers	Epikote 862	28064-14-4		0.01191672	g	92665	9.2665	23630	2.363
Substrate		Plastics/polymers	Formaldehyde, polymer with 2-methylphenol, glycidyl ether	64425-89-4		0.010797	g	83958	8.3958	21409	2.1409
Substrate		Metals	Gold, metal	7440-57-5		0.00054514	g	4239	0.4239	1090	0.109
Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.00425795	g	33110	3.311	8443	0.8443
Substrate		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4		0.00650729	g	50601	5.0601	12903	1.2903
Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.03985763	g	309935	30.9935	79035	7.9035
Substrate		Glass	Silicon dioxide	7631-86-9		0.0031639	g	26566	2.6566	6774	0.6774
Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-		0.00118995	g	8701	0.8701	2218	0.2218
Substrate		Metals	Aluminum Hydroxide	21645-51-2		0.01952199	g	151804	15.1804	38711	3.8711

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcdfs/MC9328MXLCVM15_IPC1752_v11.xml

http://www.freescale.com/mcdfs/MC9328MXLCVM15_IPC1752A.xml