

PART INFORMATION	
Mfg Item Number	MCF5208CVM166
Mfg Item Name	MABGA-FW 196 15SQ0.8P1.0
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-04-28
Response Document ID	5220A1.37
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MCF5208CVM166
Mfg Item Name	MABGA-FW 196 15SQ0.8P1.0
Version	ALL
Weight	0.514750
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

## MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Solder Balls - Lead Free	0.0366	Metals	Aluminum, metal	7429-90-5	0.00000113	g	31	0.0031		2	0.0002
Solder Balls - Lead Free		Metals	Antimony/Antimony Compounds	7440-36-0	0.00000458	g	125	0.0125		8	0.0008
Solder Balls - Lead Free		Metals	Arsenic/Arsenic Compounds	7440-38-2	0.00000271	g	74	0.0074		5	0.0005
Solder Balls - Lead Free		Metals	Bismuth/Bismuth Compounds	7440-69-9	0.00000684	g	187	0.0167		13	0.0013
Solder Balls - Lead Free		Metals	Cadmium/Cadmium Compounds	7440-43-9	0.00000044	g	12	0.0012		0	0
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8	0.00018278	g	4994	0.4994		355	0.035
Solder Balls - Lead Free		Metals	Gold, metal	7440-57-5	0.00000227	g	62	0.0062		4	0.0004
Solder Balls - Lead Free		Metals	Indium, metal	7440-74-6	0.00000227	g	62	0.0062		4	0.0004
Solder Balls - Lead Free		Solvents, additives, and other materials	Sulfur	7704-34-9	0.00000222	g	6	0.0006		0	0
Solder Balls - Lead Free		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0	0.00000227	g	62	0.0062		4	0.0004
Solder Balls - Lead Free		Metals	Iron, metal	7439-89-6	0.00000458	g	125	0.0125		8	0.0008
Solder Balls - Lead Free		Lead/Lead Compounds	Lead	7439-92-1	0.00001373	g	375	0.0375		26	0.0026
Solder Balls - Lead Free		Nickel (external applications only)	Nickel	7440-02-0	0.00000113	g	31	0.0031		2	0.0002
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4	0.00146228	g	39853	3.9953		2840	0.284
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5	0.039491207	g	953882	95.3882		67923	6.7823
Solder Balls - Lead Free		Metals	Zinc, metal	7440-66-6	0.00000007	g	19	0.0019		1	0.0001
Non-Conductive Epoxy/Adhesive	0.009					g					
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other Epoxy resins	-	0.000675	g	75000	7.5		1311	0.1311
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5	0.0018	g	200000	20		3496	0.3496
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-	0.000675	g	75000	7.5		1311	0.1311
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-	0.0018	g	200000	20		3496	0.3496
Silicon Semiconductor Die	0.0087					g				7867	0.7867
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000174	g	20000	2		338	0.0338
Silicon Semiconductor Die		Glass	Silicon, doped	-	0.008526	g	980000	98		16563	1.6563
Die Encapsulant, Halogen-free	0.3009					g				17536	1.7536
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-	0.009027	g	30000	3		5845	0.5845
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.003009	g	10000	1		17536	1.7536
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4	0.009027	g	30000	3		17536	1.7536
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-	0.009027	g	30000	3		17536	1.7536
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0	0.255765	g	850000	85		495894	49.6894
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-Halogenated Epoxy resins	-	0.015045	g	50000	5		29227	2.9227
Substrate	0.15785					g				1943	0.1943
Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (2974)	68891-46-3	0.00100061	g	6339	0.6339			
Substrate		Metals	Barium sulfate	7727-43-7	0.00928742	g	58837	5.8837		18042	1.8042
Substrate		Metals	Copper, metal	7440-50-8	0.04265944	g	271520	27.152		83262	8.3262
Substrate		Plastics/polymers	4,4'-dihydroxy-3,3,5,5-tetramethylbiphenyl diglycidyl ether	85954-11-6	0.00532475	g	33733	3.3733		10344	1.0344
Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5	0.04136617	g	262060	26.206		80361	8.0361
Substrate		Metals	Gold, metal	7440-57-5	0.00061246	g	3880	0.388		1189	0.1189
Substrate		Solvents, additives, and other materials	Silicon	7440-21-3	0.00011997	g	760	0.076		233	0.0233
Substrate		Nickel (external applications only)	Nickel	7440-02-0	0.00621692	g	39385	3.9385		12077	1.2077
Substrate		Glass	Fibrous-glass-wool	65997-17-3	0.03929218	g	248921	24.8921		76332	7.6332
Substrate		Plastics/polymers	Other acrylic resins	-	0.00706189	g	44739	4.4738		13719	1.3719
Substrate		Plastics/polymers	Other acrylic/epoxy resin mixture	-	0.00470819	g	29827	2.9827		9146	0.9146
Bonding Wire, PdCu	0.0017					g				3239	0.3239
Bonding Wire, PdCu		Metals	Copper, metal	7440-50-8	0.00166577	g	981000	98.1		3	0.0003
Bonding Wire, PdCu		Metals	Gold, metal	7440-57-5	0.0000017	g	1000	0.1		59	0.0059
Bonding Wire, PdCu		Metals	Palladium, metal	7440-05-3	0.0000306	g	18000	1.8			

**LINKS**

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
<b>GENERAL ENVIRONMENTAL COMPLIANCE LINKS</b>	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
<b>NXP ENVIRONMENTAL INFORMATION</b>	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

IPC1752 XML LINKS

[http://www.freescale.com/mcds/MCF5208CVM166\\_IPC1752\\_v11.xml](http://www.freescale.com/mcds/MCF5208CVM166_IPC1752_v11.xml)

[http://www.freescale.com/mcds/MCF5208CVM166\\_IPC1752A.xml](http://www.freescale.com/mcds/MCF5208CVM166_IPC1752A.xml)