

PART INFORMATION	
Mfg Item Number	MK20DX64VMC7
Mfg Item Name	MAPBGA 121 8*8*1.4 P0.65
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-06-26
Response Document ID	00BCK00195D010A1.15
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e1
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MK20DX64VMC7
Mfg Item Name	MAPBGA 121 8*8*1.4 P0.65
Version	ALL
Weight	0.196450
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0017	Plastics/polymers	Proprietary Material-Other Epoxy resins	-	0.0001275	g	75000	7.5		649	0.0649
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5	0.00034	g	200000	20		1730	0.173
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-	0.0001275	g	75000	7.5		649	0.0649
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-	0.00034	g	200000	20		1730	0.173
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0	0.000765	g	450000	45		3894	0.3894
Solder Balls - Lead Free	0.03145					g	269				
Solder Balls - Lead Free		Antimony/Antimony Compounds	Antimony (metallic)	7440-36-0	0.00000204	g	85	0.0065		10	0.001
Solder Balls - Lead Free		Arsenic/Arsenic Compounds	Arsenic	7440-38-2	0.00000101	g	32	0.0032		5	0.0005
Solder Balls - Lead Free		Bismuth/Bismuth Compounds	Bismuth	7440-69-9	0.00000079	g	25	0.0025		4	0.0004
Solder Balls - Lead Free		Metals	Copper, metal	7440-50-8	0.00014873	g	4729	0.4729		757	0.0757
Solder Balls - Lead Free		Metals	Iron, metal	7439-89-6	0.00000104	g	33	0.0033		6	0.0005
Solder Balls - Lead Free		Lead/Lead Compounds	Lead	7439-92-1	0.00000846	g	269	0.0064		43	0.0043
Solder Balls - Lead Free		Nickel (external applications only)	Nickel	7440-02-0	0.0000011	g	35	0.0035		5	0.0005
Solder Balls - Lead Free		Metals	Silver, metal	7440-22-4	0.00029179	g	9278	0.9278		1485	0.1485
Solder Balls - Lead Free		Metals	Tin, metal	7440-31-5	0.03099303	g	985470	98.547		157765	15.7765
Solder Balls - Lead Free		Metals	Germanium	7440-56-4	0.00000201	g	64	0.0064		10	0.001
Bonding Wire, Copper	0.0008					g					
Bonding Wire, Copper		Metals	Copper, metal	7440-50-8	0.000776	g	970000	97		3950	0.395
Bonding Wire, Copper		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000024	g	30000	3		122	0.0122
Die Encapsulant, Halogen-free	0.0872					g					
Die Encapsulant, Halogen-free		Metals	Other aluminum compounds	-	0.002616	g	30000	3		13316	1.3316
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.000872	g	10000	1		4438	0.4438
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol, polymer with formaldehyde	9003-35-4	0.002616	g	30000	3		13316	1.3316
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-	0.002616	g	30000	3		13316	1.3316
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0	0.07412	g	850000	85		377312	37.7312
Die Encapsulant, Halogen-free		Plastics/polymers	Other Non-halogenated Epoxy resins	-	0.00436	g	50000	5		22193	2.2193
Organic Substrate	0.0437					g					
Organic Substrate		Solvents, additives, and other materials	Other aromatic amines and their salts	-	0.00000782	g	179	0.0179		39	0.0039
Organic Substrate		Metals	Barium sulfate	7727-43-7	0.00026412	g	6044	0.6044		1344	0.1344
Organic Substrate		Metals	Copper, metal	7440-50-8	0.02058223	g	470989	47.0989		104770	10.4770
Organic Substrate		Plastics/polymers	Other Epoxy resins	-	0.00259971	g	59490	5.948		13233	1.3233
Organic Substrate		Metals	Gold, metal	7440-57-5	0.00062535	g	14310	1.431		3183	0.3183
Organic Substrate		Metals	Talc	14807-96-6	0.00013302	g	3044	0.3044		677	0.0677
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0	0.00487989	g	111668	11.1668		24840	2.4840
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3	0.01165432	g	264401	26.4401		58815	5.8815
Organic Substrate		Glass	Silicon dioxide	7631-86-9	0.00186616	g	42704	4.2704		9499	0.9499
Organic Substrate		Solvents, additives, and other materials	Other Aromatic carbonyl compounds	-	0.00004951	g	1133	0.1133		252	0.0252
Organic Substrate		Metals	Copper phthalocyanine	147-14-8	0.00000232	g	53	0.0053		11	0.0011
Organic Substrate		Solvents, additives, and other materials	Quinacridone pigment	1047-16-1	0.00000222	g	53	0.0053		11	0.0011
Organic Substrate		Solvents, additives, and other materials	3-methoxy-3-methyl-1-butyl acetate	103429-90-9	0.00028964	g	6628	0.6628		1474	0.1474
Organic Substrate		Plastics/polymers	Epoxy Resin	115254-47-2	0.00084127	g	19251	1.9251		4282	0.4282
Silicon Semiconductor Die	0.0316	Solvents, additives, and other materials	1,2,4-Trimethylbenzene	9543-6	0.00000232	g	53	0.0053		11	0.0011
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000632	g	20000	2		3217	0.3217
Silicon Semiconductor Die		Glass	Silicon, doped	-	0.030968	g	980000	98		157638	15.7638

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MK20DX64VMC7_IPC1752_v11.xml

http://www.freescale.com/mcds/MK20DX64VMC7_IPC1752A.xml