

<b>PART INFORMATION</b>	
Mfg Item Number	MKL03Z16VFK4R
Mfg Item Name	QFN MAP 24 4*4*0.65 P0.5
<b>SUPPLIER</b>	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2018-06-11
Response Document ID	00FRK10525D017A1.3
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
<b>DECLARATION</b>	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e4
EU RoHS Exemption(s)	
<b>MANUFACTURING</b>	
Mfg Item Number	MKL03Z16VFK4R
Mfg Item Name	QFN MAP 24 4*4*0.65 P0.5
Version	ALL
Weight	0.029500
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

## MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLE EPPM	ARTICLE%
Epoxy Die Attach	0.0003	Solvents, additives, and other materials	Proprietary Material-Other acrylates	-	0.00002648	g	88252	8.8252		897	0.0897
Epoxy Die Attach		Solvents, additives, and other materials	1,1'-(methylene-di-p-phenylene)bismaleimide	13676-54-5	0.00000993	g	33094	3.3094		336	0.0336
Epoxy Die Attach		Metals	Palladium, metal	7440-05-3	0.000005	g	1655	0.1655		16	0.0016
Epoxy Die Attach		Plastics/polymers	Proprietary Material-Other polymers	-	0.00000496	g	16547	1.6547		168	0.0168
Epoxy Die Attach		Metals	Silver, metal	7440-22-4	0.0002482	g	827358	82.7358		8413	0.8413
Epoxy Die Attach		Plastics/polymers	Proprietary Material-Other Methacrylate compounds	-	0.00000993	g	33094	3.3094		336	0.0336
Bonding Wire, Copper	0.0003	Metals	Copper, metal	7440-50-8	0.000291	g	970000	97		9864	0.9864
Bonding Wire, Copper		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000009	g	30000	3		305	0.0305
Die Encapsulant, Halogen-free	0.0243					g					
Die Encapsulant, Halogen-free		Plastics/polymers	4,4'-dihydroxy-3,3,5,5-tetramethylbiphenyl diglycidyl ether	85954-11-6	0.00037568	g	15460	1.546		12734	1.2734
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.0000442	g	1819	0.1819		1498	0.1498
Die Encapsulant, Halogen-free		Metals	Magnesium hydroxide	1309-42-8	0.00007164	g	35870	3.587		29547	2.9547
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Proprietary Material-Other organic phosphorous compounds	-	0.00001927	g	793	0.0793		653	0.0653
Die Encapsulant, Halogen-free		Plastics/polymers	1,3,5-Triazine-2,4,6-triamine, polymer with formaldehyde and phenol	25917-04-6	0.00007681	g	3161	0.3161		2603	0.2603
Die Encapsulant, Halogen-free		Plastics/polymers	Phenol p-xylylene dimethyl ether copolymer	26834-02-6	0.00088323	g	36347	3.6347		29940	2.994
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0	0.02074749	g	853806	85.3806		703315	70.3315
Die Encapsulant, Halogen-free		Metals	Zinc Hydroxide	20427-58-1	0.00040513	g	16672	1.6672		13733	1.3733
Die Encapsulant, Halogen-free		Plastics/polymers	Proprietary Material-Other Non-halogenated Epoxy resins	-	0.00087655	g	36072	3.6072		29713	2.9713
Copper Lead Frame	0.0033					g					
Copper Lead Frame		Metals	Copper, metal	7440-50-8	0.0019941	g	969521	96.9521		108454	10.8454
Copper Lead Frame		Metals	Gold, metal	7440-57-5	0.0000033	g	100	0.01		11	0.0011
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0	0.0000099	g	300	0.03		33	0.0033
Copper Lead Frame		Metals	Iron, metal	7439-89-6	0.00007552	g	22884	2.2884		2560	0.256
Copper Lead Frame		Nickel (external applications only)	Nickel	7440-02-0	0.00001715	g	5196	0.5196		581	0.0581
Copper Lead Frame		Metals	Palladium, metal	7440-05-3	0.00000188	g	600	0.06		67	0.0067
Copper Lead Frame		Metals	Zinc, metal	7440-66-6	0.00000462	g	1399	0.1399		156	0.0156
Silicon Semiconductor Die	0.0013	Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000026	g	20000	2		881	0.0881
Silicon Semiconductor Die		Glass	Silicon, doped	-	0.001274	g	980000	98		43186	4.3186

**LINKS**

MCD LINK	
NXP website	<a href="http://www.nxp.com">http://www.nxp.com</a>
<b>GENERAL ENVIRONMENTAL COMPLIANCE LINKS</b>	
RoHS signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf</a>
China RoHS	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY</a>
REACH signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf</a>
ELV signed letter	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf</a>
Conflict Minerals statement	<a href="http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf">http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf</a>
<b>NXP ENVIRONMENTAL INFORMATION</b>	
Environmental Compliance website	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX</a>
FAQ	<a href="http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ">http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ</a>
Technical Service Request	<a href="http://www.nxp.com/support/sales-and-support:SUPPORTHOME">http://www.nxp.com/support/sales-and-support:SUPPORTHOME</a>
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	<a href="http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf">http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf</a>

## IPC1752 XML LINKS

[http://www.freescale.com/mcds/MKL03Z16VFK4R\\_IPC1752\\_v11.xml](http://www.freescale.com/mcds/MKL03Z16VFK4R_IPC1752_v11.xml)

[http://www.freescale.com/mcds/MKL03Z16VFK4R\\_IPC1752A.xml](http://www.freescale.com/mcds/MKL03Z16VFK4R_IPC1752A.xml)