

PART INFORMATION

Mfg Item Number	MPC5553MZQ132
Mfg Item Name	PBGAPGE 324 23SQ1.25P1.0

SUPPLIER

Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-10-27
Response Document ID	5366K00073D071A1.31
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com

DECLARATION

EU RoHS	No
Pb Free	No
HalogenFree	Yes
Plating Indicator	e0
EU RoHS Exemption(s)	

MANUFACTURING

Mfg Item Number	MPC5553MZQ132
Mfg Item Name	PBGAPGE 324 23SQ1.25P1.0
Version	ALL
Weight	1.737850
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	245 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	<p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	0.7571						g				
Die Encapsulant		Metals	Aluminum, metal	7429-90-5		0.02339136	g	30896	3.0896	13459	1.3459
Die Encapsulant		Arsenic/Arsenic Compounds	Arsenic	7440-38-2		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Cadmium/Cadmium Compounds	Cadmium	7440-43-9		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.02339136	g	30896	3.0896	13459	1.3459
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.00233944	g	3090	0.309	1346	0.1346
Die Encapsulant		Lead/Lead Compounds	Lead	7439-92-1		0.00000076	g	1	0.0001	0	0
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-		0.00233944	g	3090	0.309	1346	0.1346
Die Encapsulant		Plastics/polymers	Proprietary Material-Other phenolic resins	-		0.04288366	g	56642	5.6642	24676	2.4676
Die Encapsulant		Glass	Silica, vitreous	60676-86-0		0.66275246	g	875383	87.5383	381379	38.1379
Epoxy Die Attach	0.0145						g				
Epoxy Die Attach		Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-[2-(2-methyl-1H-imidazol-1-yl)ethyl]	38668-46-1		0.00012254	g	8451	0.8451	70	0.007
Epoxy Die Attach		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.0018789	g	129579	12.9579	1081	0.1081
Epoxy Die Attach		Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6		0.00012254	g	8451	0.8451	70	0.007
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.01237602	g	853519	85.3519	7121	0.7121
Solder Balls - Low Lead	0.3016						g				
Solder Balls - Low Lead		Lead/Lead Compounds	Lead	7439-92-1		0.108576	g	360000	36	62477	6.2477
Solder Balls - Low Lead		Metals	Silver, metal	7440-22-4		0.006032	g	20000	2	3470	0.347
Solder Balls - Low Lead		Metals	Tin, metal	7440-31-5		0.186992	g	620000	62	107599	10.7599
Organic Substrate	0.592						g				
Organic Substrate		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (26/74)	68891-46-3		0.00167358	g	2827	0.2827	963	0.0963
Organic Substrate		Metals	Barium sulfate	7727-43-7		0.01553408	g	26240	2.624	8938	0.8938
Organic Substrate		Metals	Copper, metal	7440-50-8		0.3593659	g	607037	60.7037	206787	20.6787
Organic Substrate		Plastics/polymers	2,2'-(1-methylethylene)bis[4,1-phenyleneoxyethylene]bisoxirane	1675-54-3		0.0028493	g	4813	0.4813	1639	0.1639
Organic Substrate		Plastics/polymers	4,4'-dihydroxy-3,3',5,5'-tetramethylbiphenyl diglycidyl ether	85954-11-6		0.00890546	g	15043	1.5043	5124	0.5124
Organic Substrate		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5		0.0994637	g	168013	16.8013	57233	5.7233
Organic Substrate		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.00492958	g	8327	0.8327	2836	0.2836
Organic Substrate		Metals	Gold, metal	7440-57-5		0.00072402	g	1223	0.1223	416	0.0416
Organic Substrate		Solvents, additives, and other materials	Silicon	7440-21-3		0.00020069	g	339	0.0339	115	0.0115
Organic Substrate		Nickel (external applications only)	Nickel	7440-02-0		0.00734435	g	12406	1.2406	4226	0.4226
Organic Substrate		Glass	Fibrous-glass-wool	65997-17-3		0.07132357	g	120479	12.0479	41041	4.1041
Organic Substrate		Plastics/polymers	Other acrylic resins	-		0.01181158	g	19952	1.9952	6796	0.6796
Organic Substrate		Plastics/polymers	Other acrylic/epoxy resin mixture	-		0.00787419	g	13301	1.3301	4530	0.453
Bonding Wire, P/Cu	0.0059						g				
Bonding Wire, P/Cu		Metals	Copper, metal	7440-50-8		0.0057879	g	981000	98.1	3330	0.333
Bonding Wire, P/Cu		Metals	Gold, metal	7440-57-5		0.0000059	g	1000	0.1	3	0.0003
Bonding Wire, P/Cu		Metals	Palladium, metal	7440-05-3		0.0001062	g	18000	1.8	61	0.0061
Silicon Semiconductor Die	0.06675						g				
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-		0.001335	g	20000	2	768	0.0768
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.065415	g	980000	98	37641	3.7641

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcdfs/MPC5553MZQ132_IPC1752_v11.xml

http://www.freescale.com/mcdfs/MPC5553MZQ132_IPC1752A.xml