

PART INFORMATION	
Mfg Item Number	MPC5554MZP80
Mfg Item Name	TEPBGA 416 27*27*1.25 P1
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-10-31
Response Document ID	5252K10908D036A1.33
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	No
Pb Free	No
HalogenFree	Yes
Plating Indicator	e0
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	MPC5554MZP80
Mfg Item Name	TEPBGA 416 27*27*1.25 P1
Version	ALL
Weight	3.202800
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	245 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	3 - Item(s) does not contain RoHS restricted substances per the definition above except for lead in solders and selected exemptions, if any
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%	ARTICLEPPM	ARTICLE%
Die Encapsulant	1.17945					g		30896	3.0896		
Die Encapsulant		Metals	Aluminum, metal	7429-90-5	0.03644029	g	1	0.0001	0.0001	11377	1.1377
Die Encapsulant		Arsenic/Arsenic Compounds	Arsenic	7440-38-2	0.00000118	g	1	0.0001	0	0	0
Die Encapsulant		Cadmium/Cadmium Compounds	Cadmium	7440-43-9	0.00000118	g	1	0.0001	0	0	0
Die Encapsulant		Plastics/polymers	Proprietary Material-Other Epoxy resins	-	0.03644029	g	30896	3.0896	11377	1.1377	
Die Encapsulant		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.0036445	g	3090	0.309	1137	0.1137	
Die Encapsulant		Lead/Lead Compounds	Lead	7439-92-1	0.00000118	g	1	0.0001	0	0	0
Die Encapsulant		Solvents, additives, and other materials	Other organic phosphorous compounds	-	0.0364445	g	3090	0.309	1137	0.1137	
Die Encapsulant		Plastics/polymers	Proprietary Material-Other phenolic resins	-	0.06680641	g	56842	5.6642	20868	2.0858	
Die Encapsulant		Glass	Silica, vitreous	60678-86-0	1.03247047	g	875383	87.5383	222384	32.2384	
Epoxy Die Attach	0.0174					g				45	0.0045
Epoxy Die Attach			Solvents, additives, and other materials	1,3,5-Triazine-2,4-diamine, 6-[2-(2-methyl-1H-imidazol-1-yl)ethyl]	38668-46-1	0.00014705	g	8451	0.8451		
Epoxy Die Attach			Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5	0.00235467	g	129579	12.8679	703	0.0703
Epoxy Die Attach			Plastics/polymers	4,4'-Dihydroxydiphenyl	92-88-6	0.00014705	g	8451	0.8451	45	0.0045
Epoxy Die Attach			Metals	Silver, metal	7440-22-4	0.01485123	g	853519	85.3519	4636	0.4636
Solder Balls - Low Lead	0.4436					g					
Solder Balls - Low Lead			Lead/Lead Compounds	Lead	7439-92-1	0.159696	g	360000	36	49861	4.9861
Solder Balls - Low Lead			Metals	Silver, metal	7440-22-4	0.008872	g	20000	2	2770	0.277
Solder Balls - Low Lead			Metals	Tin, metal	7440-31-5	0.275032	g	620000	62	85872	8.5872
Bonding Wire	0.013					g				4058	0.4058
Bonding Wire			Metals	Gold, metal	7440-57-5	0.013	g	1000000	100		
Organic Substrate	1.5074					g				10002	1.0002
Organic Substrate			Metals	Barium sulfate	7727-43-7	0.03203677	g	21253	2.1253	314565	31.4565
Organic Substrate			Metals	Copper, metal	7440-50-8	1.00749189	g	668364	66.8364	1777	0.1777
Organic Substrate			Plastics/polymers	2,2'-(1-(methylmethylenediene)bis(4,1-phenyleneoxy)ethylene)bisoxirane	1675-54-3	0.00569345	g	3777	0.3777	30717	3.0717
Organic Substrate			Plastics/polymers	Poly(o-cresyl glycidyl ether)-co-formaldehyde	29690-82-2	0.09838197	g	65266	6.5266	538	0.0538
Organic Substrate			Metals	Gold, metal	7440-57-5	0.00172597	g	1145	0.1145	136	0.0136
Organic Substrate			Solvents, additives, and other materials	1-cyanoquadrin	461-59-5	0.00043564	g	289	0.0289	9215	0.9215
Organic Substrate			Solvents, additives, and other materials	1,1'-(methylenebis(p-phenylene))bismaleimide	13676-54-5	0.02951489	g	19580	1.958	3723	0.3723
Organic Substrate			Nickel (external applications only)	Nickel	7440-02-0	0.01192504	g	7911	0.7911	30717	3.0717
Organic Substrate			Plastics/polymers	4,4'-Isopropylidenediphenol-1-chloro-2,3-epoxyp propane concentrate	25068-38-6	0.09838197	g	65266	6.5266	49147	4.9147
Organic Substrate			Glass	Fibrous-glass-wool	65997-17-3	0.15741025	g	104425	10.4425	4343	0.4343
Organic Substrate			Solvents, additives, and other materials	Proprietary Material-Other miscellaneous substances	-	0.01391029	g	9228	0.9228	81	0.0081
Organic Substrate			Metals	Copper phthalocyanine	147-14-8	0.00026078	g	173	0.0173	15683	1.5683
Organic Substrate			Plastics/polymers	Other Non-halogenated Epoxy resins	-	0.05023109	g	33323	3.3323	261	0.0261
Silicon Semiconductor Die	0.04195					g				12835	1.2835
Silicon Semiconductor Die			Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.000839	g	20000	2		
Silicon Semiconductor Die			Glass	Silicon, doped	-	0.041111	g	980000	98		

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/MPC5554MZP80_IPC1752_v11.xml

http://www.freescale.com/mcds/MPC5554MZP80_IPC1752A.xml