

PART INFORMATION	
Mfg Item Number	SC705C8AE0VFNE
Mfg Item Name	PLCC 44
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-06-12
Response Document ID	0801K00028D072A1.6
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e3
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	SC705C8AE0VFNE
Mfg Item Name	PLCC 44
Version	ALL
Weight	2.386550
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	250 C
Max Time at Peak Temperature	30 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
List of Freescale Accepted Exemptions	6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight 6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight 6(c) : Copper alloy containing up to 4% lead by weight 7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead) 7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications 7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound 7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher 7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC 7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors 15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart PPM	SubPart%		ARTICLEPPM	ARTICLE%
Epoxy Die Attach	0.0013						g					
Epoxy Die Attach		Solvents, additives, and other materials	Other aliphatic amines	-		0.00007287	g	56050	5.605		30	0.003
Epoxy Die Attach		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.00020535	g	157959	15.7959		86	0.0086
Epoxy Die Attach		Metals	Silver, metal	7440-22-4		0.00094891	g	729941	72.9941		397	0.0397
Epoxy Die Attach		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.00007287	g	56050	5.605		30	0.003
Die Encapsulant, Halogen-free	1.77355						g					
Die Encapsulant, Halogen-free		Plastics/polymers	Proprietary Material-Other Epoxy resins	-		0.03677633	g	20736	2.0736		15409	1.5409
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4		0.01094458	g	6171	0.6171		4585	0.4585
Die Encapsulant, Halogen-free		Metals	Magnesium Aluminum Hydroxide Carbonate	11097-59-9		0.00350276	g	1975	0.1975		1467	0.1467
Die Encapsulant, Halogen-free		Metals	Magnesium dihydroxide	1309-42-8		0.33273217	g	187608	18.7608		139419	13.9419
Die Encapsulant, Halogen-free		Plastics/polymers	Proprietary Material-Other phenolic resins	-		0.03677633	g	20736	2.0736		15409	1.5409
Die Encapsulant, Halogen-free		Glass	Silica, crystalline - quartz (SiO2)	14808-60-7		0.08318304	g	46902	4.6902		34854	3.4854
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0		1.26963479	g	715872	71.5872		532009	53.2009
Copper Lead Frame	0.5851						g					
Copper Lead Frame		Metals	Copper, metal	7440-50-8		0.56401006	g	963955	96.3955		236328	23.6328
Copper Lead Frame		Solvents, additives, and other materials	Phosphorus, elemental (not containing red allotrope)	7723-14-0		0.00048271	g	825	0.0825		202	0.0202
Copper Lead Frame		Metals	Iron, metal	7439-89-6		0.01374985	g	23500	2.35		5761	0.5761
Copper Lead Frame		Lead/Lead Compounds	Lead	7439-92-1		0.00009947	g	170	0.017		41	0.0041
Copper Lead Frame		Metals	Silver, metal	7440-22-4		0.005851	g	10000	1		2451	0.2451
Copper Lead Frame		Metals	Tin, metal	7440-31-5		0.00017553	g	300	0.03		73	0.0073
Copper Lead Frame		Metals	Zinc, metal	7440-66-6		0.00073138	g	1250	0.125		306	0.0306
Lead Frame Plating	0.0144						g					
Lead Frame Plating		Lead/Lead Compounds	Lead	7439-92-1		0.00000288	g	200	0.02		1	0.0001
Lead Frame Plating		Metals	Tin, metal	7440-31-5		0.01439712	g	999800	99.98		6032	0.6032
Silicon Semiconductor Die	0.0101						g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%).	-		0.000202	g	20000	2		84	0.0084
Silicon Semiconductor Die		Glass	Silicon, doped	-		0.009898	g	980000	98		4147	0.4147
Bonding Wire	0.0021						g					
Bonding Wire		Metals	Gold, metal	7440-57-5		0.0021	g	1000000	100		879	0.0879

LINKS	
MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/SC705C8AE0VFNE_IPC1752_v11.xml

http://www.freescale.com/mcds/SC705C8AE0VFNE_IPC1752A.xml