

PART INFORMATION	
Mfg Item Number	SPC5777CSK3MME3
Mfg Item Name	MAPBGA 416 27SQ*2.0 P1.0
SUPPLIER	
Company Name	Freescale Semiconductor Inc
Company Unique ID	14-141-7928
Response Date	2017-11-04
Response Document ID	00G5K00218D001A1.5
Contact Name	Freescale Semiconductor Inc
Contact Title	Product Technical Support
Contact Phone	1-800-521-6274
Contact Email	support@freescale.com
Authorized Representative	Daniel Binyon
Representative Title	EPP Customer Response
Representative Phone	512-895-3406
Representative Email	eppanlst@freescale.com
URL for Additional Information	www.freescale.com
DECLARATION	
EU RoHS	Yes
Pb Free	Yes
HalogenFree	Yes
Plating Indicator	e2
EU RoHS Exemption(s)	
MANUFACTURING	
Mfg Item Number	SPC5777CSK3MME3
Mfg Item Name	MAPBGA 416 27SQ*2.0 P1.0
Version	ALL
Weight	2.823200
UoM	g
Unit Volume	EACH
J-STD-020 MSL Rating	3
Peak Processing Temperature	260 C
Max Time at Peak Temperature	40 seconds
Number of Processing Cycles	3

RoHS	
RoHS Directive	2011/65/EU
RoHS Definition	RoHS Definition: Quantity limit of 0.1% by mass (1000 PPM) of homogeneous material for: Lead (Pb), Mercury, Hexavalent Chromium, Polybrominated Biphenyls (PBB), Polybrominated Diphenyl Ethers (PBDE) and quantity limit of 0.01% by mass (100 PPM) of homogeneous material of Cadmium
RoHS Legal Definition	<p>Please indicate whether any homogeneous material (as defined by the RoHS Directive, EU 2011/65/EU and implemented by the laws of the European Union member states) of the part(s) identified on this form contains lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls and/or polybrominated diphenyl ethers (each a RoHS restricted substance) in excess of the applicable quantity limit identified below. If a homogeneous material within the part(s) contains a RoHS restricted substance in excess of an applicable quantity limit, please indicate below which, if any, RoHS exemption you believe may apply. If the part is an assembly with lower level components, the declaration shall encompass all such components. Supplier certifies that it gathered the information it provides in this form using appropriate methods to ensure its accuracy and that such information is true and correct to the best of its knowledge and belief, as of the date that Supplier completes this form. Supplier acknowledges that Company will rely on this certification in determining the compliance of its products with European Union member state laws that implement the RoHS Directive. Company acknowledges that Supplier may have relied on information provided by others in completing this form, and that Supplier may not have independently verified such information. However, in situations where Supplier has not independently verified information provided by others, Supplier agrees that, at a minimum, its suppliers have provided certifications regarding their contributions to the part(s), and those certifications are at least as comprehensive as the certification in this paragraph. If the Company and the Supplier enter into a written agreement with respect to the identified part(s), the terms and conditions of that agreement, including any warranty rights and/or remedies provided as part of that agreement, will be the sole and exclusive source of the Suppliers liability and the Companys remedies for issues that arise regarding information the Supplier provides in this form. In the absence of such written agreement, the warranty rights and/or remedies of Suppliers Standard Terms and Conditions of Sale applicable to such part(s) shall apply.</p>
RoHS Declaration	1 - Item(s) do not contain RoHS restricted substances per the definition above
Supplier Acceptance	Accepted
Signature	Daniel Binyon
Exemption List Version	2012/51/EU
<p>List of Freescale Accepted Exemptions</p> <p>6(a) : Lead as an alloying element in steel for machining purposes and in galvanized steel containing up to 0.35% lead by weight</p> <p>6(b) : Lead as an alloying element in aluminium containing up to 0.4% lead by weight</p> <p>6(c) : Copper alloy containing up to 4% lead by weight</p> <p>7(a) : Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead)</p> <p>7(b) : Lead in solders for servers, storage and storage array systems, network infrastructure equipment for switching, signaling, transmission, and network management for telecommunications</p> <p>7(c)-I : Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectric devices, or in a glass or ceramic matrix compound</p> <p>7(c)-II : Lead in dielectric ceramic in capacitors for a rated voltage of 125 V AC or 250 V DC or higher</p> <p>7(c)-III : Lead in dielectric ceramic in capacitors for a rated voltage of less than 125 V AC or 250 V DC</p> <p>7(c)-IV : Lead in PZT based dielectric ceramic materials for capacitors being part of integrated circuits or discrete semiconductors</p> <p>15 : Lead in solders to complete a viable electrical connection between semiconductor die and carrier within integrated circuit flip chip packages</p>	

MATERIAL COMPOSITION

Homogeneous Material	Weight	SubstanceClass	Substance	CAS	Exemption	SubstanceWeight	UoM	SubPart	SubPart%	ARTICLEPPM	ARTICLE%
Non-Conductive Epoxy/Adhesive	0.0092	Plastics/polymers	Proprietary Material-Other Epoxy resins	-	0.00098	g	75000	7.5		244	0.0244
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Crosslinked acrylate polymer	25767-43-5	0.00184	g	200000	20		651	0.0651
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Other polymers	-	0.00069	g	75000	7.5		244	0.0244
Non-Conductive Epoxy/Adhesive		Plastics/polymers	Proprietary Material-Other polymers	-	0.00184	g	200000	20		651	0.0651
Non-Conductive Epoxy/Adhesive		Glass	Silica, vitreous	60676-86-0	0.00414	g	450000	45		1466	0.1466
Solder Balls - Pb Free, Sn/Ag	0.3706					g					
Solder Balls - Pb Free, Sn/Ag		Metals	Silver, metal	7440-22-4	0.012971	g	35000	3.5		4594	0.4594
Solder Balls - Pb Free, Sn/Ag		Metals	Tin, metal	7440-31-5	0.357629	g	985000	96.5		126675	12.6675
Die Encapsulant, Halogen-free	0.9217					g					
Die Encapsulant, Halogen-free		Plastics/polymers	Other Epoxy resins	-	0.055302	g	60000	6		19588	1.9588
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Carbon Black	1333-86-4	0.009217	g	10000	1		3264	0.3264
Die Encapsulant, Halogen-free		Solvents, additives, and other materials	Other inorganic compounds.	-	0.018434	g	20000	2		6529	0.0629
Die Encapsulant, Halogen-free		Plastics/polymers	Other phenolic resins	-	0.046085	g	50000	5		16323	1.6323
Die Encapsulant, Halogen-free		Glass	Silica, vitreous	60676-86-0	0.702662	g	866000	86		280767	28.0767
Organic Substrate, Halogen-free	1.4902					g					
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Acrylonitrile/Butadiene copolymer, carboxyl terminated (26/74)	68891-46-3	0.00361523	g	2426	0.2426		1280	0.128
Organic Substrate, Halogen-free		Metals	Barium sulfate	7727-43-7	0.03355334	g	22916	2.2516		11884	1.1884
Organic Substrate, Halogen-free		Metals	Copper, metal	7440-50-8	0.95563248	g	641278	64.1278		338504	33.8504
Organic Substrate, Halogen-free		Plastics/polymers	4,4'-dihydroxy-3,3',5,5'-tetramethylbiphenyl diglycidyl ether	85954-11-6	0.0192355	g	12908	1.2908		6813	0.6813
Organic Substrate, Halogen-free		Plastics/polymers	Phenolic Polymer Resin, Epikote 155	9003-36-5	0.24300989	g	163072	16.3072		86076	8.6076
Organic Substrate, Halogen-free		Metals	Gold, metal	7440-57-5	0.00160942	g	1080	0.108		570	0.057
Organic Substrate, Halogen-free		Solvents, additives, and other materials	Silicon	7440-21-3	0.00043365	g	291	0.0291		153	0.0153
Organic Substrate, Halogen-free		Nickel (external applications only)	Nickel	7440-02-0	0.0163311	g	10959	1.0959		5784	0.5784
Organic Substrate, Halogen-free		Glass	Fibrous-glass-wool	65997-17-3	0.17425952	g	116937	11.6937		61724	6.1724
Organic Substrate, Halogen-free		Plastics/polymers	Other acrylic resins	-	0.02551222	g	17120	1.712		9036	0.9036
Organic Substrate, Halogen-free		Plastics/polymers	Other acrylic/epoxy resin mixture	-	0.01700765	g	11413	1.1413		6024	0.6024
Silicon Semiconductor Die	0.026					g					
Silicon Semiconductor Die		Solvents, additives, and other materials	Other miscellaneous substances (less than 5%)	-	0.00052	g	20000	2		184	0.0184
Silicon Semiconductor Die		Glass	Silicon, doped	-	0.02548	g	980000	98		9025	0.9025
Bonding Wire, PdCu	0.0055					g					
Bonding Wire, PdCu		Metals	Copper, metal	7440-50-8	0.0053955	g	981000	98.1		1911	0.1911
Bonding Wire, PdCu		Metals	Gold, metal	7440-57-5	0.0000055	g	1000	0.1		1	0.0001
Bonding Wire, PdCu		Metals	Palladium, metal	7440-05-3	0.000099	g	18000	1.8		35	0.0035

LINKS

MCD LINK	
NXP website	http://www.nxp.com
GENERAL ENVIRONMENTAL COMPLIANCE LINKS	
RoHS signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ROHS-DECLARATION.pdf
China RoHS	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/china-rohs:ENV_CHINA_ROHS_STRATEGY
REACH signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf
ELV signed letter	http://www.nxp.com/files/corporate/doc/support_info/NXP-ELV-STATEMENT.pdf
Conflict Minerals statement	http://www.nxp.com/files/corporate/doc/support_info/NXP-STATEMENT-CONFLICT-MINERALS.pdf
NXP ENVIRONMENTAL INFORMATION	
Environmental Compliance website	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization:ABUENVPRFPRDX
FAQ	http://www.nxp.com/about/corporate-responsibility/environmental-compliance-organization/eco-product-faqs:ENVIRON_FAQ
Technical Service Request	http://www.nxp.com/support/sales-and-support:SUPPORTHOME
LINKS TO BLANK IPC1752 FORMS	
Blank IPC1752 v1.1 Form	http://www.NXP.com/files/abstract/corporate/ehs_epp/IPC-1752-2_v1.1_MCD_Template.pdf

IPC1752 XML LINKS

http://www.freescale.com/mcds/SPC5777CSK3MME3_IPC1752_v11.xml

http://www.freescale.com/mcds/SPC5777CSK3MME3_IPC1752A.xml