



S32K3x4-Q172 General-Purpose Development Board

S32K3X4EVB-Q172

Archived

This page contains information on a product that is no longer manufactured (discontinued). Specifications and information herein are available for historical reference only.

Last Updated: Dec 6, 2024


This development board is no longer manufactured. NXP will maintain support for this product but recommends the [S32K3X4EVB-T172](#) Board for optimized performance and support.

The S32K3X4EVB-Q172 is an evaluation and development board for general-purpose industrial and automotive applications.

Based on the 32-bit Arm®Cortex®-M7 S32K3 MCU in a 172 HDQFP package, the S32K3X4EVB-Q172 offers dual cores configured in lockstep mode, ASIL D safety hardware, HSE security engine, OTA support, advanced connectivity and low power.

The S32K3X4EVB-Q172 offers a standard-based form factor compatible with the Arduino® UNO pin layout, providing a broad range of expansion board options for quick application prototyping and demonstration.

S32K3X4EVB-Q172 Block Diagram Block Diagram



S32K3 Family Features Block Diagram

K311	K312	K314	Common Features	K322	K324	K341	K342	K344	K328	K338	K348	K358
1 x Arm® Cortex-M7 @120 MHz		1x Cortex-M7 @240MHz	AEC-Q100, 125 °C, 3,3/5 V	2 x Cortex-M7 @240 MHz		1 Lockstep Cortex-M7 @ 240 MHz			2 x Cortex-M7 @ 240 MHz	3 x Cortex-M7 @ 240 MHz	1 LS Cortex-M7 @ 240 MHz	1 LS Cortex-M7 + 1 Cortex-M7 @ 240 MHz
1 MB Flash	2 MB Flash	4 MB Flash	HSE-B Crypto Security Engine	2 MB Flash	4 MB Flash	1 MB Flash	2 MB Flash	4 MB Flash	8 MB Flash			
128 K SRAM	192 K SRAM	512 K SRAM	FOTA (Firmware Over-the-Air)	256 k SRAM	512 k SRAM	256 k SRAM	256 k SRAM	512 k SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM	1152 KB SRAM
up to 84 I/Os	up to 143 I/Os	up to 218 I/Os	Low-Power Operating Modes and Peripherals (LP UART, FlexIO)	up to 143 I/Os	up to 218 I/Os	up to 143 I/Os	up to 143 I/Os	up to 218 I/Os	up to 218 I/Os			
16-ch, eDMA		32-ch, eDMA	ASIL B/D Safety: (ECC Memories, MPU, CRC, Watchdogs)	32-ch, eDMA		32-ch, eDMA		32-ch, eDMA				
3 x CAN (3 x FD)	6 x CAN (6 x FD)		100 Mbit/s Ethernet (TSN)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	4 x CAN (4 x FD)	4 x CAN (4 x FD)	6 x CAN (6 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)	8 x CAN (8 x FD)
			100 Mbit/s Ethernet (TSN)	100 Mbit/s Ethernet (TSN)					1 Gbit/s Ethernet (TSN)			
2 x I2C	2 x I2C	2 x I2C	eMIOS Timers, Analogue Comparator, Logic Control Unit, Body Cross Triggering Unit, Trigger Mux	2 x I2C	2 x I2C	2 x I2C	2 x I2C	2 x I2C	2 x I2C			
4 x SPI*		6 x SPI*	JTAG	4 x SPI*	6 x SPI*	4 x SPI*	4 x SPI*	6 x SPI*	6 x SPI*			
2 x 24-ch, 12-bit ADC		3 x 24-ch, 12-bit ADC	S32 Design Studio IDE	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	2 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC	3 x 24-ch, 12-bit ADC			
			Quad SPI	2 x SAI (FS)					2 x SAI (FS)			
			Real-Time Drivers (AUTOSAR® and Non-AUTOSAR)	Quad SPI					Quad SPI + SDHC (SDIO)			
LOFP-48	HDQFP-172		Security FW Safety Software Framework Application Software	HDQFP-172					HDQFP-172			
HDQFP-100				HDQFP-100		HDQFP-100	HDQFP-100					
				MAPBGA-257				MAPBGA-257	MAPBGA-289			

View additional information for [S32K3x4-Q172 General-Purpose Development Board](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2025 NXP B.V.