

APPLICANT : Sewang Hitech Co., Ltd.

ADDRESS: 30-11, Singok-ro, Gochon-eup,

Gimpo-si, Gyeonggi-do, Korea

PAGE: 1 of 11

REPORT NO. RT20R-S3195-E DATE: Jun. 18, 2020

SAMPLE DESCRIPTION : The following submitted sample(s) said to be:-

NAME/TYPE OF PRODUCT : Q3-6633

NAME OF MATERIAL : Silicone Based

SAMPLE ID NO. : RT20R-S3195

ITEM NO. : Q3-6633

MANUFACTURER/VENDOR : Sewang Hitech Co., Ltd.

SAMPLE RECEIVED : Jun. 12, 2020

TESTING DATE : Jun. 12, 2020 ~ Jun. 18, 2020

TEST METHOD(S) : Please see the following page(s).
TEST RESULT(S) : Please see the following page(s).

Approved by,

Authorized by,

Authenticity check

Jade Jang / Lab. Technical Manager

2628

Bo Park / Lab. General Manager

Intertek Testing Services Korea Ltd.



<sup>\*</sup> Note 1 : The test results presented in this report refer only to the object tested.

<sup>\*</sup> Note 2 : This report shall not be reproduced except in full without the written approval of the testing laboratory.

<sup>\*</sup> Note 3 : The item no. is assigned by client and indicated according to their requirement and guarantee letter.



PAGE: 2 of 11 DATE: Jun. 18, 2020

REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

TEST ITEM	UNIT	TEST METHOD	MDL	RESULT
Cadmium (Cd)	mg/kg	With reference to IEC 62321-5 Edition 1.0 : 2013,	0.5	N.D.
Lead (Pb)	mg/kg	by acid digestion and determined by ICP-OES	5	N.D.
Mercury (Hg)	mg/kg	With reference to IEC 62321-4 Edition 1.0 : 2013, by acid digestion and determined by ICP-OES	2	N.D.
Hexavalent Chromium (Cr <sup>6+</sup> )	mg/kg	With reference to IEC 62321-7-2 Edition 1.0: 2017, by alkaline/toluene digestion and determined by UV-VIS Spectrophotometer	8	N.D.
Polybrominated Biphenyl (PBBs)	_			T
Monobromobiphenyl	mg/kg		5	N.D.
Dibromobiphenyl	mg/kg		5	N.D.
Tribromobiphenyl	mg/kg		5	N.D.
Tetrabromobiphenyl	mg/kg	With reference to	5	N.D.
Pentabromobiphenyl	mg/kg	IEC 62321-6 Edition 1.0 : 2015,	5	N.D.
Hexabromobiphenyl	mg/kg	by solvent extraction and	5	N.D.
Heptabromobiphenyl	mg/kg	determined by GC/MS	5	N.D.
Octabromobiphenyl	mg/kg		5	N.D.
Nonabromobiphenyl	mg/kg		5	N.D.
Decabromobiphenyl	mg/kg		5	N.D.
Polybrominated Diphenyl Ether (				
Monobromodiphenyl ether	mg/kg		5	N.D.
Dibromodiphenyl ether	mg/kg		5	N.D.
Tribromodiphenyl ether	mg/kg		5	N.D.
Tetrabromodiphenyl ether	mg/kg	With reference to	5	N.D.
Pentabromodiphenyl ether	mg/kg	IEC 62321-6 Edition 1.0 : 2015,	5	N.D.
Hexabromodiphenyl ether	mg/kg	by solvent extraction and	5	N.D.
Heptabromodiphenyl ether	mg/kg	determined by GC/MS	5	N.D.
Octabromodiphenyl ether	mg/kg	]	5	N.D.
Nonabromodiphenyl ether	mg/kg	]	5	N.D.
Decabromodiphenyl ether	mg/kg	]	5	N.D.

Tested by: Jooyeon Lee, Seulgi Park, Jessica Kang

Notes: mg/kg = ppm = parts per million

< = Less than

N.D. = Not detected ( <MDL )
MDL = Method detection limit

Intertek Testing Services Korea Ltd.







REPORT NO. RT20R-S3195-E

# **TEST REPORT**

PAGE: 3 of 11 DATE: Jun. 18, 2020

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

TEST ITEM	UNIT	TEST METHOD	MDL	RESULT
Bromine (Br)	mg/kg	With reference to EN 14582, by oxygen combustion with bomb and determined by IC	30	N.D.
Chlorine (Cl)	mg/kg	With reference to EN 14582, by oxygen combustion with bomb and determined by IC	30	N.D.
Fluorine (F)	mg/kg	With reference to EN 14582, by oxygen combustion with bomb and determined by IC	30	N.D.
lodine (I)	mg/kg	With reference to EN 14582, by oxygen combustion with bomb and determined by IC	30	N.D.
Beryllium (Be)	mg/kg	With reference to US EPA 3052, by acid digestion and determined by ICP-OES	2	N.D.
Antimony (Sb)	mg/kg	With reference to US EPA 3052, by acid digestion and determined by ICP-OES	2	N.D.
Hexabromocyclododecane (HBCDD)	mg/kg	With reference to IEC 62321-9(111/409/CD), by solvent extraction and determined by LC/MS and GC/MS	10	N.D.
Perfluorooctanoic acid (PFOA)	mg/kg	With reference to US EPA 3550C/8321B, by ultrasonic extraction and determined by LC/MS or LC/MS/MS	0.1	N.D.
Perfluorooctane sulfonate (PFOS)	mg/kg	With reference to US EPA 3550C/8321B, by ultrasonic extraction and determined by LC/MS or LC/MS/MS	0.1	N.D.

Tested by: Hyojoo Kim, Jooyeon Lee, Jessica Kang

Notes: mg/kg = ppm = parts per million

< = Less than

N.D. = Not detected ( <MDL )
MDL = Method detection limit

Intertek Testing Services Korea Ltd.







PAGE: 4 of 11 DATE: Jun. 18, 2020

REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

TEST ITEM	CAS NO.	UNIT	TEST METHOD	MDL	RESULT
Phthalates					
Dibutyl phthalate (DBP)	84-74-2	mg/kg		50	N.D.
Di(2-ethylhexyl) phthalate (DEHP)	117-81-7	mg/kg		50	N.D.
Di-n-octyl phthalate (DNOP)	117-84-0	mg/kg		50	N.D.
Diisononyl phthalate (DINP)	28553-12-0 68515-48-0	mg/kg		100	N.D.
Diisodecyl phthalate (DIDP)	26761-40-0 68515-49-1	mg/kg		100	N.D.
Benzyl butyl phthalate (BBP)	85-68-7	mg/kg	With reference to IEC 62321-8 Edition 1.0 : 2017,	50	N.D.
Diisobutyl phthalate (DIBP)	84-69-5	mg/kg	by solvent extraction and determined by GC/MS	50	N.D.
Dimethyl phthalate (DMP)	131-11-3	mg/kg		50	N.D.
Diethyl phthalate (DEP)	84-66-2	mg/kg		50	N.D.
Di-n-pentyl phthalate (DPP)	131-18-0	mg/kg		50	N.D.
Di-n-hexyl phthalate (DNHP)	84-75-3	mg/kg		50	N.D.
1,2-Benzenedicarboxylic acid, di-C6-8-branched alkyl esters, C7-rich (DIHP)	71888-89-6	mg/kg		50	N.D.

Tested by: Jessica Kang

Notes: mg/kg = ppm = parts per million

< = Less than

N.D. = Not detected ( <MDL )
MDL = Method detection limit

Intertek Testing Services Korea Ltd.







REPORT NO. RT20R-S3195-E

### **TEST REPORT**

PAGE: 5 of 11 DATE: Jun. 18, 2020

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

					ı
TEST ITEM	CAS NO.	UNIT	TEST METHOD	MDL	RESULT
1,2-Benzenedicarboxylic acid, di-C7-11-branched and linear alkyl esters (DHNUP)	68515-42-4	mg/kg	With reference to	50	N.D.
Di(2-methoxyethyl) phthalate (DMEP)	117-82-8	mg/kg	Edition 1.0 : 2017, by solvent extraction and determined by	50	N.D.
Diisopentyl phthalate (DIPP)	605-50-5	mg/kg	GC/MS	50	N.D.

Tested by: Jessica Kang

Notes: mg/kg = ppm = parts per million

< = Less than

N.D. = Not detected ( <MDL )
MDL = Method detection limit

\* View of sample as received;-



Intertek Testing Services Korea Ltd.








PAGE: 6 of 11 DATE: Jun. 18, 2020

REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION: Q3-6633



Remarks:
\*1: List of appropriate acid:

_	2 · List of appropriate dold ·						
	Material	Acid added for digestion					
	Polymers	HNO <sub>3</sub> , HCl, HF, H <sub>2</sub> O <sub>2</sub> , H3BO <sub>3</sub>					
	Metals	HNO₃, HCl, HF					
	Electronics	HNO <sub>3</sub> , HCl, H <sub>2</sub> O <sub>2</sub> , HBF <sub>4</sub>					

<sup>\*2 :</sup> The samples were dissolved totally by pre-conditioning method according to above flow chart.

Intertek Testing Services Korea Ltd.








PAGE: 7 of 11 DATE: Jun. 18, 2020

REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633



# Intertek Testing Services Korea Ltd.








PAGE: 8 of 11
REPORT NO. RT20R-S3195-E
DATE: Jun. 18, 2020

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633



<sup>\*\*</sup> Remarks : The samples were dissolved totally by pre-conditioning method according to above flow chart.

Intertek Testing Services Korea Ltd.







PAGE: 9 of 11 DATE: Jun. 18, 2020


REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

# Flow Chart (HBCDD) Receipt Sample preparation

Extraction

Concentration



# Intertek Testing Services Korea Ltd.







PAGE: 10 of 11 DATE: Jun. 18, 2020

REPORT NO. RT20R-S3195-E

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633

Receipt
Sample preparation
Loading in a vial
Methanol loading
Ultrasonication
Filtering & Cleaning
Make up (Methanol)

Analyzed by LC/MS or LC/MS/MS

Report

Intertek Testing Services Korea Ltd.












PAGE: 11 of 11
REPORT NO. RT20R-S3195-E DATE: Jun. 18, 2020

SAMPLE ID NO. : RT20R-S3195 SAMPLE DESCRIPTION : Q3-6633



Except where explicitly agreed in writing, all work and services performed by Intertek is subject to our standard Terms and Conditions which can be obtained at our website: http://www.intertek.com/terms/. Intertek's responsibility and liability are limited to the terms and conditions of the agreement.

This report is made solely on the basis of your instructions and / or information and materials supplied by you and provide no warranty on the tested sample(s) be truly representative of the sample source. The report is not intended to be a recommendation for any particular course of action, you are responsible for acting as you see fit on the basis of the report results. Intertek is under no obligation to refer to or report upon any facts or circumstances which are outside the specific instructions received and accepts no responsibility to any parties whatsoever, following the issue of the report, for any matters arising outside the agreed scope of the works. This report does not discharge or release you from your legal obligations and duties to any other person. You are the only one authorized to permit copying or distribution of this report (and then only in its entirety). Any such third parties to whom this report may be circulated rely on the content of the report solely at their own risk.

This report shall not be reproduced, except in full.

This report is related to the scope of Korea Laboratory Accreditation Scheme.

### Intertek Testing Services Korea Ltd.



