



# i.MX RT1040 Crossover MCU with Arm® Cortex®-M7 Core Operating Up to 600 MHz and Extended Temperature Range

## i.MX-RT1040


Last Updated: Apr 11, 2024

i.MX RT1040 Crossover MCUs are based on the Arm® Cortex®-M7 core for real-time performance and high integration for Industrial and IoT applications.

The i.MX RT1040 CM7 operates at up to 600 MHz with 512 KB on-chip RAM that can be configured as TCM or general-purpose. The family offers various memory interfaces and a wide range of connectivity interfaces including UART, SPI, I<sup>2</sup>C, USB and CAN. The i.MX RT1040 provides additional flexibility with 169 BGA compact packages and an extended temperature range up to 125°C.

The i.MX RT1040 family is supported by the [MCUXpresso ecosystem](#), which includes an SDK, a choice of IDEs, and secure provisioning and configuration tools to enable rapid development

# i.MX RT1040 MCU Block Diagram



View additional information for [i.MX RT1040 Crossover MCU with Arm® Cortex®-M7 Core Operating Up to 600 MHz and Extended Temperature Range](#).

**Note:** The information on this document is subject to change without notice.

[www.nxp.com](http://www.nxp.com)

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.