## INTEGRATED CIRCUITS

# APPLICATION NOTE

#### **ABSTRACT**

The objective of this application note is to show the specifics of Philips SC16C750 and the comparison to other industry standard 16C750. This application note is also applicable to Philips SC16C752.

# AN10165 SC16C750 application note

Author: Dong Nguyen 2003 Jun 11





Philips Semiconductors Application note

# SC16C750 application note

AN10165

The objective of this application note is to show the differences between Philips SC16C750 and other industry standard devices from TI. In most cases, the Philips SC16C750 is a direct drop-in replacement, but because software drivers vary from application to application, occasionally a minor software change may be required. This application note will point out areas to check if proper operation is not observed.

This application note is also applicable to Philips SC16C752.

#### 1. READING THE ISR REGISTER

Whenever reading the ISR register, the LCR bit 7 must be set to 0.

#### 2. HARDWARE FLOW CONTROL USING MCR BIT 5

Hardware flow control using MCR register bit 5 is not supported by Philips SC16C750. Hardware flow control is supported by another register called Enhanced Features Register (EFR) bit 7 and bit 6.

#### 3. CLEARING OF TRANSMIT EMPTY INTERRUPT

If the transmit FIFO is empty and the interrupt on transmit FIFO empty is enabled (IER bit 1), the UART will generate a hardware interrupt. This hardware interrupt can be cleared by either reading the ISR register, or by writing a byte into the transmit FIFO. However, if the software does not write at least one byte into the transmit FIFO, then the transmit empty interrupt cannot be set again.

#### 4. ADDITIONAL ENHANCED REGISTER

Our 16C750 device includes an enhanced register that is not available in the competitor devices. This extra register allows users to do auto hardware and software flow control (available on the TI16C752 only).

#### 5. CLEARING RECEIVE INTERRUPT BY READING THE RECEIVE CHARACTER

If receive holding interrupt is enabled (IER register bit 0 = 1), upon receiving a character the UART will generate a receive interrupt. To clear this interrupt the software must read the ISR register and the received character.

#### 6. DISABLE RECEIVE DATA TIMEOUT INTERRUPT

When the receive holding interrupt is enabled (IER bit 0 = 1), and the receiver receives a number of characters, the software must read the receive FIFO before the receive timeout interrupt is generated (refer to the data sheet to calculate the timeout). If the receive timeout interrupt is generated, the software must read all the data in the receive FIFO before disabling the receive ready interrupt.

### 7. SETTING TCR REGISTER (SC16C752 ONLY)

If the TCR register is used to set-up the trigger levels for hardware or software flow control, FCR register bit [7:6] must be set to a value other than 11b. Otherwise the receiver will continuously send out garbage data once the RTS signal is negated or XOFF control character has been sent.

2003 Jun 11 2

Philips Semiconductors Application note

# SC16C750 application note

AN10165

#### **Digital DataComm**

Web address: www.philipslogic.com

Email address: DataCom.tech-support@philips.com

#### **Definitions**

**Short-form specification** — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Application information** — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

#### **Disclaimers**

**Life support** — These products are not designed for use in life support appliances, devices or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

#### **Contact information**

For additional information please visit

http://www.semiconductors.philips.com. Fax: +31 40 27 24825

For sales offices addresses send e-mail to: sales.addresses@www.semiconductors.philips.com

© Koninklijke Philips Electronics N.V. 2003 All rights reserved. Printed in U.S.A.

Date of release: 06-03

Document order number: 9397 750 10323

Let's make things better.

Philips Semiconductors



