

AN13647

ICODE 3 and ICODE 3 TagTamper features and hints

Rev. 1 — 29 March 2024

Application note

Document information

Information	Content
Keywords	ICODE 3, ICODE 3 TagTamper, implementation hints
Abstract	This document introduces features and hints for application development on the ICODE 3 and ICODE 3 TagTamper.



1 Introduction

The application note describes a few features of the ICODE 3 and ICODE 3 TagTamper (ICODE 3 TT) products. The document is a complement to ICODE 3 (TagTamper) data sheet [\[1\]](#).

1.1 Purpose and scope

The application note is addressed to developers of applications based on ICODE 3 and ICODE 3 TagTamper (ICODE 3 TT) products.

The document is focused on the security mechanisms used to protect the data stored in ICODE 3 and ICODE 3 TagTamper.

Note: For more details on ICODE 3 and ICODE 3 TT, refer to [\[1\]](#) and [\[3\]](#).

1.2 Disclaimer

ICODE 3 and ICODE3 TT are not security certified products. Terms like locking, read-only, fraud protection, or security do not guarantee protection against any attack to circumvent a feature. Depending on the value of the assets that need protection, consider using Common Criteria certified products. For example, consider the security features that demonstrate some resistance to specific attacks during certification.

2 ASCII mirroring

With ASCII mirroring, information in ASCII code is reflected over the physical memory of the IC. The ICODE 3 and ICODE 3 TagTamper (ICODE 3 TT) use ASCII mirroring on the following:

- 8 bytes UID
- 8 bytes UID + 3 bytes counter
- 8 bytes UID + 3 bytes counter + 4 bytes TagTamper message (ICODE 3 TT only)
- 8 bytes UID + 3 bytes counter + 4 bytes TagTamper message + 1 byte current TagTamper status (ICODE 3 TT only)

If the mirrored information is a combination (for example UID + counter), the "x" character (78h ASCII code, 1-byte length) is added as separator between the items.

Note: In ASCII format, the byte length of the combinations doubles, excluding separators.

The ICODE 3/ICODE 3 TT responds to a READ or FAST READ command to the involved user memory pages with the virtual content in ASCII code including:

- The UID,
- The NFC counter value,
- The TagTamper message (ICODE 3 TT only).

[Figure 1](#) shows the example of ICODE 3 configured to mirror its UID + Counter to the end of the URL `https://www.nxp.com/?`

- NFC_MIRROR_SEL bits are set to 010b.
- NFC_MIRROR_BLK defines the first block within the user memory where the NFC mirror starts. In the example, NFC mirror starts at block number 5.
- NFC_MIRROR_BYTE defines the byte within the defined block in NFC_MIRROR_BLK where the mirror starts. In this example, the byte is 0.

Note: The ASCII code is part of NDEF message record. The size or length of the NDEF message and NDEF record must be defined so the URL including the mirrors is accounted for. For example:

Protocol field (1 byte) + `nxp.com/?` (9 bytes) + UID (16 bytes) + separation (1 byte) + counter (6 bytes) = 33 bytes (0x21)

Block [Hex]	Byte 0	Byte 1	Byte 2	Byte 3	ASCII
00	E1	40	20	00	á@
01	03	25	D1	01	\$Ñ
02	21	55	02	6E	U□n
03	78	70	2E	63	xp.c
04	6F	6D	2F	3F	om/?
05	45	30	30	34	E004
06	30	31	32	30	0120
07	30	30	33	35	0035
08	42	39	46	32	B9F2
09	78	30	30	30	x000
0A	30	31	35	FE	0015p
.

- Capability container
- NDEF message header
- NDEF record
- UID mirror
- Separator
- Counter mirror

Figure 1. UID + Counter ASCII mirror

3 TagTamper feature

The ICODE 3 TagTamper (ICODE 3 TT) can detect and store the opening event of a connected TagTamper loop. The TagTamper detection can be enabled or disabled by setting the "OTP_TT_EN" bit accordingly. The ICODE 3 TT supports two TagTamper statuses:

- Actual status: the state of the TagTamper loop at the given moment.
- Stored status: the state permanently stored at the first detection of the opened TagTamper loop.

The TT_SHOW_STATUS byte is used to configure how the ICODE 3 TT responds to a READ TT command, and the behavior of the NFC mirror feature.

If the ICODE 3 TT is configured to store the first detection of an opened TagTamper loop (stored status of TagTamper), you can program a 4-byte customizable open message TT_OPEN_MSG. The TT_OPEN_MSG can be mirrored if ASCII mirroring is enabled.

Note: To avoid fraud, use an encrypted message which is not predictable. For example, use an AES_CMAC calculated string including the unique identifier (UID) of the tag, and a constant. Next, use defined bytes from AES_CMAC calculated string. For more details and examples, refer to [\[2\]](#).

4 Counter

ICODE 3 and ICODE 3 TT support the 24-bit counter feature.

Two counter modes are available: NFC counter and command-based counter. The COUNTER MODE bit is used to set the mode in the configuration memory. For more details, refer to [\[1\]](#).

If the counter mode is set to command-based, the WRITE SINGLE BLOCK command to block 75 is used to increment the counter. The counter can be incremented by values of one to 0xFF. Here is how:

- If password protection is enabled, send the SET PASSWORD command with the read password before issuing the WRITE SINGLE BLOCK command.
- Set the PROT byte in block 75 to 0x80.
- To increment the counter by one, use WRITE SINGLE BLOCK command to block 75 with a value of 0x01.
- To increment the counter by a value in the range of one to 0xFF, use the WRITE SINGLE BLOCK command with a value in the range of 0x01 to 0xFF.

If the counter mode is set to NFC counter (COUNTER MODE bit set to one), the ICODE 3 and ICODE 3 TT automatically increase the counter when tapped, for more information refer to [\[1\]](#)

The ICODE 3 and ICODE 3 TT also support mirroring of the current counter value. Refer to [Section 2](#) and [\[1\]](#).

5 References

- [1] Data sheet - SL2S3003/SL2S3003TT ICODE 3 (TagTamper)
- [2] Application note - AN6121 - NTAG Secure Services Architecture and API
- [3] Application note - AN13428 - ICODE Coil Design Guide

6 Revision history

Table 1. Revision history

Document ID	Release date	Description
AN13647 v.1	29 March 2024	• Initial version

Legal information

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP B.V. — NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

ICODE and I-CODE — are trademarks of NXP B.V.

Tables

Tab. 1. Revision history8

Figures

Fig. 1. UID + Counter ASCII mirror 4

Contents

1	Introduction	2
1.1	Purpose and scope	2
1.2	Disclaimer	2
2	ASCII mirroring	3
3	TagTamper feature	5
4	Counter	6
5	References	7
6	Revision history	8
	Legal information	9

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.
