

Freescale Semiconductor

Engineering Bulletin

Document Number: EB729

Rev. 0, 03/2010

Migrating Single-Chip Applications from MC68HC711E9 to MC68HC711E20

1 Introduction

This engineering bulletin explains how existing users of the MC68HC711E9 could migrate to the MC68HC711E20.

Here are the items to consider when migrating from the MC68HC711E9 to the MC68HC711E20:

- Pin assignments and packages are identical.
- The register set has two differences (see Section 2, "Differences in Registers").
- The memory maps are different but all code from the MC68HC711E9 will run on the MC68HC711E20 (see Section 3, "Differences in Memory Maps"). Customers may want to fill unused RAM and flash memory with illegal opcode if they are worried about code runaway.
- Electrical specifications are identical.

For complete information on the MC68HC711E9 and the MC68HC711E20, refer to *M68HC11E Family Technical Data* (document number M68HC11E) available on the Freescale web site, Freescale.com.

Contents

l	Introduction	í
2	Differences in Registers	2
3	Differences in Memory Maps	2





Differences in Registers

2 Differences in Registers

The SCI system in the MC68HC711E20 MCU has an enhanced SCI baud rate generator. A divide-by-39 stage has been added. It is enabled by an extra bit (SCP2) in the BAUD register. This increases the available baud rate selections.

PPROG is the combined EPROM/OTPROM and EEPROM programming register on all devices with EPROM/OTPROM except the MC68HC711E20. For the MC68HC711E20, there is a separate register for EPROM/OTPROM programming called the EPROG register.

3 Differences in Memory Maps

There are 256 more bytes of RAM in the MC68HC711E20. There is no conflict in single-chip mode: MC68HC711E9 code should port directly to the MC68HC711E20 device with no modification.

An EPROM programming algorithm change is required because of register changes. (The programmer vendor should provide an MC68HC711E20 algorithm.)

The MC68HC711E20 has a separate register (EPROG) to program EPROM.

Memory Type	MC68HC711E9 Size	MC68HC711E9 Range	MC68HC711E20 Size	MC68HC711E20 Range
Boot ROM		BF00		BF00
RAM	512 B	0000-01FF	768 B	0000-02FF
EEPROM	512 B	B600-B7FF	512 B	B600-B7FF
EPROM	12 KB	D000-FFFF	20 KB	9000–AFFF D000–FFFF

NOTE

Expanded mode operation may conflict with the extra 8K EPROM: internal memory from 0x9000–0xAFFF will conflict with external memory if decoded in this space.







Figure 1. Memory Map for MC68HC711E9



^{* 20} Kbytes ROM/EPROM are contained in two segments of 8 Kbytes and 12 Kbytes each.

Figure 2. Memory Map for MC68HC711E20



How to Reach Us:

Home Page:

www.freescale.com

Web Support:

http://www.freescale.com/support

USA/Europe or Locations Not Listed:

Freescale Semiconductor, Inc.
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
+1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor China Ltd. Exchange Building 23F No. 118 Jianguo Road Chaoyang District Beijing 100022 China +86 10 5879 8000 support.asia@freescale.com

For Literature Requests Only: Freescale Semiconductor Literature Distribution Center 1-800-441-2447 or 303-675-2140 Fax: 303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics as their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

Freescale[™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2010. All rights reserved.

Document Number: EB729

Rev. 0 03/2010

