

EIQTRN

eIQ Toolkit Release Notes

Rev. 20 — 22 April 2025

Release notes

Document information

Information	Content
Keywords	Machine Learning, AI, TensorFlow, Neural Networks, eIQ, Computer Vision
Abstract	This document contains information about the content, new features, and limitations of the eIQ Toolkit package. eIQ Toolkit is a machine learning environment which enables its users to train and run machine learning models as efficiently as possible on NXP hardware.



1 Overview

This document contains information about the content, new features, and limitations of the eIQ Toolkit package. The eIQ Toolkit is a machine-learning environment which enables its users to train and run machine-learning models on NXP hardware as efficiently as possible.

Table 1. Component overview

Component	Version
eIQ Portal	2.15.1
Model Tool	2.11.0
eIQ Time Series Studio	1.2.5
eIQ Converter	2.8.0
eIQ Converter (ONNX plug-in)	2.8.0
eIQ Converter (RTM plug-in)	2.8.0
eIQ Converter (TF Lite plug-in)	2.9.0
eIQ Converter (Arm Vela plug-in)	1.2.0
eIQ Converter (Neutron plug-in)	1.1.0
eIQ Converter (ONNX2Tflite plug-in)	1.0.0
eIQ Datastore	2.4.0
eIQ Importer	2.4.0
DeepViewRT	2.4.46
Modelrunner	2.6.0
Modelrunner Client	1.3.0
Modeleditor	1.1.0
eIQ Trainer	2.8.2
eIQ Validator	2.8.0
eIQ Python	2.8.5
Python	3.10.11
Python – Tensorflow	2.16.2
Python – ONNX	1.15.0
Python – ONNX Runtime	1.17.3
Extension - Arm Vela	1.3.1
Extension - Explainability	0.4.0
Extension - Vision Pipeline	1.4.0-rc2
Extension - Watermarking	1.2.3
Extension - TAO	0.0.1

2 References

This release includes the following references and additional information:

- *eIQ Toolkit User's Guide* (document EIQTUG)
- *eIQ Toolkit Release Notes* (document EIQTRN)

3 1.15 Features and fixes

- **General Updates**
 - Added modelrunner for the Yocto BSP version LF_6.12.3_1.0.0
- **Neutron Converter**
 - Added Neutron Converter for MCU SDK 25.03
 - Updated Neutron Converter Yocto BSP version LF_6.12.3_1.0.0 (Linux only)
 - Neutron Converter for i.MX95 with **NXP i.MX Yocto BSP LF6.6.52_2.2.x** is available only in **eIQ Toolkit 1.14**.
- **eIQ Time Series Studio**
 - Added version 1.2.5

4 Known issues and workarounds

The following list specifies the current known issues (which may impact the user experience) and workarounds:

- Do not use batch sizes of less than 4 in eIQ Portal.
- Validation may not work when the proxy settings are enabled.
- Issues are observed for the H5/TF Lite to ONNX conversions due to differences between the 2 formats and third-party library usage.
- Issues are observed in quantized conversions from the TF SavedModel format.
- Unable to quantize LSTM layer in TF Lite.
- CUDA/GPU acceleration is supported only on Linux and through WSL on Windows due to TensorFlow. This means that the Linux installer is much bigger than the Windows installer, because it includes CUDA and the eIQ Toolkit for Windows is not accelerated on the GPU.
- Direct export for the eIQ Neutron NPU and Ethos-U (i.MX93) in the eIQ Portal (BYOM) is not supported. The model must be exported to quantized TF Lite and then converted using the Model Tool.
- When using the Neutron Converter plugin, you may try to pass the “input” or “output” parameter through the “custom options” argument and not the standard way. As this would cause conflicts with the default behavior, the plugin will disregard these parameters and warn you about it.
- Due to a TensorFlow issue, when training a detection model on Ubuntu using GPU, the GUI may show an error. The workaround is to either disable the GPU so that the model is trained on the CPU instead or simply trying to run the training again until it succeeds.
- During model validation, the process may hang sometimes when the validation is executed before everything is loaded properly. Wait for a few seconds on the validation screen before starting it.
- When using the Neutron Converter with i.MX95 devices, while loading firmware for models in the `tflite.Interpreter()` call, the correct sequence is:

```
Interpreter1 = tflite.Interpreter(model1, ...)
Interpreter1.invoke()
Interpreter2 = tflite.Interpreter(model2, ...)
Interpreter2.invoke()
```

- When converting large models (e.g. yolov8m) using the Neutron Converter with i.MX95 devices, it may fail with the “internal error” message. The conversion will work if you switch to an x86 host with a bigger system memory (64 GB).

5 Revision history

Table 2. Revision history

Document ID	Release date	Description
EIQTRN v20.0	22 April 2025	Updated release of eIQ Toolkit 1.15.1
EIQTRN v19.0	7 April 2025	Updated release of eIQ Toolkit 1.15.0
EIQTRN v18.0	20 January 2025	Updated release of eIQ Toolkit 1.14.0
EIQTRN v17.0	28 November 2024	Updated release of eIQ Toolkit 1.13.3
EIQTRN v16.0	30 October 2024	Updated release of eIQ Toolkit 1.13.2
EIQTRN v15.0	25 October 2024	Updated release of eIQ Toolkit 1.13.1
EIQTRN v14.0	9 October 2024	Updated release of eIQ Toolkit 1.13.0
EIQTRN v13.0	3 June 2024	Updated release of eIQ Toolkit 1.12
EIQTRN v12.0	2 April 2024	Updated release of eIQ Toolkit 1.11
EIQTRN v11.0	10 January 2024	Updated release of eIQ Toolkit 1.10
EIQTRN v10.0	12 October 2023	Updated release of eIQ Toolkit 1.9
EIQTRN v9.0	3 July 2023	Updated release of eIQ Toolkit 1.8
EIQTRN v8.0	11 April 2023	Updated release of eIQ Toolkit 1.7
EIQTRN v7.0	1 February 2023	Updated release of eIQ Toolkit 1.6
EIQTRN v6.0	3 October 2022	Updated release of eIQ Toolkit 1.5.2
EIQTRN v5.0	8 July 2022	Updated release of eIQ Toolkit 1.4.5
EIQTRN v4.0	31 March 2022	Updated release of eIQ Toolkit 1.3.4
EIQTRN v3.0	18 January 2022	Updated release of eIQ Toolkit 1.2.5
EIQTRN v2.0	19 October 2021	Updated release of eIQ Toolkit 1.1.8
EIQTRN v1.0	24 June 2021	Updated release of eIQ Toolkit 1.0.5
EIQTRN v0.1	15 June 2021	Initial release of eIQ Toolkit 1.0.3

Legal information

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

HTML publications — An HTML version, if available, of this document is provided as a courtesy. Definitive information is contained in the applicable document in PDF format. If there is a discrepancy between the HTML document and the PDF document, the PDF document has priority.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP B.V. — NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Contents

1 Overview2

2 References3

3 1.15 Features and fixes4

4 Known issues and workarounds5

5 Revision history6

Legal information7

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.