

Android™ Release Notes

Contents

1 Release Description

i.MX android-10.0.0_2.0.0 is the GA (RFP) release for Android 10 on NXP's i.MX 8M Mini, i.MX 8M Nano, i.MX 8M Quad, i.MX 8QuadMax, and i.MX 8QuadXPlus applications processors.

i.MX android-10.0.0_2.0.0 release includes all necessary codes, documents, and tools to assist users in building and running Android 10 on the i.MX 8M Mini EVK, i.MX 8M Nano, i.MX 8M Quad EVK, i.MX 8QuadMax MEK, and i.MX 8QuadXPlus MEK Board.

The prebuilt images are also included for a quick trial on NXP i.MX 8M Mini EVK, i.MX 8M Nano, i.MX 8M Quad EVK, i.MX 8QuadMax MEK, and i.MX 8QuadXPlus MEK Board and Platforms.

This release includes all porting and enhancements based on the Android open source code.

Most of the deliveries in this release are provided in source code with the exception of some proprietary modules/libraries from third parties.

2 Supported Hardware SoC/Boards

The supported hardware system-on-chip (SoCs)/boards are listed as follows:

- i.MX 8M Mini EVK LPDDR4 Rev. C Board and Platform
- i.MX 8M Nano EVK DDR4 Board and Platform
- i.MX 8M Quad EVK Rev. A Board and Platform
- i.MX 8QuadMax (Silicon Revision B0) MEK Board and Platform
- i.MX 8QuadXPlus (Silicon Revision B0) MEK Board and Platform

3 Release Package Contents

The android10.0.0_2.0.0 release package includes the following software and documents.

Table 1. Release package contents

i.MX Android proprietary source code package	<ul style="list-style-type: none"> • imx-android-10.0.0_2.0.0.tar.gz: i.MX Android proprietary source code package to enable Android on i.MX boards. For example, Hardware Abstraction Layer implementation, hardware codec acceleration, etc.
Documents	<p>The following documents are included in android-10.0.0_2.0.0_docs.zip:</p> <ul style="list-style-type: none"> • <i>Android™ Quick Start Guide (AQSUG)</i>: A document that explains how to run the Android platform on an i.MX board using prebuilt images.

Table continues on the next page...

1 Release Description..... 1

2 Supported Hardware
SoC/Boards..... 1

3 Release Package
Contents..... 1

4 Features 2

5 Multimedia Codecs.....8

6 Extended Features..... 9

7 Change Logs..... 9

8 Known Issues and
Limitations.....9

9 Revision History..... 10



Table 1. Release package contents (continued)

	<ul style="list-style-type: none"> • <i>Android™ User's Guide</i> (AUG): A document describing procedures for configuring and building this release package. • <i>Android™ Release Notes</i> (ARN): A document that introduces key updates and known issues in this release. • <i>i.MX Android™ Security User's Guide</i> (ASUG): A document that describes how to do customization work on security features supported by i.MX Android software. • <i>i.MX Graphics User's Guide</i> (IMXGRAPHICUG): A document that describes GPU 2D API, Tools, Memory, and Application programming guidelines.
Prebuilt images	<p>You can test the Android platform with a prebuilt image on i.MX reference board before building any code:</p> <ul style="list-style-type: none"> • android-10.0.0_2.0.0_image_8mmevk.tar.gz: Prebuilt images with NXP extended features for the i.MX 8M Mini EVK board. • android-10.0.0_2.0.0_image_8mnevk.tar.gz: Prebuilt images with NXP extended features for the i.MX 8M Mini EVK DDR4 board. • android-10.0.0_2.0.0_image_8mqevk.tar.gz: Prebuilt images with NXP extended features for the i.MX 8M Quad EVK board. • android-10.0.0_2.0.0_image_8qmek.tar.gz: Prebuilt images with NXP extended features for the i.MX 8QuadMax/8QuadXPlus MEK board. <p>All prebuilt images are in a separate package. See the <i>Android™ Quick Start Guide</i> (AQSUG) and <i>Android™ User's Guide</i> (AUG) to choose the appropriate image.</p>

4 Features

Table 2. Features

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
Google Android 10 release	Y	Y	Y	Y	Y	Based on android-10.0.0_r32 release
Linux 5.4.3 kernel (merge with AOSP kernel)	Y	Y	Y	Y	Y	Based on Linux® OS BSP L5.4.3_1.0.0 release.
U-Boot	Y	Y	Y	Y	Y	v2019.04.
Trusty OS	Y	Y	Y	Y	Y	-
Graphic-HW	Y	Y	Y	Y	Y	VeriSilicon GC7000NanoUltr GPU with the 6.4.0.p2 driver for i.MX 8M Mini. VeriSilicon GC7000UL GPU with 6.4.0.p2 driver for i.MX 8M Nano EVK.

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
						VeriSilicon GC7000L GPU with 6.4.0.p2 driver for i.MX 8M Quad. VeriSilicon GC7000XSVX GPU with 6.4.0.p2 driver for i.MX 8QuadMax. VeriSilicon GC7000L GPU with 6.4.0.p2 driver for i.MX 8QuadXPlus.
Graphic-HW 3D acceleration	Y	Y	Y	Y	Y	OpenGL ES1.1/2.0 through GC7000NanoUltra for i.MX 8M Mini. OpenGL ES1.1/2.0/3.1 through GC7000UL for i.MX 8M Nano EVK. OpenGL ES1.1/2.0/3.1 through GC7000L for i.MX 8M Quad. OpenGL ES 1.1/2.0/3.1/3.2 through GC7000XSVX for i.MX 8QuadMax. OpenGL ES 1.1/2.0/3.1 via GC7000L for i.MX 8QuadXPlus.
Graphic-HW accelerated UI surface composition	Y	Y	Y	Y	Y	OpenGL ES2.0 through GC7000NanoUltra for i.MX 8M Mini. OpenGL ES3.1 via GC7000UL for i.MX 8M Nano EVK. OpenGL ES3.1 through GC7000L for i.MX 8M Quad. OpenGL ES 3.2 through GC7000XSVX for i.MX 8QuadMax. OpenGL ES 3.1 through GC7000L for i.MX 8QuadXPlus.
Boot source	SD/eMMC	SD/eMMC	SD/eMMC	SD/eMMC	SD/eMMC	-
SCFW	N	N	N	Y	Y	Version 1.2.10.1
SECO firmware	N	N	N	Y	Y	Version 2.3.1
Splash Screen	Y	Y	Y	Y	Y	-

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
UI (input)	Y	Y	Y	Y	Y	i.MX 8M Mini EVK, i.MX 8M Nano EVK, and i.MX 8M Quad EVK support USB Mouse and Multi-touch on the MIPI panel display. i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK support USB Mouse.
UI (display)	MIPI-DSI-to-HDMI/MIPI panel display	MIPI-DSI-to-HDMI/MIPI panel display	HDMI/MIPI-DSI-to-HDMI/MIPI panel display	HDMI display	HDMI display	i.MX 8M Mini supports MIPI-DSI to HDMI display and MIPI Panel display. i.MX 8M Nano EVK supports MIPI-DSI-to-HDMI display and MIPI panel display. i.MX 8M Quad supports physical HDMI display, MIPI-DSI to HDMI display, and MIPI panel display. i.MX 8QuadMax supports LVDS-to-HDMI/MIPI-DSI-to-HDMI and physical HDMI display.
UI (dual displays, UI mirror displayed on second device)	N	N	Y	Y	Y	i.MX 8M Quad EVK supports on MIPI-DSI-to-HDMI and HDMI dual displays. i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK support dual LVDS-to-HDMI displays.
UI (brightness control)	N	N	N	N	N	-
Storage - External Media	Y	Y	Y	Y	Y	For i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK, USB 2.0 port supports udisk, but USB 3.0 port does not support udisk.
Connectivity - Ethernet	Y	Y	Y	Y	Y	-
Connectivity - Bluetooth® wireless technology	Y	Y	Y	Y	Y	Hardware: <ul style="list-style-type: none">Qualcomm 1PJ QCA9377 for i.MX 8M Mini EVK LPDDR4 board

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
						<ul style="list-style-type: none"> • BCM 1MW BCM43455 for i.MX 8M Nano EVK • Broadcom 1CX BCM4356 for i.MX 8M Quad EVK Rev. A, i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK Profiles: <ul style="list-style-type: none"> • A2DP Source • AVRCP • BLE Host • HSP • HID Host • HID Device • PAN • OPP
Connectivity - Wi-Fi	Y	Y	Y	Y	Y	Hardware: <ul style="list-style-type: none"> • Qualcomm 1PJ QCA9377 for i.MX 8M Mini EVK LPDDR4 board • BCM 1MW BCM43455 for i.MX 8M Nano EVK Features: <ul style="list-style-type: none"> • STA mode • AP mode • Wi-Fi Direct • AP/STA Concurrency Hardware: <ul style="list-style-type: none"> • Broadcom 1CX BCM4356 for i.MX 8M Quad EVK Rev. A, i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK Features: <ul style="list-style-type: none"> • STA mode • AP mode • Wi-Fi Direct

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
Connectivity - USB Tethering	Y	Y	Y	Y	Y	Supports Wi-Fi and Ethernet as upstream.
Power - CPU Freq	Y	Y	Y	Y	Y	-
Power - Bus Freq	Y	Y	Y	Y	Y	-
Media - Music Play	Y	Y	Y	Y	Y	SSI + WM8524 for i.MX 8M Mini, i.MX 8M Nano EVK, and i.MX 8M Quad. ESAI+CS42888 for i.MX 8QuadMax (not support multichannel). ESAI+CS42888 for i.MX 8QuadXPlus (supports multichannel).
Media - Sound Record	Y	Y	Y	Y	Y	SSI+wm8524 for i.MX 8M Nano EVK
Media - Video Play	Y	Y	Y	Y	Y	-
Media - Camera	Y	Y	Y	Y	Y	OV5640CSI for i.MX 8M Mini, i.MX 8M Nano EVK, and i.MX 8M Quad. OV5640MIPI for i.MX 8QuadXPlus. For i.MX 8M Quad, the camera cannot co-work with MIPI Display due to the I2C address conflict.
Media - TVIN	N	N	N	N	N	-
Media - Dual Camera	Y	Y	Y	Y	Y	Dual OV5640MIPI for i.MX 8QuadMax OV5640MIPI and OV5640CSI for i.MX 8QuadXPlus.
Media - Camcorder	Y	Y	Y	Y	Y	-
Media - USB Camera	Y	Y	Y	N	N	USB camera supports C920, C270, and C525.
Media - USB Mic	Y	Y	Y	Y	Y	-
Media - HDMI audio output	N	N	Y	Y	N	-

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
Media-DSD Playback	Y	N	Y	N	N	DSD stream output from Audio Expansion Board.
Media-PlayReady DRM	N	N	Y	N	N	Moderated download for licensees
Media-WideVine DRM	Y	N	Y	N	N	Supports WideVine DRM Level 3.
Media-M4 Playback	Y	N	N	N	N	Audio playback based on FreeRTOS on the Cortex-M4 core for i.MX 8M Mini.
Media-Hi-Res audio output	Y	N	Y	Y	Y	<p>High resolution audio output from Audio Expansion Board for i.MX 8M Mini EVK and i.MX 8M Quad EVK.</p> <ul style="list-style-type: none"> • 2 channel: 384000, 768000 sampling rate • 4 channel: 48000, 96000, 192000, 384000, 768000 sampling rate • 6 channel: 48000, 96000, 192000, 384000 sampling rate • 8 channel: 48000, 96000, 192000, 384000 sampling rate <p>High resolution audio output from Audio Expansion Board for i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK:</p> <ul style="list-style-type: none"> • 4 channel: 48000, 96000, 192000 sampling rate • 6 channel: 48000, 96000, 192000 sampling rate • 8 channel: 48000, 96000, 192000 sampling rate
Misc - ADB over USB	Y	Y	Y	Y	Y	-
Misc - Fastboot utility	Y	Y	Y	Y	Y	-

Table continues on the next page...

Table 2. Features (continued)

Feature	i.MX 8M Mini EVK	i.MX 8M Nano EVK	i.MX 8M Quad EVK	i.MX 8QuadMax MEK	i.MX 8QuadXPlus MEK	Remarks
Misc - SW update and factory reset	Y	Y	Y	Y	Y	-
Sensor - Magnetometer	N	N	N	Y	Y	FXOS8700
Sensor - Accelerometer	N	N	N	Y	Y	FXOS8700
Sensor - Gyroscope	N	N	N	Y	Y	FXAS2100
Sensor - Light	N	N	N	Y	Y	ISL29023
Sensor - Pressure	N	N	N	Y	Y	MPL3115
Sensor - Temperature	N	N	N	Y	Y	MPL3115
File Based Encryption	Y	Y	Y	Y	Y	-
USB Accessory	Y	Y	Y	Y	Y	Google AOA v2.0
Ethernet APK	Y	Y	Y	Y	Y	-
webGL	Y	Y	Y	Y	Y	-
Vulkan	N	N	Y	Y	Y	-
OTA for A/B	Y	Y	Y	Y	Y	-
USB Type-C PD	Y	Y	Y	Y	Y	Supports power role switch with devices that support USB power delivery
DM Verity	Y	Y	Y	Y	Y	-
TEE backed Keymaster HAL	Y	Y	Y	Y	Y	This is based on i.MX Trusty OS TEE firmware.
TEE backed AVB	Y	Y	Y	Y	Y	This is based on i.MX Trusty OS TEE firmware and secure storage of eMMC chip. In this release, users need to initialize the RPMB part manually.

5 Multimedia Codecs

For multimedia codecs and features, see Section 5 in the [Google Android 10 Compatibility Definition Document \(CDD\)](#).

6 Extended Features

An enhanced multimedia experience is available for the Android platform. This release delivers an error-resilient, feature-rich multimedia solution by extending the existing multimedia features of the Android platform and introduces additional features.

For detailed extended and additional features, see *i.MX Android™ Extended Codec Release Notes* (IMXACRN).

For more information and details, contact "L2manager-android@nxp.com".

7 Change Logs

Compared to the android-10.0.0_1.0.0 release, android-10.0.0_2.0.0 for i.MX 8M Mini EVK, i.MX 8MQuad EVK, i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK has the following major changes:

- Upgraded the Android code base from android-10.0.0_r14 to android-10.0.0_r32.
- Upgraded the kernel from v4.19.42 to v5.4.3.
- Enabled dynamic partition feature.
- Upgraded the SCFW from v1.2.7.1 to v1.2.10.1 for i.MX 8QuadMax MEK and i.MX 8QuadXPlus MEK.

Compared to the P9.0.0_2.3.4 release, android-10.0.0_2.0.0 for i.MX 8M Nano EVK has the following major changes:

- Upgraded the Android code base from android-9.0.0_r47 to android-10.0.0_r32.
- Upgraded the kernel from v4.14.98 to v5.4.3.
- Upgraded the U-Boot from v2018.03 to v2019.04.
- Upgraded mapper HAL from 2.0 to 2.1.
- Upgraded composer HAL from 2.1 to 2.3.
- Integrated power HAL.
- Integrated thermal HAL.
- Integrated oemlock HAL.
- Enabled dynamic partition feature.

8 Known Issues and Limitations

The known issues about the hardware and hardware rework instructions are not included in this document. There may be hardware-related reference materials for some reference boards. Make sure to check the link [i.MX Application Processors](#) to see if it is applicable.

Table 3. Known issues and limitations

Issue description	Remarks
The Google USB driver must be installed multiple times for the MTP, PTP, MTP&ADB, PTP&ADB, and ADB function settings.	Some Windows XP environments may display MTP and PTP windows even with only PTP enabled in the device.
U-Boot will hang when erasing Kingston SD card.	U-Boot will hang when sending the erase command on some Kingston SD cards.
For i.MX 8QuadXPlus silicon revision B0, it fails to boot from some types of eMMC.	In the default settings, the UUU script burns the boot image into the eMMC Boot Partition with 32KB offset. Although it works properly on the MEK board, it fails to read the boot image on some types of eMMC.

Table continues on the next page...

Table 3. Known issues and limitations (continued)

Issue description	Remarks
	<p>There are two possible solutions:</p> <ul style="list-style-type: none"> • Download flash.bin in the eMMC Boot Partition + 0KB offset + eMMC fastboot enabled in fuse. • Download flash.bin in the eMMC User Partition + 32KB offset (eMMC fastboot can be either enabled or disabled in fuse). <p>For more information, see https://community.nxp.com/docs/DOC-342877.</p>

9 Revision History

Table 4. Revision history

Revision number	Date	Substantive changes
P9.0.0_1.0.0-beta	11/2018	Initial release
P9.0.0_1.0.0-ga	01/2019	i.MX 8M, i.MX 8QuadMax, i.MX 8QuadXPlus GA release.
P9.0.0_2.0.0-ga	04/2019	i.MX 8M, i.MX 8QuadMax, i.MX 8QuadXPlus GA release.
P9.0.0_2.0.0-ga	08/2019	Updated the location of the SCFW porting kit.
android-10.0.0_1.0.0	02/2020	i.MX 8M Mini, i.MX 8M Quad, i.MX 8QuadMax, and i.MX 8QuadXPlus GA release.
android-10.0.0_1.0.0	03/2020	Deleted the Android 10 image.
android-10.0.0_2.0.0	05/2020	i.MX 8M Mini, i.MX 8M Nano, i.MX 8M Quad, i.MX 8QuadMax, and i.MX 8QuadXPlus GA release.

How To Reach Us

Home Page:

nxp.com

Web Support:

nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/SalesTermsandConditions.

While NXP has implemented advanced security features, all products may be subject to unidentified vulnerabilities. Customers are responsible for the design and operation of their applications and products to reduce the effect of these vulnerabilities on customer's applications and products, and NXP accepts no liability for any vulnerability that is discovered. Customers should implement appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP, the NXP logo, NXP SECURE CONNECTIONS FOR A SMARTER WORLD, COOLFLUX, EMBRACE, GREENCHIP, HITAG, I2C BUS, ICODE, JCOP, LIFE VIBES, MIFARE, MIFARE CLASSIC, MIFARE DESFire, MIFARE PLUS, MIFARE FLEX, MANTIS, MIFARE ULTRALIGHT, MIFARE4MOBILE, MIGLO, NTAG, ROADLINK, SMARTLX, SMARTMX, STARPLUG, TOPFET, TRENCHMOS, UCODE, Freescale, the Freescale logo, Altivec, C-5, CodeTEST, CodeWarrior, ColdFire, ColdFire+, C-Ware, the Energy Efficient Solutions logo, Kinetis, Layerscape, MagniV, mobileGT, PEG, PowerQUICC, Processor Expert, QorIQ, QorIQ Qonverge, Ready Play, SafeAssure, the SafeAssure logo, StarCore, Symphony, VortiQa, Vybrid, Airfast, BeeKit, BeeStack, CoreNet, Flexis, MXC, Platform in a Package, QUICC Engine, SMARTMOS, Tower, TurboLink, UMEMS, EdgeScale, EdgeLock, eIQ, and Immersive3D are trademarks of NXP B.V. All other product or service names are the property of their respective owners. AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamiQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, µVision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. Oracle and Java are registered trademarks of Oracle and/or its affiliates. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org.

© NXP B.V. 2018-2020.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 20 May 2020

Document identifier: ARN

