PN7160 evaluation kit quick start guide Rev. 1.1 — 13 September 2021

Application note COMPANY PUBLIC

Document information

Information	Content
Keywords	OM27160, PN7160, Raspberry Pi, Arduino, eval kit, NFC, P2P, Card Emulation, Linux, Android, RTOS, Null OS
Abstract	This document gives a description on how to get started with the PN7160 evaluation kit.



1 Revision history

Revision history			
Rev	Date	Description	
1.1	20210913	Security status changed into "Company public", no content change	
1.0	20210825	Initial version	

2 Introduction

This document gives a description on how to get started with the PN7160 evaluation kit, referenced as OM27160A1EVK for the I²C host interface version (featuring PN7160A1HN I²C variant) and OM27160B1EVK (featuring PN7160B1HN SPI variant).

It provides a step by step guide to the installation procedure of the hardware and the software.

Finally it shows PN7160 NFC Controller functionalities through demo applications.

2.1 PN7160 evaluation kit description

PN7160 evaluation kit exits in 2 versions:

- OM27160A1EVK: embeds PN7161A1HN I²C variant in HVQFN40 package
- OM27160B1EVK: embeds PN7161B1HN SPI variant in HVQFN40 package



Both versions are composed of 3 printed circuit boards and an NTAG card.

PN7160 evaluation kit quick start guide





2.2 Linux driver support

PN7160 NFC controller is supported under GNU/Linux system using the NXP Linux libnfc-nci software stack (see [2]).

2.3 Android driver support

PN7160 NFC controller is supported from the official Android Open Source Project (refer to [3] for more details) with the addition of dedicated patches (see [4]).

2.4 RTOS and Null OS support

Since implementing NFC Forum NCI 2.0 standardized API, the PN7160 NFC Controller can be easily integrated into system based on RTOS or even without OS.

Code examples are given in the form of MCUXpresso projects (dedicated to specific NXP's MCUs) and can easily be ported to any other system (refer to [5]).

3 Quick Startup with Raspberry Pi interface board

3.1 Required items


• Raspberry Pi [1] running raspbian distribution.

3.2 Hardware setup

First of all assemble the PN7160 NFC controller board (OM27160A1HN or OM27160B1HN) with the Raspberry Pi interface board (OM29110RPI).



Then stacked together the boards with the Raspberry Pi board.



3.3 Software setup

Use Raspbian (<u>https://www.raspberrypi.org/software/operating-systems/</u>). Guidelines to set up Linux environment on raspberry pi can be found here: <u>https://www.raspberrypi.org/</u><u>documentation/installation/installing-images/</u>).

Application note COMPANY PUBLIC

Below is the step-by-step procedure run from the Raspberry Pi to add software support for PN7160:

3.3.1 Enable I²C interface (only for OM27160A1EVK)

1. Run command:

sudo raspi-config

- 2. Use the down arrow to select "Interface Options"
- 3. Arrow down to "P5 I2C"
- 4. Select "yes" when it asks you to enable I2C
- 5. Use the right arrow to select the <Finish> button

Raspberry Pi	Software Configuration Tool (raspi-config)	
Pl Camera	Enable/disable connection to the Raspberry Pi Camera	
P2 SSH	Enable/disable remote command line access using SSH	
P3 VNC	Enable/disable graphical remote access using RealVNC	
P4 SPI	Enable/disable automatic loading of SPI kernel module	
P5 I2C	Enable/disable automatic loading of I2C kernel module	
	Enable/disable shell messages on the serial connection	
P7 1-Wire	Enable/disable one-wire interface	
P8 Remote GPIO	Enable/disable remote access to GPIO pins	
<sel< td=""><td>ect> <back></back></td><td></td></sel<>	ect> <back></back>	
(001)	CCC (Back)	

To verify the l^2C interface is enabled, enter the following command ls /dev/i2c*.

The Pi should respond with "/dev/i2c-1" which represents the user-mode l^2C interface to which is connected the PN7160.

3.3.2 Enable SPI interface (only for OM27160B1EVK)

1. Run command:

sudo raspi-config

- 2. Use the down arrow to select "Interface Options"
- 3. Arrow down to "P4 SPI"
- 4. Select "yes" when it asks you to enable SPI
- 5. Use the right arrow to select the <Finish> button

PN7160 evaluation kit quick start guide

 Raspberry Pi	Software Config	guration Tool (raspi-config)	
Pl Camera	Enable/disable	connection to the Raspberry Pi Camera	
P2 SSH		remote command line access using SSH	
P3 VNC		graphical remote access using RealVNC	
P4 SPI		automatic loading of SPI kernel module	
P5 I2C	Enable/disable	automatic loading of I2C kernel module	
P6 Serial Port	: Enable/disable	shell messages on the serial connection	
P7 1-Wire	Enable/disable	e one-wire interface	
P8 Remote GPIC) Enable/disable	e remote access to GPIO pins	
<sel< td=""><td>.ect></td><td><back></back></td><td></td></sel<>	.ect>	<back></back>	

Figure 7. Enabling SPI interface on raspian

To verify the SPI interface is enabled, enter the following command ls /dev/spi*.

The Pi should respond with "/dev/spi0.0" which represents the user-mode SPI interface to which is connected the PN7160.

3.3.3 Install necessary tools

Execute the command:

sudo apt-get install autoconf automake libtool git

3.3.4 Clone Linux libnfc-nci library repository

Execute the command:

git clone https://github.com/NXPNFCLinux/linux_libnfc-nci.git -b NCI2.0_PN7160

3.3.5 Configure the library

Execute the commands:

```
cd linux_libnfc-nci
./bootstrap
./configure
```

3.3.6 Set the library to map I²C interface (only for OM27160A1EVK)

Edit linux_libnfc-nci/conf/libnfc-nxp.conf file to update NXP_TRANSPORT and NXP_NFC_DEV_NODE settings as shown below:

```
NXP TRANSPORT=0x02
```

3.3.7 Set the library to map I²C interface (only for OM27160B1EVK)

Edit linux_libnfc-nci/conf/libnfc-nxp.conf file to update NXP_TRANSPORT and NXP NFC DEV NODE settings as shown below:

3.3.8 Build and install the library

Execute the commands:

```
make
sudo make install
export LD_LIBRARY_PATH=/usr/local/lib
```

To make this last setting permanent, run the following command:

```
echo "export LD_LIBRARY_PATH=/usr/local/lib" >> .bashrc
```

3.3.9 Run the demo application (built and installed together with the library during previous step)

To simply display all data collected from remote NFC device (Peer, reader/writer or card), run the demo application in "poll mode" executing the command:

nfcDemoApp poll

For more details about the demo application modes execute command:

nfcDemoApp --help

For more detailed information about the demo application, but also for additional example applications, please refer to [2].

4 Quick Startup with Arduino interface board

Refer to [5] for details about PN7160 demonstration using OM27160 ARD configuration on Arduino compatible NXP's MCU boards.

5 References

- [1] The Raspberry Pi is a low cost, credit-card sized computer that plugs into a computer monitor or TV, and uses a standard keyboard and mouse. It is a capable little device that enables people of all ages to explore computing, and to learn how to program in languages like Scratch and Python. It is capable of doing everything you would expect a desktop computer to do, from browsing the Internet and playing high-definition video, to making spreadsheets, word-processing, and playing games. For more information about it please visit https://www.raspberrypi.org/
- [2] AN13287 PN7160 Linux porting guide: https://www.nxp.com/doc/AN13287
- [3] Android is an open source software stack for a wide range of mobile devices and a corresponding open source project led by Google.
- For more information about it please visit <u>https://source.android.com/</u>
- [4] AN13189 PN7160 Android porting guide: <u>https://www.nxp.com/doc/AN13189</u>
- [5] AN13288 PN7160 NXP-NCI2.0 MCUXpresso examples guide: <u>https://www.nxp.com/doc/AN13288</u>

AN12991

PN7160 evaluation kit quick start guide

6 Legal information

6.1 Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

6.2 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by

customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Evaluation products — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer. In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages. Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

- Customer understands that all NXP products may be subject Security to unidentified or documented vulnerabilities. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP. NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

6.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Figures

Fig. 1.	PN7160 evaluation kit3	
Fig. 2.	OM27160A1EVK I2C dev kit overview4	
Fig. 3.	OM27160B1EVK SPI dev kit overview4	
Fig. 4.	OM27160 RPI configuration6	

Fig. 5.	OM27160 evaluation kit and Raspberry Pi	
	board stacked together	6
Fig. 6.	Enabling I2C interface on raspian	7
Fig. 7.	Enabling SPI interface on raspian	8

PN7160 evaluation kit quick start guide

Contents

1	Revision history	2
2	Introduction	
2.1	PN7160 evaluation kit description	3
2.2	Linux driver support	5
2.3	Android driver support	5
2.4	RTOS and Null OS support	5
3	Quick Startup with Raspberry Pi interface	
	board	6
3.1	Required items	6
3.2	Hardware setup	6
3.3	Software setup	6
3.3.1	Enable I2C interface (only for	
	OM27160A1EVK)	7
3.3.2	Enable SPI interface (only for	
	OM27160B1EVK)	
3.3.3	Install necessary tools	8
3.3.4	Clone Linux libnfc-nci library repository	8
3.3.5	Configure the library	8
3.3.6	Set the library to map I2C interface (only for	
	OM27160A1EVK)	8
3.3.7	Set the library to map I2C interface (only for	
	OM27160B1EVK)	9
3.3.8	Build and install the library	9
3.3.9	Run the demo application (built and	
	installed together with the library during	
	previous step)	9
4	Quick Startup with Arduino interface	
	board	. 10
5	References	
6	Legal information	. 12

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2021.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 13 September 2021 Document identifier: AN12991