

1 Introduction

This document describes the estimated product lifetimes for the i.MX 8QuadXPlus/8DualXPlus/8DualX application processors based on the criteria used in the qualification process.

The product lifetimes described here are estimates and do not represent a guaranteed life time for a product.

The i.MX 8QuadXPlus/8DualXPlus/8DualX series consist of several processors that deliver a wide range of processing and multimedia capabilities across various qualification levels. This document intends to provide you with guidance on how to interpret the different i.MX 8QuadXPlus/8DualXPlus/8DualX qualification levels in terms of the target operating frequency of the device, the maximum supported junction temperature (T_j) of the processor, and how it relates to the lifetime of the device.

2 Device qualification level and available PoH

Each qualification level supported (automotive and industrial) defines a number of Power-on Hours (PoH) available to the processor under a given set of conditions such as:

- Target voltage for the application (automotive and industrial)
 - The target frequency is determined by the input voltage to the processor's core complex (VDD_A35) .
- Percentage of active use vs. the Low power mode
 - Active use means that the processor is running in an active performance mode.
 - For the automotive tier of 8QuadXPlus/8DualXPlus/8DualX, two performance modes are available: 1.2 GHz and 900 MHz.
 - For the industrial tier of 8QuadXPlus/8DualXPlus/8DualX, the maximum performance mode is 1.2 GHz.
 - In the Low power (KS1) mode, the datasheet defines lower operating conditions for the VDD_A35, reducing power consumption and junction temperature. In this mode, the voltage and temperature are set low enough so that the effect on the lifetime calculations is negligible and treated as if the device was powered off.
- The junction temperature of the processor (T_j)
 - The maximum junction temperature of the device is different for a given qualification level. For example, 125°C for the automotive tier and 105°C for the industrial tier. It is important to note that while the automotive device is guaranteed to operate at 125°C, operating the device at 125°C for an extended period of time will have negative consequences on the lifetime of the device.
 - Ensure that your device is appropriately thermally managed, such that the maximum junction temperature is not exceeded.

NOTE

All data provided within this document are estimates for PoH based on extensive qualification experience and tested with the i.MX 8QuadXPlus/8DualXPlus/8DualX series. These statistically derived estimates should not be viewed as a limit on an individual device lifetime, nor should they be construed as a guarantee by NXP as to the actual lifetime of the device. Sales and warranty terms and conditions still apply.

Contents

1	Introduction.....	1
2	Device qualification level and available PoH.....	1
2.1	Automotive lifetime estimates.....	2
2.2	Industrial qualification.....	2
3	Conclusion.....	3
4	Revision history.....	3




2.1 Automotive lifetime estimates

Table 1 provides the number of PoH for the typical use conditions for the automotive device.

Table 1. Automotive qualification lifetime estimates

Operating mode	Cortex®-A35 speed grade(MHz)	Power-on Hours [PoH] (Hrs)	Arm® core operating voltage(V)	Junction Temperature [Tj] (°C)
Overdrive	1200	13,132	1.1	105
Overdrive	1200	4,462	1.1	125
Nominal	900	60,339	1.0	105
Nominal	900	20,504	1.0	125

Figure 1 establishes guidelines for estimating PoH as a function of junction temperature. PoH can be read directly from the curves below to determine the necessary trade-offs to the junction temperature at the maximum CPU frequency.




2.2 Industrial qualification

Table 2 provides the number of PoH for the typical use conditions for the industrial device.

Table 2. Industrial qualification lifetime estimate

Operating mode	Cortex-A35 speed grade (MHz)	Power-on Hours [PoH] (Hrs)	Arm core operating voltage (V)	Junction temperature [Tj] (°C)
Overdrive	1200	87,669	1.1	105

Figure 2 establishes guidelines for estimating PoH as a function of junction temperature. PoH can be read directly from the curves below to determine the necessary trade-offs to the junction temperature at the maximum CPU frequency.



3 Conclusion

Selecting the optimal operating performance point and thermal envelope is paramount to meet the application lifetime targets. Trade-offs between the target operating voltage/frequency of the device and the operating junction temperature (Tj) of the processor can greatly improve the lifetime of the device.

Lowering the operating junction temperature in the application is the most effective means to increase the lifetime of the device without affecting the performance of the device. This can be accomplished by increasing the thermal dissipation capacity in the application. In cases where the thermal properties cannot be altered, a lower operating voltage can be used to increase the lifetime of the device. Lowering the voltage may result in lowered performance; the operating frequency may have to be adjusted lower to match the voltage specified in the datasheet.

The data and examples provided in this application note help you to determine the estimated lifetime for your particular application.

4 Revision history

Rev.	Date	Substantive changes
0	25 May, 2021	Initial release

How To Reach Us

Home Page:

nxp.com

Web Support:

nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/SalesTermsandConditions.

Right to make changes - NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Security — Customer understands that all NXP products may be subject to unidentified or documented vulnerabilities. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP. NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

NXP, the NXP logo, NXP SECURE CONNECTIONS FOR A SMARTER WORLD, COOLFLUX, EMBRACE, GREENCHIP, HITAG, ICODE, JCOP, LIFE, VIBES, MIFARE, MIFARE CLASSIC, MIFARE DESFire, MIFARE PLUS, MIFARE FLEX, MANTIS, MIFARE ULTRALIGHT, MIFARE4MOBILE, MIGLO, NTAG, ROADLINK, SMARTLX, SMARTMX, STARPLUG, TOPFET, TRENCHMOS, UCODE, Freescale, the Freescale logo, Altivec, CodeWarrior, ColdFire, ColdFire+, the Energy Efficient Solutions logo, Kinetis, Layerscape, MagniV, mobileGT, PEG, PowerQUICC, Processor Expert, QorIQ, QorIQ Qonverge, SafeAssure, the SafeAssure logo, StarCore, Symphony, VortiQa, Vybrid, Airfast, BeeKit, BeeStack, CoreNet, Flexis, MXC, Platform in a Package, QUICC Engine, Tower, TurboLink, EdgeScale, EdgeLock, eIQ, and Immersive3D are trademarks of NXP B.V. All other product or service names are the property of their respective owners. AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamIQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, μ Vision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. Oracle and Java are registered trademarks of Oracle and/or its affiliates. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org.

© NXP B.V. 2021.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: May 25, 2021

Document identifier: AN13273

