Rev. 0 — 5 December 2022

**Application note** 

### **Document information**

Information	Content
Keywords	AN13768, RT1170, MIPI DSI, Low-power mode
Abstract	This application note describes how to add low-power mode operation on the MIPI DSI host controller and LCDIFv2 controller.



# 1 Introduction

This application note describes how to add low-power mode operation on the Mobile Industry Processor Interface (MIPI) Display Serial Interface (DSI) host controller and LCDIFv2 controller. It is done to drive a DSI-compliant LCD panel on i.MX RT1170 to switch off and then back on again.

In this application note, software mode is used to enter and exit from the sleep mode and DISPLAY MIX is switched off to save maximum power. This document uses SSARC to save and restore LCDIFV2 and Video mux related registers when it is switched off and switched on back. Here, we have modified the clock\_freertos (vglite\_examples) included with the SDK to understand how to power up and power down the display. The clock\_freertos project shows how to drive the TFT panel using the LCDIFv2 driver. The example toggles between display off and on for certain interval in an infinite loop.

**Note:** The code is simple and not extensive since it focuses on how to power on and off display rather than providing an implementation for product. For GPU internal low-power mode, an API is added to power on GPU from deep sleep.

# 2 MIPI DSI host controller


The MIPI DSI is a versatile, high-speed interface for LCD displays in smartphones, automotive, and other platforms.

MIPI DSI controller of i.MX RT1170 implements all protocol functions defined in MIPI DSI specification. It provides an interface that allows communication between MCUs and MIPI DSI-compliant LCDs.

MIPI DSI D-PHY of i.MX RT1170 is a high-frequency and low-power physical layer that supports the MIPI Alliance Standard for D-PHY and provides a physical implementation for DSI.

### 2.1 DSI host controller core

<u>Figure 1</u> shows the DSI layer definitions of DSI specification. The MIPI DSI controller of the i.MX RT1170 implements all three DSI layers (lane management, low-level protocol, and application).




MIPI DSI uses differential signals to transmit clock and data between DSI host and display module. It includes 1 clock lane and 1~4 data lanes. For DSI controller in i.MX RT1170, it can support 1 clock lane and up to 2 data lanes. DSI greatly reduces the number of data and signal lines compared to the parallel interface, which saves hardware resources.

DSI-compliant LCD supports two basic modes of operation: Command mode and Video mode. The architecture and capabilities of the LCD decide which mode is used.

Command mode refers to an operation in which transactions primarily send commands and data to a display module. The display module may include local registers and a compressed or an uncompressed frame buffer.


Video mode refers to an operation in which transfers from the host processor to the peripheral take the form of a real-time pixel stream. Video information should be transmitted using high-speed mode. Figure 2 shows examples for Command and Video modes.



In general, MIPI DSI controller provides the following key features:

- Supports for Command and Video modes
- Scalable data lane support, 1 to 2 data lanes
- · Supports high-speed and low-power operation
- Flexible packet-based user interface
  - APB interface option (status and control)
  - Display Pixel Interface Core (DPI-2) option

Figure 3 shows the DSI host controller core structure.



AN13768 Application note

D-PHY interface connects directly to MIPI PPI-compliant D-PHYs, described in further sections.

DSI host controller core sends and receives DSI commands and data via packet interface. There are two packet-based interfaces: APB interface and Display Pixel (DPI-2) interface.

# 3 LCDIFv2 controller

The i.MX RT1170 includes the enhanced Liquid Crystal Display Interface (eLCDIF) and the LCDIF Interface version 2 (LCDIFv2). They are both display controllers used to fetch graphics stored in memory and display them on an LCD panel.

This chapter mainly introduces LCDIFv2 controller. LCDIFv2 includes the following features:

- Support RGB interface only
- Display layers can support up to maximum 8 layers of alpha blending
- Support one parallel camera interface input and typical data formats of CSI-2: 16 bpp (YUV422 8-bit), 24 bpp (RGB888), 18 bpp (RGB666), 16 bpp (RGB565), 15 bpp (RGB555), 12 bpp (RGB444)

### 3.1 RGB interface

RGB interface is the mode used in moving picture displays. It includes VSYNC, HSYNC, DOTCLK, and ENABLE signals.


LCD (TFT) display with RGB interface can drive three segments (1 pixel) per clock with variable electric field strength. The RGB interface provides the following features:

- Supports many colors
- Always supports 1 pixel per clock (three segments of Red, Green, and Blue)
- Contains the color levels depending on the number of data lines on the LCD panel and the number of LCD controller data output signals. It may be 24 lines, 24 bits per pixel (bpp), or 18 bpp, 16 bpp
- Supports the parallel data interface. 1 clock requires 24 bits (or other formats) for 1 pixel

For the LCD RGB interface, on every pixel clock edge (rising or falling) and within the LCD active area, the controller fetches one-pixel of data from its FIFO. Then, the controller converts it to the pixel panel format (coded in the RGB888 or other formats), puts it in the signal generator unit, and drives out to the RGB interface. The pixel data is then displayed on the screen.

To drive correct picture on LCD, some timing parameters should be considered for a size of LCD display. The parameters should be programmed to match the display specifications.


### Switch LCD Display On/Off in Low-Power Mode on i.MX RT1170



# 4 Video mux controller

The i.MX RT1170 supports various LCD/camera interfaces and display controllers, so a video mux controller is used to provide mux control between interfaces and controllers.

<u>Figure 5</u> shows the video mux block. For example, LCDIFv2 can be selected to control MIPI DSI.



# 5 Low-power modes

The i.MX RT1170 provides new power and clock architecture design. Compared to the previous i.MX RT10xx family MCUs, software, hardware, or a combination of both can control the i.MX RT1170 power and clock state.


Software or hardware can control each module. For most of the modules, a combination of hardware and software control is allowed (PGMC, SRC, CCM, and PMU). The rest of the modules allows exclusive control by software or hardware (DC-DC).

## 5.1 Software control mode

When the software control mode is selected for the appropriate module, the application code becomes responsible for the module settings and module behavior. The application code must follow all the recommendations, such as the power-up and power-down sequences, PLL enable sequences, and so on. When any changes of the clock or power settings are requested, the application code must check if the planned change is valid and ensure that all the changes are executed in a correct order. Otherwise, the chip behavior can be unpredictable or unstable. The software control is the default control mode of all modules.

## 5.2 Hardware control mode

When the hardware control mode is selected, the application code determines the hardware control mechanism used for each resource. The i.MX RT1170 controls the resources (modules) via the CPU mode control, Setpoint mode control, or Standby mode control. The state of the CPUs, preconfigured setpoint, and enabled or disabled Standby mode defines the final power mode of the whole MCU. There are 4 states of the CPU (Run, Wait, Stop, or Suspend) and 16 preconfigured setpoints.



The advantages of this mode are that the General Power Controller (GPC) takes responsibility for correct power-up and power-down sequences, setpoints transition sequences, and so on. Even in the hardware control mode, incorrect settings can be

created, but the chip hardware can check most of the consequences. It does not allow the mode transition into an invalid configuration.

## 5.3 Power Gating and Memory Controller (PGMC) settings

The PGMC consists of three submodules which control each power domain. These submodules are the Basic Power Controller (BPC), CPU Power Controller (CPC), and PMIC Power Controller (PPC). <u>Table 1</u> shows the general PGMC control options. For more information about domain assignment, see section 20 of *i.MX RT1170 Processor Reference Manual* (document <u>IMXRT1170RM</u>).


	CPU mode control CM7 domain	CPU mode control CM4 domain	Setpoint mode control	Standby mode control	Software control mode
BPC0 - MEGAMIX	$\checkmark$	$\checkmark$	$\checkmark$		$\checkmark$
BPC1 - DISPLAYMIX		$\checkmark$			
BPC2 - WAKEUPM IX		$\checkmark$			$\checkmark$
BPC3 - LPRSMIX	$\checkmark$	$\checkmark$			
BPC4 - MIPIPHY	$\checkmark$	$\checkmark$			
CPC0 - CM7 core platform			√ (MLPL only)		$\checkmark$
CPC1 - CM4 core platform		$\checkmark$	√ (MLPL only)		$\checkmark$
PPC0 - PMIC control			$\checkmark$	$\checkmark$	

Table 1. PGMC general control settings

# 6 State Save and Restore Controller (SSARC)

The SSARC saves the registers of functional modules in a memory (Located in the LPSR domain) before powering down and restores the registers from memory after the module is powered up. This module configures a peripheral before the CPU wakes up. Once the CPU wakes up, it can use the peripheral without initialization. Figure 7 shows the basic functions of SSRAC.

Switch LCD Display On/Off in Low-Power Mode on i.MX RT1170



## 6.1 Descriptor

Descriptor is the most basic element in SSARC. The SSARC has up to 1024 descriptors. The descriptor supports most operations like CPU, such as write, read, delay, and polling.

It supports 4 operations and 7 types of operation:


Operations:

- Save disable and restore disable
- Save enable and restore disable
- · Save disable and restore enable
- Save enable and restore enable

Type of operation:


- Read value and write back
- · Write a fixed value
- Read a register or with a value then write it back (OR)
- Read a register and with a value then write it back (AND)
- Delay several cycles (delay)
- Read a register until the bit or bits in it changed to 0 (polling 0)
- Read a register until the bit or bits in it changed to 1 (polling 1)






The 1024 descriptors can be divided into 16 groups that control the descriptors. Each group contains a number of continuous descriptors. The group can be triggered by software or hardware. Each group has its own priority for both saving and restoring. There are 16 priority settings from 0 to 15, and 0 has the highest priority. Usually, the save operation does not need to care about the priority, but the restore operation must care. Such as, if a peripheral needs to use a pin, the initialization of the pins should have a higher priority than other settings.

Switch LCD Display On/Off in Low-Power Mode on i.MX RT1170



### 6.2.1 Group trigger by software

The software trigger method can be used to verify whether the SSARC settings are correct or not before entering the low power. The bit 0 and bit 1 in DESC\_CTRL1\_x (x means index for each group) can use software trigger for saving and restoring operations.



Besides this register, there is an API for save and restore:

void SSARC\_TriggerSoftwareRequest(SSARC\_LP\_Type \*base, uint8\_t
groupID, ssarc\_software\_trigger\_mode\_t mode)

See the software trigger example in SDK at boards\evkmimxrt1170\driver\_ examples\ssarc\software\_trigger.

# 7 API added to application for display on and off scenario

© 2022 NXP B.V. All rights reserved.

## 7.1 API added at application

### Display power down:

Display power down is achieved by using Display\_Powerdown API. As part of this API, SSARC module is requested to save all required registers needed by LCDIFV2 and Video mux module using API SSARC\_TriggerSoftwareSave. PGMC module is requested to power off the domain: DISPLAY\_MIX (BPC 1) and MIPIPHY (BPC 4) using API PGMC\_BPC\_ControlPowerDomainBySoftwareMode.

### Display power up:

Display power up is achieved by using Display\_Powerup API. As part of this API, first PGMC module is requested to switch on power for DISPLAY\_MIX (BPC 1) domain followed by resetting display mix using API BOARD\_ResetDisplayMix. Then, the SSARC module is called to restore registers for LCDFIV2, and Video mux using API SSARC\_TriggerSoftwareRestore. Then, the GPU is powered up calling API GPU\_Powerup which resets and re-initialize GPU after power on from deep sleep. At the end, MIPI is powered up using MIPI\_Powerup API. For powering on MIPI module, first Video mux and MIPI clocks are enabled, and MIPI is powered on. This process is followed by asserting MIPI software reset (MIPI DSI APB clock domain, MIPI DSI Byte clock domain, MIPI DSI Pixel clock domain, and MIPI DSI Escape clock domain). Afterward, deassert software reset for the MIPI DSI APB clock domain and ESC clock domain, configure the peripherals, and deassert software reset for the MIPI DSI Byte clock domain and MIPI DSI Pixel clock domain. The last part is to configure the LCD.

**Note:** Remember the sequence in which LCDIFV2 and Video mux registers are saved and should be followed as provided in the application note software.

# 8 Run the demo

There is a project named clock\_freertos in the i.MX RT1170 SDK package provided as part of this application note software. The project demonstrates the LCDIFv2 controller, MIPI DSI host controller functionalities, and vglite driver.

### 8.1 clock\_freertos

The clock\_freertos demo can be found in the boards\evkmimxrt1170\vgli te\_examples\clock\_freertos directory for i.MX RT1170 SDK provided with the software package for this application note. The project can also be imported using MCUXpresso IDE import projects from the file system option. The demo application displays a clock with high render quality on the screen, and the screen is switched on and off continuously.

Build, download, and run the demo on i.MX RT1170-EVK to drive a 720 × 1280 LCD panel. The LCD is connected to the board via the MIPI DSI interface. Once the board is switched on, notice a high-render quality clock on display, with display being switched on and off at a particular interval.

# 9 Conclusion

This application note describes the use case of adding low-power mode operation to display. For more information, refer to:

i.MX RT1170 Processor Reference Manual (document IMXRT1170RM)

• The readme.txt file in the clock\_freertos demo

# **10 References**

- *i.MX RT1170 Processor Reference Manual* (document <u>IMXRT1170RM</u>)
- Use Case of RT1170 LCD Display System based on MIPI DSI (document AN12940)
- I.MXRT1170 Low-Power Modes (document AN13148)

# 11 Revision history

Table 2 summarizes the changes done to this document since the initial release.

Table 2. Revision history

Revision number	Date	Substantive changes
0	05 December 2022	Initial release

### Switch LCD Display On/Off in Low-Power Mode on i.MX RT1170

# 12 Legal information

## 12.1 Definitions

**Draft** — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

# 12.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

**Translations** — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at <u>PSIRT@nxp.com</u>) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

# 12.3 Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

# Switch LCD Display On/Off in Low-Power Mode on i.MX RT1170

# Contents

1	Introduction	2
2	MIPI DSI host controller	2
2.1	DSI host controller core	2
3	LCDIFv2 controller	5
3.1	RGB interface	5
4	Video mux controller	6
5	Low-power modes	7
5.1	Software control mode	
5.2	Hardware control mode	7
5.3	Power Gating and Memory Controller	
	(PGMC) settings	8
6	State Save and Restore Controller	
	(SSARC)	8
6.1	Descriptor	9
6.2	Group	
6.2.1	Group trigger by software	11
7	API added to application for display on	
	and off scenario	
7.1	API added at application	12
8	Run the demo	12
8.1	clock_freertos	12
9	Conclusion	12
10	References	
11	Revision history	
12	Legal information	14

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© 2022 NXP B.V.

All rights reserved.

For more information, please visit: http://www.nxp.com