AN4269

Diagnostic and protection features in eXtreme switch family Rev. 2.0 — 25 January 2017 Application note

Document information

Information	Content
Keywords	AN4269
Abstract	The purpose of this document is to provide an overview of the diagnostic features offered in MC12XS3 eXtreme switch family.



Diagnostic and protection features in eXtreme switch family

1 Introduction

This document provides an overview of the diagnostic features offered in eXtreme switch MC12XS3 family, specifically for quads and the dual high-side drive devices. A description of the diagnostic functionality, including it's limitations (at very low or very high duty cycles), is further developed.

This document extends the information already stated in the data sheet, so consider the data sheet as main source of information. Values presented in graphs throughout the document represent only one sample characterization and do not replace the parameters shown in the specification. They are mainly to highlight how certain parameters behave with changes in temperature and supply voltage.

2 Diagnostic and protection features

<u>Table 1</u> summarizes the diagnostic features offered within the MC12XS3 eXtreme switch family, which is further explained in each of the sub-sections.

Table 1. MC12XS3 eXtreme switch diagnostic and protection duty cycle limitations

Diagnostic and protection features	Low duty cycle limitation	High duty cycle limitation
Open load ON	3.40 %	100 %
Open load OFF	0 %	86 %
Short-circuit to VBATT	0 %	96 %
Short-circuit to GND	3.40 %	100 %
Current sensing	3.40 %	100 %
Temperature feedback	0 %	100 %
Undervoltage	0 %	100 %
Overvoltage	0 %	100 %

The following conditions are used to create the above table:

- bulb loads (200 Hz) with default slew rate selection
- LED
- loads (400 Hz) with fast slew rate selection
- done on evaluation board with soldered part and 22 nF output capacitor, with V_{PWR} from 11 V to 18 V and -40 to 125 °C ambient temperature

In case of a 100 Hz switching frequency (bulb load), the diagnostic limitations are reduced by half of what is considered in $\underline{\text{Table 1}}$ for 200 Hz. For example, the open load ON low duty cycle limitation of 3.4 % at 200 Hz, would actually be 1.7 % low duty cycle limitation at 100 Hz, since both represent the same amount of detection time.

2.1 Open load in ON state (for bulbs)

The internal mechanism used to detect an open load condition operates basically by monitoring the amount of current flowing through the high-side switch. When it is configured for regular bulbs, the threshold would be at a typical 300 mA value.

AN4269

Diagnostic and protection features in eXtreme switch family

This detection circuitry integrates a typical 4.0 μ s filter, to properly recognize an open load condition in the ON state. Due to the output transition from OFF to ON, it is not possible to detect an open load condition for a short output pulse (low duty cycle). In this case, the open load in OFF state diagnosis can be used to report this fault.




Figure 1. "Bulb" open load current threshold variation in the ON state across supply voltage and temperature

2.2 Open load in ON state (for LEDs)

In case of an open load when the ON state diagnostic is configured for LEDs, the detection threshold is reduced to a typical $5.0\,\text{mA}$ value. The detection concept (patented) is based on initiating a controlled turn-off of the power MOSFET, together with a "weak" pull-up of the output (a current source circuit is only activated for a short period of time, typically $150\,\mu\text{s}$, while in the ON state).

The behavior of the output voltage, compared to the gate voltage of the power MOSFET, is evaluated during this time. If the output voltage is higher than the gate voltage during this short period, it is recognized as an open load in the ON state condition.




Figure 2. "LED" open load in the ON state current threshold variation across supply voltage and temperature

Diagnostic and protection features in eXtreme switch family

2.3 Open load in OFF state

This diagnostic operates differently from the previous two open load ON diagnostic features. The detection principle used is to allow a very small current (55 μ A typical) to flow through the load, just enough to increase the output voltage. The voltage is continuously measured and compared to the open load threshold.

If the voltage is above a predefined 2.3 V typical threshold, this condition is identified as an open load condition. To perform this diagnosis mechanism, a certain amount of time is required, thus limiting the diagnostic capabilities at very high duty cycles.

<u>Figure 3</u> and <u>Figure 4</u> are shown as references to illustrate the behavior of the threshold and the source current variations at different temperatures and supply voltages. These graphs represent the average value of tests performed in one lot of devices.




Figure 3. Open load in the OFF state threshold variation due to temperature and supply voltage




Figure 4. Open load in the OFF state detection source current variation due to temperature and supply voltage

2.4 Short-circuit to V_{BATT}

To detect this condition, the voltage at the output is monitored in the OFF state. If the voltage is higher than the predefined $V_{OSD(THRES)}$ threshold voltage, the output is reported to be a short-circuit to V_{RATT} .

AN4269


All information provided in this document is subject to legal disclaimers.

© NXP Semiconductors N.V. 2017. All rights reserved.

Diagnostic and protection features in eXtreme switch family

Since this measurement is done in the OFF state, the output needs to remain in this state for a short period of time to be able to perform this diagnostic measurement. By using this feature, it is possible to distinguish between a short-circuit to V_{BATT} and an open load in the OFF state.

<u>Figure 5</u> shows how the $V_{OSD(THRES)}$ typical value varies with temperature and supply voltage on each of the different outputs.



The voltage shown in Figure 5 is the voltage difference between V_{BATT} and the output.

2.5 Short-circuit to GND

Detecting a short-circuit to GND is done by monitoring the high-side MOSFET current. This information is used to detect both a severe short-circuit condition or an overload of the high-side switch.

This detection circuitry has a typical time filter of $3.0 \mu s$, meaning that the output needs to be turned ON for a minimum duration for this condition to be detected.

2.6 Severe short-circuit to GND

During the OFF to ON transition of the output, the load impedance is compared to an internal reference. When the impedance is smaller than the internal reference, the output is turned OFF without allowing the current to reach it's maximum possible level. In this way, the thermal stress inside the device is minimized.

This R_{SHORT} value is guaranteed by design.

The duration of the OFF to ON transition depends on the characteristics of the short-circuit (inductance, resistance, and ground shift).

2.7 Overload current on the high-side MOSFET

The current monitored through the high-side switch is compared with a level that changes according to a selected overcurrent protection profile, and also with the amount of time the load has been turned ON. See <u>AN4049</u> for more details.

Diagnostic and protection features in eXtreme switch family

2.8 Current sensing

The current sensing functionality is explained in detail in the <u>AN3848</u> (MC15XS3400) and the <u>AN3853</u> (MC35XS3400) application notes.

2.9 Temperature feedback

In addition to the temperature sensors located on each of the different power MOSFETs, these devices contain an additional temperature sensor, located on the "control die" and positioned on top of the main ground terminal. This temperature is accessible to be read through the CSNS pin.


Different from the behavior of the current sense feedback, a proportional current to the load current comes out of the CSNS pin. For temperature feedback, the output is a voltage that can be directly read by an A/D pin from the MCU.

2.10 Undervoltage detection

These devices contain a monitoring circuit for the supply voltage. If this voltage drops below a predefined 3.85 V typical threshold, due to a long input line and severe short-circuit condition, the outputs are automatically turned OFF before reaching the overcurrent level.

The outputs are automatically latched-OFF, in case of an undervoltage condition.

<u>Figure 6</u> shows the variation of the undervoltage threshold and it's behavior versus temperature.



2.11 Overvoltage detection

If the supply voltage goes above a predefined 32 V typical threshold, the outputs are turned OFF. The outputs remain OFF until the overvoltage condition is removed (considering the defined hysteresis of the detection circuit).

<u>Figure 7</u> shows the variation of the overvoltage threshold and it's behavior versus temperature.

AN4269

Diagnostic and protection features in eXtreme switch family




Figure 7. Overvoltage detection behavior versus temperature variation

3 Revision history

Table 2. Revision history

Revision	Date	Description of changes
2.0	1/2017	Corrected minor typos
1.0	8/2011	Initial release

Diagnostic and protection features in eXtreme switch family

4 Legal information

4.1 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

4.2 Disclaimers

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume

any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/ or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/salestermsandconditions.

4.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

NXP — is a trademark of NXP B.V.

the NXP logo — is a trademark of NXP B.V.

Freescale — is a trademark of NXP B.V.

the Freescale logo — is a trademark of NXP B.V.

Diagnostic and protection features in eXtreme switch family

Т	a	h	29	
	a	v	C 3	

Tab. 1.	MC12XS3 eXtreme switch diagnostic and protection duty cycle limitations2	Tab. 2.	Revision history	7
Figur	res			
Fig. 1.	"Bulb" open load current threshold variation in the ON state across supply voltage and	Fig. 4.	Open load in the OFF state detection source current variation due to temperature and	4
Fig. 2.	temperature	Fig. 5.	supply voltage VOSD(THRES) variation due to ambient temperature and supply voltage variations	
	and temperature3	Fig. 6.	Undervoltage detection behavior versus	_
Fig. 3.	Open load in the OFF state threshold variation due to temperature and supply voltage4	Fig. 7.	temperature variation Overvoltage detection behavior versus temperature variation	

Diagnostic and protection features in eXtreme switch family

Contents

1	Introduction	2
2	Diagnostic and protection features	
2.1	Open load in ON state (for bulbs)	2
2.2	Open load in ON state (for LEDs)	3
2.3	Open load in OFF state	
2.4	Short-circuit to VBATT	4
2.5	Short-circuit to GND	5
2.6	Severe short-circuit to GND	5
2.7	Overload current on the high-side MOSFET	5
2.8	Current sensing	6
2.9	Temperature feedback	6
2.10	Undervoltage detection	
2.11	Overvoltage detection	6
3	Revision history	7
4	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.